


## **ORIGINAL INSTRUCTIONS**

## Instruction Manual Multistage Ejector Series ZL3/ZL6



The intended use of this product is to generate vacuum.

## 1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) <sup>\*1)</sup>, and other safety regulations. <sup>\*1)</sup> ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots -Safety. etc.

- Refer to product catalogue, Operation Manual and Handling Precautions for SMC Products for additional information.
- Keep this manual in a safe place for future reference.

<b>A</b> Caution	Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
<b>A</b> Warning	Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
▲ Danger	Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

### **↑** Warning

- Always ensure compliance with relevant safety laws and standards.
- All work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.

## 2 Specifications

Refer to catalogue for more details.

#### 2.1 ZL3 Series

Model	ZL3M□□	ZL3H□□
Nozzle diameter [mm]	1.9	1.5
Standard supply pressure	0.35 MPa	0.50 MPa
Maximum vacuum pressure *1	-91 kPa	-93 kPa
Max suction flow rate*1	280 L/min (ANR)	
Branch, Port exhaust	300 L/min (ANR)	
Air consumption*1	150 L/min (ANR)	135 L/min (ANR)
Supply pressure range	0.2 to 0.6 MPa	
Operating temperature range	-5 to 50 °C (No freezing or condensation)	
Fluid	Air	
Vibration resistance*2	20 m/s <sup>2</sup>	
Impact resistance*3	100	m/s <sup>2</sup>
0.0 71.0 Comics		

#### 2.2 ZL6 Series

Model		ZL6M□□	ZL6H□□
Nozzle diameter [mm]		1.9 x 2	1.5 x 2
Standard supply	Without valve	0.35 MPa	0.50 MPa
pressure	With valve	0.37 MPa	0.52 MPa
Maximum vacuum pressure *1		-91 kPa	-93 kPa
Max suction flow rate*1		580 L/min (ANR)	
Branch, Port exhaust		600 L/min (ANR)	
Air consumption*1		300 L/min (ANR)	270 L/min (ANR)
Supply pressure range		0.2 to 0	).6 MPa
Operating temperature range		-5 to 50 °C (No freezing or condensation)	
Fluid		Air	
Vibration resistance*2		20 m/s <sup>2</sup>	
Impact resistance*3		100 m/s <sup>2</sup>	

NOTE \*1) Values are at the same standard supply pressure and based on SMC's measurement standards. They depend on atmospheric pressure (weather, altitude, etc.) and measurement method.

NOTE \*2) 10 to 500Hz for 2 hours in each direction of X, Y and Z (de-energised, initial value).

NOTE \*3) 3 times in each direction of X, Y and Z (de-energised, initial value). NOTE \*4) Refer to operation manual of solenoid valve (JSY3000 series) and pressure switch (ZSE10 series) for the characteristics.

## 2.3 Vacuum pressure switch specifications

2.3 Vacuum pressure switch specifications				
		ZSE10		
Model		Vacuum pressure switch	Compound pressure switch	Pressure switch for vacuum with energy saving function
Ra ran	ted pressure ge	0 to -101 kPa	-101 kPa -100 to 100 kPa	
Set	t pressure range	10 to -105 kPa -105 to 105 kPa		to 105 kPa
Pro	of pressure		500 kPa	
Mir	nimum setting unit		0.1 kPa	
Power supply voltage		12 to 24 VDC ± 10%, Ripple (p-p) 10% or less (with power supply polarity protection)		
Cu	rrent consumption		40 mA or less	
Switch output		NPN or PNP open collector 2 outputs (selectable)		NPN or PNP open collector OUT1: General purpose OUT 2: Valve control
	Max. load current	80 mA  28V (at NPN output)  26.4V (at NPN output)  2 V or less (with load current of 80 mA)  2.5 ms or less (with anti chattering function 20,100,500,1000, 2000 ms)		1
	Max. applied voltage			,
	Residual voltage			nt of 80 mA)
	Response time			•
	Short circuit protection	Yes		
Repeatability		±0.2% F.S. ±1 digit		
<sub>ω</sub> Hysteresis mode		Va	riable (0 or abov	/e)
Hysteresis	Window comparator mode	Variable (0 or	above)	-
Display		3 ½ digit, 7-segment LED, 1-color display (Red)		
Dis	play accuracy	±2% F.S. ± 1 digit (Ambient temperature of 25 ± 3°C)		
Indicator light		Lights up when output is turned on. OUT1: Green, OUT2: Red		

	Enclosure	IP40
	Ambient	Operation: -5 to 50°C (No condensation or freezing)
tempe Ambie	temperature	Storage: -10 to 60°C (No condensation or freezing)
	Ambient humidity	Operation/Storage: 35 to 85% RH (No condensation)
Environmental resistance	Withstand voltage	1000 VAC for 1 minute between terminals and housing
Envir	Insulation resistance	50MΩ or more (500 VDC measured via megohmmeter) between terminals and housing
Temperature characteristics		±2% F.S. ±1 digit (at 25°C in an ambient temperature of -5 and 50°C)
Lead wire		Oil proof heavy-duty vinyl cable
		5 core Conductor area: 0.15 mm <sup>2</sup> (AWG26)
		Insulator O.D.: 1.0 mm

#### 2.4 Vacuum Pressure Switch with IO-Link

Mode	el	ZL3-VP□-1-EL□□-A	ZL3-VP□-1-FL□□-A	
Rated pressure range		0 to -101kPa	100 to -100 kPa	
Set pressure range		10 to -105 kPa	105 to -105 kPa	
Proof pressure		500 kPa		
Minimum setting unit		0.1 kPa		
Power supply voltage		24 VDC ± 10%, Ripple (p-p) 10% or less (with power supply polarity protection)		
Current consumption		40 mA or less		
Switch output		PNP open collector 2 outputs (For valves)		
	Residual voltage	2 V or less (at 80	mA load current)	
	Short circuit protection	Provided		

Repeatability		±0.2% F.S. ±1 digit	
Hysteresis		Variable from 0.1	
Display type		3 ½ digit, 7-segment LED, 1-color display (Red)	
Display accuracy		±2% F.S. ± 1 digit (Ambient temperature of 25 ± 3°C)	
Indication LED		Lights up when the valve is turned on. Release valve (OUT1): Green Supply valve (OUT2): Red	
Digital t	filter	Variant from 0 to 10s (0.01s steps)	
Digital	Enclosure	IP40	
Environmental resistance	Ambient temperature	Operation: -5 to 50°C (No condensation or freezing)  Storage: -10 to 60°C (No condensation or freezing)  Operation/Storage: 35 to 85% RH (No	
	Ambient humidity	condensation)  1000 VAC for 1 minute between terminals	
viro	Withstand voltage	and housing	
En	Insulation resistance	50MΩ or more (500 vdc measured via megohmmeter) between terminals and housing	
Temperature characteristics		±2% F.S. (25°C standard)	
Lead wire		Cable: 3 wires, φ3.4, 300 mm, Insulator O.D.: 1.0 mm Valve connector lead wire: 100 mm, Insulator O.D.: 1.5 mm	

## 3 Installation

#### 3.1 Installation

## **Marning**

- Do not install the product unless the safety instructions have been read and understood.
- When mounting the product, tighten with the recommended tightening torque of the following screws.
  - Top surface and side surface mounting: 0.56 to 0.76 N•m
  - Bottom mounting: 0.29 to 0.30 N·m
- When installing the product, secure the space required for maintenance and inspection of the product.
- Do not drop, hit, or apply excessive impact to the product.

#### 3.2 Environment

## **Marning**

- Do not use in an environment where corrosive gases, chemicals, salt water or steam are present.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
- Do not install in a location subject to vibration or impact in excess of the product's specifications.
- Do not mount in a location exposed to radiant heat that would result in temperatures in excess of the product's specifications.
- This product does not have a built-in suction filter. If there is dust in the usage environment of the product, consider using a vacuum filter (AFJ series)
- Do not use in place where static electricity build-up can occur.
- . Do not use in an environment where surges occur.

## 3.3 Air Supply

## **⚠** Caution

- Do not use air containing chemicals, synthetic oils containing organic solvents, salts, or corrosive gases.
- Recommended quality of the supplied air be equivalent to the compressed air cleanliness grade "2: 6: 3" according to ISO8573-1: 2010
- Do not supply the pressure in excess of the product's specifications.


## 3.4 Piping

#### **↑** Caution

- Before connecting piping make sure to clean up chips, cutting oil, dust etc.
- When installing piping and fittings, make sure that no sealing material gets inside the port. When using sealing tape, wind it with one thread loft.
- Tighten fittings to the specified tightening torque shown in the table below.

Port type	Port size	Recommended
		tightening torque
Vacuum (2/V) port	1/2 or 3/4 (Rc, G, NPT)	28 to 30 N·m
Exhaust (3/E) port	1 (Rc, G, NPT)	36 to 38 N·m
Vacuum pressure	1/8 (Rc, NPT)	3 to 5 N⋅m

 Fix the side of the body when piping to the vacuum (2 / V) port and pressure detection (G) port and fix the side of the port block when piping to the exhaust (3 / E) port.




#### 3.5 Wiring to the solenoid valve and pressure switches

Refer to the operation manual of solenoid valve (JSY3000 series), pressure switch (ZSE10 series), and IO-Link compatible digital pressure switch.

#### ZL3-TF2Z370EN-A

## 4 Settings

## 4.1 Manual Override (With supply valve and release valve)



Refer to the operation manual of the solenoid valve JSY3000 series for the manual operation method.

#### 4.2 Release flow adjusting needle

When the release valve is turned on, vacuum break air is let out. The release flow adjusting needle allows to control the vacuum break air flow rate.

To adjust the break air flow, pull the push-locking handle to unlock it. Then, turn the push-locking handle clockwise to reduce the vacuum break flow, and turn the handle anti-clockwise to increase the flow.

#### 5 How to Order

Refer to the catalogue for 'How to Order'.

## 6 Outline Dimensions (mm)

Refer to the catalogue for outline dimensions.

#### 7 Maintenance


#### 7.1 General Maintenance

## **A** Caution

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous.
- Maintenance of pneumatic systems should be performed only by qualified personnel.
- Before performing maintenance, turn off the power supply and be sure to cut off the supply pressure. Confirm that the air is released to atmosphere.
- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly, and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions.
- Implement the maintenance and check shown below to use the multistage ejector safely and in an appropriate way for a long period of time.
- Drain the air filter and mist separator regularly.
- Replace the sound absorbing material (silencer) built into the ejector regularly.
- Refer to the online operation manual for replacement parts.
- Do not use benzene or thinner for cleaning.

#### 7.2 Replacement method of sound absorbing material (ZL3)


- 1) Loosen the two mounting screws of the silencer assembly and remove the silencer case (Fig.1)
- 2) Replace the sound absorbing material inside the silencer case (Fig.2)
- Attach the silencer assembly using the mounting screws.
   (Recommended tightening torque: 0.76 to 0.84 Nm)



## 7 Maintenance - continued

#### 7.3 Silencer assembly (ZL6)

- Align the hook of the silencer assembly with the groove of the body, break it, and push it in the direction of the arrow until it clicks.
- 2) When removing, slide the silencer assembly in the direction opposite to the mounting direction to remove it.



Push in until clicks

#### 8 Limitations of Use

# **8.1** Limited warranty and Disclaimer/Compliance Requirements Refer to Handling Precautions for SMC Products.



## • Exhaust from Multistage ejector

- For the silencer exhaust type, make sure that there is no obstruction around the exhaust port.
- 2) In the case of port exhaust type, exhaust resistance may be affected depending on the pipe diameter and length, so make sure that the back pressure is 1 kPa or less.
- 3) Do not block the exhaust port.

#### Eiector exhaust noise

When the vacuum ejector generates a vacuum, an intermittent noise (abnormal noise) may be generated from the exhaust section near the standard supply pressure where the vacuum pressure peaks, and the vacuum pressure may not be constant. There is no problem in use as

long as the vacuum pressure range is sufficient for adsorption, but if you are concerned about the sound or affect the setting of the pressure switch, slightly change the supply pressure and reduce the range of the intermittent sound. Please avoid it.

## · About the breaking flow rate adjusting needle

- 1) Leakage cannot be reduced to zero when the needle is fully closed.
- 2) Check that the push lock handle is locked.
- 3) When unlocking the push lock handle, do not pull it with excessive force
- 4) This release flow adjustment needle does not rotate more than 12 rotations from fully closed. If you try to rotate the needle any further, it may be damaged.
- 5) Do not tighten the handle with tools such as pliers.
- About solenoid valve and pressure switch
- For the solenoid valve (JSY3000 series) and pressure switch (ZSE10 series), refer to each instruction manual.

## 9 Product disposal

This product should not be disposed of as municipal waste. Check your local regulations and guidelines to dispose this product correctly, in order to reduce the impact on human health and the environment.

## 10 Contacts

Refer to <u>www.smcworld.com</u> or <u>www.smc.eu</u> for your local distributor/importer.

# **SMC** Corporation

URL: https:// www.smcworld.com (Global) https:// www.smc.eu (Europe) SMC Corporation, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, Japan Specifications are subject to change without prior notice from the manufacturer. © 2024 SMC Corporation All Rights Reserved. Template DKP50047-F-085M

Page 2 of 2