# **Digital Pressure Switch Operation Manual** ZSE10(F)/ISE10



Thank you for purchasing the SMC ZSE10(F)/ISE10 Series Digital Pressure Switch

Please read this manual carefully before operating the digital pressure switch and make sure you understand the digital pressure switch, its capabilities and limitations.

Please keep this manual handy for future reference.

To get information in detail for operating this product, refer to SMC website (URL http://www.smcworld.com) or contact us.

## Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage

These instructions indicate the level of potential hazard with the labels of "Caution", " Warning" or "Danger". They are all important notes for safety and must be followed in addition to International standards (ISO/IEC), Japan Industrial Standards (JIS) and other safety regulations.

<b>▲</b> Caution:	Operator error could result in injury or equipment damage.
A Warning:	Operator error could result in serious injury or loss of life.
 ▲ Danger:	In extreme conditions, there is a possibility of serious injury or loss of life.

### Operator

- This operation manual is intended for those who have knowledge of machinery using pneumatic equipment, and have sufficient knowledge of assembly, operation and maintenace of such equipment. Only those persons are allowed to perform assembly, operation and maintenance. Read and understand this operation manual carefully before assembling,
- operating or providing maintenance to the product.

## ■Safetv Instructions

∆Warning
Do not disassemble, modify (including changing the printed circuit board) or repair. An injury or failure can result.
Do not operate the product outside of the specifications.
Do not use for flammable or harmful fluids.
Fire, malfunction, or damage to the product can result.
Verify the specifications before use.
Do not operate in an atmosphere containing flammable or explosive gases.
Fire or an explosion can result.
This product is not designed to be explosion proof.
Do not use the product in a place where static electricity is a problem.     Otherwise it can cause failure or malfunction of the system.     If using the product in an interlocking circuit:
Check the product regularly for proper operation
Otherwise malfunction can result, causing an accident.
The following instructions must be followed during maintenance: • Turn off the power supply
<ul> <li>Stop the air supply, exhaust the residual pressure and verify that the air is released before performaintenance.</li> </ul>
Otherwise an injury can result.
<b>∆</b> Caution
Do not touch the terminals and connectors while the power is on. Otherwise electric shock, malfunction or damage to the product can result.
· ·


After maintenance is complete, perform appropriate functional inspections and leak tests Stop operation if the equipment does not function properly or there is a leakage of fluid. When leakage occurs from parts other than the piping, the product might be faulty Disconnect the power supply and stop the fluid suppl Do not apply fluid under leaking conditions. Safety cannot be assured in the case of unexpected malfunction

## ■NOTE

- The direct current power supply to be used should be UL approved as follows: Circuit (of class 2) which is of maximum 30Vrms (42.4V peak) or less, with UL 1310 class 2 power supply unit or UL 1585 class 2 transformer
- The Pressure switch is a a proved product only if it has a a a mark on the body.

# Names and Functions of Product

## Names of individual parts



Output (OUT1) display (Green): Lights ON when the switch output (OUT1) is turned ON.

Output (OUT2) display (Red): Lights ON when the switch output (OUT2) is turned 0Ň

LED display: Displays the current status of pressure, setting mode and error code. button (UP): Selects the mode or increases the ON/OFF set value. Press this button to change to the peak display mode.


Dutton (DOWN): Selects the mode or decreases the ON/OFF set value. Press this button to change to the bottom display mode.

In button (SET): Press this button to change to either mode and to set a value.

# Mounting and Installation

## Installation

- OMounting \*: The tightening torque of piping port must be 1 Nm for M5 (This is equivalent to approximate 1/6extra tighting after manual tighting.) and 7 to 9 Nm for R1/8 and
- NPT1/8. • Mount with the set screws M3 size (2 pcs.)
- for direct installation The tightening torque of the mounting screw must be 0.5 to 0.7 Nm.
- OMounting with panel mount adapter · Panel mount adapter + Front protective cover (Model: ZS-39-D)



- It is necessary to prepare a DIN rail adapter for the mounting on the DIN rail. (Model: ZS-39-R)
- Take care not to bend the claws of the DIN rail adapter when mounting.
- <Mounting of DIN rail adapter> Engage the pressure switch with claw 2 of the DIN rail adapter then press down horizontally on to claw 1 until it clicks.

#### <Mounting on DIN rail>

Engage claw 1 of the adapter on to the DIN rail as indicated [1], apply force in direction [2] indicated, then press downward horizontally [3] until claw 2 clicks on to the DIN rail.

#### <Removal of DIN rail>

Move in the direction [1], and remove claw 1 as indicated with [2]

## ■Piping

ning

- Ocnnection using One-touch fitting Cut the tube perpendicularly.
   Hold the tube and insert it into the One-
- touch fitting slowly until it bottoms out. One-touch fitt
- Allow sufficient tube length to prevent twist, tensile and moment load from being applied to the fitting and tube . When using a tube manufactured by another company, check its outside
- diameter accuracy satisfies the following conditions. 1) Nylon tube: ±0.1 mm maximum 2) Soft nylon tube: ±0.1 mm maximum
- 3) Polyurethane tube: +0.15 mm/-0.2 mm maximum

## ■Wiring

### OConnection

- Make connection after turning the power off
- •Use a separate route when connecting the wire of the Pressure switch. Malfunction stemming from noise may occur if the wire is installed in the same route as that of power or high-voltage cable.
- ·Be sure to ground terminal FG when using a commercially available switchmode power supply. When the switch-mode power supply is connected to the Pressure switch, switching noise will be superimposed and product specification can no longer be met. This can be prevented by inserting a noise filter, such as a line noise filter and ferrite core, between the switchmode power supply and the Pressure switch, or by using a series power supply instead of the switch-mode power supply


#### Oconnector Connecting/Disconnecting

- •When mounting the connector, insert it straight into the socket, holding the lever and connector body, and fit the hook of the lever into the groove in the housing to lock.
- •When removing the connector, press down the lever to release the hook from the groove and pull the connector straight out. Pin No. of the Conn

OUT1

OUT2

(FUNC)





#### **Pressure Setting** Set ON point and OFF point of the Pressure switch. Operation When the pressure exceeds a set value, the Pressure switch will be turned on. When the pressure falls below the set value by the amount of hysteresis or more, the Pressure switch will be turned off. Switch ON The default setting of the output For normal output Switch OFF ---set value is the central value Time (s) between the atmospheric pressure and the upper limit of the rated pressure range. If the operation shown the right does not cause any problem, keep this operation setting. <How to operate> [Hysteresis mode] (1) Press the B button once in measurement mode Normal output Displays in tu (2) [P\_1] or [n\_1] and the set value are 50 displayed in turn. Reversed output n., (3) Press the or button to change the set value. The button is for increase and the button is for decrease • Press the button once to increase by one figure, and 10 m 5 10 press it continuously to keep Com Co 490 increasing the set figure. Press the substant button once to decrease by one figure, and press it continuously to keep decreasing the set figure. (4) Press the button to finish the setting. If 2 outputs specification is selected, [P\_2] is displayed. Set OUT2 in the same way as OUT1.

[Window comparator mode]

The Pressure switch turns on within a set pressure range (from P1L to P1H) during window comparator mode. Set P1L (switch lower limit) and P1H (switch upper limit) using the setting procedure above.

#### \_\_\_\_\_ Zero clear of indication

Indication is reset to zero when 
and
buttons are pressed simultaneously for 1 second

For the first operation, perform zero clear without pressure supply

# Setting of Function

## Default setting

At the time of shipment, the following settings are provided. If the setting is acceptable, keep it for use To change setting, refer to SMC website (URL http://www.smcworld.com) to get

information in detail or contact us

[F 0] Unit conversion function

Unit specification	Pressure range	Default setting	
Nil or M	ISE10	MPa	
	ZSE10(F)	kPa	
Р	ISE10	PSI	
F	ZSE10(F)		

#### •[F 1] Setting of OUT1


Item	Explanation	Default setting
Output mode	Selects hysteresis mode or window comparator mode.	Hysteresis mode
Reversed output	Selects reversed output.	Normal output
Pressure setting	Sets ON point or OFF point of the switch output	ISE10: 0.500 MPa ZSE10: -50.5 kPa ZSE10F: 50.0 kPa
Hysteresis	Chattering can be prevented by setting hysteresis.	5%


•[F 2] Setting of OUT2


Other parameter setting

Same setting as [F 1] OUT1.

#### Item [F 3] Setting of response time 2.5 ms [F 4] Setting of auto-pre Manual [F 6] Setting of fine adjustment of display va 0% [F11] Setting of display res 1000-split OFF [F80] Setting of power saving mode [F81] Setting of security cod OFF [F90] Setting of all functions OFF [F97] Selection of copy function OFF [F98] Check of output Normal F99] Reset to the default OFF




























## ■Measurement mode

The measurement mode is the condition where the pressure is detected and indicated, and the switch function is operating. This is the basic mode, and other modes should be selected for setting change and other function setting change



## Function selection mode

In measurement mode, press the I button for 2 seconds or longer to display [F 0]. Select to display the function setting to be changed,  $[F \Box \Box]$ Press the I button for 2 seconds or longer in function selection mode to return to measurement mode.



\*: Some functions are not available depending on part number. All functions are displayed with [F ] ] and followed with function description. If a function is not available for specified type, the function is displayed as [---].

# Other Settings

#### OPeak/Bottom hold value indication

OZero clear

- •Key lock
- To set each function the above in detail, refer to SMC website
- (URL http://www.smcworld.com) to get information in detail or contact us.

# Maintenance

How to reset the product for power cut or forcible de-energizing The setting of the product will be retained as it was before a power cut or de eneraizina

The output condition is also basically recovered to that before a power cut or deenergizing, but may change depending on the operating environment. Therefore, check the safety of the whole facility before operating the product. If the facility is using accurate control, wait until it has warmed up. (Approximately 10 minutes)

# Troubleshooting

## Error indication function

This function is to display error location and content when a problem or an error occurs

Error Name	Error Display	Error Type	Troubleshooting Method	
Over current Error	Er 1 Er 2	A load current of switch output is 80 mA or more.	Turn the power off and remove the output factor for the over current. Then turn the power on.	
Zero-clear Error	Er B	During zero clear operation, pressure over $\pm7\%$ F.S. $\pm3.5\%$ F.S.for compound pressure) is applied. After 1 s, the mode will reset to the measurement mode. $\pm1\%$ F.S. of the zero clear range varies with individual product differences.	Perform zero clear operation again after restoring the applied pressure to an atmospheric pressure condition.	
Pressurizing	ннн	Pressure has exceeded the upper limit of the set pressure range.	Reset applied pressure to a level	
Error	LLL	Pressure has exceeded the lower limit of the set pressure range.	within the set pressure range.	
System Error	0 7 6 7 8 9 5 5 5 7 8 9 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5	Displayed in the case of an internal data error.	Turn the power off and turn it on again. If resetting fails, an investigation by SMC CORPORATION will be required.	

If the error can not be reset after the above measures are taken, then please contact SMC

# Specification

Refer to the product catalogue or SMC website (URL http://www.smcworld.com) to get information about product specifications in detail.

# Outline with Dimensions (in mm)

Refer to the product catalogue or SMC website (URL http://www.smcworld.com) to get information about outline dimensions in detail

### SMC Corporation URL http://www.smcworld.com

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: +81 3-5207-8249 Fax: +81 3-5298-5362

Ver.A

Note: Specifications are subject to change without prior notice and any obligation on the part of the manufacture © 2009 SMC Corporation All Bights Bese