# **Before Use Digital Pressure Switch**

# ZSE20B(F)-L/ISE20B-L

Thank you for purchasing an SMC ZSE20B(F)-L/ISE20B-L Series Digital Pressure Switch

Please read this manual carefully before operating the product and make sure you understand its capabilities and limitations. Please keep this manual handy for future reference

> To obtain the operation manual about this product and control unit, please refer to the SMC website (URL http://www.smcworld.com) or contact SMC directly.

# Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage.

These instructions indicate the level of potential hazard with the labels of "Caution", "Warning" or "Danger". They are all important notes for safety and must be followed in addition to International standards (ISO/IEC) and other safety regulations.

<b>▲</b> Caution:	CAUTION indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
A Warning:	WARNING indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
<b>∆</b> Danger:	DANGER indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

#### Operator

- The operation manual is intended for those who have knowledge of machinery using pneumatic equipment, and have sufficient knowledge of assembly, operation and maintenance of such equipment. Only those persons are allowed to perform assembly, operation and maintenance
- Read and understand the operation manual carefully before assembling, operating or providing maintenance to the product.


## ■Safety Instructions

	🖄 Warning
Do not disassemble, An injury or failure can	modify (including changing the printed circuit board) or repair. result.
Do not operate the pr Do not use for flammat	oduct outside of the specifications.
	amage to the product can result.
Verify the specification	
Do not operate in an a Fire or an explosion ca	atmosphere containing flammable or explosive gases.
	igned to be explosion proof.
Do not use the produ Otherwise it can cause	ct in a place where static electricity is a problem. failure or malfunction of the system.
<ul> <li>Provide a double interest</li> </ul>	n an interlocking circuit: erlocking system, for example a mechanical system
	egularly for proper operation can result, causing an accident.
•Turn off the power s •Stop the air supply, maintenance work	exhaust the residual pressure and verify that the air is released before performing
Otherwise an injury car	Tresuit.
	🛆 Caution
Do not touch the term	ninals and connectors while the power is on.

After maintenance is complete, perform appropriate functional inspections and leak tests Stop operation if the equipment does not function properly or there is a leakage of fluid. Such operation if the equipment does not function properly of interests a teakage of When leakage occurs from parts other than the piping, the product might be faulty. Disconnect the power supply and stop the fluid supply. Do not apply fluid under leaking conditions. Safety cannot be assured in the case of unexpected malfunction.

# Summary of Product parts

#### ONames of individual parts




# Mounting and Installation

# ■Installation

**OIO**-Link


OMounting Mount the optional bracket and panel mount adapter to the pressure switch. When the pressure switch is to be mounted in a place where water and dust splashes occur, insert a tube into the atmospheric vent port of the pressure switch. (Refer to "Tube attachment")

•Mounting with bracket •Mount the bracket to the body with mounting screws (Self tapping screws: Nominal size 3 x 8L (2 pcs)), then set the body to the specified position. \*: Tighten the bracket mounting screws to a torque of 0.5±0.05 Nm. Self tapping screws are used, and should not be re-used several times. •Bracket A (Part No.: ZS-46-A1) •Bracket B (Part No.: ZS-46-A2)



#### OMounting with panel mount adapter

 Mount part (a) to the front of the body and fix it. Then insert the body with (a) into the panel until (a) comes into contact with the panel front surface. Next, mount part (b) to the body from the rear and insert it until (b) comes into contact with the panel for fixing.



Refer to the product catalog or SMC website (URL http://www.smcworld.com) for more information about panel cut-out and mounting hole dimensions

# ■Piping

- OTightening the connection thread
- •For connecting to the body (piping specification: -M5) After hand tightening, apply a spanner of the correct size to the spanner flats of the piping body, and tighten with a 1/6 to 1/4 rotation.
- As a reference, the tightening torque is 1 to 1.5 Nm. (When replacing the piping adapter ZS-46-N\*, tighten it using the same method.)
- Piping specification: -01, -N01 After hand tightening, hold the hexagonal spanner flats of the pressure port with a spanner, and tighten with 2 to 3 rotations.
- As a reference, the tightening torque is 3 to 5 Nm.
- When tightening, do not hold the pressure switch body with a spanner



- OTube attachment
- •When the pressure switch is used in a place where water and dust splashes may occur, insert a tube in the atmospheric vent port, and position the other end of the tube at a safe position to protect the vent port from water
- and dust (see the figure right).
  The tube should be inserted to the end of the atmospheric vent port.
  SMC TU0425 (polyurethane, O.D ø4, I.D ø2.5) is a suitable tubing.

# ■Wiring

- Owiring connections Connections should be made with the power supply turned off. Use a separate route for the product wiring and any power or high voltage wiring. Otherwise, malfunction may result due to noise.

Tube -

To a safe position

to protect from

water and dust.

•

6

Lead wire

(Blue)

Connector

0

Atmospheric

vent port

Concave

- Hool

\Pins

Lead wire

(Brown)

 If a commercially available switching power supply is used, be sure to ground the frame ground (FG) terminal. If the switching power supply is connected for use, switching noise will be superimposed and it will not be able to meet the product specifications. In that case, insert a noise filter such as a line noise filter/ferrite between the switching power supplies or change the switching power supply to the series power supply.

#### OHow to use connector


- •When connecting the connector, insert it straight onto the pins, holding the lever and connector body, and lock the connector by pushing the lever hook into the concave groove on the housing.
- To detach the connector, remove the hook
- from the groove by pressing the lever downward, and pull the connector straight out.

# Connector pin numbers


Pin\_No. DC(+) Brown 5 OUT1 Black 4 – NC White 3 – NC Grav 2 – Gray DC(-) Blue

# **Outline of Settings [Measurement mode]**

#### Power is supplied. ł



- The outputs will continue to operate during setting. If a button operation is not performed for 3 seconds during the setting, the display will flash. (This is to prevent the setting from remaining incomplete if, for instance, an operator were to leave during
- setting.) \*: 3 step setting mode, simple setting mode and function selection mode settings are reflected each other.
- Pressure Setting



the atmospheric pressure and upper limit of the rated pressure range. If this condition, shown to the right, is acceptable, then keep these settings

## 3 Step Setting Mode

[3 step setting mode (hysteresis mode)]

In the 3 step setting mode, the set value (P\_1 or n\_1) and hysteresis (H\_1) can be changed. Set the items on the sub display (set value or hysteresis) with a or b button. When changing the set value, follow the operation below. The hysteresis setting can be changed in the same way.

- changed is displayed on the sub display. The set value on the sub display (right) will start value flashing
- (2) Press the 🔿 or 😒 button to change the set value. The set value can be increased with button and can be reduced with button. When and buttons are pressed and held simultaneously for <u>1 second or</u> longer, the set value is displayed as [- - -], and the set value will be the same as the current pressure value automatically (snap shot function).

Afterwards, it is possible to adjust the value by pressing i or i button. (3) Press the setting.

## The pressure switch turns on within a set pressure range (from P1L to P1H) during window comparator mode. Set P1L, the lower limit of the switch operation, and P1H, the upper limit of the switch

(When reversed output is selected, the sub display (left) shows [n1L] and [n1H].)

- \*: Set OUT2 in the same way. (ex. P\_2, H\_2)
- \*: Setting of the normal/reverse output switching and hysteresis/window comparator mode switching are performed with the function selection mode [F 1] OUT1 setting and [F 2] OUT2 setting.

# Simple Setting Mode

(1) Press and hold the 
button <u>between 1 and 3 seconds</u> in measurement mode. [SEt] is displayed on the main display. When the button is released while in the [SEt] display, the current pressure value is displayed on the main display, [P\_1] or [n\_1] is displayed on the sub display (left), and the set value is displayed on the sub display (right) (Flashing).



- (2) Change the set value with 🔿 or 😒 button, and press the 🗉 button to set the value. Then, the setting moves to hysteresis setting. (The snap shot function can be used.)
- (3) Change the set value with or v button, and press the v button to set the value. Then, the setting moves to the delay time of the switch output. (The snap shot function can be used.)
- (4) Press the 
  one of 
  button, the delay time of the switch output can be selected Delay time setting can prevent the output from chattering.
- (5) Press the button for <u>2 seconds or longer</u> to complete the setting.
  \*: If the button is pressed for less than 2 seconds, the setting will moves to the OUT2 setting

In the window comparator mode, set P1L, the lower limit of the switch operation, and P1H, the upper limit of the switch operation, WH1 (hysteresis) and dt1 (delay time) following the instructions given above.

(When reversed output is selected, the sub display (left) shows [n1L] and [n1H].) \*: Set OUT2 in the same way.

Current pressure



(1) Press the s button once when the item to be

# **Function Selection Mode**

#### ■Function selection mode

In measurement mode, press the s buttor between 3 and 5 seconds, to display [F 0]. Select to display the function to be changed [F ] ]. Press and hold the 🗊 button for 2 seconds or longer in function selection mode to return to measurement mode.

\*: Some products do not have all the functions. If no function is available or selected due to configuration of other functions, [- -] is displayed on the sub display (right).

#### ■Default setting

The default setting is as follows. If no problem is caused by this setting keep these settings.

• [F 0] Display units, switch output specifications and diagnostic information selection function

Units specification Pressure range Default setting

"Nil" or M	ISE20B	MPa	
	ZSE20B(F)	kPa	
Р	ISE20B	psi	
F	ZSE20B(F)		
Item		Default setting	
Switch output specifications		PNP	

Measurement mode
Press the s button between 3 and 5 seconds.
F0 Function setting         F1 Function setting         F99 Function setting

#### •[F 1] Setting of OUT1

Item	Default setting	
Output mode	Hysteresis mode	
Reversed output	Normal output	
Pressure setting	ISE20B: 0.500 MPa/ZSE20B: -50.0 kPa/ ZSE20BF: 50.0 kPa	
Hysteresis	ISE20B: 0.050 MPa/ZSE20B: 5.0 kPa/ ZSE20BF: 5.0 kPa	
Delay time	0.00 sec.	
Display color	Output ON: Green/Output OFF: Rec (Linked to OUT1)	
• IF 21 Setting of OUT2		

Same setting as [F 1] OUT1

Switch output specifications Other parameter settings

Diagnostic information

Item	Default setting	Item	Default setting
[F 3] Digital filter setting	0.00 ms	[F80] Power saving mode	OFF
[F 4] Auto-preset function	OFF	[F81] Security code	OFF
[F 6] Fine adjustment of display value	0.0%	[F90] Setting of all functions	OFF
[F10] Sub display setting	std (Standard)	[F96] Number of pressurizing errors	-
[F11] Display resolution setting	1000-split		N/A (normal output)
[F14] Zero cut-off setting	0.0	[F99] Reset to default settings	OFF

If you use the product by changing the setting, refer to the SMC website

ALI

(URL http://www.smcworld.com) for more detailed information, or contact SMC.

## Other Settings

#### ○Peak/bottom value indication

The max. (min.) pressure when the power is supplied is detected and updated. The value can be displayed on the sub display by pressing a or so button in asurement mode

#### Snap shot function

The current pressure value can be stored to the switch output ON/OFF set point. When the set value and hysteresis are set, press the and buttons for <u>1 second</u> or longer simultaneously. Then, the set value of the sub display (right) shows [---], and the values corresponding to the current pressure values are automatically displayed. ○Zero-clear function

In measurement mode, when the  $\bigtriangleup$  and  $\boxtimes$  buttons are pressed for <u>1 second or</u> longer simultaneously, the main display shows [- - -], and the reset to zero The display returns to measurement mode automatically.

#### ○Kev-lock function

To set each of these functions refer to the SMC website

(URL <u>http://www.smcworld.com</u>) for more detailed information, or contact SMC.

#### Maintenance

#### How to reset the product after a power cut or forcible de-energizing

The setting of the product will be retained as it was before a power cut or de-energizing. The output condition is also basically recovered to that before a power cut or dethe safety of the whole installation before operating environment. Therefore, check the safety of the whole installation before operating the product. If the installation is using accurate control, wait until the product has warmed up (approximately 10 to 15 minutes).

# Troubleshooting

#### Error indication function

This function is to display error location and content when a problem or error has occurred.

Error	Error displayed	Description	Measures	
Over current error	Er 1, Er 2 ,	The switch output load current is 80 mA or more.	Turn the power off and remove the cause of the over current. Then supply the power again.	
Residual pressure error	Ero J	During zero clear operation, pressure greater than $\pm7\%F.S.$ is present. Note that the mode is returned to measurement mode automatically 1 sec. later. The zero clear range varies by $\pm1\%F.S.$ due to variation between individual products.	Release the applied pressure to atmospheric pressure, and retry the zero clear operation.	
Pressurizing	XXX	Pressure exceeding the upper limit of the set pressure range is applied.	Reset applied pressure to a	
error		Pressure exceeding the lower limit of the set pressure range is applied.	level within the set pressure range.	
System error		Displayed if an internal data error has occurred.	Turn the power off and on again. If the failure cannot be solved, contact SMC.	
Version does not match	Er 15 1 0	IO-Link Master and product version are not matched.	Align the master IO-Link version to the device.	

If the error cannot be reset after the above measures are taken, or errors other than above are displayed, please contact SMC. Refer to the SMC website (URL <u>http://www.smcworld.com</u>) for more information about

troubleshooting

# Specifications/Outline with Dimensions (in mm)

Refer to the product catalog or SMC website (URL <a href="http://www.smcworld.com">http://www.smcworld.com</a>) for more information about the product specifications and outline dimensions.

#### SMC Corporation URL http://www.smcworld.com

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: +81 3-5207-8249 Fax: +81 3-5298-5362

Note: Specifications are subject to change without prior notice and any obligation on the part of the manufacturer © 2017 SMC Corporation All Rights Reserved PS: PS\*\*\*-OMV0007