Speed Controller with Indicator

In-line Type

The numerical indication of flow rate knob rotations

reduces flow

etting time and setting errors!

In-line Stainless steel **Brass** 1 1

RoHS

"Made to Order" section has been added.	Pages 3, 8
 Lubricant: Vaseline 	-X12
Grease-free + RestrictorRestrictor	-X21 -X214
Clean Series	10-

Flow rate can be controlled indicator window. numerically with the




Bod	y size 1	Body siz	e 2
Indicator window	Number of needle rotations	Indicator window	1 nee
1	1	1	
2	2	2	
:	•	:	
8	8	10	


	Body size 2 or larger								
r of ations	Indicator window	Number of needle rotations							
	1	1							
	2	2							
	:								
	10	10							

3


4 indicator window directions available



Larger **Push-lock type** knob




The larger knob and marking of every 90° mark allows for easier operation.









AS-FS Series








Easy Identification of Product Type

By index plate

By colour

It is possible to identify the product when multiple controllers are mounted **Release button colour** and identify the flow direction by attaching an identification label. Model Metric Inch Page 3 Light grey Orange AS-FS Page 8 White White Index plate AS-FSG (Example with identification label attached)





Push-Lock Series Variations



Speed Controller with One-touch Fittings In-line Type *AS Series*



SMC

Speed Controller with Indicator (In-line Type) **AS-FS** Series



Model

	1			٨	nnlin	oblo	tubin	~ ^				
						able	lubin	g O.I				
Model		I	Metri	c size	Э				Inch	size		
	3.2	4	6	8	10	12	1/8"	5/32"	1/4"	5/16"	3/8"	1/2"
AS1002FS												
AS2002FS												
AS2052FS				•					•			
AS3002FS				٠	٠	٠			٠			
AS4002FS												

Specifications

Fluid	Air
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperatures	−5 to 60 °C (No freezing)
Applicable tubing material	Nylon, Soft nylon, Polyurethane*1, FEP, PFA

*1 Use caution at the max. operating pressure when using soft nylon or polyurethane tubing. (Refer to the web catalogue on www.smc.eu for details.)

Flow Rate and Sonic Conductance

Mod	Model AS1		1002FS /		AS200	AS2002FS		AS2052FS		AS3002FS			AS4002FS	
Tubing	Metric size	Ø 3.2	Ø 4	Ø 6	Ø 4	Ø6	Ø 6	Ø 8	Ø6	Ø 8	Ø 10	Ø 12	Ø 10	Ø 12
Tubing O.D.	Inch size	Ø 1/8"	Ø 5/32"	Ø 1/4"	Ø 5/32"	Ø 1/4"	Ø 1/4"	Ø 5/16"	Ø 1/4"	Ø 5/16"	Ø 3/8"		Ø 3/8"	Ø 1/2"
C values: Sonic	Free flow	0.3	0.4	0.6	0.4	0.6	1.0	1.2	1.1	1.6	2.2	2.6	2.4	3.5
conductance dm ³ /(s·bar)	Controlled flow		0.3		0.4	0.6	1.0	1.2	1.3	1.9	2.7	3.3	2.8	4.1
b values: Critical	Free flow	0.3	0.	2	0.3	0.1	0	.2		0.	2		0.3	0.2
pressure ratio	Controlled flow	0.2	0.3	0.4	0.	.2	0.2	0.3	0	.1	0.	2	0.1	0.2

Flow Direction Symbol on Body Symbol

> Made to Order


-X1

-X21

10-

* C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.

* The same specifications also apply to the AS-FSG series (stainless steel type).



Speed Controller with Indicator (In-line Type) **AS-FS** Series

Options

1Adapter for Direct Mounting


* For use when the mounting surface interferes with the bonnet.								
Part no.	Applicable model							
AS-10A1	AS1002FS							
AS-20A1	AS2002FS							
AS-25A1	AS2052FS							
AS-30A1	AS3002FS							


* The AS4002FS^{__} can be mounted without the adapter.


Adapter for direct mounting



② DIN Rail Mounting Bracket Part no. Applicable model AS-10D AS1002FS□ AS-20D AS2002FS□ AS-25D AS2052FS□







*1 Prepare DIN rail by user.

*2 It is included in the threaded stud kit for manifold (excluding the AS4002FSD). Refer to the following details of the kit.

4 Threaded Stud Kit for Manifold


	Part n	umber	Applicable model			
4 stations	6 stations	8 stations	10 stations	Metric size	Inch size	
	AS-3AB	AS-5AB	AS-7AB	AS1002FS□-23	AS1002FS□-01	
AS-1AB	AS-SAD	AS-SAD	A3-7AD	AS1002FS□-04	AS1002FS□-03	
	AS-4AB	AS-6AB	AS-8AB	AS1002FS□-06	—	
AS-2AB	AS-4AD	AS-0AD	AS-23AB	—	AS1002FS□-07	
				AS2002FS□-04	AS2002FS□-03	
AS-9AB	AS-10AB	AS-11AB	AS-12AB	AS2002FS□-06	—	
				—	AS2002FS□-07	
				AS2052FS□-06		
AS-13AB	AS-14AB		AB AS-16AB	—	AS2052FS□-07	
				AS2052FS□-08	AS2052FS□-09	
				AS3002FS□-06	_	
			AS-22AB	—	AS3002FS□-07	
AS-17AB	AS-19AB			AS3002FS□-08	AS3002FS□-09	
	AS-ISAD	A3-20AD		AS3002FS□-10	_	
				_	AS3002FS□-11	
AS-24AB			AS-25AB	AS3002FS□-12		
				AS4002FS□-10		
AS-43B	AS-45B	AS-47B	AS-48B		AS4002FS□-11	
A3-43D	A3-43D	A2-4/B	A3-40D	AS4002FS□-12	—	
				_	AS4002FS□-13	

Details of Threaded Stud Kit for Manifold

				<u>ei ma</u>	moiu			
Part no.	Adapter for manife	old mounting	Thread	ed stud		Acces	sories	
Fait no.	Part no.	Quantity	Length	Quantity	Hexagon nut	Quantity	Flat washer	Quantity
AS-1AB	i artiio.	3	72	2				
AS-2AB		3	90	2				
AS-3AB		5	104	2				
AS-4AB		5	114	2				
AS-5AB	AS-10A	7	135	2				
AS-6AB		1	143	2				
AS-7AB			167	2	M3	4	M3	4
AS-8AB		9	170	2				
AS-23AB			180	2				
AS-9AB		3	90	2				
AS-10AB	AS-20A	5	135	2				
AS-11AB	AS-20A	7	180	2				
AS-12AB		9	220	2				
AS-13AB		3	111	2				
AS-14AB	AS-25A	5	147	2				
AS-15AB	A3-23A	7	191	2				
AS-16AB		9	236	2				
AS-17AB		3	111	2				
AS-24AB		3	119	2				
AS-19AB		5	179	2				
AS-20AB	AS-30A	7	236	2	M4	4	M4	4
AS-21AB		9	258	2				
AS-22AB		9	277	2				
AS-25AB		9	293	2				
AS-43B			119	2				
AS-45B			179	2				
AS-47B			236	2				
AS-48B			277	2				

Ordering Example

Threaded studs for manifold are not included when L-bracket and DIN rail mounting bracket are ordered. Please order them according to the number of stations.



It is included in the threaded stud kit for manifold (excluding the AS4002FS□) Refer to the details of the kit shown on the left.

* AS4002FS type can be mounted with the threaded stud kit only (Adapter for manifold mounting is not required).


AS-FS Series


Needle Valve: Flow Rate Characteristics


* The flow rate characteristics are representative values.

AS1002FSD


AS3002FS









AS4002FS




* The numbers above the flow rate characteristic curves in the charts show the applicable tubing outside diameter as defined by the product number.

Construction






L-Bracket



Component Parts

No.	Description	Material
1	Bracket	Steel strip
_1	Bracket	Steel strip

DIN Rail Mounting Bracket



Component Parts


No.	Description	Material
1	Bracket	Steel strip
2	Cross recessed round head screw	Steel wire
3	Clasp	Steel strip

Component Parts

No. Description Material Note 1 Body A PBT 2 Knob POM 3 Body B PBT 4 Needle PBT 5 Needle guide Brass 6 U-seal HNBR 7 Spacer PBT*1 8 Cassette - 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM 16 Clin Stainless steel				
2 Knob POM 3 Body B PBT 4 Needle PBT 5 Needle guide Brass Electroless nickel plating 6 U-seal HNBR 7 Spacer PBT*1 8 Cassette 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	No.	Description	Material	Note
3 Body B PBT 4 Needle PBT 5 Needle guide Brass Electroless nickel plating 6 U-seal HNBR 7 Spacer PBT*1 8 Cassette 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	1	Body A	PBT	
4 Needle PBT 5 Needle guide Brass Electroless nickel plating 6 U-seal HNBR 7 Spacer PBT*1 8 Cassette — 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	2	Knob	POM	
5 Needle guide Brass Electroless nickel plating 6 U-seal HNBR 7 Spacer PBT*1 8 Cassette — 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	3	Body B	PBT	
6 U-seal HNBR 7 Spacer PBT*1 8 Cassette — 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	4	Needle	PBT	
7 Spacer PBT*1 8 Cassette 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	5	Needle guide	Brass	Electroless nickel plating
8 Cassette 9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	6	U-seal	HNBR	
9 Seal NBR 10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	7	Spacer	PBT*1	
10 O-ring NBR 11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	8	Cassette	—	
11 O-ring NBR 12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	9	Seal	NBR	
12 Bonnet A POM 13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	10	O-ring	NBR	
13 Bonnet B POM 14 Gear PPS 15 Indicator gear POM	11	O-ring	NBR	
14 Gear PPS 15 Indicator gear POM	12	Bonnet A	POM	
15 Indicator gear POM	13	Bonnet B	POM	
	14	Gear	PPS	
16 Clip Stainless steel	15	Indicator gear	POM	
	16	Clip	Stainless steel	

*1 The AS3002FS□-11, AS4002FS□-11, AS4002FS□-13 are made of electroless nickel plated brass.

Dimensions



Metric Size

Model	Applicable tubing	D 1	Rele but	ease ton	D2	D3	D4	D5	L1	L2	L3	L	4 *1	L5	L6	L7	L8	M 1	W1	W2	X 1	X 2	Weight
	0.D. Ø d		Ø X (X)	Υ								Max.	Min.										[g]
AS1002FS□-23	3.2	8.4	6.7	9.5					36.6	5.1	11.8	36.4	33.9				10.1						5.2
AS1002FS□-04	4	9.3	7.7	10	3.3	5.5	9.4	10	37.6	5.1	11.0	30.4	33.9	11	15.4	8.8	10.1	13.5	13.6	15.1	5.5	9.6	5.5
AS1002FS□-06	6	11.6	9.7	12					40.1	6.1	12.8	37.4	34.9				12.3						6.6
AS2002FS□-04	4	9.3	7.7	10	3.3	5.5	12	12	41.3	6.3	13.4	44.5	10	12.6	17	10.5	12.3	13.5	20	21.5	6.5	15	9.5
AS2002FS□-06	6	11.6	9.7	12	3.3	5.5	12	12	43.1	0.5	13.4	44.5	43	12.0	17	10.5	12.3	13.5	20	21.5	0.5	15	10.4
AS2052FS□-06	6	12.8	11.5	—	4.3	7.8	13	16	54.2	7.6	17.2	49	47.6	17	22.5	12	16.1	17	21.5	24	7.8	16.2	16
AS2052FS□-08	8	15.2	13.5	—	4.3	7.0	15	10	57.2	8.5	18.1	49.9	48.5	17	22.5	12	10.1	19	21.5	24	7.0	10.2	18.4
AS3002FS□-06	6	13.2	11.5	—					60									17					23.8
AS3002FS□-08	8	15.2	13.5	—	4.5	8	16.6	20	65	9.8	21.7	55.7	54.3	21.8	25	12	20.5	19	24.5	28.5	9.3	19.2	26
AS3002FS□-10	10	18.5	16.5	—	4.5	0	10.0	20	70.4					21.0	25	12		21	24.5	20.5	9.3	19.2	30.6
AS3002FS□-12	12	20.9	18.5	—					76	10.9	22.8	56.8	55.4				22.1	22					34.2
AS4002FS□-10	10	18.5	16.5	—	4.3	8	18.8	26	76.9	11.3	23.7	64.3	62.7	28	33	14	26.0	21	26	29	10	19	42.5
AS4002FS□-12	12	21.7	18.5	—	4.3	0	10.8	20	81.3	11.3	23.7	04.3	02.7	20	33	14	26.2	22	20	29	10	19	47.9

*1 Reference dimensions

Inch Size

Model	Applicable tubing	D1	Rele but		D2	D3	D4	D5	L1	L2	L3	L	↓ *1	L5	L6	L7	L8	M1	W 1	W2	X 1	X 2	Weight
	0.D. Ø d		Ø X (X)	Υ								Max.	Min.										[g]
AS1002FS□-01	1/8"	8.4	6.7	9.5					36.6	5.1	11 0	36.4	22.0				10.1						5.2
AS1002FS□-03	5/32"	9.3	7.7	10	3.3	5.5	9.4	10	37.6	5.1	11.0	30.4	33.9	11	15.4	8.8	10.1	13.5	13.6	15.1	5.5	9.6	5.5
AS1002FS□-07	1/4"	12	10.9	—					40.1	6.2	12.9	37.5	35				12.8						6.7
AS2002FS -03	5/32"	9.3	7.7	10	3.3	5.5	12	12	41.3	6.3	13.4	44.5	43	12.6	17	10.5	12.3	13.5	20	21.5	6.5	15	9.5
AS2002FS□-07	1/4"	12	10.9	—	3.3	5.5	12	12	43.2	6.5	13.6	44.7	43.2	12.0	17	10.5	12.8	13.5	20	21.5	0.5	15	10.6
AS2052FS□-07	1/4"	13.2	12	—	4.3	7.8	13	16	53.4	7.6	17.2	49	47.6	17	22.5	12	16.1	17	21.5	04	7.8	16.2	16.4
AS2052FS□-09	5/16"	15.2	13.5	—	4.3	7.0	15	10	57.2	8.5	18.1	49.9	48.5	17	22.5	12	10.1	19	21.5	24	7.0	10.2	18.4
AS3002FS□-07	1/4"	13.2	12	—					59									17					23.6
AS3002FS□-09	5/16"	15.2	13.5	—	4.5	8	16.6	20	65	9.8	21.7	55.7	54.3	21.8	25	12	20.5	19	24.5	28.5	9.3	19.2	26
AS3002FS□-11	3/8"	18.5	16	—					69.8									21					38.1
AS4002FS□-11	3/8"	18.5	16	—	4.3	8	18.8	26	76.9	11.3	22.7	64.3	62.7	28	33	14	26.2	21	26	29	10	19	50.2
AS4002FS□-13	1/2"	21.7	20	—	4.3	0	10.0	20	81.3	11.3	23.1	04.3	02.7	20	33	14	20.2	22	20	29	10	19	57.4


*1 Reference dimensions

AS-FS Series

Dimensions


L-Bracket

Bracket on a single side




L13

L12




Part no.	Applicable model	D 5	L9	L10	L11	L12	L13	L 14	L15	L16	L17	t1
	AS1002FS	24	14.8	18.3	11	27.5	19.5	21	10	70	10	1
AS-20L	AS2002FS	3.4	15.6	19.6	12.6	29	21	3.4	4.9	1.3	12	1.2
AS-25L	AS2052FS		19.6	24.6	17	38	28					
AS-30L	AS3002FS	4.5	24.8	29.8	22	43	33	4.5	6.5	9.5	15.5	- 1
AS-40L	AS4002FS		25.7	30.7	28	49	39					1.4

Part no.: AS-DDA




L-Bracket Brackets on both sides



- * Refer to page 6 for L8.
- The figure above shows the manifold with speed controllers connected using two L-brackets, adapters and a threaded stud kit for manifold. Refer to page 4 for threaded stud kits for manifold.
- Cannot connect the speed controller when the indicator window direction is 90° or 270°.

DIN Rail Mounting Bracket Brackets on both sides




- * Refer to page 6 for L8.
- * The figure above shows the manifold with speed controllers connected using two DIN rail mounting brackets, adapters and a threaded stud kit for manifold. Refer to page 4 for threaded stud kits for manifold
- Cannot connect the speed controller when the indicator window direction is 90° or 270°.

22 27 17 AS-25D AS2052FS 25.8 11.3 1.6 AS-30D AS3002FS 4.5 4.4 27.2 32.2 22 30.8 4.4 AS-40D AS4002FS 28.1 33.1 28 36.8

Adapter for Direct Mounting

Part no.: AS-DDA1




Part no.	Applicable model	D 7	L27	L28			
AS-10A1	AS1002FS	9.2	4.5	18.7			
AS-20A1	AS2002FS	9.4	9.3	20.4			
AS-25A1	AS2052FS	11.4	7.1	27			
AS-30A1	AS3002FS	11.8	6.4	32.1			
TI 101000E0							

The AS4002FS□ can be mounted without the adapter.

Adapter

Direct mounting

* For use when the mounting surface interferes with the bonnet.



- * Refer to page 6 for L8.
- * The AS4002FS can be mounted directly without the adapter.

Stainless Steel Type Speed Controller with Indicator (In-line Type)

AS-FSG Series

Model

	Applicable tubing O.D.											
Model		1	Metri	c size	Э				Inch	size		
	3.2	4	6	8	10	12	1/8"	5/32"	1/4"	5/16"	3/8"	1/2"
AS1002FSG		•						•	•			
AS2002FSG												
AS2052FSG												
AS3002FSG			•	•	٠	٠				•		
AS4002FSG												

Specifications


Fluid	Air
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperatures	-5 to 60 °C (No freezing)
Applicable tubing material	Nylon, Soft nylon, Polyurethane*1, FEP, PFA

111

*1 Use caution at the max. operating pressure when using soft nylon or polyurethane tubing. (Refer to the web catalogue on www.smc.eu for details.)

Flow Rate and Sonic Conductance

Model		AS1002FSG		AS2002FSG		2FSG		AS3002FSG			AS4002FSG			
Tubin	Metric size	Ø 3.2	Ø 4	Ø6	Ø 4	Ø6	Ø 6	Ø 8	Ø6	Ø 8	Ø 10	Ø 12	Ø 10	Ø 12
Tubing O.D.	Inch size	Ø 1/8"	Ø 5/32"	Ø 1/4"	Ø 5/32"	Ø 1/4"	Ø 1/4"	Ø 5/16"	Ø 1/4"	Ø 5/16"	Ø 3/8"	_	Ø 3/8"	Ø 1/2"
C values: Sonic	Free flow	0.3	0.4	0.6	0.4	0.6	1.0	1.2	1.1	1.6	2.2	2.6	2.4	3.5
conductance dm ³ (s·bar)	Controlled flow		0.3		0.4	0.6	1.0	1.2	1.3	1.9	2.7	3.3	2.8	4.1
b values: Critical	Free flow	0.3	0.	.2	0.3	0.1	0	.2		0.	2		0.3	0.2
pressure ratio	Controlled flow	0.2	0.3	0.4	0.	.2	0.2	0.3	0	.1	0.	.2	0.1	0.2



Made to

Order


-X1

RoHS

Stainless steel

In-line

* C and b values are for controlled flow with the needle fully open and free flow with the needle fully closed.



Indicator direction


Nil	0°	Index plate	2	90°	Index plate
1	180°	Index plate	3	270°	Index plate

Made to Order

Lubricant: Vaseline

Example) AS2002FSG-04-X12

Grease-free (Seal: Fluorine-coated) + Restrictor (Without check valve)	-X21
Example) AS2002FSG-04-X21 * Not particle-free	



Clean Series	10-

Example) 10-AS2002FSG-04 *1 Fluorine grease is used.


*2 The cleanliness class (ISO class) is 5.


Dimensions, flow rate characteristics and options are the same as standard product (brass needle guide). Refer to page 4 for the manifolds (DIN rail bracket mounting/L-bracket mounting).



AS-FSG Series

Construction






Component Parts

No.	Description	Material	Note
1	Body A	PBT	
2	Knob	POM	
3	Body B	PBT	
4	Needle	PBT	
5	Needle guide	Stainless steel	
6	U-seal	HNBR	
7	Spacer	PBT*1	
8	Cassette	—	
9	Seal	NBR	
10	O-ring	NBR	
11	O-ring	NBR	
12	Bonnet A	POM	
13	Bonnet B	POM	
14	Gear	PPS	
15	Indicator gear	POM	
16	Clip	Stainless steel	

*1 The AS3002FS□-11, AS4002FS□-11, AS4002FS□-13 are made of stainless steel.


L-Bracket



Component Parts

No.	Description	Material
1	Bracket	Steel strip

DIN Rail Mounting Bracket



Component Parts

No.	Description	Material
1	Bracket	Steel strip
2	Cross recessed round head screw	Steel wire
3	Clasp	Steel strip


Related Equipment Holder for Speed Controller **TMH Series**

A holder for securing a speed controller with One-touch fittings (In-line type)

Possible to hold a single controller



Holder mounting



Specifications

Ambient temperature	-20 to 60 °C
Material	Polypropylene
Colour	White

Accessory: Cross Recessed Round Head Screw for Mounting (Zinc chromated)

Part	no.	Size	Quantity	
Metric size	Inch size	(Nominal x Length)	Quantity	
TMH-23J	TMH-01J	M3 x 15		
TMH-04J	TMH-03J	1013 X 13		
TMH-06J	TMH-07J	M3 x 20		
TMH-06	TMH-07	M4 x 25	1	
TMH-08	TMH-09	IVI4 X 25	-	
TMH-10	—	M4 x 35		
TMH-12	TMH-13	IVI4 X 33		

Series

Select the applicable holder/TMH for each speed controller from the table below.

Metric Size


Tubing size	Applicable tubing								
	23	04	06	08	10	12			
Applicable model	Ø 3.2	Ø 4	Ø 6	Ø 8	Ø 10	Ø 12			
AS1002FS	TMH-23J								
AS2002FS		TMH-04J	T IVIH-00J						
AS2052FS			TMH-06						
AS3002FS			TMH-07	TMH-08	TMH-10	TMH-12			
AS4002FS						TMH-13			

* The applicable TMH for the AS1002FSD-02 is not available.

Inch Size

Tubing size	Applicable tubing								
	01	03	07	09	11	13			
Applicable model	Ø 1/8"	Ø 5/32"	Ø 1/4"	Ø 5/16"	Ø 3/8"	Ø 1/2"			
AS1002FS	TMH-01J	TMH-03J							
AS2002FS		TIVIH-03J	TIVIH-07J						
AS2052FS			TMH-07	TMH-09					
AS3002FS				TMH-09	TMU 40				
AS4002FS					TMH-10	TMH-13			

Dimensions



Part	no.	α D1	Ø D2	H1	H2	H3	H4	H5	L1	L2	L3	Currente e l				
Metric size	Inch size	וטפ	0 02	пі	пг	пэ	Π4	пэ	61	LZ	LJ	Symbol				
TMH-23J	TMH-01J	8.5	3.3	4.5	4.0	7.5	6	10	7.0	0.0	10	1/8J				
TMH-04J	TMH-03J	9.4	3.3	4.5	4.6	7.5	0	12	7.2	6.6	18	4 5/32J				
TMH-06J	—	11.7	0.0		3.3	0.0	0.0	6.3	6.4	9.3	7.7	15.4	8.5	8.3	21	6J
—	TMH-07J	12.1	3.3	0.3	0.4	9.3	1.1	15.4	0.0	0.5	21	1/4J				
TMH-06	_	13.1	4.3											6		
_	TMH-07	13.5		7.1	7.2	11.1	10) 20	11	10.6	26.5	1/4				
TMH-08	TMH-09	15.5										8 5/16				
TMH-10	_	18.8										10				
TMH-12	_	21.2	4.3 9	9.5	9.6	13.5	14	28	14.2	2 14.6	34	12				
_	TMH-13	22										1/2				



A Safety Instructions

I

I

I

н

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

-

▲ Caution:	Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
A Warning:	Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
\land Danger :	Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

🗥 Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3.Do not service or attempt to remove product and machinery/equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
 - 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
 - 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation

▲ Caution

- 1. The product is provided for use in manufacturing industries. The product herein described is basically provided for peaceful use in manufacturing industries
- If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.

If anything is unclear, contact your nearest sales branch.

▲ Safety Instructions Be sure to read "Handling Precautions for SMC Products" (M-E03-3) before using.

SMC Corporation (Europe)

Austria	2 +43 (0)2262622800	www.smc.at	office@smc.at	Lithuania	🕿 +370 5 2308118	www.smclt.lt	info@smclt.lt
Belgium	2 +32 (0)33551464	www.smcpneumatics.be	info@smcpneumatics.be	Netherlands	🕿 +31 (0)205318888	www.smcpneumatics.nl	info@smcpneumatics.nl
Bulgaria	2 +359 (0)2807670	www.smc.bg	office@smc.bg	Norway	2 +47 67129020	www.smc-norge.no	post@smc-norge.no
Croatia	a +385 (0)13707288	www.smc.hr	office@smc.hr	Poland	🖀 +48 222119600	www.smc.pl	office@smc.pl
Czech Republic	2 +420 541424611	www.smc.cz	office@smc.cz	Portugal	🕿 +351 226166570	www.smc.eu	postpt@smc.smces.es
Denmark	2 +45 70252900	www.smcdk.com	smc@smcdk.com	Romania	🖀 +40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Estonia	2 +372 6510370	www.smcpneumatics.ee	smc@smcpneumatics.ee	Russia	🕿 +7 8127185445	www.smc-pneumatik.ru	info@smc-pneumatik.ru
Finland	2 +358 207513513	www.smc.fi	smcfi@smc.fi	Slovakia	2 +421 (0)413213212	www.smc.sk	office@smc.sk
France	2 +33 (0)164761000	www.smc-france.fr	info@smc-france.fr	Slovenia	🕿 +386 (0)73885412	www.smc.si	office@smc.si
Germany	2 +49 (0)61034020	www.smc.de	info@smc.de	Spain	2 +34 902184100	www.smc.eu	post@smc.smces.es
Greece	🕿 +30 210 2717265	www.smchellas.gr	sales@smchellas.gr	Sweden	2 +46 (0)86031200	www.smc.nu	, post@smc.nu
Hungary	2 +36 23513000	www.smc.hu	office@smc.hu	Switzerland	🕿 +41 (0)523963131	www.smc.ch	info@smc.ch
Ireland	2 +353 (0)14039000	www.smcpneumatics.ie	sales@smcpneumatics.ie	Turkey	🕿 +90 212 489 0 440	www.smcpnomatik.com.tr	info@smcpnomatik.com.tr
Italy	2 +39 0292711	www.smcitalia.it	mailbox@smcitalia.it	UK	🕿 +44 (0)845 121 5122	www.smcpneumatics.co.uk	sales@smcpneumatics.co.uk
Latvia	2 +371 67817700	www.smclv.lv	info@smclv.lv			·	

SMC CORPORATION Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 FAX: 03-5298-5362 1st printing WP printing WP 00 Printed in Spain Specifications are subject to change without prior notice and any obligation on the part of the manufacturer.

*1) ISO 4414: Pneumatic fluid power - General rules relating to systems. ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety. etc.

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements". Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years product is delivered, wichever is first.*2) after the Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
 - *2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

▲ Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country