# **Pressure Gauge for General Purpose**

# G33/GA33 Series ROHS





#### Standard Specifications

Model		G33	GA33	
Type		Back side thread	Vertical side thread	
Port size (1)		R 1/8		
Fluid (2,3)		Air		
Indication pr	ecision (4)	±3% F.S. (Full span)		
	Case	Stainless steel		
Material	Clear cover	Gla	Glass	
iviaterial	Stud	Brass		
Bourdon tube		Brass		
Weight [kg]		0.03	0.033	
Applicable model		IP5000, IR1000, IT1000	ARM2500, 3000	

Note 1) When mounting a pressure gauge, use caution not to tighten excessively. Excessive tightening will cause product to be damaged. Use a pipe tape for sealing.

#### Model (Standard)

Model	Pressure range <sup>(1)</sup> MPa	Indication unit	Connection thread	Note
G33-2-01	0 to 0.2			
G33-3-01	0 to 0.3			
G33-4-01	0 to 0.4			
G33-6-01	0 to 0.6			
G33-10-01	0 to 1.0	MPa	R 1/8	_
GA33-2-01	0 to 0.2			
GA33-4-01	0 to 0.4			
GA33-7-01	0 to 0.7			
GA33-10-01	0 to 1.0			

Note 1) Do not apply pressure more than the maximum display pressure. This will cause a malfunction.

#### Model (Made to Order)

Madal	Pressure range (1)		Indication	Connection	Note
Model	MPa	psi	unit	thread	Note
G33-2-01-X2	0 to 0.2	_			VO. Childran
G33-4-01-X2	0 to 0.4	_			X2: Stud parts electroless
G33-6-01-X2	0 to 0.6	_			nickel plated
G33-10-01-X2	0 to 1.0	_			Theker plated
GA33-2-01-X2	0 to 0.2	_	MPa	R 1/8	
GA33-4-01-X2	0 to 0.4	_			X2: Stud parts
GA33-7-01-X2	0 to 0.7	_			nickel plated
GA33-10-01-X2	0 to 1.0	_			
G33-10-01-X4	0 to 1.0	_			X4: Oil-free (Wetted parts degreasing)
GA33-P10-01-X30 (2)	0 to 1.0	0 to 150	MPa, psi	R 1/8	_

Note 1) Do not apply pressure more than the maximum display pressure. This will cause a malfunction. Note 2) Under the New Measurement Law, products for overseas use only (SI unit type for use in Japan)

Note 2) When using other fluids, please consult with SMC for fluid compatibility information concerning corrosive potential.

Note 3) Avoid freezing as this may cause a malfunction.

Note 4) The guaranteed temperature range is 23°C ±5°C.

## G33/GA33 Series

## **How to Order**



				D	
	Symbol	Description	intion T	Гуре	
	Symbol	Description	G33	GA33	
			Back side thread	Vertical side thread	
	+				
	2	0.2 MPa	•	•	
	3	0.3 MPa	•	_	
	4	0.4 MPa	•	•	
	6	0.6 MPa	•	_	
	7	0.7 MPa	•	•	
2 Max. display pressur	10	1.0 MPa	•	•	
	<b>P2</b> (1)	0.2 MPa, 30 psi	○ (2)	_	
	P3 (1)	0.3 MPa, 45 psi	○ <sup>(2)</sup>	_	
	P4 (1)	0.4 MPa, 60 psi	○ (2)	_	
	<b>P7</b> (1)	0.7 MPa, 100 psi	○ (2)	_	
	P10 (1)	1.0 MPa, 150 psi	(2)	○ (2)	
	+	·			
Connection thread	01	R 1/8	•	•	

3 Connection thread	01	R 1/8	
	+		

		Special specification Note 3)	_	_
4			X2	Stud parts nickel plated
	4		X4	Oil-free (Wetted parts degrease washing)
			X30	Both MPa and psi

•	•
•	•
•	•
○ (2)	○ (2)

GA33-□□-01

- ymbol must be used with Special fication "X30."
- Note 2) Under the New Measurement Law, products for overseas use only (SI unit type for use in Japan)
- Note 3) X3 (Wetted parts stainless steel) specifications are not available.
- Note 4) Cover ring assembly is not available.

## **Dimensions**



