Compact Cylinder

Ø 12, Ø 16, Ø 20, Ø 25, Ø 32, Ø 40, Ø 50, Ø 63, Ø 80, Ø 100 RoHS





Overall length shortened

10 mm stroke

10 mm stroke

JCQ Ø 20









Port thread types G, Rc, NPT, added.

Width shortened



Height shortened





Current product Ø 20 (CDQS series)



JCQ Ø 20



SMC DE



150 g**⇒82** g (Compared with the current CDQS series, Ø 25, 10 mm stroke)















Compact

(Compared with the current product) [mm]

Bore size	CDQS	JCDQ
Ø 12	43 g	Weight 29 g 23 + Stroke
Ø 16	57 g	weight 37 g 26.5 24 + Stroke
Ø 20	106 g	weight 61 g 32 30 27.5 + Stroke
Ø 25	150 g	Weight 82 g 36 30 + Stroke
ø 32	202 g	Weight 135 g 43.5 weight 135 g 43.5 weight reduction 41 32.5 + Stroke

Bore size	Wei	ight	Reduction rate %				
[mm]	CDQ2	JCDQ	Weight	Volume			
Ø 40	290 g	201 g	31 %	35 %			
Ø 50	455 g	332 g	27 %	28 %			
Ø 63	627 g	513 g	18 %	29 %			
Ø 80	1162 g	961 g	17 %	26 %			
Ø 100	1966 g	1490 g	24 %	26 %			

1



^{*1} For the CDQ2 series *2 Weight comparison is at 10 mm stroke. *3 For built-in magnet cylinders

Compact Cylinder


Double Acting, Single Rod

JCQ Series

 \varnothing 12, \varnothing 16, \varnothing 20, \varnothing 25, \varnothing 32, \varnothing 40, \varnothing 50, \varnothing 63, \varnothing 80, \varnothing 100



How to Order



Applicable Auto Switches/Refer to the Auto Switch Guide for further information.

		Ele etrice el	light	Wiring	L	oad volta	age	Auto swit	ch model	Lea	d wir	e ler	igth [m]	Due mine d																	
Туре	Special function	Electrical entry	Indicator light	(Output)	DC		DC AC		In-line	0.5 (—)	1 (M)	3 (L)		None (N)	Pre-wired connector	Applica	ble load															
				3-wire (NPN)		5 V,		M9NV	M9N	•	•	•	0	_	0	IC																
switch				3-wire (PNP)		12 V		M9PV	M9P	•	•	•	0		0	circuit																
				2-wire		12 V 5 V, 12 V 12 V		M9BV	M9B	•	•	•	0	_	0	_																
auto		1		3-wire (NPN)				M9NWV	M9NW	•	•	•	0		0	IC	Dalan															
	Diagnostic indication	Grommet	Yes	3-wire (PNP)	24 V			M9PWV	M9PW	•	•	•	0	_	0	circuit	Relay, PLC															
tate	(2-colour indicator)			2-wire				M9BWV	M9BW		•	•	0		0	_	1 20															
				3-wire (NPN)	_	1]]]])))))))))	5 V,		M9NAV**	M9NA**	0	0	•	0	_	0	IC	
Solid	(2-colour indicator)			3-wire (PNP)		12 V		M9PAV**	M9PA**	0	0	•	0	_	0	circuit																
0)	(2-colour indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	•	0	_	0	_																

^{**} Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Please contact SMC regarding water resistant types with the above model numbers.

* Lead wire length symbols: 0.5 m....-(Example) M9NW 1 m.....M

(Example) M9NWM (Example) M9NWL (Example) M9NWZ

^{*} Solid state auto switches marked with "O" are produced upon receipt of order.


^{*} For details about auto switches with pre-wired connector, refer to the Auto Switch Guide.

^{*} Auto switches are shipped together, (but not assembled).



Symbol

Rubber bumper



Specifications

Bore size [mm]	12	16	20	25	32	40	50	63	80	100
Action				Doub	le actin	g, Sing	le rod			
Fluid		Air								
Proof pressure	1.0 MPa									
Maximum operating pressure					0.7 M	Pa *1				
Minimum operating pressure	0.07	MPa				0.05	MPa			
Ambient and fluid temperature		5 to 60 °C								
Lubrication				Not	required	d (Non-	lube)			
Piston speed*		50 to	500 mr	n/s *1			50 to	300 mr	n/s *1	
Cushion				-	Rubber	bumpe	r			
Allowable kinetic energy [J]	0.022	0.038	0.055	0.09	0.15	0.26	0.46	0.77	1.36	2.27
Rod end thread		Female thread								
Stroke length tolerance		^{+1.3} mm ^{Note)}								

Note) Stroke length tolerance does not include the deflection of the bumper.

- * Depending on the system configuration selected, the specified speed may not be satisfied.
- *1 Maximum operating pressure and piston speed are different from the current product (CQ2 series).

Standard Strokes

Bore size [mm]	Standard stroke [mm]
12, 16	5, 10, 15, 20, 25, 30
20, 25, 32, 40	5, 10, 15, 20, 25, 30, 35, 40, 45, 50
50, 63, 80, 100	10, 15, 20, 25, 30, 35, 40, 45, 50

^{*} Intermediate strokes are available as a special order.

Theoretical Output

			OUT	[N]
_		 D: .	O	

Bore size	Rod size	Operating	Piston area							
[mm]	[mm]	direction	[mm ²]	0.2	0.3	0.4	0.5	0.6	0.7	
12	6	OUT	113	23	34	45	57	68	79	
12	0	IN	85	17	25	34	42	51	59	
16	6	OUT	201	40	60	80	101	121	141	
10	0	IN	173	35	52	69	86	104	121	
20	8	OUT	314	63	94	126	157	188	220	
20	٥	IN	264	53	79	106	132	158	185	
25	10	OUT	491	98	147	196	245	295	344	
25	10	IN	412	82	124	165	206	247	289	
32	12	OUT	804	161	241	322	402	483	563	
32	12	IN	691	138	207	276	346	415	484	
40	14	OUT	1257	251	377	503	628	754	880	
40	14	IN	1103	221	331	441	551	662	772	
50	18	OUT	1963	393	589	785	982	1178	1374	
50	10	IN	1709	342	513	684	855	1025	1196	
63	18	OUT	3117	623	935	1247	1559	1870	2182	
03	10	IN	2863	573	859	1145	1431	1718	2004	
80	22	OUT	5027	1005	1508	2011	2513	3016	3519	
80	22	IN	4646	929	1394	1859	2323	2788	3252	
100	26	OUT	7854	1571	2356	3142	3927	4712	5498	
100	20	IN	7323	1465	2197	2929	3662	4394	5126	

Refer to page 8 for cylinders with auto switches.

- Auto switch proper mounting position (detection at stroke end) and mounting height
- · Minimum stroke for auto switch mounting
- · Operating range
- · Auto switch mounting

Allowable Kinetic Energy

Load Mass and Piston Speed [J]											
Bore size [mm]	12	16	20	25	32	40	50	63			
Standard/ Allowable kinetic energy: Ea	0.022	0.038	0.055	0.09	0.15	0.26	0.46	0.77			

Kinetic energy E [J] = $\frac{(m_1 + m_2) V^2}{2}$

 $\begin{array}{ll} \textbf{m}_1{:} \ \text{Mass of cylinder moving parts} & \text{kg} \\ \textbf{m}_2{:} \ \text{Load mass} & \text{kg} \\ \textbf{V}{:} \ \text{Piston speed} & \text{m/s} \end{array}$


Mass of Cylinder Moving Parts: Without Magnet for Auto Switch

Bore size				Cyli	nder s	troke [mm]			
[mm]	5	10	15	20	25	30	35	40	45	50
12	5	6	7	8	9	10	_	_	_	_
16	5	6	7	9	10	11	_	_	_	_
20	9	11	13	15	17	19	21	23	25	27
25	15	18	21	24	27	30	33	37	40	43
32	27	32	36	41	45	50	54	59	63	67
40	42	48	54	60	66	73	79	85	91	97
50	_	91	101	111	121	131	141	151	161	171
63	_	130	140	150	159	169	179	189	199	209
80	_	240	255	270	285	300	315	329	344	359
100	_	426	446	467	488	509	530	551	572	592

Mass of Cylinder Moving Parts:


With Magnet for Auto Switch [g]													
Bore size				Cyli	nder s	troke [mm]						
[mm]	5	10	15	20	25	30	35	40	45	50			
12	6	7	8	9	10	11	_	_	_	_			
16	7	8	9	10	11	12	_	_	_	_			
20	16	17	19	21	23	25	27	29	31	33			
25	25	28	31	34	37	40	43	46	49	53			
32	43	48	52	57	61	66	70	75	79	83			
40	69	75	81	87	93	99	105	111	117	123			
50	_	127	137	147	157	167	177	187	197	207			
63	_	180	190	200	210	220	230	240	250	260			
80		329	344	359	374	389	404	419	433	448			
100		545	565	586	607	628	649	670	690	711			

Allowable Lateral Load at Rod End




Without Magnet for Auto Switch

[g]



With Magnet for Auto Switch



Weight

Without Magnet for Auto Switch [g]												
Bore size	Cylinder stroke [mm]											
[mm]	5	10	15	20	25	30	35	40	45	50		
12	21	25	30	35	39	44	_	_	_	_		
16	28	33	38	43	49	54	_	_	_	_		
20	40	47	55	62	69	77	84	91	99	106		
25	55	64	73	83	92	101	110	119	128	138		
32	94	108	121	135	148	162	175	189	202	215		
40	145	161	177	194	210	226	243	259	275	292		
50	_	284	309	334	359	384	410	435	460	485		
63	_	452	483	514	545	576	606	637	668	699		
80	_	850	899	948	997	1046	1095	1144	1193	1242		
100	_	1348	1407	1465	1524	1582	1641	1700	1758	1817		

With Mag	gnet	for A	Auto	Swi	tch					[g]	
Bore size	Cylinder stroke [mm]										
[mm]	5	10	15	20	25	30	35	40	45	50	
12	25	29	34	38	43	48	_	_	_	_	
16	32	37	43	48	53	58	_	_	_	_	
20	53	61	68	75	83	90	98	105	112	120	
25	73	82	91	100	109	119	128	137	146	155	
32	122	135	149	162	176	189	203	216	230	243	
40	184	201	217	233	250	266	282	299	315	331	
50	_	332	357	383	408	433	458	483	508	533	
63	_	513	544	575	606	637	667	698	729	760	
80	_	961	1010	1059	1109	1158	1207	1256	1305	1354	
100	_	1490	1549	1608	1666	1725	1783	1842	1901	1959	

Bore Size

Ø **12**, Ø **16**


Standard (Through-hole): JCQ, JCDQ

Ø 12




Both ends tapped: JCQA, JCDQA


O1 thread R R




Both Fud	Both Ends Tapped [mm											
Bore size	O 1	R										
12	M4 x 0.7	7										
16	M4 x 0.7	7										



Ø 16





Standard

Stariuai	u																			[mm]
Poro cizo	Stroke range	i vviinouii mannei	for auto switch	With magnet	for auto switch	_	ם	П	_	G	_	-	_	V	_	М	N	0	W	7
bore size	Stroke range	Α	В	Α	В		ט	_	Г	G	п	'	J	I.	_	IVI	IN	Q	VV	
12	5 to 30	19.5	16	23	19.5	6	6	23	4	21.5	M3 x 0.5	26	1.5	5	3.5	14	3.5	7	23	8
16	5 to 30	20.5	17	24	20.5	6	6	26	4	25	M3 x 0.5	31	1.5	5	3.5	17	3.5	8	26.5	8

Bore Size


20 to Ø 40

Standard (Through-hole): JCQ, JCDQ


Ø 20




Both ends tapped: JCQA, JCDQA





Both End	ls Tapped	[mm]
Bore size	O ₁	R
20	M4 x 0.7	7
25	M4 x 0.7	7
32	M5 x 0.8	8
40	M5 x 0.8	8





Ø 25 to Ø 40






Standar	ď																			[mm]
Poro sizo	Stroke range	Without magne	t for auto switch	With magnet	for auto switch	_	7	_	_	G	Н		-	V		М	N	Q	W	7
Dore Size	Stroke range	Α	В	Α	В		D	_	Г	G	п	'	J	,	_	IVI	IN	Q	VV	
20	5 to 50	21	17.5	27.5	24	8	8	30	5	29.5	M4 x 0.7	36	2.5	6	3.5	21	3.5	7.5	32	8
25	5 to 50	23.5	19	30	25.5	7	10	33.5	5	_	M5 x 0.8	40	2.5	8	4.5	24	3.5	8	36	8
32	5 to 50	26	21	32.5	27.5	12	12	41	5	_	M6 x 1.0	51	2.5	10	5	31	4.5	9	43.5	10
40	5 to 50	31	25	37.5	31.5	13	14	47	6	_	M8 x 1.25	60	3.5	12	6	37	4.5	11	50.5	10

Bore Size

Ø 50 to Ø 100

Standard (Through-hole): JCQ, JCDQ


Ø 50 to Ø 80







Both ends tapped: JCQA, JCDQA


Both End	ls Tapped	[mm]
Bore size	O ₁	R
50	M6 x 1.0	10
63	M6 x 1.0	10
80	M10 x 1.5	18
100	M10 x 1.5	18



Ø 100








Standa	rd																				[mm]
Poro cizo	Stroke range	Without magne	t for auto switch	With magnet t	or auto switch	С	D	Е	_	G	ш		-	V		М	N	D	Q	W	7
Dore Size	Stroke range	Α	В	Α	В	C	ט	_	Г	G	- "	'	J	I.	_	IVI	IN	r	Q	VV	_
50	10 to 50	37	29	42.5	34.5	15	18	57	9	_	M10 x 1.5	74	6.5	16	8	46	5.5	1/8	13	63.5	15
63	10 to 50	41.5	33.5	46.5	38.5	15	18	70	10	_	M10 x 1.5	88	6.5	16	8	56	5.5	1/8	14	76.5	15
80	10 to 50	49	40	55	46	21	22	89	12	_	M14 x 2.0	113	9	19	9	70	9	1/4	14	98	19
100	10 to 50	56	46	62	52	21	26	109	12	105.5	M16 x 2.0	134	12.5	22	10	85	9	1/4	19	118	19


Auto Switch Mounting


Auto Switch Proper Mounting Position (Detection at stroke end) and Mounting Height

[mm]









Auto Switch Proper Mounting Position


Auto switch model	D-M9 D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV □A
Bore size	Α	В
12	5	2.5
16	5.5	3
20	6	6
25	6	7.5
32	8	8
40	11	9
50	11.5	11
63	13.5	13.5
80	16.5	18
100	19.5	21

Auto 9	Switch	Mounting	Height
--------	--------	----------	--------

uto Switch Mour	iting Height [mm]
Auto switch mode	
Jana alian	
Bore size	U
12	19.5
16	21
20	23
25	24.5
32	28.5
40	31.5
50	36.5
63	43
80	52.5
400	

Minimum Stroke for Auto Switch Mounting

				[mm]
Number of auto switches	D-M9□V	D-M9□WV D-M9□AV	D-M9 □	D-M9□W D-M9□A
1	5	10	15 (5)	15 (10)
2	5	15	15 (5)	15



Operating Range

										[mm]
Auto switch					Bore	size				
model	12	16	20	25	32	40	50	63	80	100
D-M9□(V) D-M9□W(V) D-M9□A(V)*	3	3	4.5	4.5	4	4.5	5.5	6	6	6.5


* Values which include hysteresis are for guideline purposes only, they are not a guarantee (assuming approximately ±30 % dispersion) and may change substantially depending on the ambient environment.

Auto Switch Mounting

Applicable auto switch		D-M9□/M9□V D-M9□W/M9□V D-M9□A/M9□A	
Bore size [mm]	Ø 12	Ø 16	Ø 20 to Ø 100
Surfaces with auto switch mounting slot			

Note) Auto switch mounting bracket and auto switch are enclosed with the cylinder for shipment. For an environment that needs the water resistant auto switch, select the D-M9 \square A(V) type.

Mounting of auto switch



• When tightening the auto switch mounting screw, use a watchmakers' screwdriver with a handle 5 to 6 mm in diameter.

Tightening Torque for Auto Switch Mounting Screw [N-m]

ignicining residue for reace entition instanting estern [it?							
Auto switch model	Tightening torque						
D-M9□(V) D-M9□W(V) D-M9□A(V)	0.05 to 0.15						




Prior to Use Auto Switch Connection and Example

Sink Input Specifications


Source Input Specifications


3-wire, NPN



3-wire, PNP Black Auto switch COM (PLC internal circuit)

2-wire






Connect according to the applicable PLC input specifications, as the connection method will vary depending on the PLC input specifications.


Example of AND (Series) and OR (Parallel) Connection

* When using solid state auto switches, ensure the application is set up so the signals for the first 50 ms are invalid.


3-wire AND connection for NPN output (Using relays)




(Performed with auto switches only)




3-wire OR connection for NPN output




3-wire AND connection for PNP output (Using relays)




(Performed with auto switches only)



3-wire OR connection for PNP output



2-wire AND connection




When two auto switches are connected in series, a load may malfunction because the load voltage will decline when in the ON state.

The indicator lights will light up when both of the auto switches are in the ON state. Auto switches with load voltage less than 20 V

Load voltage at ON = Power supply voltage -Residual voltage x 2 pcs. = 24 V - 4 V x 2 pcs. = 16 V

Example: Power supply is 24 V DC Internal voltage drop in auto switch is 4 V.

2-wire OR connection




(Solid state) When two auto switches are connected in parallel, malfunction may occur because the load voltage will increase when in the OFF state

Load voltage at OFF = Leakage current x 2 pcs. x

Load impedance = 1 mA x 2 pcs. x $3 \text{ k}\Omega$

Example: Load impedance is $3 \text{ k}\Omega$.



(Reed) Because there is no current leakage, the load voltage will not increase when turned OFF However, depending on the number of auto switches in the ON state. the indicator lights may sometimes grow dim or not light up, due to the dispersion and reduction of the current flowing to the auto switches.





JCQ Series Specific Product Precautions 1

Be sure to read this before handling the products. Refer to the back cover for Safety Instructions. For Actuator and Auto Switch Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual on SMC website, http://www.smc.eu

Mounting

⚠ Caution

Compact cylinders are designed to create compact mechanical equipment and promote space saving. Thus, if it is used in the same manner as conventional cylinders such as tierod cylinders, it may degrade the performance. Pay sufficient attention to the operating conditions when using.

1. Allowable lateral load

Lateral load that can apply to the piston rod end is limited. If a cylinder is used with a lateral load over the limit, it may cause air leakage due to abnormal friction of seals, galling of cylinder tubes and pistons, or abnormal friction of the bearing part. The lateral load applied to the piston rod must be within the allowable range indicated in this catalogue. When the load exceeds the limit, install a guide or change the bore size to suit the load in order to make the load within the allowable range.

2. Connection with a workpiece

When a workpiece is mounted on the piston rod end, connect them aligning the centre of piston rod and a workpiece. If they are off-centre, lateral load is generated and phenomena mentioned in (1) may occur. In order not to apply the off-centre load, use of a floating joint or simple joint is recommended.

3. Simultaneous use of multiple cylinders

It is difficult to control the speed of pneumatic cylinders. The following conditions cause speed change: change in supply pressure, load, temperature and lubrication, performance difference of each cylinder, deterioration of each part over time, etc. Speed controller can be used to control the speed of multiple cylinders simultaneously for a short period of time, but depending on conditions, it may not work as desired. If multiple cylinders cannot operate simultaneously, unreasonable force is applied to the piston rod because cylinder positions may not be the same. This may cause abnormal friction of seals and bearings, and galling of cylinder tubes and pistons. Do not use an application to operate several cylinders simultaneously by adjusting cylinder speed. If this is inevitable, use a high rigid guide against load, so that the cylinder is not damaged even when the each cylinder output is slightly different.

 Depending on the system configuration selected, the specified speed may not be satisfied.





JCQ Series Specific Product Precautions 2

Be sure to read this before handling the products. Refer to the back cover for Safety Instructions. For Actuator and Auto Switch Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual on SMC website, http://www.smc.eu

Mounting Fittings and Speed Controllers (for \emptyset 12 to \emptyset 32)

⚠ Caution

Use the series models listed below when connecting speed controllers and fittings directly to cylinders.

1. After tightening the fitting by hand, use a wrench to tighten the fitting an additional approximately 1/4 turn for a port size of M3 x 0.5 or 1/6 turn for a port size of M5 x 0.8. For elbow type fittings, tighten an additional 1/2 turn for a port size of M3 x 0.5 or 1/3 turn for a port size of M5 x 0.8 if gaskets are mounted in two places. If screws are tightened excessively, air leakage may result due to broken threads or a deformed gasket. If screws are tightened insufficiently, looseness and accompanying air leakage are likely to occur.

<One-touch Fittings>

With Magnet for Auto Switch


g								
Bore size [mm]		12	16	20	25	32		
Port size		M3 x	¢ 0.5	M5 x 0.8				
Stroke [mm]		5 or more						
Male connector (with hexagon socket head)	KQ2S04-M3G	•	•	_	_	_		
	KQ2S04-M5□	_	_	•	•	•		
	KQ2S06-M5□	_	_	•	•	•		
Male connector	KQ2H04-M3G	0	0	_	_	_		
	KQ2H04-M5□	_	_	•	•	•		
	KQ2H06-M5□	_	_	0	0	0		
Male elbow	KQ2L04-M3G	•	•	_	_	_		
	KQ2L04-M5□	_	_	•	•			
	KQ2L06-M5□	_	_	•	•	•		

- •: Applicable to mounting condition 1 and 2.
- O: Applicable to mounting condition 1.

Without Magnet for Auto Switch

Without Magnet for Auto Switch								
Bore	Bore size [mm]		16	20 25		25	32	
Port size M3 x 0.5			M5 x 0.8					
Stroke [mm]		5 or more	5 or more	5	10 or more	5	10 or more	5 or more
Male connector (with hexagon socket head)	KQ2S04-M3G	•	•	_		_	l —	_
	KQ2S04-M5□	_	_	•	•	•	•	•
	KQ2S06-M5□	_	_	•	•	•	•	•
Male connector	KQ2H04-M3G	0	0	_	_	_	_	-
	KQ2H04-M5□	_	_	•	•	•	•	
	KQ2H06-M5□	_	_	_	0	_	0	0
Male elbow	KQ2L04-M3G	•	•	_	_	_	<u> </u>	_
	KQ2L04-M5□	_	_	•	•	•	•	•
	KQ2L06-M5□	_	_		•	•	•	

- •: Applicable to mounting condition 1 and 2.
- O: Applicable to mounting condition 1.



Mounting condition 1

Mounting condition 2

* The above figures show the mounting conditions with the KQ2S One-touch fittings.

<Speed Controllers>

With Magnet for Auto Switch


Bore size [mm]		12	16	20	25	32	
	Port size	M3 x	k 0.5	M5 x 0.8			
	Stroke [mm]	5 or more	5 or more	5 or more	5 or more 5 or more 5 or		
	AS12□1F-M3-04		•	_	_	_	
Elbow type	AS12□1F-M5E-04A	_	_	•	•	•	
туре	AS12□1F-M5E-06A	_	_	•	•		
Universal	AS13□1F-M3-04	•	•	_	_	_	
	AS13□1F-M5E-04A	_	_	•	•	•	
	AS13□1F-M5E-06A	_	_	•	•	•	

• : Applicable to mounting condition 1 and 2.

Without Magnet for Auto Switch

Bore size [mm]		12	16	20	25	32
	Port size	M3 x	M3 x 0.5 M5 x 0.8			3
	Stroke [mm]	5 or more	5 or more	5 or more	5 or more	
Elbow type	AS12□1F-M3-04	•	•	_	_	_
	AS12□1F-M5E-04A	_	_	•	•	•
	AS12□1F-M5E-06A	_	_	•	•	•
Universal type	AS13□1F-M3-04	•	•	_	_	_
	AS13 TF-M5E-04A	_	_	•	•	•
	AS13□1F-M5E-06A	_	_	•	•	•

• : Applicable to mounting condition 1 and 2.



Mounting condition 1

Mounting condition 2

* The above figures show the mounting conditions with the AS12□1F-M5E-□A elbow type speed controllers.





⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

Caution indicates a hazard with a low level of risk **⚠** Caution: which, if not avoided, could result in minor or moderate

⚠ Warning: injury.

Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious

Danger indicates a hazard with a high level of risk Danger: which, if not avoided, will result in death or serious injury. *1) ISO 4414: Pneumatic fluid power - General rules relating to systems. ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

⚠ Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- not service or attempt to remove product and machinery/equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
 - 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
 - 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, wichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular
 - *2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

∕∴Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary

If anything is unclear, contact your nearest sales branch.

∕∴Caution

SMC products are not intended for use as instruments for legal

metrology.Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

Safety Instructions

Be sure to read "Handling Precautions for SMC Products" (M-E03-3) before using.

SMC Corporation (Europe)

Austria 2 +43 (0)2262622800 www.smc.at office@smc.at Lithuania **3**+370 5 2308118 info@smclt It www.smclt.lt Belgium *****+32 (0)33551464 www.smcpneumatics.be info@smcpneumatics.be Netherlands *****+31 (0)205318888 www.smcpneumatics.nl info@smcpneumatics.nl **2** +359 (0)2807670 ***** +47 67129020 Bulgaria www.smc.bg office@smc.bg Norway www.smc-norge.no post@smc-norge.no ***** +385 (0)13707288 office@smc.hr Poland *****+48 222119600 Croatia office@smc.pl www.smc.hr www.smc.pl *****+420 541424611 postpt@smc.smces.es Czech Republic www.smc.cz office@smc.cz **Portugal ***+351 226166570 www.smc.eu Denmark **2** +45 70252900 smc@smcdk.com Romania **2**+40 213205111 www.smcdk.com www.smcromania.ro smcromania@smcromania.ro Estonia *****+372 6510370 www.smcpneumatics.ee smc@smcpneumatics.ee Russia *****+7 8127185445 info@smc-pneumatik.ru www.smc-pneumatik.ru **2**+358 207513513 Finland smcfi@smc fi Slovakia *****+421 (0)413213212 office@smc.sk www.smc.fi www.smc.sk France *****+33 (0)164761000 www.smc-france.fr info@smc-france.fr Slovenia *****+386 (0)73885412 www.smc.si office@smc.si Germany **2** +49 (0)61034020 www.smc.de info@smc.de Spain *****+34 902184100 www.smc.eu post@smc.smces.es Greece ***** +30 210 2717265 www.smchellas.gr sales@smchellas.gr Sweden **2** +46 (0)86031200 post@smc.nu www.smc.nu Switzerland Hungary ***** +36 23511390 www.smc.hu office@smc.hu *****+41 (0)523963131 www.smc.ch info@smc.ch Ireland **2** +353 (0)14039000 www.smcpneumatics.ie sales@smcpneumatics.ie Turkey 212 489 0 440 **212** 489 0 440 www.smcpnomatik.com.tr info@smcpnomatik.com.tr Italy *****+39 0292711 www.smcitalia.it mailbox@smcitalia.it UK ### +44 (0)845 121 5122 www.smcpneumatics.co.uk sales@smcpneumatics.co.uk ★+371 67817700 info@smclv.lv Latvia www.smclv.lv