
Self-seal Fittings Series KC



One-touch fitting (With built-in self-seal mechanism) to prevent air exhaust when removing tube.

Best for multiple use areas when pressure cannot be shut down.

10 styles are available.

Electroless nickel plated for copper-free applications.



Tube material	Nylon, Soft nylon, Polyurethane
Tube O.D.	ø4, ø6, ø8, ø10, ø12

Specifications

Operating fluid		Air					
Max. operating pressu	ıre	1.0MPa					
Proof pressure		3.0MPa					
Ambient and fluid tem	perature	-5 to 60°C (No freezing)					
-	Thread portion	JIB B0203 (Taper pipe thread)					
Thread	Nut	JIB B0211 Class 2 (Metric fine thread)					
Sealant (Thread portion	on)	With sealant (Standard)					
Copper-free application	on	All brass parts with electroless nickel plated					

Component Materials

C3604BD, PBT
C3604BD (Thread portion)
Stainless Steel (SUS304)
SUS304, C3604BD, Polyacetal (POM)
Polyacetal (POM)
Polyacetal (POM)
C3604BD, Polyacetal (POM)
NBR

Self-seal Fittings Series KC

Model

Male connector

KCH



Used to pipe in the same direction from female threaded portion.

Straight union

КСН 7-69



Used to connect tubes in the same direction. One of two ports has a self-seal function.

Male elbow

KCL



Used to pipe in right angles to female threaded portion. Most common style.

Straight plug for frequent use



Used to connect a selfseal fitting and a tube in the same direction. It can save the tube cutting labor in the case of frequent tube installation and removal.

Elbow plug for frequent use



Used to pipe a tube at right angles to a self-seal fitting. It can save the tube cutting labor in the case of frequent tube installation and removal.

Union tee



7-68

Used to connect tubes in both 90° directions.

Union "Y"



Used to connect tubes in the same direction.2 branched ports has a self-seal function.

KCJ



Used to add the self-seal mechanism to the usual Onetouch fittings, Series KQ.

Bulkhead union

KCE



Used for junction connection of tubes for installation on a panel. One of two ports has a self-seal function.

Bulkhead female union



Used for transit connection of a tube and a male screw for installation on a panel.

⚠ Precautions

Tube Insertion and Removal from Self-seal Fitting

△ Caution

- ●Installing Tube
- ①Cut the tube perpendicularly, taking care not to damage the outside surface. (Use tube cutter TK-1, 2 or 3. Do not cut the tube with cutting pliers, nippers, scissors, etc.) Flat or angled cuts will make it difficult to connect to fittings or, if connected, tube will release or air leakage will occur.
- ②Grasp the tube, then slowly push it until it comes to a stop.
- ③Pull it back gently to make sure that it has a positive seal.
 - Incomplete installation may cause air leakage or tube release.
- Removing Tube
- ①Push the release button into the fitting.
 The button should be pushed evenly.
- ②Pull out the tube while keeping the release button depressed. (If the release button is not held down, the tube cannot be withdrawn.)
- 3To reuse the tubing, cut off the previously lodged portion of the tube.
 - If using tubing without cutting the damaged portion off, it may cause the air leakage or make it difficult to release the tube.

The Number of Insertions and Removals from Self-seal Fitting

⚠ Caution

- The number of insertions and removals as a rough quide is as follows.
 - ●Tube-----300 times
 - •Metal stem 1000 times

Installation of Self-seal Fitting

Caution

①The fitting should be installed (Installation of R (PT) thread portion) by screwing with a spanner at the hexagonal portion of the body.

The position of spanner should be a root as close as possible to R (PT) thread.

Use the spanner corresponding to the size of hexagonal portion, or hexagonal portion may be deformed.

Tightening the thread portion of an M5 size fitting

⚠ Caution

①First, tighten it by hand, then give it an additional 1/6 turn with a wrench. Excessive tightening may damage the threaded portion or deform the gasket to cause air leakage. Insufficient tightening.

threaded portion or deform the gasket to cause air leakage. Insufficient tightening may leave the thread loosened or cause air leakage.


Distinction of plug and applicable fitting

△ Caution

- 1)The applicable fitting should be chosen depending on the style of plug.
- Check adaptor

How to use: Use it for addition of self-seal mechanism to a standard One-touch fitting series KQ.


Self-seal fittings with check adaptor are not available. It causes the air leakage.



 Elbow plug for frequent use, straight plug for frequent use.

How to use: For use in the case of frequent tube installation and removing, tube cutting labor can be saved. These plugs are not available for a standard One-touch fittings Series KQ.

If trying to install the plug into a KQ, plug will jump out of the fitting. Note the exclusive marking for self-seal fittings before use.



Tube Insertion and Removal under a pressurized condition

Caution

①When inserting/removing of the tube is difficult under a pressurized condition, it should be inserted or removed by lowering the pressure or after fully exhausting.

Self-seal Fittings *Series KC*

Male connector: KCH

-M5\








_										
	Tube O.D. (mm)	Thread R(PT)	Part No.	H (Hex.)	L	A*	М	area	ctive (mm²) Urethane	Weight (g)
	4	M5	KCH04-M5	9.8	30.8	27.3	18	2.1	2.1	8
	*	1/8	KCH04-01S	10	25.2	22.1	10	2.6	2.6	0
		M5	KCH06-M5	11.8	32.4	28.9	19.5	2.4	2.4	10
	6	1/8	KCH06-01S	12	36.5	33.4	19	6.8	6.8	16
		1/4	KCH06-02S	14	28.4	22.9	19	0.0	0.0	14
		1/8	KCH08-01S	14	41.5	38.4				20
	8	1/4	KCH08-02S	14	45.2	39.7	21.5	16.2	13.1	27
		3/8	KCH08-03S	17	34	27.5				25
	10	1/4	KCH10-02S	17	50	44.5	24	25.6	20.4	34
	10	3/8	KCH10-03S	17	50.4	45	24	25.0	20.4	43
	12	3/8	KCH12-03S	19	53.1	47.7	25.5	35.4	30.4	48
	12	1/2	KCH12-04S	22	40.7	33.6	20.0	33.4	30.4	41

*Reference dimensions after R(PT) installation.



Thread (With sealant)

Μ

øD2
H
Thread
(With sealant)


Applicable tube

Male elbow: KCL



	Tube O.D. (mm)	Thread R(PT)	Part No.	H (Hex.)	øD1	øD2	L ₁	L2	A*	М	area	(111111-)	Weight (g)
			1/01 04 145	, ,				40.7	10.1			Urethane	
	4	M5	KCL04-M5	8	10.4	8	25.3	16.7	18.4	18	1.9	1.9	6
	4	1/8	KCL04-01S	10	10.4	10	25.5	22.1	24.2	10	2.3	2.3	11
		M5	KCL06-M5	8		8	26.8	17.4	20.3	19.5	2.2	2.2	7
	6	1/8	KCL06-01S	12	12.8	10	28	24.2	27.5	10		0.0	13
		1/4	KCL06-02S	14		12	28	28.6	29.5	19	6.2	6.2	21
		1/8	KCL08-01S	14		2 14	34.1	26.2	30.7	21.5	13.0	10.5	16
	8	1/4	KCL08-02S	14	15.2			30.6	32.7				24
		3/8	KCL08-03S	17				30	34.2				37
	10	1/4	KCL10-02S	17	18.5	17	38	33.4	37.2	24	19.5	10.5	29
	10 -	3/8	KCL10-03S	''	10.5	17	30	34.8	38.7	24	19.5	16.5	38
		3/8	KCL12-03S	22	20.0	20.9	40.7	39.2	44.3	25.5	04.0	01.0	63
		1/2	KCL12-04S	22	20.9	20.9	40.7	42.3	45.7		24.8	21.3	81


*Reference dimensions after R(PT) installation.
Note1) ØD1: max. diameter





Tube O.D. (mm)	Part No.	øD ⁽¹⁾	L	Q	М	area	ctive (mm²) Urethane	Weight (g)
4	KCT04-00	10.4	28.6	5.3	18	2.8	2.8	8
6	KCT06-00	12.8	32.7	6.1	19	7.6	7.6	15
8	KCT08-00	15.2	39.2	7.1	21.5	13.7	11.1	23
10	KCT10-00	18.5	45.5	7.9	24	21.1	19.0	39
12	KCT12-00	20.9	49.2	8.6	25.5	28.3	24.3	52

Note1) øD: max. diameter




Union "Y": KCU



Tube O.D. (mm)	Part No.	øD ⁽¹⁾	L1	L2	Р	Q	M1	M2	area	Effective area (mm²) Nylon Urethane		
4	KCU04-00	10.4	43.1	27.3	10.4	10.6	18	16	3.7	3.7	8	. '
6	KCU06-00	12.8	48	31.2	12.8	12.5	19	17	10.0	10.0	14	
8	KCU08-00	15.2	57.6	38.9	15.2	14.7	21.5	18.5	21.7	15.1	22	
10	KCU10-00	18.5	65.2	44.9	18.5	17.1	24	21	33.3	25.6	37	
12	KCU12-00	20.9	70.1	48.8	20.9	19.1	25.5	22	48.9	38.7	49	_


Note1) øD: max. diameter




Check adaptor: KCJ



Tube O.D. (mm)	Part No.	ød	øD ⁽¹⁾	L	А	М	Effective area (mm²) Nylon Urethane		Weight (g)
4	KCJ04-99	4	9.8	49.5	33.5	18	2.6	2.6	9
6	KCJ06-99	6	11.8	54	37	19	6.8	6.8	13
8	KCJ08-99	8	14	61	42.5	21.5	16.2	13.1	20
10	KCJ10-99	10	17	70.4	49.4	24	25.6	20.4	33
12	KCJ12-99	12	19	74.4	52.4	25.5	35.4	30.4	43






Bulkhead union: KCE




Tube O.D. (mm)	Part No.	T (M)	H (Hex.)	L	Mounting hole	M1	M2		(mm-)	Weight (g)
4	KCE04-00	M12 X 1	14	42	13	18	16	2.6	2.6	21
6	KCE06-00	M14 X 1	17	45.5	15	19	17	6.8	6.8	30
8	KCE08-00	M16 X 1	19	52.5	17	21.5	18.5	16.2	13.1	39
10	KCE10-00	M20 X 1	24	59.5	21	24	21	25.6	20.4	84
12	KCE12-00	M22 X 1	27	63.2	23	25.5	22	35.4	30.4	115



Bulkhead female union: KCE




	Tube O.D. (mm)	Thread Rc (PT)	Part No.	T (M)	H1 (Hex.)	H2 (Hex.)	L ₁	L2	Mounting hole		Effe area Nylon		Weight (g)
	4	1/4	KCE04-02	M12 X 1	17	14	40.5	14.7	13	18	2.6	2.6	32
	6	1/4	KCE06-02	M14 X 1	17	17	42.7	14.7	15	19	6.8	6.8	36
	8	3/8	KCE08-03	M16 X 1	19	19	49.4	15	17	21.5	16.2	13.1	42
	10	3/8	KCE10-03	M20 X 1	22	24	53.9	14.2	21	24	25.6	20.4	79
Ī	12	3/8	KCE12-03	M22 X 1	24	27	56.1	13.7	23	25.5	35.4	30.4	105




Straight union: KCH



Tube O.D. (mm)	Part No.	øD ⁽¹⁾	L	M1	M2	area (mm²)		Weight	
(11111)						Nylon	Urethane	(g)	
4	KCH04-00	10.4	42.1	18	16	2.6	2.6	5	
6	KCH06-00	12.8	45.8	19	17	6.8	6.8	7	
8	KCH08-00	15.2	52.8	21.5	18.5	16.2	13.1	10	
10	KCH10-00	18.5	59.8	24	21	25.6	20.4	18	
12	KCH12-00	20.9	63.5	25.5	22	35.4	30.4	24	







Straight plug for frequent use: KCH



Tube O.D. (mm)	Part No.	ød	øD ⁽¹⁾	L	Α	М	Effective area (mm²) Nylon Urethane		Weight (g)
4	KCH04-99	4	9.8	40.6	22.6	16	5.6	4	5
6	KCH06-99	6	11.8	43.1	24.1	17	13.1	10.4	8
8	KCH08-99	8	14	46.7	25.2	18.5	26.1	18.0	11
10	KCH10-99	10	17	52.6	28.6	21	41.5	29.5	18
12	KCH12-99	12	19	54.9	29.4	22	58.3	46.1	24






Self-seal Fittings Series KC

Elbow plug for frequent use: KCL



Tube O.D. (mm)	Part No.	ød	øD1	øD2	L1	L2	A	М	area	ctive (mm²) Urethane	Weight (g)
4	KCL04-99	4	10.4	10	18	34.3	22.6	16	4.2	4.2	7
6	KCL06-99	6	12.8	10	20	36.5	24.1	17	11.4	9.0	8
8	KCL08-99	8	15.2	12	23	40.3	25.2	18.5	21.6	14.9	12
10	KCL10-99	10	18.5	17	26.5	44.3	28.6	21	35.2	25.0	25
12	KCL12-99	12	20.9	17	28.5	46.8	29.4	22	50.2	39.7	30



Note1) øD₁, øD₂: max. diameter