



# Heavy Duty Stopper Cylinder/ Lock Release Specification

RoHS

∅ 50, ∅ 63, ∅ 80

## Prevents lever damage when a transferred workpiece moves backward

Prevents damage by releasing the locked lever when a pallet suddenly moves backward and collides with the lever



### ■ A part number for the built-in shock absorber with a scraper (option) is available.

A scraper is mounted on the piston rod of the shock absorber. This can reduce the entry of dust, foreign matter, and coolant.

Example)

**RS2H50-30DL-D Y -M9BW-XC102**

● Built-in Shock Absorber with Scraper

## RS2H-XC102



19-EU730-UK

# RS2H-XC102



## How to Order

RS2H **50** **□** **□** - **30** **D** **L** - **D** **□** **□** **□** - **M9BW** **□** - **XC102**

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

With lock mechanism      Lock release specification



### ① Bore size

50	50 mm
63	63 mm
80	80 mm

### ② Port thread type

—	Rc
TN	NPT
TF	G

### ③ Piping direction

—	Flange side 
A	Axial direction (tube) 

### ④ Cylinder stroke

30	30 mm (Ø 50, Ø 63)
40	40 mm (Ø 80)

### ⑥ Roller material

L	Resin
M	Carbon steel

### ⑤ Action

D	Double acting
B	Double acting spring type
T	Single acting/spring extend





### ⑦ Option\*1

—	Without option
C	With cancel cap
S	With lever detection switch*2

\*1 Options can be combined. Indicate the option symbols in the order of "C" then "S."

\*2 For details on the lever detection switch, refer to the standard model.

### ⑧ Positional relationship of the lever and port

—		Q	
P		R	

### ⑨ Shock absorber

—	Standard
Y	Shock absorber with scraper

### ⑩ Auto switch

—	Without auto switch (Built-in magnet)
---	---------------------------------------

\* The applicable auto switches are the same as those for the standard model.

\* Auto switches are shipped together with the product but do not come assembled.

### ⑪ Number of auto switches (Number of auto switches mounted)

—	2
S	1

### Replacement Parts/Shock Absorber

Bore size [mm]	Order no.	
	Standard	With scraper
50	RS2H-R50	RS2H-R50-X2666
63	RS2H-R63	RS2H-R63-X2666
80	RS2H-R80	RS2H-R80-X2666

\* The shock absorber can be replaced individually. Mounting of the built-in shock absorber with a scraper is interchangeable with the standard shock absorber (RS2H-R□).

## ■ Specifications and dimensions: Same as those of the standard model

**⚠ Safety Instructions** Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

## SMC Corporation

Akihabara UDX 15F,  
4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN  
Phone: 03-5207-8249 Fax: 03-5298-5362  
<https://www.smcworld.com>  
© 2020 SMC Corporation All Rights Reserved

Specifications are subject to change without prior notice and any obligation on the part of the manufacturer.

D-G

Printing YT 7760KS Printed in Japan.