

Flow Controller for Water (€ UK CA

RoHS

For the stepless control
of water flow rate in
proportion to electrical signals

New



IO-Link

IP65

Flow rate control accuracy

± 5 % F.S.

Response time

10 s or less


Parts in contact with
fluid: Grease-free

New

Rated control flow rate range:
A 5 to 40 (l/min) specification
has been added.



38 mm



Variations

Series	Rated control flow rate range [l/min]							Port size		
	0.5	2	4	5	16	40		3/8	1/2	3/4
FC3W504								●	—	—
FC3W520								●	●	—
New FC3W540								—	●	●


FC3W Series



CAT.EUS100-160B-UK




It's difficult to adjust the flow rate settings of multiple lines.



With manual valve control, when the upstream pressure changes, the flow rate of each line becomes unstable, making adjustment difficult.


With a FC3W

The flow rate of each line is adjusted to a stable value when the upstream pressure changes.




Application Examples


Mold cooling



Printer roller cooling




For cooling during the wafer production process



New IO-Link Compatible FC3W5□-□□-L□-□□

Visualization of operation/equipment status/Remote monitoring and control by communication



IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard, IEC 61131-9.



IO-Link Compatible Device
FC3W5□-L

Port class B compliant

* When using a port class A IO-Link master, use the Y branch connector described on page 12.

- Visualizes control and equipment status, and enables remote control and monitoring by communication
 - Equipped with a valve opening position control mode providing direct command of the valve opening position (amount of restriction) (IO-Link compatible models only)
 - Implement various status diagnostic bits in the process data.
- It is possible to obtain the control completion status and component error status in real-time based on information in the cyclic (periodic) process data.

Input Process Data

Bit offset	Item	Note
0 to 1	Control mode	0: Control stop 1: Flow control 2: Valve opening position control 3: Return to origin
2	Flow control completed	0: Not completed 1: Completed
3	Valve opening position control completed	0: Not completed 1: Completed
7	Origin detection	0: Not detected 1: Detected (Valve opening position control available)
8	Measurement diagnosis	0: Within the rated flow 1: Out of range (Measured flow rate value out of rated flow range)
9	Output PD diagnosis	0: Within the range 1: Out of range (Output process data out of range)
10	Insufficient flow rate	0: Normal 1: Insufficient flow rate
11	Lifespan diagnosis	0: Normal 1: Exceeded lifespan judgment threshold
14	Error (Other than system error)	0: Error not generated 1: Error generated
15	System error	0: Error not generated 1: Error generated
16 to 31	Valve opening position	Signed 16 bit
32 to 47	Measured flow rate value	Signed 16 bit

Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32
Item	Measured flow rate value (Signed 16 bit)															

Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Valve opening position (Signed 16 bit)															

Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	System error	Error	Reservation	Lifespan diagnosis	Insufficient flow rate	Output PD diagnosis	Measurement diagnosis	Origin detection	Reservation	Valve opening position control completed	Flow control completed	Control mode				

Error description
· Outside of power supply voltage range
· Over current
· Out of control
· Insufficient flow rate
· IO-Link master version error
· Abnormal internal electronic circuit

Output Process Data

Bit offset	Item	Note
0 to 1	Control mode	0: Control stop mode 1: Flow control mode 2: Valve opening position control mode 3: Return to origin mode
16 to 31	Valve opening position command value	Signed 16 bit
32 to 47	Flow rate command value	Signed 16 bit

Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32
Item	Flow rate command value (Signed 16 bit)															

Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Valve opening position command value (Signed 16 bit)															


Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	Reservation															Control mode

* Variation of Control Modes (Bit offset 0, 1)

Valuation of control modes (Bit offset 0, 1)				
Bit offset		Control mode	Description	
1	0			
0	0	Control stop	The valve opening position is fixed to its current position, regardless of the command value.	
0	1	Flow control	The device is controlled using the flow rate command value (corresponding to the rated control flow rate).	
1	0	Valve opening position control	The device is controlled using the valve opening position command value (corresponding to a valve opening position of between 0 to 100 %).	
1	1	Return to origin	Returns the valve opening position to the origin position (which can be set to either fully closed or fully open), regardless of the command value.	

CONTENTS

Flow Controller for Water *FC3W Series*



How to Order	p. 4
Specifications	p. 5
Flow Rate Command Input and Control Flow Rate	p. 7
Control Flow Rate and Analogue Output	p. 7
Pressure Loss	p. 7
Internal Circuits and Wiring Examples	p. 8
Construction: Parts in Contact with Fluid	p. 8
Dimensions	p. 9
Accessories	p. 11
List of Functions, Product Operating Life, and Water Hammer	p. 14
Safety Instructions	Back cover

Flow Controller for Water

FC3W Series

IO-Link

CE UK CA

RoHS

IP65

How to Order

FC3W5 04 - F 03 - A1 C - R Y

Rated control flow rate range

Symbol	Rated control flow rate range
04	0.5 to 4 l/min
20	2 to 16 l/min
40	5 to 40 l/min

Thread type

Symbol	Thread type
R	Rc
N	NPT
F	G

Port size

Symbol	Port size	Rated control flow rate range		
		04	20	40
03	3/8	●	●	—
04	1/2	—	●	●
06	3/4	—	—	●

Input/Output specifications

Symbol	IN1	IN2	OUT1
A1	Voltage 1 to 5 V	External input (Control stop)	Voltage 1 to 5 V
A2	Current 4 to 20 mA		Current 4 to 20 mA
A3	Voltage 0 to 10 V		Voltage 0 to 10 V
L	IO-Link		

Operation manual/ Calibration certificate

Symbol	Description	
	Operation manual	Calibration certificate
Y	Without	Without
Z	With	Without
T	Without	With
K	With	With

Option 2 (Bracket)

Symbol	Bracket
R	With bracket*1
N	None




*1 The bracket is shipped together with the product but does not come assembled.

Option 1 (Lead wire)




Symbol	Accessory cable
C	Lead wire with M12 connector (3 m, 5 cores)
Q	Lead wire with M12-M12 connector (3 m, 5 cores)*1
N	None

*1 The lead wire has an M12 (socket) connector on one side and an M12 (plug) connector on the other side.

Option 1 (Lead wire)

N	C	Q
None	Lead wire with M12 connector (3 m, 5 cores)	Lead wire with M12-M12 connector (3 m, 5 cores)
	ZS-53-A 	ZS-53-D 

Option 2 (Bracket)

N	R	
None	For the FC3W504 and FC3W520	For the FC3W540
	 ZS-54-A The bracket and 6 tapping screws (3 x 8 L) are included with the product.	 ZS-54-B The bracket and 4 screws (M4 x 8 L) are included with the product.

FC3W Series

Specifications

Analogue Input/Output Type (FC3W5□-□□-A1/A2/A3□-□□)

			Analogue input/output type		
Model			FC3W504	FC3W520	FC3W540
Fluid	Applicable fluid		Water		
	Fluid temperature range		0 to 50 °C (No freezing or condensation)		
Flow	Flow rate detection method		Karman vortex		
	Rated control flow rate range*1		0.5 to 4.0 l/min	2.0 to 16.0 l/min	5.0 to 40.0 l/min
	Leakage when fully closed*2		0.4 l/min or less	1.0 l/min or less	2.0 l/min or less
Control	Control accuracy*3		±5 % F.S.		
	Control dead band*4		Within ±2 % F.S. of the flow rate command value		
	Repeatability		±3 % F.S.		
	Temperature characteristics		±5 % F.S. (0 to 50 °C, 25 °C reference)		
	Settling time*5		10 s or less within ±5 % F.S. of flow command		
	Operation when power is cut off*6		Maintains valve opening position		
Pressure	Operating pressure range*7		0.2 to 0.4 MPa		
	Min. operating differential pressure		0.2 MPa		
	Proof pressure		0.6 MPa		
Analogue input*8 (Flow rate command)	Voltage	Input type	1 to 5 VDC/0 to 10 VDC		
		Input impedance	Approx. 1 kΩ		
	Current	Input type	4 to 20 mA DC		
		Input impedance	250 Ω or less		
Analogue output (Flow rate output)	Voltage	Output type	1 to 5 VDC/0 to 10 VDC		
		Output impedance	Approx. 1 kΩ		
	Current	Output type	4 to 20 mA DC		
		Load impedance	50 to 600 Ω		
External input (Control stop input)	Input type		Non-voltage input (0.4 V or less), Input time: 30 ms or more		
	Operation		Flow rate control operation stop (maintains valve opening position)		
Electrical	Power supply voltage		24 VDC ±10 %		
	Current consumption*9		0.1 A or less (at control stop/at control settling) 0.5 A or less (during control operation)		
Indicator LED			PWR (Green): Power status display ERR (Red): Error status display CTRL (Green): Control status display		
Environmental resistance	Enclosure		IP65		
	Operating temperature range		0 to 50 °C (No freezing or condensation)		
	Operating humidity range		Operating/Stored: 35 to 85 % RH (No condensation)		
	Withstand voltage		1000 VAC for 1 min between terminals and housing		
	Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing		
Standards			CE/UKCA marking		
Materials of parts in contact with fluid			Fluororubber, Stainless steel 304, Stainless steel 303, PP + PE, POM, PPS		
Piping			3/8 (Rc, NPT, G)	3/8, 1/2 (Rc, NPT, G)	1/2, 3/4 (Rc, NPT, G)
Weight	Body		Approx. 480 g	Approx. 500 g	Approx. 1330 g
	Bracket		Approx. 50 g		Approx. 110 g
	Lead wire (3 m)		Approx. 180 g		

*1 Outside the rated control flow rate range, operation may become unstable.

*2 This product is not suitable for applications in which the flow rate needs to be at exactly 0.
If it is necessary to completely shut off the flow rate, install a stop valve, etc. separately.

*3 Includes a control dead band (±2 % F.S.)

*4 Control operation is stopped when the control flow rate is ±2 % F.S. of the flow rate command value (control dead band).

*5 Operating pressure: 0.3 MPa, Flow rate command value: Changes from 0 % to 100 % in steps
The settling time may be longer in other operating conditions.

*6 When the power is turned OFF, the control valve operation is stopped to maintain the valve opening position.

*7 Outside the operating pressure range, normal control operation may not be possible.

*8 When the analogue input terminal is open (no signal is input), the valve is fully closed.

*9 If there is an abnormal control operation, such as when there is no supply pressure, the supply current may exceed the specification value.

* Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Specifications**IO-Link Type (FC3W5□-□□-L□-□□)**

			IO-Link type		
Model			FC3W504	FC3W520	FC3W540
Fluid	Applicable fluid		Water		
	Fluid temperature range		0 to 50 °C (No freezing or condensation)		
Flow	Flow rate detection method		Karman vortex		
	Rated control flow rate range*1		0.5 to 4.0 l/min	2.0 to 16.0 l/min	5.0 to 40.0 l/min
	Leakage when fully closed*2		0.4 l/min or less	1.0 l/min or less	2.0 l/min or less
Control	Control accuracy*3		±5 % F.S.		
	Control dead band*4		Within ±0 to 10 % F.S. of the flow rate command value (Default: ±2 % F.S., Variable)		
	Repeatability		±3 % F.S.		
	Temperature characteristics		±5 % F.S. (0 to 50 °C, 25 °C reference)		
	Settling time*5		10 s or less within ±5 % F.S. of flow command		
	Operation when power is cut off*6		Maintains valve opening position		
Pressure	Operating pressure range*7		0.2 to 0.4 MPa		
	Min. operating differential pressure		0.2 MPa		
	Proof pressure		0.6 MPa		
Electrical	Power supply voltage		L+: 24 VDC ±10 % (Control power supply) 2L+: 24 VDC ±10 % (Valve driving power supply)		
	Current consumption*8	At control stop/at control settling	L+: 0.06 A or less (Control power supply) 2L+: 0.02 A or less (Valve driving power supply)		
		During control	L+: 0.06 A or less (Control power supply) 2L+: 0.5 A or less (Valve driving power supply)		
Indicator LED			PWR (Green): Power status display ERR (Red): Error status display CTRL (Green): Control status display IO-Link (Green): Communication status display		
Environmental resistance	Enclosure		IP65		
	Operating temperature range		0 to 50 °C (No freezing or condensation)		
	Operating humidity range		Operating/Stored: 35 to 85 % RH (No condensation)		
	Withstand voltage		1000 VAC for 1 min between terminals and housing		
	Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing		
Standards			CE/UKCA marking		
Materials of parts in contact with fluid			Fluororubber, Stainless steel 304, Stainless steel 303, PP + PE, POM, PPS		
Piping			3/8 (Rc, NPT, G)	3/8, 1/2 (Rc, NPT, G)	1/2, 3/4 (Rc, NPT, G)
Weight	Body		Approx. 480 g	Approx. 500 g	Approx. 1330 g
	Bracket		Approx. 50 g		Approx. 110 g
	Lead wire (3 m)		Approx. 180 g		

*1 Outside the rated control flow rate range, operation may become unstable.

*2 This product is not suitable for applications in which the flow rate needs to be at exactly 0.
If it is necessary to completely shut off the flow rate, install a stop valve, etc. separately.

*3 Includes a control dead band (±2 % F.S.)

*4 Control operation is stopped when the control flow rate falls within the range of the flow rate command value ±control dead band.

*5 Operating pressure: 0.3 MPa, Flow rate command value: Changes from 0 % to 100 % in steps
The settling time may be longer in other operating conditions.

*6 When the power is turned OFF, the control valve operation is stopped to maintain the valve opening position.

*7 Outside the operating pressure range, normal control operation may not be possible.

*8 If there is an abnormal control operation, such as when there is no supply pressure, the supply current may exceed the specification value.


* Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Communication	IO-Link type		Device
	IO-Link version		V1.1
	Communication speed		COM2 (38.4 kbps)
	Port		Class B
	Configuration file		IODD file*1
	Minimum cycle time		5.7 ms
	Process data length		Input data: 6 bytes Output data: 6 bytes
	On request data communication		Supported
	Data storage function		Supported
	Event function		Supported
	Vendor ID		131 (0x0083)
	Device ID		FC3W504-□□-L□-□□: 0x02DF (735) FC3W520-□□-L□-□□: 0x02E0 (736) FC3W540-□□-L□-□□: 0x02E1 (737)


*1 The configuration file can be downloaded from the SMC website: <https://www.smc.eu>

FC3W Series

Flow Rate Command Input and Control Flow Rate




Control Flow Rate and Analogue Output




* When using 0-10 V output (model A3), keep the current flowing into the analogue output wire below 20 μ A. If a current higher than 20 μ A flows, large errors may occur in the output area of approx. 0.5 V or less.

Pressure Loss


FC3W504-□



FC3W520-□




FC3W540-□




Internal Circuits and Wiring Examples

Analogue input/output type (FC3W5□-□□-A1/A2/A3□-□□)



Model	IN1 (Analogue input)	IN2 (External input)	OUT1 (Analogue output)
FC3W5□-□□-A1□-□□	1-5 V	Voltage input below 0.4 V: Control stopped (maintains valve opening position) Open: Control start	1-5 V
FC3W5□-□□-A2□-□□	4-20 mA		4-20 mA
FC3W5□-□□-A3□-□□	0-10 V		0-10 V


IO-Link type (FC3W5□-□□-L□-□□)



* When using a port class A IO-Link master, use the Y branch connector described on page 12.


Construction: Parts in Contact with Fluid

FC3W504/520



No.	Description	Material
1	Fitting for piping	Stainless steel 304
2	O-ring	Fluororubber
3	Sensor body	PPS
4	Sensor	PPS
5	O-ring	Fluororubber
6	O-ring	Fluororubber
7	Control valve body	PPS
8	Orifice	Stainless steel 303
9	O-ring	Fluororubber
10	Bellows	PP + PE
11	O-ring	Fluororubber
12	Needle guide	POM
13	O-ring	Fluororubber
14	O-ring	Fluororubber
15	Piping plate	Stainless steel 304
16	O-ring	Fluororubber
17	Bottom plate	Stainless steel 304
18	Needle	Stainless steel 304

FC3W540





No.	Description	Material
1	Fitting for piping	Stainless steel 304
2	O-ring	Fluororubber
3	Sensor body	PPS
4	Sensor	PPS
5	O-ring	Fluororubber
6	O-ring	Fluororubber
7	Control valve body	Stainless steel 304
8	O-ring	Fluororubber
9	Bellows	PP + PE
10	O-ring	Fluororubber
11	O-ring	Fluororubber
12	Spacer	Stainless steel 304
13	O-ring	Fluororubber
14	O-ring	Fluororubber
15	Needle guide	POM
16	Bottom plate	Stainless steel 304
17	Needle	Stainless steel 304

FC3W Series

Dimensions

FC3W504/520







Pin no.	Wire colour	Analogue input/output type FC3W5□-□□-A1/A2/A3□-□□		IO-Link type FC3W5□-□□-L□-□□	
		Description	Function	Description	Function
1	Brown	DC (+)	Power supply +24 V	L+	Control power supply +24 V
2	White	IN1	Analogue input	2L+	Valve driving power supply +24 V
3	Blue	DC (-)	Power supply 0 V	L-	Control power supply 0 V
4	Black	OUT1	Analogue output	C/Q	IO-Link communication data
5	Grey	IN2	External input	2L-	Valve driving power supply 0 V

Model	Port size	A	B	C	D	E	F
FC3W504-R03-□	Rc3/8	20	121.9	137.2	58.8	20.9	—
FC3W504-N03-□	NPT3/8	20	121.9	137.2	58.8	20.9	—
FC3W504-F03-□	G3/8	20	121.9	137.2	58.8	—	23.9
FC3W520-R03-□	Rc3/8	24	129.9	141.2	62.8	20.9	—
FC3W520-N03-□	NPT3/8	24	129.9	141.2	62.8	20.9	—
FC3W520-F03-□	G3/8	24	129.9	141.2	62.8	—	23.9
FC3W520-R04-□	Rc1/2	24	129.9	141.2	62.8	23.9	—
FC3W520-N04-□	NPT1/2	24	129.9	141.2	62.8	23.9	—
FC3W520-F04-□	G1/2	24	129.9	141.2	62.8	—	26.9

Dimensions

FC3W540




Pin no.	Wire colour	Analogue input/output type FC3W5□-□□-A1/A2/A3□-□□		IO-Link type FC3W5□-□□-L□-□□	
		Description	Function	Description	Function
1	Brown	DC (+)	Power supply +24 V	L+	Control power supply +24 V
2	White	IN1	Analogue input	2L+	Valve driving power supply +24 V
3	Blue	DC (-)	Power supply 0 V	L-	Control power supply 0 V
4	Black	OUT1	Analogue output	C/Q	IO-Link communication data
5	Grey	IN2	External input	2L-	Valve driving power supply 0 V

Model	Port size	A	B
FC3W540-R04-□	Rc1/2	23.9	—
FC3W540-N04-□	NPT1/2	23.9	—
FC3W540-F04-□	G1/2	—	26.9
FC3W540-R06-□	Rc3/4	29.9	—
FC3W540-N06-□	NPT3/4	29.9	—
FC3W540-F06-□	G3/4	—	31.9

FC3W Series Accessories

① Cable

ZS-53-A




Cable material specifications

Conductor	Nominal cross section	AWG21
Insulator	O.D.	Approx. 1.60 mm
	Colours	Brown, Grey, White, Black, Blue
Sheath	Material	Oil-resistant PVC
Outer diameter		Ø 6

② Cable

ZS-53-D



Cable material specifications

Conductor	Nominal cross section	AWG21
Insulator	O.D.	Approx. 1.60 mm
	Colours	Brown, Grey, White, Black, Blue
Sheath	Material	Oil-resistant PVC
Outer diameter		Ø 6



③ Cable

EX500-AP 050 - S


Cable length (L) • Connector specification

010	1000 mm
050	5000 mm

S	Straight
A	Angled




Straight connector type



Item	Specifications
Cable O.D.	Ø 6 mm
Conductor nominal cross section	0.3 mm ² /AWG22
Wire O.D. (Including insulator)	1.5 mm
Min. bending radius (Fixed)	40 mm

Angled connector type




Item	Specifications
Cable O.D.	Ø 6 mm
Conductor nominal cross section	0.3 mm ² /AWG22
Wire O.D. (Including insulator)	1.5 mm
Min. bending radius (Fixed)	40 mm

④ Cable

EX9-AC 005 -SSPS (With connectors on both sides (Socket/Plug))


● Cable length (L)

005	500 mm
010	1000 mm
020	2000 mm
030	3000 mm
050	5000 mm
100	10000 mm




⑤ Y Branch Connector

EX9-ACY02-S This connector is used to supply valve driving power by branching the IO-Link communication cable when a port class A IO-Link master is used.



IO-Link compatible device connection examples




FC3W Series

⑥ Bracket


ZS-54-A (For the FC3W504 and FC3W520)

6 tapping screws (3 x 8 L) are included with the product.



ZS-54-B (For the FC3W540)

4 mounting screws (M4 x 8 L) are included with the product.



Functions

■ Analogue input function (Flow rate command)

Allows for the control of the flow rate according to the analogue voltage/current flow rate command

■ Analogue output function (Flow rate output)

Allows for the output of the analogue voltage/current corresponding to the current control flow rate value

■ IO-Link (FC3W□-L)

Visualizes control and equipment status, and enables remote control and monitoring by communication

■ External input function (Control stop input)

Allows for the valve opening position to be immediately maintained via external input

This prevents the valve body from fully opening when the flow supply is cut off, such as when the pump is stopped or when the valve is shut off, thus shortening the control settling time when the pump is restarted.

In addition, as repeated unnecessary valve operation can be prevented, it will lead to an improvement in product life.

■ LED display function

This product features a built-in power status display LED, error display LED, control status display LED, and IO-Link communication status display LED.

Operating Life

Operating life under the following conditions

FC3W504, 520: 1 [million operations]

FC3W540: 0.5 [million operations]

Target operation Full stroke opening and closing operations (one-way operation x 1)

Ambient temperature 20 to 25 [°C]

Fluid temperature 20 to 25 [°C]

Water quality Clear water


Water Hammer (Reference Data)

Rapid shutting on the out side of product may result in product damage due to water hammer.

When flow velocity in piping is within the graph below, take the following measures to reduce it.

<Measures to reduce water hammer>

- Select a thick piping diameter.
- Turn control flow rate with a small amount of FC3W before shutting down.
- Keep piping as short as possible.
- Install a water hammer relieving valve.
- Use a flexible material for piping (such as a rubber hose) and an accumulator that can absorb impact pressure.



⚠ Caution

In the state where the flow rate is insufficient for the control flow rate (such as when the valve is shut or the pump is stopped), the control valve in the product fully opens.

As a result, the flow rate settling time at the time of control restart may be longer, or the operating life may be shortened if such an operation is performed repeatedly. This may be caused by the valve shutting, the pump stopping, etc.

We recommend turning OFF the power to the product prior to stopping the water flow or fixing (maintaining) the opening position of the control valve using the external input function (control stop input).

When starting flow control, supply water before turning ON the power or releasing the external input (control start) so that the product can start flow control.

Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of “Caution,” “Warning” or “Danger.” They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) ¹⁾, and other safety regulations.

Danger:

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

Warning:

Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

Caution:

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

- 1) ISO 4414: Pneumatic fluid power – General rules and safety requirements for systems and their components.
ISO 4413: Hydraulic fluid power – General rules and safety requirements for systems and their components.
IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1: Robots.
etc.

Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/equipment until safety is confirmed.

1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments.

Use under such conditions or environments is not covered.

1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogues and operation manuals.
3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in Japan.

Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following “Limited warranty and Disclaimer” and “Compliance Requirements”. Read and accept them before using the product.

Limited warranty and Disclaimer

1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first. ²⁾ Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty.
A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Safety Instructions

Be sure to read “Handling Precautions for SMC Products” (M-E03-3) before using.

Revision History

Edition B	- Rated control flow rate range: A 5 to 40 (l/min) specification has been added. - An IO-Link compatible type has been added. - The number of pages has been increased from 12 to 17.	DU
-----------	---	----

SMC Corporation (Europe)

Austria	+43 (0)2262622800	www.smc.at	office.at@smc.com
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	sales.bg@smc.com
Croatia	+385 (0)13707288	www.smc.hr	sales.hr@smc.com
Czech Republic	+420 541424611	www.smc.cz	office.at@smc.com
Denmark	+45 70252900	www.smc.dk	smc.dk@smc.com
Estonia	+372 651 0370	www.smcee.ee	info.ee@smc.com
Finland	+358 207513513	www.smc.fi	smc.fi@smc.com
France	+33 (0)164761000	www.smc-france.fr	supportclient.fr@smc.com
Germany	+49 (0)61034020	www.smc.de	info.de@smc.com
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office.hu@smc.com
Ireland	+353 (0)14039000	www.smcautomation.ie	technical.ie@smc.com
Italy	+39 03990691	www.smcitalia.it	mailbox.it@smc.com
Latvia	+371 67817700	www.smc.lv	info.lv@smc.com

Lithuania	+370 5 2308118	www.smclt.lt	info.lt@smc.com
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post.no@smc.com
Poland	+48 22 344 40 00	www.smc.pl	office.pl@smc.com
Portugal	+351 214724500	www.smc.eu	apoiocliente.pt@smc.com
Romania	+40 213205111	www.smcromania.ro	office.ro@smc.com
Russia	+7 (812)3036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	sales.sk@smc.com
Slovenia	+386 (0)73885412	www.smc.si	office.si@smc.com
Spain	+34 945184100	www.smc.eu	post.es@smc.com
Sweden	+46 (0)86031240	www.smc.nu	order.se@smc.com
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter.ch@smc.com
Turkey	+90 212 489 0 440	www.smcturkey.com.tr	satis.tr@smc.com
UK	+44 (0)845 121 5122	www.smc.uk	sales.gb@smc.com
South Africa	+27 10 900 1233	www.smcza.co.za	Sales.za@smc.com