Предназначен для термоконтроля различного оборудования за счет теплового контакта

с термостабилизированной циркулирующей жидкостью.


- Устанавливается в стандартную 19-дюймовую стойку (высота 7U, 9U)
- Заправка резервуара и органы управления вынесены на переднюю панель. Сменные элементы также размещены за передней панелью. Это позволяет обслуживать устройство, не вынимая его из стойки.
- Доступно воздушное и водяное охлаждение конденсатора
- Мощность охлаждения от 1000 до 2500 Вт
- Точность поддержания температуры в установившемся режиме ±0.1°C
- Напряжение питания: 1-фазное 200-230 В, 50 Гц





Номер для заказа

W



*При выборе нескольких опций, символы указываются в алфавитном порядке.

Rc
G (комплект переходников Rc-G)
NPT (комплект переходников Rc-NPT)

Водяное охлаждение

Принадлежности (заказываются отдельно)

Наименование	Номер для заказа	Примечание
Измеритель		
концентрации	HRZ-BR002	
этиленгликоля		
Фильтрующий элемент	EJ202S-005X11	
Картридж		
деионизирующего	HRR-DF001	Опция DM
фильтра		



Насос высокого давления

Технические характеристики: Воздушное охлаждение

	Серия	HRR012-A	HRR018-A	HRR024-A	HRR030-A				
O	лаждение конденсатора	Воздушное охлаждение							
χı	адагент	R410A (HFC)							
K	личество хладагента в системе [кг]	0.38 0.47							
-	етод управления температурой		PID-контроль						
Те вь	мпература и влажность окр. среды, ісота над уровнем моря ^{*1, 13}	Температура от 5 до 4	0°C, влажность от 30 до 7	70%, высота над уровнем	и моря не более 3000 м				
	Теплоноситель*2	Вод	опроводная вода, 15% во	дный раствор этиленгли	коля				
	Диапазон настройки температуры*1 [°C]		От 10	до 35					
	Мощность охлаждения ^{*3} [Вт]	1000	1600	2000	2500				
	Мощность нагрева ^{*4} [Вт]	4.	50	5	50				
	Точность поддержания темп.*5 [°C]		±0	0.1					
쯔	Давление, обеспечиваемое насосом ^{*6} [МПа]	Стандарт: 0.13 (при	Стандарт: 0.13 (при 7 л/мин.), опция Т: 0.42 (при 10 л/мин.), опция МТ: 0.32 (при 10 л/мин.)						
Ē	Номинальный расход ^{*7} [л/мин.]	Стандарт: 7, опции Т, МТ: 10						
C	Отображаемый диапазон расхода [л/мин.]	От 3 до 16						
теплоносителя	Отображаемый диапазон удельной электропроводности теплоносителя [мкСм/см]	От 2 до 48 (тольн	ко для опции DM)					
Контур тег	Настраиваемый диапазон удельной электропроводности теплоносителя [мкСм/см]	От 5 до 45 (только для опции DM)						
	Номинальная тонкость фильтрации [мкм]		5						
	Байпасный клапан		Устан	Установлен					
-	Емкость резервуара [л]		Около 4						
	Присоединение (Вход. Выход)		Ro	1/2					
	Присоединение (Дренаж)		Rc1/4, c k	колпачком					
	Защита от протечек			датчиком утечки воды)					
	Материалы, контактирующие с теплоносителем	Нерж. сталь, медный углепластик, РР, РЕ, РОМ	й припой (теплообменник И, РА, FKM, EPDM, PVC, F) ^{*11} , латунь ^{*16} , SiC, алюм PPS, AS, фторполимер ^{*12}	ооксидная керамика, ² , ионообменная смола ^{*12}				
<u>a</u>	Источник питания	1-фазн., 20	00~230 В перем. тока, 50	Гц, допустимые отклонен	ия ±10% ^{*14}				
H	Защита от перегрузки по току [А]		10; опции	T, MT: 15					
Š	Рекомендуемый дифф. автомат ^{*8}	Номинал	ьный ток 10 A (опции T, N	ИТ: 15 А), чувствительнос	сть 30 мА				
подключение	Рекомендуемый кабель (включая кабель заземления)*15		3 провода x 14 AWG	G (3 провода x 2.0 мм²)					
	Номинальный Стандарт	3.6	3.6	5.2	5.5				
Ē	рабочий ток ^{*3} Опции Т, МТ	4.7	4.7	6.3	6.5				
Электр	Номинальная Стандарт [кВт(кВА	0.6 (0.7)	0.7 (0.7)	0.9 (1.1)	1.0 (1.1)				
ო	потребл. мощность*17 Опции Т, МТ	0.9 (0.9)	0.9 (1.0)	1.2 (1.3)	1.3 (1.3)				
	редача данных		Входные/выходные сигналы, RS-485/RS-232C						
	овень шума ^{*9} [д Б]	59	59	61	61				
	ринадлежности ^{*18}	Разъ	ём питания, фильтрующи	ий элемент, ключ для фил	льтра				
Ве	ec ^{*10} [кг]		0	4	ŀ6				
× 4			*10 D	<i>6</i>					

- *1 Не допускается выпадение конденсата. Если предполагается использовать устройство при окружающих температурах, близких к точке замерзания, проконсультируйтесь с представителем компании SMC.
- *2 Вода, используемая в качестве теплоносителя, должна соответствовать требованиям Стандарта качества японской ассоциации промышленного охлаждения и кондиционирования (JRA GL-02-1994).
- *3 При следующих условиях: (1) Окружающая температура 25°С, (2) Температура теплоносителя: 20°С, (3) Расход теплоносителя: номинальный, (4) Теплоноситель: чистая вода, (5) Напряжение питания: 200 VAC, (6) Длина трубопроводов: минимальная У исполнений с насосом высокого давления (опции Т, МТ),

у исполнении с насосом высокого давления (опции 1, м1), мощность охлаждения ниже на 300 Вт.

- *4 При следующих условиях: (1) Окружающая температура 25°С, (2) Температура теплоносителя: 2 0°С, (3) Расход теплоносителя: номинальный, (4) Теплоноситель: чистая вода, (5) Напряжение питания: 200 VAC, (6) Длина трубопроводов: минимальная
- *5 Температура на выходе при номинальном расходе, выход теплоносителя напрямую соединён с его входом, окружающие условия и напряжение питания стабильны и соответствуют техническим требованиям.
- *6 Выход чиллера, температура теплоносителя 20°С.
- Минимальный расход, необходимый для поддержания мощности охлаждения или температурной стабильности.
- *8 Подготавливается пользователем.
- *9 Расстояние 1 м, высота 1 м, стабильная работа без нагрузки. Остальные условия, как в п.*3.

- *10 Вес в сухом состоянии, без теплоносителя. Вес исполнения DM больше на 1 кг. Вес исполнения T/MT больше на 5 кг.
- *11 В исполнениях М и МТ нет меди и латуни.
- *12 Для опции DM
- *13 Особенности использования устройства на высоте 1000-3000 м над уровнем моря приведены в Руководстве по эксплуатации.
- *14 Без продолжительных колебаний напряжения питания
- *15 Подготавливается пользователем.
- 16 Для опции Т.
- *17 При следующих условиях: (1) Окружающая температура 25°C, (2) Температура теплоносителя: 2 0°C, (3) Расход теплоносителя: номинальный, (4) Теплоноситель: чистая вода, (5) Напряжение питания: 200 VAC, (6) Длина трубопроводов: минимальная, (7) С номинальной охлаждаемой нагрузкой
- 18 В комплект поставки исполнения DM входит деионизирующий фильтр.
 - В комплект поставки исполнения F входит комплект переходников Rc-G.
 - В комплект поставки исполнения N входит комплект переходников Rc-NPT.



Технические характеристики:

Водяное охлаждение

	Серия		HRR012-W	HRR018-W	HRR024-W	HRR030-W			
Охлаж	кдение конденсатора			Водяное о	хлаждение				
Хлада	гент		R410A (HFC)						
Колич	ество хладагента в системе	[кг]	0.25 0.40						
Метод	ц управления температурой			PID-ко	нтроль				
высот	ратура и влажность окр. сред а над уровнем моря ^{*1, 14}	ы,	Температура от 5 до 40°C, влажность от 30 до 70%, высота над уровнем моря не более 3000 м						
Теп	лоноситель ^{*2}		Водо	проводная вода, 15% вс	дный раствор этиленгли	коля			
Диа	апазон настройки температуры ^{*1}	[°C]		От 10	до 35				
		[Вт]	1000	1600	2000	2500			
Мо	щность нагрева ^{*4}	[Вт]	45	50	55	50			
Tov	ность поддержания темп. *5	[°C]		±C).1				
дав	вление, обеспечиваемое насосом ^{*6}	[МПа]	Стандарт: 0.13 (при	7 л/мин.), опция Т: 0.42 (г	при 10 л/мин.), опция MT:	0.32 (при 10 л/мин.)			
Ho	минальный расход ^{*7}	[л/мин.]		Стандарт: 7, о	пции T, MT: 10	5			
5 Отс	ображаемый диапазон расхода	[л/мин.]		От 3 до 16					
	ображаемый диапазон удельной ектропроводности теплоносителя	[мкСм/см]		От 2 до 48 (тольк	ко для опции DM)				
	страиваемый диапазон удельной ектропроводности теплоносителя	[мкСм/см]		От 5 до 45 (тольк	ко для опции DM)				
_	минальная тонкость фильтрации	[мкм]			5				
Баі	йпасный клапан			Устан	овлен				
Ем	кость резервуара	[л]		Око	ло 4				
Прі	исоединение (Вход. Выход)		Rc1/2						
Прі	исоединение (Дренаж)			Rc1/4, с колпачком					
	цита от протечек		Дренажный поддон (с датчиком утечки воды)						
1,110,500,000,000	териалы, контактирующие еплоносителем	,	Нерж. сталь, медный углепластик, PP, PE, PON	припой (теплообменник) И, РА, FKM, EPDM, PVC, F	^{*11} , латунь ^{*17} , SiC, алюмс PPS, AS, фторполимер ^{*12}	оксидная керамика, ионообменная смола			
о Диа	апазон температуры	[°C]	От 5 до 40						
Ди		[МПа]		От 0.3	to 0.5				
He	обходимый расход ^{*13}	[л/мин.]	8	12	14	15			
Диа Диа Нес Охл При	репад давления на входе/ выходе наждающей воды	[МПа]	0.3 и более						
Пр	исоединение		Rc3/8						
Ma	териалы, контактирующие с в	одой	Нерж. сталь, медн	ный припой (теплообменн	ник), бронза, латунь, синт	етический каучук			
у Ист	точник питания		1-фазн., 20	0~230 В перем. тока, 50 Г	Гц, допустимые отклонен	ия ±10% ^{*15}			
3aı	цита от перегрузки по току	[A]		10; опции					
Per	комендуемый дифф. автомат*	3	Номинал	ьный ток 10 А (опции Т, М	ИТ: 15 A), чувствительнос	ть 30 мА			
Рен Каб	комендуемый кабель (включая бель заземления)*16	1	3 провода х 14 AWG (3 провода х 2.0 мм²)						
	минальный Станлапт		3.2	3.3	4.9	4.9			
pa	бочий ток *3 Опции T, МТ	[A]	4.3	4.4	6.0	6.0			
ž 110.	Стоиворт		0.6 (0.7)	0.6 (0.7)	0.8 (1.0)	0.8 (1.0)			
топ б	требл. мощность ^{*18} Опции Т, МТ	[KRL(KRY)]	0.9 (0.9)	0.9 (0.9)	1.1 (1.4)	1.1 (1.4)			
Теред	ача данных		processor Virginian P	Входные/выходные сиг		A			
	×a.	[дБ]	59	59	61	61			
	длежности ^{*19}		(5.5	ём питания, фильтрующи	і ій элемент, ключ для фил	15.03			
)	[кг]	4		4				

- *1 Не допускается выпадение конденсата. Если предполагается использовать устройство при окружающих температурах, близких к точке замерзания, проконсультируйтесь с представителем
- *2 Вода, используемая в качестве теплоносителя, должна соответствовать требованиям Стандарта качества японской ассоциации промышленного охлаждения и кондиционирования (JRA GL-02-1994).
- *3 При следующих условиях: (1) Температура охлаждающей воды 2 5 °C. (2) Температура теплоносителя 2 0 °C, (3) Расход теплоносителя: номинальный, (4) Теплоноситель: чистая вода, (5) Напряжение питания: 2 0 0 VAC, (6) Длина трубопроводов: минимальная
 - У исполнений с насосом высокого давления (опции Т, МТ), мощность охлаждения ниже на 300 Вт..
- При следующих условиях: (1) Окружающая температура 25°С, (2) Температура охлаждающей воды: 25°С, (3) Температура теплоносителя: 20°С, (4) Расход теплоносителя: номинальный, (5) Теплоноситель: чистая вода, (6) Напряжение питания: 200 VAC, (7) Длина трубопроводов: минимальная
- *5 Температура на выходе при номинальном расходе, выход теплоносителя напрямую соединён с его входом, окружающие условия и напряжение питания стабильны и соответствуют техническим требованиям.
- *6 Выход чиллера, температура теплоносителя 20°С.
- Минимальный расход. необходимый для поддержания мощности охлаждения или температурной стабильности.

- Подготавливается пользователем.
- Расстояние 1 м, высота 1 м, стабильная работа без нагрузки. Остальные условия, как в п.*3.
- Вес в сухом состоянии, без теплоносителя и охлаждающей воды. Вес исполнения DM больше на 1 кг. Вес исполнения Т/МТ больше на 5 кг.
- В исполнениях М и МТ нет меди и латуни.
- *12 Для опции DM *13 Требуемый расход для соблюдения условий п.*3.
- *14 Особенности использования устройства на высоте 1000-3000 м над уровнем моря приведены в Руководстве по эксплуатации.
- *15 Без продолжительных колебаний напряжения питания.
- *16 Подготавливается пользователем.
- Для опции Т.
- Для Опции 1. При следующих условиях: (1) Температура охлаждающей воды: 25°C, (2) Температура теплоносителя: 20°C, (3) Расход теплоносителя: номинальный, (4) Теплоноситель: чистая вода, (5) Напряжение питания: 200 VAC, (6) Длина трубопроводов: минимальная, (7) С номинальной охлаждаемой нагрузкой
- В комплект поставки исполнения DM входит деионизирующий
 - фильтр. В комплект поставки исполнения F входит комплект переходников
 - В комплект поставки исполнения N входит комплект переходников Rc-NPT.

Circulating Fluid Temperature Controller

Thermo-chiller/Rack Mount Type

Air-cooled Refrigeration Water-cooled Refrigeration



A 5.0 kW (50 Hz) cooling capacity option has been added.

Operable without the need to remove the unit from the rack

Front access

Simple to control, service, and maintain with all filters and drainage accessible via the front panel

Space saving

Multiple chillers can be mounted to a 19-inch rack.

*1 Refer to page 1 for details on 19-inch

Fluid fill

Drain port

New 710

mm

Equivalent to 16U

port

221

Equivalent to 5U (EIA standards*1)

310 mm

Equivalent to 7U . (EIA standards*1)

399

mm

Equivalent to 9U (EIA standards*1)

Cooling capacity

0.9/1.0/1.6/2.0/2.5/4.6/5.0 kW (50 Hz)

Temperature stability

Bypass valve (Standard)

+ 0.1 °C

Particle filter (Standard)

Global power supply

Single-phase 100 VAC (50/60 Hz)/115 VAC (60 Hz)

Single-phase 200 to 230 VAC (50/60 Hz)

DI filter (Option)




HRR050-W Water-cooled

HRR Series





CAT.EUS40-60D-UK



Front access

Maintenance


DI filter replacement

Optional Accessories p. 36




Drain pan (Built-in water leakage sensor)


The leakage sensor detects fluid leakage. The drain pan prevents leaked fluid from pooling at the bottom of the product.



Discharge of the circulating fluid



Cleaning of the dustproof filter




Replacement particle filter element

Optional Accessories p. 36



Space saving

Footprint can be reduced by 53 % by installing the product in a 19-inch rack (EIA standards*1).



*1 19-inch Rack Standards

11 13 mon raok otandaras								
Standard	EIA (Electronic Industries Alliance)							
Standard no.	o. EIA310-D 44.5 mm (=1U)							
Height								
Length	450 mm (min)							
Width	483.4 mm							




630 mm

Setting and Adjustment

A bypass valve and flow sensor are built in (standard).

Flow rate and pressure adjustment can be seen on the displayed panel.

- * Option Z does not come with a bypass valve or flow sensor.
- * Option Z1 does not come with a flow sensor.



Colour LCD screen



Current value (displayed in white): Discharge temperature, pressure, flow rate, etc.

Set value (displayed in green): Set temperature, Angled inlet allows for the easy supply of circulating fluid



Height

422 mm reduction



Volume

35 % reduction



Caster Adjuster-foot Kit

Optional Accessories p. 38




Applicable for installation in locations other than 19-inch racks

This is a set of unfixed casters and adjuster feet stop.



Temperature stability: ± 0.1 °C

A precision temperature control method which utilises expansion valves and temperature sensors allowed for the realisation of a product with a high temperature stability of ± 0.1 °C.



Refrigeration circuit

- The compressor compresses the refrigerant gas and discharges high-temperature, high-pressure refrigerant gas.
- In the case of air-cooled refrigeration, the high-temperature, high-pressure refrigerant gas is cooled down by fan ventilation in the air-cooled condenser, where it is then liquefied. In the case of water-cooled refrigeration, the refrigerant gas is cooled by the facility water in the facility water circuit in the water-cooled condenser, where it is then liquefied.
- The liquefied high-pressure refrigerant gas expands and its temperature lowers when it passes through expansion valve A, where it vapourizes after receiving heat from the circulating fluid in the evapourator.
- The vapourized refrigerant gas is sucked into the compressor and compressed again.
- When heating the circulating fluid, the high-pressure, high-temperature refrigerant gas is bypassed into the evapourator by expansion valve B to heat the circulating fluid.



The combination of the precise control of expansion valve A for cooling and expansion valve B for heating allows for high temperature stability.

Circulating fluid circuit

- After the circulating fluid discharged from the pump is heated or cooled by the user's equipment, it returns to the thermo-chiller.
- The circulating fluid is controlled to remain at a set temperature by the refrigeration circuit. It will then be discharged to the user's equipment side again by the thermo-chiller.



Since the refrigeration circuit is controlled by the signals from 2 temperature sensors (for return and discharge) , precise temperature control of the circulating fluid can be achieved. Therefore, there is no need for a tank with a large capacity to absorb the circulating fluid temperature difference, as high temperature stability can be achieved even with a smallalso contributes to space saving

Facility water circuit

For water-cooled refrigeration HRR□-W

• The water-regulating valve opens and closes to keep the refrigerant gas pressure consistent. The facility water flow rate is controlled by the water-regulating valve.

Air-cooled Refrigeration **HRR050-A** Pressure Temperature Circulating fluid outlet Flow rate sensor* Circulating fluid return moto



Self-diagnosis function and alarm code display

Display of 24 types of alarm codes (For details → p.29)

Operation is monitored at all times by the integrated sensor. The applicable alarm code (24 types) is displayed after self-diagnosis.

Changeable alarm set values

Setting item	Set range*1
Circulating fluid discharge temperature rise	5 to 45 °C
Circulating fluid discharge temperature drop	1 to 35 °C
Circulating fluid discharge pressure rise	0.05 to 0.5 MPa
Circulating fluid flow rate reduction	2.0 to 15.0 LPM


^{*1} Set values vary depending on the model.



Menu for maintenance schedule

When it is time for periodical checks of the pumps, fan motor, dustproof filter, etc., a maintenance code will be generated as a reminder. Helpful for facility maintenance

Ex.) MT01 "Pump maintenance notice"




Displaying screen for operating conditions

Thermo-chiller internal temperature, pressure, etc., can be displayed.



With heating function

As the heating method uses discharged heat, a heater is unnecessary. The heating function is effective in maintaining a constant temperature, particularly in the winter when the ambient temperature is low.



* This is just an example diagram.




Communication functions

Serial communication (RS-232C/RS-485) and contact input/output signals (2 inputs and 3 outputs) are equipped as standard. This allows for communication with the user's equipment and system construction, depending on the application.


Ex. 1 Remote signal I/O through serial communication

Remote operation is enabled (to start and stop operation) through serial communication.




Ex. 2 Remote operation signal input

The chiller can be operated remotely by contact input signals.



Ex. 3 Alarm and operation status (start, stop, etc.) signal output

The alarm and status generated in the product are assigned to 3 output signals based on their contents, which can then be output.



Output setting example

Output 1: Temperature rise Output 2: Pressure rise

Output 3: Operation status (start, stop, etc.)

Variations

Model		Cooling capacity [W] (50/60 Hz)	Heating capacity [W] (50/60 Hz)	Cooling method	Temperature stability	Power supply	Circulating fluid	Option (p. 32 to 35)	Optional accessories (p. 36 to 38)	International standards								
	HRR010	950/1100	250/300	Air-cooled refrigeration							- Single-phase			Particle filter element for replacement	C€			
	HKKU1U	1000/1100	200/200	 Water- cooled refrigeration 		(50/60 Hz)			Anti-quake bracket*4									
	HRR012	1000/1200	· 400/500 (100 V type)			- Single-phase 100 VAC (50/60 Hz)/ 115 VAC (60 Hz)		With electric										
	HRR018	1600/1800	(200 V type)					· 450/500 (200 V type)		- Air-cooled refrigeration - Water-cooled refrigeration ± 0.1 °C	refrigeration	refrigeration		- Single-phase 200 to 230 VAC (50/60 Hz)		conductivity control function, Applicable to DI water piping	Concentration meter Particle filter	(UL Standards)
	HRR024	2000/2400	550/700	cooled refrigeration	cooled refrigeration	cooled refrigeration	cooled refrigeration	cooled refrigeration	cooled refrigeration			Tap water15 % ethylene	Applicable to DI water piping High-pressure	element for replacement DI filter	(UL Standards) Air-cooled: Option U Water-cooled: Standard			
	HRR030	2500/3000						-	0.1 0	glycol aqueous solution	pump mounted*1 Inverter pump mounted*2	replacement cartridge Anti-quake						
	HRR050	4600/5100	1000/1200					refrigeration	refrigeration		- Single-phase 200 to 230 VAC (50/60 Hz)		With feet/Without rack mounting brackets Removed parts*3	bracket*4 • Piping conversion fitting • Power supply cable • Caster	C€			
	11111000	5000/5900	1.555,7250	· Water- cooled refrigeration					adjuster-foot kit* ⁴									

^{*1} Applicable to the HRR012 to 030 *2 Only applicable to the HRR010 *3 Applicable to the HRR010 to 050

^{*4} Only applicable to the option: with feet/without rack mounting brackets




Inverter specification mechanical sealless pump (HRR010 option)

- As the pump has no external leakage of the circulating fluid, a periodic leakage check and replacement of the mechanical seal are not necessary.
- Circulating fluid pressure adjustable (Pressure adjustment via bypass piping is not required.)
- There is no pump capacity difference between the 50 Hz and the 60 Hz.

Power supply (24 VDC) available


Power can be supplied from the contact input/output communication connector to external switches, etc.




Application Examples



























Global Supply Network

SMC has a comprehensive network in the global market.


We now have a presence of more than 560 branch offices and distributors in 83 countries and regions worldwide. With this global network, we are able to provide a global supply of our substantial range of products and high-quality customer service. We also provide full support to local factories, foreign manufacturing companies, and Japanese companies in each country.





Circulating Fluid/Facility Water Line Equipment

For details, refer to the SMC website.



For details, refer to the SMC website.

Material

Nvlon

Polyurethane

Super PFA PFA



CONTENTS



Thermo-chiller/Rack Mount Type HRR Series

HRR010	Required Facility Water Flow Ratep. 24
How to Order	Dimensions
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)p. 9	Air-cooled Refrigeration p. 25, 26, 28
Water-cooled Refrigeration (Single-phase 200 to 230 VAC) p. 9	Water-cooled Refrigeration p. 25, 27, 28
Specifications	Operation Display Panelp. 29
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)p. 10	Alarmp. 29
Water-cooled Refrigeration (Single-phase 200 to 230 VAC)p. 11	Communication Functionsp. 30, 31
HRR012/018	Options
How to Order	With Electric Conductivity Control Function,
Air-cooled Refrigeration (Single-phase 100/115 VAC)p. 12	Applicable to DI Water Pipingp. 32
Water-cooled Refrigeration (Single-phase 100/115 VAC)p. 12	Applicable to DI Water Pipingp. 32
Specifications	Inverter Pump Mountedp. 33
Air-cooled Refrigeration (Single-phase 100/115 VAC)p. 13	High-Pressure Pump Mountedp. 34
Water-cooled Refrigeration (Single-phase 100/115 VAC)p. 13	With Feet/Without Rack Mounting Bracketsp. 35
HRR012/018/024/030	Removed Partsp. 35
How to Order	
LIOW TO CHUEL	
	Optional Accessories
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)p. 14	Optional Accessories① Concentration Meter p. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	•
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	①Concentration Meterp. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	① Concentration Meterp. 36 ② Particle Filter Element for Replacementp. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	① Concentration Meter p. 36 ② Particle Filter Element for Replacement p. 36 ③ DI Filter Replacement Cartridge p. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Oncentration Meter p. 36 Particle Filter Element for Replacement p. 36 DI Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Piping Conversion Fitting (For Water-cooled Refrigeration) p. 37
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Oncentration Meter p. 36 Particle Filter Element for Replacement p. 36 Oncentration Meter p. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Oncentration Meter p. 36 Particle Filter Element for Replacement p. 36 DI Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Piping Conversion Fitting (For Water-cooled Refrigeration) p. 37
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Concentration Meter p. 36 Particle Filter Element for Replacement p. 36 DI Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Power Supply Cable p. 37
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Concentration Meter p. 36 Particle Filter Element for Replacement p. 36 DI Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Power Supply Cable p. 37
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Oncentration Meter p. 36 Particle Filter Element for Replacement p. 36 In Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Fiping Conversion Fitting (For Water-cooled Refrigeration) p. 37 Power Supply Cable p. 37 Replacement Cartridge p. 36
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	Concentration Meter p. 36 Particle Filter Element for Replacement p. 36 DI Filter Replacement Cartridge p. 36 Anti-quake Bracket p. 36 Fiping Conversion Fitting (For Air-cooled Refrigeration) p. 37 Power Supply Cable p. 37 Caster Adjuster-foot Kit p. 38 Cooling Capacity Calculation
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	1 Concentration Meter p. 36 2 Particle Filter Element for Replacement p. 36 3 DI Filter Replacement Cartridge p. 36 4 Anti-quake Bracket p. 36 5 Piping Conversion Fitting (For Air-cooled Refrigeration) p. 37 6 Piping Conversion Fitting (For Water-cooled Refrigeration) p. 37 7 Power Supply Cable p. 37 8 Caster Adjuster-foot Kit p. 38 Cooling Capacity Calculation Required Cooling Capacity Calculation p. 39, 40
Air-cooled Refrigeration (Single-phase 200 to 230 VAC)	1 Concentration Meter p. 36 2 Particle Filter Element for Replacement p. 36 3 DI Filter Replacement Cartridge p. 36 4 Anti-quake Bracket p. 36 5 Piping Conversion Fitting (For Air-cooled Refrigeration) p. 37 6 Piping Conversion Fitting (For Water-cooled Refrigeration) p. 37 7 Power Supply Cable p. 37 8 Caster Adjuster-foot Kit p. 38 Cooling Capacity Calculation Required Cooling Capacity Calculation p. 39, 40 Precautions on Cooling Capacity Calculation p. 40



Thermo-chiller/Rack Mount Type Single-phase 200 to 230 VAC









How to Order

HRR010

Air-cooled refrigeration Water-cooled refrigeration



When multiple options are combined, indicate symbols in alphabetical order.



When multiple options are combined, indicate symbols in alphabetical order.



Specifications: 200 to 230 VAC Air-cooled Refrigeration

Model			HRR010-A-20				
Cooling method			Air-cooled refrigeration				
Refrigerant			R410A (HFC)				
Refrigerant charge [kg]			0.22				
	ontrol method		PID control				
Ar	mbient temperature/Humidity/Altitu	ıde* ^{1, 14}	Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m				
	Circulating fluid*2		Tap water, 15 % ethylene glycol aqueous solution				
	Set temperature range*1	[°C]	15 to 35				
	Cooling capacity (50/60 Hz)*3	[W]	950/1100				
	Heating capacity (50/60 Hz)*4	[W]	250/300				
	Temperature stability*5	[°C]	± 0.1				
system	Pump capacity (50/60 Hz)*6	[MPa]	0.09 (at 5 l/min)/0.11 (at 5 l/min) For Option T1: 0.35 (at 5 l/min)/0.35 (at 5 l/min)				
sys	Rated flow (50/60 Hz)*7	[l/min]	5/5 For Option T1: 5/5				
	Flow display range*20	[l/min]	2 to 16				
Ę	Electric conductivity display range	[μ S/cm]	0.1 to 48 (Only for Option DM)				
ing	Electric conductivity setting range	[μ S/cm]	0.5 to 45 (Only for Option DM)				
at	Particle filter nominal filtration rating*19	⁹ [μ m]	35				
Circulating fluid	Bypass valve*19		Installed				
Ö	Tank capacity	[L]	Approx. 3				
	Outlet, Return port size		Rc1/2				
	Drain port size		Rc1/4, With cap				
	Leakage protection		Drain pan (With water leakage sensor*19)				
	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*12, Alumina ceramic, Carbon, PP, PE, PPE, POM, PET, PA, FKM, EPDM, NBR, PVC, PPS, Fluoropolymer*13, Ion exchange resin*13				
	Power supply		Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range ± 10 %*15				
	Circuit protector	[A]	10				
system	Applicable earth leakage breaker ca	apacity*8	Rated current: 10 A Sensitivity current: 30 mA				
sys	Cable quantity x Size (Including grounding	g cable)*16	3 cores x 14 AWG (3 cores x 2.0 mm ²)				
	B		2.5/3.0				
Electrical	Rated operating current (50/60 Hz)*17	[A]	For Option T1				
<u>e</u>	(30/00 112)		4.3/4.7				
ш			0.48/0.60 (0.51/0.61)				
	Rated power consumption (50/60 Hz)*17	[kW (kVA)]	For Option T1				
	(30/00 112)		0.73/0.80 (0.85/0.94)				
Co	ommunication function		Contact input/output, Serial RS-485/RS-232C				
	pise level (50/60 Hz)*9	[dB(A)]	59/59				
	mensions*10	[mm]	W 483 x D 550 x H 221				
	ccessories*18		Power supply connector, Operation manual, Particle filter element*19				
W	eight*11	[kg]	29				

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC.
- *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL- 0 2 - 1 9 9 4 cooling water system - circulating type make-up water).
- *3 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest For models with an inverter pump mounted (Option T1), the cooling capacity will decrease by 300 W.
- Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest
- *5 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected
 - The installation environment and power supply are within the specification range and stable.
- *6 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *7 The required flow rate for maintaining the cooling capacity or temperature stability
 The specification of the cooling capacity and the temperature stability
- may not be satisfied if the flow rate is lower than the rated flow.

 *8 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA and a power supply of 200 VAC separately.

- *9 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *4.
- *10 Dimensions between panels, not including the dimensions of protrusion When Option Y (With feet/Without rack mounting brackets) is selected, refer to page 35.
- *11 Weight in the dry state without circulating fluids The weight will increase by 1 kg when Option DM (With electric conductivity control function, Applicable to DI water piping) is selected. The weight will increase by 2 kg when Option T 1 (Inverter pump mounted) is selected.
- *12 Option M (Applicable to DI water piping) does not contain copper.
- *13 For Option DM (With electric conductivity control function, Applicable to DI water piping)
- *14 If the product is used at an altitude of 1000 m or higher, refer to "For altitudes of 1000 m or higher" on page 42.
- *15 No continuous voltage fluctuation
- *16 To be prepared by the customer
- *17 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 2 0 0 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
- *18 For Option DM (With electric conductivity control function, Applicable to DI water piping), a DI filter is included. For pipe thread type F, a G thread conversion fitting set is included.
 - For pipe thread type N, an NPT thread conversion fitting set is included.
- *19 Not included for Option Z (Removed parts)
- *20 Not included for Options Z and Z1 (Removed parts)





Specifications: 200 to 230 VAC Water-cooled Refrigeration

Ref	oling method						
	<u> </u>		Water-cooled refrigeration				
	rigerant		R410A (HFC)				
Refrigerant charge [kg]			0.15				
	ntrol method		PID control				
Ambient temperature/Humidity/Altitude*1, 15			Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m				
	Circulating fluid*2		Tap water, 15 % ethylene glycol aqueous solution				
	Set temperature range*1	[°C]	15 to 35				
	Cooling capacity (50/60 Hz)*3	[W]	1000/1100				
H	Heating capacity (50/60 Hz)*4	[W]	200/200				
	Temperature stability*5	[°C]	± 0.1				
system	Pump capacity (50/60 Hz)*6	[MPa]	0.09 (at 5 l/min)/0.11 (at 5 l/min) For Option T1: 0.35 (at 5 l/min)/0.35 (at 5 l/min)				
1 8	Rated flow (50/60 Hz)*7	[l/min]	5/5 For Option T1: 5/5				
틸	Flow display range*21	[l/min]	2 to 16				
≝ ī	Electric conductivity display range	[µS/cm]	0.1 to 48 (Only for Option DM)				
	Electric conductivity setting range	[µ S/cm]	0.5 to 45 (Only for Option DM)				
1 <u>at</u>	Particle filter nominal filtration rating*20	[µ m]	35				
5 1	Bypass valve*20		Installed				
5 −	Tank capacity	[L]	Approx. 3				
(Outlet, Return port size		Rc1/2				
	Drain port size		Rc1/4, With cap				
I	Leakage protection		Drain pan (With water leakage sensor*20)				
ſ	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*12, Alumina ceramic, Carbon, PP, PE, PPE, POM, PET, PA, FKM, EPDM, NBR, PVC, PPS, Fluoropolymer*13, Ion exchange resin*13				
Ę, T	Temperature range	[°C]	5 to 35				
Facility water system	Pressure range	[MPa]	0.3 to 0.5				
1 ig	Required flow rate*14	[l/min]	6				
l Ma	Inlet-outlet pressure differential of facility water	[MPa]	0.3 or more				
∰	Port size		Rc3/8				
1 m	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing), Bronze, Brass, Synthetic rubber				
Г	Power supply		Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range ± 10 %*16				
	Circuit protector	[A]	10				
system	Applicable earth leakage breaker ca	pacity*8	Rated current: 10 A Sensitivity current: 30 mA				
Sys	Cable quantity x Size (Including grounding	cable)*17	3 cores x 14 AWG (3 cores x 2.0 mm ²)				
			2.4/3.0				
Electrical	Rated operating current (50/60 Hz)*18	[A]	For Option T1				
65	(50/60 HZ)***		4.2/4.6				
			0.47/0.59 (0.50/0.60)				
	Rated power consumption	[kW (kVA)]	For Option T1				
((50/60 Hz)* ¹⁸		0.72/0.78 (0.84/0.93)				
Cor	mmunication function		Contact input/output, Serial RS-485/RS-232C				
Nois	se level (50/60 Hz)*9	[dB(A)]	57/58				
	nensions*10	[mm]	W 483 x D 550 x H 221				
	cessories*19		Power supply connector, Operation manual, Particle filter element*20				
	ight*11	[kg]	27				

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC.
- *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL-02-1994 cooling water system circulating type make-up water).
- (JRA GL-02-1994 cooling water system circulating type make-up water).

 *3 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest For models with an inverter pump mounted (Option T1), the cooling cannot be with the cooling ca
- *4 ① Ambient temperature: 25 °C, ② Facility water temperature: 25 °C, ③ Circulating fluid temperature: 20 °C, ④ Circulating fluid at the rated flow, ⑤ Circulating fluid: Tap water, ⑥ Power supply: 2 0 0 VAC, ⑦ Piping length: Shortest
- *5 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected. The installation environment and power supply are within the specification range and stable.
- *6 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *7 The required flow rate for maintaining the cooling capacity or temperature stability
 - The specification of the cooling capacity and the temperature stability may not be satisfied if the flow rate is lower than the rated flow.
- *8 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA and a power supply of 200 VAC separately.
- *9 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *4.

- *10 Dimensions between panels, not including the dimensions of protrusion When Option Y (With feet/Without rack mounting brackets) is selected, refer to page 35.
- *11 Weight in the dry state without circulating fluids and facility water (for water-cooled refrigeration)
 - The weight will increase by 1 kg when Option DM (With electric conductivity control function, Applicable to DI water piping) is selected. The weight will increase by 2 kg when Option T 1 (Inverter pump mounted) is selected.
- *12 Option M (Applicable to DI water piping) does not contain copper.
- *13 For Option DM (With electric conductivity control function, Applicable to DI water piping)
- *14 The required flow rate when the cooling capacity load is applied under the conditions in *3
- *15 If the product is used at an altitude of 1000 m or higher, refer to "For altitudes of 1000 m or higher" on page 42.
- *16 No continuous voltage fluctuation
- 17 To be prepared by the customer
- *18 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
- *19 For Option DM (With electric conductivity control function, Applicable to DI water piping), a DI filter is included.
 - For pipe thread type F, a G thread conversion fitting set is included.
 - For pipe thread type N, an NPT thread conversion fitting set is included.
- *20 Not included for Option Z (Removed parts)
- *21 Not included for Options Z and Z1 (Removed parts)




Thermo-chiller/Rack Mount Type Single-phase 100/115 VAC ROHS


HRR012/018





How to Order





Single-phase 100 VAC (50/60 Hz) Single-phase 115 VAC (60 Hz) High-pressure pump mounted

When multiple options are combined, indicate symbols in

alphabetical order.

HRR Series

Specifications: 100/115 VAC

Model		HRR012-A-10	HRR018-A-10	HRR012-W-10	HRR018-W-10				
Cooling method		Air-cooled r	efrigeration	Water-cooled	d refrigeration				
Refrigerant			R410A	A (HFC)					
Refrigerant charge	[kg]	0.36	0.36	0.25	0.25				
Control method			PID o	control					
Ambient temperature/Humidity/Altit	ude*1, 14	Temperati	Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m						
Circulating fluid*2			Tap water, 15 % ethylene glycol aqueous solution						
Set temperature range*1	[°C]		5 to	o 35					
Cooling capacity (50/60 Hz)*3	[W]	1000/1200	1600/1800	1000/1200	1600/1800				
Heating capacity (50/60 Hz)*4	[W]	40	00	50	00				
Temperature stability*5	[°C]	±0.1							
Pump capacity (50/60 Hz)*6 Rated flow (50/60 Hz)*7	[MPa]	0.13 (at 7 l/min)/0.18 (at 7 l/min) For Options T, MT: 0.36 (at 7 l/min)/0.42 (at 10 l/min)							
ิ Rated flow (50/60 Hz)*7	[l/min]		7/7 For Option	ons T, MT: 7/10					
Flow display range*21	[l/min]			o 16					
Electric conductivity display range	[μ S/cm]		0.1 to 48 (Only for Option DM)						
Flow display range*21 Electric conductivity display range Electric conductivity setting range Particle filter nominal filtration rating*2 Bypass valve*20 Tank capacity	[μ S/cm]	0.5 to 45 (Only for Option DM)							
Particle filter nominal filtration rating*2	²⁰ [μ m]		5						
Bypass valve*20			Inst	alled					
Ö Tank capacity	[L]		Approx. 4						
Outlet, Return port size		Rc1/2							
Drain port size		Rc1/4, With cap							
Leakage protection		Drain pan (With water leakage sensor)*20							
Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*11, Bronze*17, SiC, Alumina ceramic, Carbon PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS, Fluoropolymer*12, Ion exchange resin*12							
E Temperature range	[°C]			5 to	40				
Temperature range Pressure range	[MPa]			0.3 t	o 0.5				
Required flow rate (50/60 Hz)*13	[l/min]			8	12				
Required flow rate (50/60 Hz)*13 Inlet-outlet pressure differential of facility water Port size Fluid contact material	r [MPa]	-	_	0.3 or more					
Port size				Rc3/8					
Fluid contact material				Stainless steel, Copper (Heat exchan	ger brazing), Bronze, Synthetic rubbe				
Power supply		Single-phase 100 VAC (50/60 Hz), 115 VAC (60 Hz) Allowable voltage range ± 10 %* ¹⁵							
E Circuit protector	[A]			15					
Applicable earth leakage breaker of Cable quantity x Size (Including grounding	apacity*8		Rated current: 15 A, S	ensitivity current: 30 mA					
Cable quantity x Size (Including grounding	g cable)*16		3 cores x 14 AWG	(3 cores x 2.0 mm ²)					
		8.9/8.9	9.1/9.6	8.5/8.5	8.7/8.7				
Rated operating current*18	[A]		For Opti	ons T, MT					
Rated operating current*18 (50/60 Hz)		10.7/10.7	11.0/11.0	10.5/10.5	10.8/10.8				
		0.8/0.9 (1.0/1.0)	0.9/1.1 (1.1/1.1)	0.7/0.8 (0.9/0.9)	0.8/0.9 (1.0/1.0)				
Rated power consumption*18 (50/60 Hz)	[kW (kVA)]	0.9/1.1 (1.1/1.1)	For Opti 1.0/1.3 (1.2/1.3)	ons T, MT 0.9/1.0 (1.1/1.0)	1.1/1.1 (1.2/1.1)				
Communication function		. ,	,	Serial RS-485/RS-232C	. ,				
Noise level (50/60 Hz)*9	[dB]	59/60	59/60	59/60	59/60				
Accessories*19		Power supply conne	ctor, Particle filter element	and maintenance handle*	Operation manual				
Weight*10	[kg]	4			.0				
*1 No condensation should be prese		seasons or in locations	*9 Front: 1 m height	: 1 m. stable with no load. (Other conditions → See */				

*1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC. Use 1 5 % ethylene glycol aqueous solution when operating at a temperature of 10 °C or less.

*2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL-02-1994 cooling water system - circulating type - make-

up water).
① Ambient temperature: 25 °C, ② Facility water temperature: 25 °C, ③ Circulating fluid temperature: 20 °C, ④ Circulating fluid at the rated flow, ⑤ Circulating fluid: Tap water, ⑥ Power supply: 1 0 0 VAC, ⑦ Piping length: Shortest

For models with a high-pressure pump mounted (Options T, MT), the cooling capacity will decrease by 300 W.

① Ambient temperature: 25 °C, ② Facility water temperature: 25 °C, ③ Circulating fluid temperature: 20 °C, ④ Circulating fluid at the rated flow, ⑤ Circulating fluid: Tap water, ⑥ Power supply: 1 0 0 VAC, ⑦ Piping length: Shortest

- *5 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected The installation environment and power supply are within the specification range and stable
- *6 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
 *7 The required flow rate for maintaining the cooling capacity or temperature
- The specification of the cooling capacity and the temperature stability may not be satisfied if the flow rate is lower than the rated flow.
- *8 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA and a power supply of 100 VAC separately.

Front: 1 m, height: 1 m, stable with no load, Other conditions → See *4. Weight in the dry state without circulating fluids and facility water (for water-

cooled refrigeration)
The weight will increase by 1 kg when Option DM (With electric conductivity control function, Applicable to DI water piping) is selected.

The weight will increase by 5 kg when Options T (High-pressure pump mounted) or MT (Applicable to DI water piping + High-pressure pump mounted) are selected.

The weight will decrease by 1 kg for Option Z (Removed parts)

*11 Options M (Applicable to DI water piping) and MT (Applicable to DI water piping + High-pressure pump mounted) do not contain copper or bronze. *12 For Option DM (With electric conductivity control function, Applicable

to DI water piping)

- *13 The required flow rate when the cooling capacity load is applied under the conditions in *3
 *14 If the product is used at an altitude of 1000 m or higher, refer to "For al-
- titudes of 1000 m or higher" on page 42.

 *15 No continuous voltage fluctuation

- *15 No continuous voltage iluctuation
 *16 To be prepared by the customer
 *17 Option T (High-pressure pump mounted) contains this material.
 *18 ① Ambient temperature: 25 °C, ② Facility water temperature: 25 °C, ③
 Circulating fluid temperature: 2 0 °C, ④ Circulating fluid at the rated flow, ⑤ Circulating fluid: Tap water, ⑥ Power supply: 1 0 0 VAC, ⑦ Piping length: Shortest, ⑧ With the rated cooling load applied
 *19 For Option DM (With electric conductivity control function, Applicable
- to DI water piping), a DI filter is included.

 For pipe thread type F, a G thread conversion fitting set is included.

 For pipe thread type N, an NPT thread conversion fitting set is included.

 *20 Not included for Option Z (Removed parts)
- *21 Not included for Options Z and Z1 (Removed parts)




Thermo-chiller/Rack Mount Type Single-phase 200 to 230 VAC ROHS


HRR012/018/024/030





How to Order





Power supply

20 Single-phase 200 to 230 VAC (50/60 Hz)

· When multiple options are combined, indicate symbols in

alphabetical order



Specifications: 200 to 230 VAC Air-cooled Refrigeration

	Model		HRR012-A-20	HRR018-A-20	HRR024-A-20	HRR030-A-20		
Co	ooling method		Air-cooled refrigeration					
Re	frigerant			R410A	(HFC)			
Re	frigerant charge	[kg]	0.38 0.47					
	entrol method		PID control					
Ar	nbient temperature/Humidity/Altitu	ıde* ^{1, 13}	Temperat	ure: 5 to 40 °C, Humidity: 3	0 to 70 %, Altitude: less tha	an 3000 m		
	Circulating fluid*2			Tap water, 15 % ethylene	e glycol aqueous solution			
	Set temperature range*1	[°C]		5 to	35			
	Cooling capacity (50/60 Hz)*3	[W]	1000/1200					
	Heating capacity (50/60 Hz)*4	[W]	450/500 550/700					
	Temperature stability*5	[°C]						
system	Pump capacity (50/60 Hz)*6	[MPa]		0.13 (at 7 l/min), For Option T: 0.42 (at 1 For Option MT: 0.32 (at 1	0 l/min)/0.4 (at 14 l/min)			
S	Rated flow (50/60 Hz)*7	[l/min]		7/7 For Option	ns T, MT: 10/14			
ള	Flow display range*20	[l/min]		2 to	16			
) Ħ	Electric conductivity display range	[μ S/cm]		0.1 to 48 (Only	for Option DM)			
i,	Electric conductivity setting range	[µS/cm]		0.5 to 45 (Only	for Option DM)			
nat	Particle filter nominal filtration rating*19	⁹ [μ m]		Ę	5			
Circulating fluid	Bypass valve*19			Insta	alled			
	Tank capacity	[L]		Appr	ox. 4			
	Outlet, Return port size		Rc1/2					
	Drain port size		Rc1/4, With cap					
	Leakage protection			Drain pan (With water	r leakage sensor*19)			
	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*11, Bronze*16, SiC, Alumina ceramic, Carbon, PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS, Fluoropolymer*12, Ion exchange resin*12					
	Power supply		Single-pha	Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range ± 10 %*14				
	Circuit protector	[A]	10 For Options T, MT: 15					
system	Applicable earth leakage breaker ca	apacity*8	Rated current: 10 A For Options T, MT: 15 A Sensitivity current: 30 mA					
sys	Cable quantity x Size (Including grounding	g cable)*15		3 cores x 14 AWG ((3 cores x 2.0 mm ²)			
ā	Dated energting		3.6/4.0	3.6/4.3	5.2/5.8	5.5/6.2		
Ĕ	Rated operating current (50/60 Hz)*17	[A]		For Option	ons T, MT			
Electrical	(56/56 112)		4.7/6.2	4.7/6.5	6.3/8.0	6.5/8.3		
ш	Data da a como a constituir		0.6/0.8 (0.7/0.8)	0.7/0.9 (0.7/0.9)	0.9/1.2 (1.1/1.2)	1.0/1.2 (1.1/1.3)		
	Rated power consumption (50/60 Hz)*17	[kW (kVA)]		For Option	ons T, MT			
L	(00,00112)		0.9/1.2 (0.9/1.2)	0.9/1.3 (1.0/1.3)	1.2/1.6 (1.3/1.6)	1.3/1.6 (1.3/1.7)		
Co	mmunication function			Contact input/output, S	erial RS-485/RS-232C			
	oise level (50/60 Hz)*9	[dB]	59/60	59/60	61/64	61/64		
	cessories*18		Power supply conne	ctor, Particle filter element	and maintenance handle*	19, Operation manual		
	eight*10	[kg]	Power supply connector, Particle filter element and maintenance handle*19, Operation manual 40 46					

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC. Use 1 5 % ethylene glycol aqueous solution when operating at a temperature of 10 °C or less.
- *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL- 0 2 - 1 9 9 4 cooling water system - circulating type make-up water).
- *3 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest For models with a high-pressure pump mounted (Options T, MT), the
- cooling capacity will decrease by 300 W.

 4 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C,
 ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest
- *5 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected
 - The installation environment and power supply are within the specification range and stable.
- *6 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *7 The required flow rate for maintaining the cooling capacity or temperature stability.
 - The specification of the cooling capacity and the temperature stability may not be satisfied if the flow rate is lower than the rated flow.
- *8 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA and a power supply of 200 VAC separately.

- *9 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *4.
 - 10 Weight in the dry state without circulating fluids The weight will increase by 1 kg when Option DM (With electric conductivity control function, Applicable to DI water piping) is selected. The weight will increase by 5 kg when Options T (High-pressure pump mounted) or MT (Applicable to DI water piping + High-pressure pump mounted) are selected.
 - The weight will decrease by 1 kg for Option Z (Removed parts)
- *11 Options M (Applicable to DI water piping) and MT (Applicable to DI water piping + High-pressure pump mounted) do not contain copper or bronze.
- *12 For Option DM (With electric conductivity control function, Applicable to DI water piping)
- *13 If the product is used at an altitude of 1000 m or higher, refer to "For altitudes of 1000 m or higher" on page 42.
- *14 No continuous voltage fluctuation
- *15 To be prepared by the customer
- *16 Option T (High-pressure pump mounted) contains this material. *17 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C,
- 17 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid: Tap water, ⑤ Power supply: 2 0 0 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
- *18 For Option DM (With electric conductivity control function, Applicable to DI water piping), a DI filter is included.
 - For pipe thread type F, a G thread conversion fitting set is included. For pipe thread type N, an NPT thread conversion fitting set is included.
- *19 Not included for Option Z (Removed parts)
- *20 Not included for Options Z and Z1 (Removed parts)



Specifications: 200 to 230 VAC Water-cooled Refrigeration

Cooling method Refrigerant Refrigerant charge Control method Ambient temperature/Humidity/Altitu Circulating fluid*2 Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5	[kg]		Water-cooled R410A 25	(HFC)				
Refrigerant charge Control method Ambient temperature/Humidity/Altitu Circulating fluid*2 Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5				· ,				
Control method Ambient temperature/Humidity/Altitu Circulating fluid*2 Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5			25	0.4				
Ambient temperature/Humidity/Altitu Circulating fluid*2 Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5	de*1, 14			0.25 0.40				
Circulating fluid*2 Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5	de*1, 14	_	PID control					
Set temperature range*1 Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5		Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m						
Cooling capacity (50/60 Hz)*3 Heating capacity (50/60 Hz)*4 Temperature stability*5			Tap water, 15 % ethylene glycol aqueous solution					
Heating capacity (50/60 Hz)*4 Temperature stability*5	[°C]		5 to	35				
Temperature stability*5	[W]	1000/1200	1600/1800	2000/2400	2500/3000			
	[W]	450	[′] 500	550/	700			
E Pump capacity (50/60 Hz)*6	[°C]	± 0.1						
F Pump capacity (50/60 Hz)*6			0.13 (at 7 l/min)/	0.18 (at 7 l/min)				
i amp capacity (corco riz)	[MPa]		For Option T: 0.42 (at 10	, (
Pump capacity (50/60 Hz)*5			For Option MT: 0.32 (at 1	0 l/min)/0.32 (at 14 l/min)				
	[l/min]	7/7 For Options T, MT: 10/14						
Flow display range*21 Electric conductivity display range Electric conductivity setting range Particle filter nominal filtration rating*20 Bypass valve*20 Tank capacity	[l/min]	2 to 16						
Electric conductivity display range	[µS/cm]		0.1 to 48 (Only	for Option DM)				
Electric conductivity setting range	[µS/cm]		0.5 to 45 (Only	for Option DM)				
Particle filter nominal filtration rating*20 [μm]		5						
Bypass valve*20		Installed						
Tank capacity	[L]		Appr	ox. 4				
Outlet, Return port size		Rc1/2						
Drain port size		Rc1/4, With cap						
Leakage protection		Drain pan (With water leakage sensor*20)						
Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*11, Bronze*17, Si0 Alumina ceramic, Carbon, PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS, Fluoropolymer*12, Ion exchange resin*12			^{*17} , SiC, PVC,			
E Temperature range	[°C]	5 to 40						
Temperature range Pressure range Required flow rate (50/60 Hz)**13 Inlet-outlet pressure differential of facility water Port size Fluid contact material	[MPa]		0.3 to					
Required flow rate (50/60 Hz)*13	[l/min]	8	12	14	15			
Inlet-outlet pressure differential of facility water	[MPa]		0.3 or	more				
Port size		Rc3/8						
Fluid contact material		Stainless steel	, Copper (Heat exchanger	brazing), Bronze, Brass, Sv	ynthetic rubber			
Power supply		Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range ± 10 %*15						
Circuit protector	[A]	- 3 - 1	10 For Option					
Applicable earth leakage breaker ca	pacity*8	Rated current: 10 A For Options T, MT: 15 A Sensitivity current: 30 mA						
Cable quantity x Size (Including grounding	cable)*16		3 cores x 14 AWG (3 cores x 2.0 mm ²)				
		3.2/3.6	3.3/3.6	4.9/5.1	4.9/5.2			
Rated operating current (50/60 Hz)*18	[A]	4.3/5.8	For Optic 4.4/5.8	ons T, MT 6.0/7.3	6.0/7.4			
		0.6/0.7 (0.7/0.7)	0.6/0.7 (0.7/0.7)	0.8/1.0 (1.0/1.0)	0.8/1.0 (1.0/1.0)			
Rated power consumption (50/60 Hz)*18	[kW (kVA)]		For Option	ns T, MT				
(30/00 FIZ)		0.9/1.1 (0.9/1.2)	0.9/1.1 (0.9/1.2)	1.1/1.2 (1.4/1.4)	1.1/1.2 (1.4/1.4)			
Communication function		. ,	Contact input/output, S	erial RS-485/RS-232C	. ,			
Noise level (50/60 Hz)*9	[dB]	59/60	59/60	61/64	61/64			
Accessories*19		Power supply conne	ctor, Particle filter element	and maintenance handle*2	0, Operation manual			
Weight*10	[kg]	4	· · · · · · · · · · · · · · · · · · ·	4	· · ·			

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC. Use 1 5 % ethylene glycol aqueous solution when
- operating at a temperature of 10 °C or less.

 *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association
- ards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL-02-1994 cooling water system circulating type make-up water).

 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest
 For models with a high-pressure pump mounted (Options T, MT), the cooling capacity will decrease by 300 W.

 ① Ambient temperature: 25 °C, ② Facility water temperature: 25 °C, ③ Circulating fluid temperature: 20 °C, ④ Circulating fluid at the rated flow, ⑤ Circulating fluid: Tap water, ⑥ Power supply: 2 0 0 VAC, ⑦ Piping length: Shortest
- length: Shortest
- Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected The installation environment and power supply are within the specification range and stable.
- *6 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
 *7 The required flow rate for maintaining the cooling capacity or temperature
- The specification of the cooling capacity and the temperature stability
- may not be satisfied if the flow rate is lower than the rated flow.

 *8 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA
- and a power supply of 200 VAC separately
- *9 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *4.

- *10 Weight in the dry state without circulating fluids and facility water (for water-cooled refrigeration)
 The weight will increase by 1 kg when Option DM (With electric con
 - ductivity control function, Applicable to DI water piping) is selected. The weight will increase by 5 kg when Options T (High-pressure pump mounted) or MT (Applicable to DI water piping + High-pressure pump
- mounted) are selected.

 The weight will decrease by 1 kg for Option Z (Removed parts)

 *11 Options M (Applicable to DI water piping) and MT (Applicable to DI water piping + High-pressure pump mounted) do not contain copper or bronze.

 *12 For Option DM (With electric conductivity control function, Applicable to DI water piping)

 *13 The required flow rate when the cooling capacity load is applied under the conditions in *3
- the conditions in *3
 *14 If the product is used at an altitude of 1000 m or higher, refer to "For al-
- titudes of 1000 m or higher" on page 42. No continuous voltage fluctuation
- To be prepared by the customer
- *17 Option T (High-pressure pump mounted) contains this material. *18 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20
- *18 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
 *19 For Option DM (With electric conductivity control function, Applicable
- to DI water piping), a DI filter is included.
- For pipe thread type F, a G thread conversion fitting set is included.
 For pipe thread type N, an NPT thread conversion fitting set is included.

 *20 Not included for Option Z (Removed parts)

 *21 Not included for Options Z and Z1 (Removed parts)



Thermo-chiller/Rack Mount Type Single-phase 200 to 230 VAC ROHS

HRR050







How to Order

Water-cooled refrigeration

Air-cooled refrigeration





Specifications: 200 to 230 VAC Air-cooled Refrigeration

Model			HRR050-A-20-(DM)U(YZ)	
Cooling method			Air-cooled refrigeration	
Refrigerant			R410A (HFC)	
Re	frigerant charge	[kg]	0.72	
	entrol method		PID control	
Ar	nbient temperature/Humidity/Altitu	ıde* ^{1, 13}	Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m	
	Circulating fluid*2		Tap water, 15 % ethylene glycol aqueous solution	
	Set temperature range*1	[°C]	5 to 35	
	Cooling capacity (50/60 Hz)*3	[W]	4600/5100	
	Heating capacity (50/60 Hz)*3	[W]	1000/1200	
	Temperature stability*4	[°C]	± 0.1	
E H	Pump capacity (50/60 Hz)*5	[MPa]	0.34 (at 15 l/min)/0.34 (at 23 l/min)	
/st	Rated flow (50/60 Hz)*6	[l/min]	15/23	
S	Flow display range*19	[l/min]	5 to 40	
Ĕ	Electric conductivity display range	[μ S/cm]	0.1 to 48 (Only for Option DM)	
lg f	Electric conductivity setting range	[μ S/cm]	0.5 to 45 (Only for Option DM)	
atir	Particle filter nominal filtration rating*1	⁸ [μ m]	5	
Circulating fluid system	Bypass valve*18		Installed	
جَا	Tank capacity	[L]	Approx. 5	
	Outlet, Return port size		Rc1/2	
	Drain port size		Rc1/4, With cap	
	Leakage protection		Drain pan (With water leakage sensor*18)	
	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*11, Bronze*11, SiC, Alumina ceramic, Carbon, PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS, Fluoropolymer*12, Ion exchange resin*12	
	Power supply		Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range ± 10 %*14	
_	Circuit protector	[A]	20	
system	Applicable earth leakage breaker c	apacity*7	Rated current: 20 A Sensitivity current: 30 mA	
<u>a</u>	Cable quantity x Size (Including grounding	g cable)*15	3 cores x 12 AWG (3 cores x 3.5 mm ²)	
Electrical	Rated operating current (50/60 Hz)*16	[A]	9.3/11.8	
Ш	Rated power consumption [kW (kVA)]		1.9/2.4 (1.9/2.5)	
Co	Communication function		Contact input/output, Serial RS-485/RS-232C	
No	oise level (50/60 Hz)*8	[dB(A)]	63/67	
Di	mensions ^{*9}	[mm]	W 483 x D 550 x H 710	
	cessories*17		Power supply connector, Maintenance handle for particle filter*18, Operation manual, Particle filter element*18	
W	eight*10	[kg]	74	
_	-			

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC.
- *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL-02-1994 cooling water system - circulating type make-up water).
- *3 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ⑤ Circulating fluid at the rated flow, ⑥ Circulating fluid: Tap water, ⑦ Power supply: 200 VAC, ⑧ Piping length: Shortest
- *4 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected
 - The installation environment and power supply are within the specification range and stable.
- *5 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *6 The required flow rate for maintaining the cooling capacity or temperature stability
 - The specification of the cooling capacity and the temperature stability may not be satisfied if the flow rate is lower than the rated flow.
- *7 Purchase an earth leakage breaker with a sensitivity current of 30 mA and a power supply of 200 VAC separately.
- *8 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *3.
- *9 Dimensions between panels, not including the dimensions of protrusion When Option Y (With feet/Without rack mounting brackets) is selected, refer to page 35.

- *10 Weight in the dry state without circulating fluids
 The weight will increase by 1 kg when Option DM (With electric con
 - ductivity control function, Applicable to DI water piping) is selected. The weight will decrease by 2 kg for Option Z (Removed parts).
- *11 Options M (Applicable to DI water piping) and DM (With electric conductivity control function, Applicable to DI water piping) do not contain copper or bronze.
- *12 For Option DM (With electric conductivity control function, Applicable to DI water piping)
- *13 If the product is used at an altitude of 1000 m or higher, refer to "For altitudes of 1000 m or higher" on page 42.
- *14 No continuous voltage fluctuation
- *15 To be prepared by the customer
- *16 ① Ambient temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
- *17 For Option DM (With electric conductivity control function, Applicable to DI water piping), a DI filter is included.
 - For pipe thread type F, a G thread conversion fitting set is included. For pipe thread type N, an NPT thread conversion fitting set is included.
- *18 Not included for Option Z (Removed parts)
- *19 Not included for Options Z and Z1 (Removed parts)





Specifications: 200 to 230 VAC Water-cooled Refrigeration

Model			HRR050-W-20-(DM)U(YZ)	
Cooling method			Water-cooled refrigeration	
Refrigerant			R410A (HFC)	
R	Refrigerant charge [kg]		0.59	
	ontrol method		PID control	
Α	mbient temperature/Humidity/Altitu	de*1, 14	Temperature: 5 to 40 °C, Humidity: 30 to 70 %, Altitude: less than 3000 m	
	Circulating fluid*2		Tap water, 15 % ethylene glycol aqueous solution	
	Set temperature range*1	[°C]	5 to 35	
	Cooling capacity (50/60 Hz)*3	[W]	5000/5900	
	Heating capacity (50/60 Hz)*3	[W]	1000/1200	
_	Temperature stability*4	[°C]	± 0.1	
system	Pump capacity (50/60 Hz)*5	[MPa]	0.34 (at 15 l/min)/0.34 (at 23 l/min)	
\S	Rated flow (50/60 Hz)*6	[l/min]	15/23	
8	Flow display range*20	[l/min]	5 to 40	
Circulating fluid	Electric conductivity display range	[µS/cm]	0.1 to 48 (Only for Option DM)	
E	Electric conductivity setting range	[µ S/cm]	0.5 to 45 (Only for Option DM)	
∃ŧ	Particle filter nominal filtration rating*19	[µm]	5	
Ħ	Bypass valve*19		Installed	
15	Tank capacity	[L]	Approx. 5	
	Outlet, Return port size		Rc1/2	
	Drain port size		Rc1/4, With cap	
	Leakage protection		Drain pan (With water leakage sensor*19)	
	Fluid contact material		Stainless steel, Copper (Heat exchanger brazing)*11, Bronze*11, SiC, Alumina ceramic, Carbon, PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS, Fluoropolymer*12, Ion exchange resin*12	
em	Temperature range	[°C]	5 to 40	
system	Pressure range	[MPa]	0.3 to 0.5	
ţ.	Required flow rate*13	[l/min]	16	
N W	Inlet-outlet pressure differential of facility water	[MPa]	0.3 or more	
Facility water	Port size		Rc3/8	
ã			Stainless steel, Copper (Heat exchanger brazing), Bronze, Brass, Synthetic rubber	
	Power supply		Single-phase 200 to 230 VAC, 50/60 Hz, Allowable voltage range \pm 10 $\%^{*15}$	
E	Circuit protector	[A]	20	
system	Applicable earth leakage breaker capacity*7		Rated current: 20 A Sensitivity current: 30 mA	
	Cable quantity x Size (Including grounding	cable)*16	3 cores x 12 AWG (3 cores x 3.5 mm ²)	
Electrical	Rated operating current (50/60 Hz)*17	[A]	8.5/11.0	
	Rated power consumption (50/60 Hz)*17	[kW (kVA)]	1.7/2.2 (1.7/2.3)	
	Communication function		Contact input/output, Serial RS-485/RS-232C	
	oise level (50/60 Hz)*8	[dB(A)]	63/67	
D	mensions*9	[mm]	W 483 x D 550 x H 532	
Α	Accessories*18		Power supply connector, Maintenance handle for particle filter*19, Operation manual, Particle filter element*19	
	eight*10			

- *1 No condensation should be present. During seasons or in locations where the ambient temperature is likely to fall below freezing point, please contact SMC.
- *2 If tap water is used, use water that is compliant with the Water Quality Standards of the Japan Refrigeration and Air Conditioning Industry Association (JRA GL-02-1994 cooling water system circulating type make-up water).
- *3 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest
- *4 Temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected The installation environment and power supply are within the specification range and stable.
- *5 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *6 The required flow rate for maintaining the cooling capacity or temperature stability
 - The specification of the cooling capacity and the temperature stability may not be satisfied if the flow rate is lower than the rated flow.
- *7 Purchase an earth leakage breaker with a sensitivity current of 3 0 mA and a power supply of 200 VAC separately.
- *8 Front: 1 m, height: 1 m, stable with no load, Other conditions → See *3.
- *9 Dimensions between panels, not including the dimensions of protrusion When Option Y (With feet/Without rack mounting brackets) is selected, refer to page 35.

- *10 Weight in the dry state without circulating fluids
 - The weight will increase by 1 kg when Option DM (With electric conductivity control function, Applicable to DI water piping) is selected. The weight will decrease by 2 kg for Option Z (Removed parts).
- *11 Option M (Applicable to DI water piping) does not contain copper or bronze.
- *12 For Option DM (With electric conductivity control function, Applicable to DI water piping)
- *13 The required flow rate when the cooling capacity load is applied under the conditions in *3
- *14 If the product is used at an altitude of 1000 m or higher, refer to "For altitudes of 1000 m or higher" on page 42.
- *15 No continuous voltage fluctuation
- *16 To be prepared by the customer
- *17 ① Facility water temperature: 25 °C, ② Circulating fluid temperature: 20 °C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: Tap water, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest, ⑦ With the rated cooling load applied
- *18 For Option DM (With electric conductivity control function, Applicable to DI water piping), a DI filter is included.
 - For pipe thread type F, a G thread conversion fitting set is included. For pipe thread type N, an NPT thread conversion fitting set is included.
 - Not included for Option 7 (Removed parts)
- *19 Not included for Option Z (Removed parts)
- *20 Not included for Options Z and Z1 (Removed parts)



Thermo-chiller/Rack Mount Type HRR Series

* If the product is used at an altitude of 1000 m or higher, refer to "Operating Environment/Storage Environment" (page 42) Item 14 "For altitudes of 1000 m or higher."

For models with an inverter pump mounted (-T1) and models with a high-pressure pump mounted (-T, -MT), the cooling capacity will decrease by about 300 W from each graph.

HRR010-A-20-□ 2000 1500


20

Cooling Capacity

0

10

15




25


Circulating fluid temperature [°C]


30


35


40




















HRR Series


Cooling Capacity


- If the product is used at an altitude of 1000 m or higher, refer to "Operating Environment" (Storage Environment" (page 42) Item 14 "For altitudes of 1000 m or higher."
- * For models with a high-pressure pump mounted (-T, -MT), the cooling capacity will decrease by about 300 W from each graph.

























Heating Capacity
























HRR Series

Heating Capacity












Pump Capacity

HRR010-A-20, HRR010-W-20






HRR050-A-20, HRR050-W-20




Required Facility Water Flow Rate

HRR010-W-20




This is the required facility water flow rate at the circulating fluid rated flow and the cooling capacity listed in the "Cooling Capacity" specifications.

HRR 012 018 024 030



* This is the required facility water flow rate at the circulating fluid rated flow and the cooling capacity listed in the "Cooling Capacity" specifications.

HRR050-W-20



* This is the facility water flow rate at the circulating fluid rated flow and the cooling capacity listed on pages 20 and 21.




HRR Series

Dimensions

Air-cooled Refrigeration

HRR010-A-20-□




- *1 Without bypass valve for Option Z (Removed parts)

 * For Option Y (With feet/Without rack mounting brackets), refer to page 35.

Water-cooled Refrigeration

HRR010-W-20-□




- *1 Without bypass valve for Option Z (Removed parts)
- * For Option Y (With feet/Without rack mounting brackets), refer to page 35.

Dimensions


Air-cooled Refrigeration

HRR012-A, HRR018-A

Model	Α	В
HRR012/018-A-10-□	70	45
HRR012/018-A-20-□	80	61
HRR012/018-A-20-U	80	50



HRR024-A, HRR030-A




HRR Series


Dimensions

Water-cooled Refrigeration

HRR012-W, HRR018-W




HRR024-W, HRR030-W



Dimensions

Air-cooled Refrigeration


HRR050-A-20



- *1 Without bypass valve for Option Z (Removed parts)
- * For Option Y (With feet/Without rack mounting brackets), refer to page 35.

Water-cooled Refrigeration

HRR050-W-20




- *1 Without bypass valve for Option Z (Removed parts)
- * For Option Y (With feet/Without rack mounting brackets), refer to page 35.



Operation Display Panel

For details, refer to the "Operation Manual" on the SMC website.

The basic operation of this unit is controlled through the operation panel on the front of the product.



No.	Description Function				
1	Digital display (7-segment, 5 digits)	Displays the current circulating fluid discharge temperature, pressure, flow rate, alarm codes, and other set values			
2	Digital display (11-segment, 5 digits)	Displays the circulating fluid discharge temperature and the set values of other menu items			
3	[°C] lamp	Lights up when temperature is displayed on the digital display			
4	[MPa] lamp	Lights up when pressure is displayed on the digital display			
(5)	[LPM] lamp	Lights up when flow rate is displayed on the digital display			
6	[H] lamp	Lights up when time is displayed on the digital display			
7	[SEC] lamp	Lights up when seconds are displayed on the digital display			
8	[%] lamp	Lights up when the pump output set value is displayed on the digital display			
9	[RUN] lamp	Lights up during operation, and goes off when it is stopped			
10	[ALM] lamp	Lights up when the FLT alarm occurs (This product will stop.)			
		Lights up when the WRN alarm occurs (This product will continue operation.)			
12	[ᆸ] lamp	Lights up when "AL.01 Low level in tank abnormal" or "AL.02 Low level in tank" alarm is generated			
13 Digital display (11-segment, 1 digit)		"X" is displayed when maintenance notification is generated.			
14 [RMT] lamp		Lights up during remote operation by communication function			
15)	[KEYLOCK] lamp	Lights up when key lock setting is active			
16	[RUN/STOP] key	Press and hold for 1 second to start or stop.			
17	[MENU] key	Switching of each menu and cancellation of setting values			
18	[ENT] key	Switch to setting mode and set values.			
19	[▲] key	Move item upward or increase the set value.			
20	[▼] key	Move item downward or decrease the set value.			
21)	[RESET] key	Reset the alarm.			

Alarm

Various alarms are displayed with the ALM indicator and the alarm code in the white upper section of the operation display. These alarms can also be output through communication protocols.

A.I		1 201 1	Display unit		
Alarm	Alarm message	Initial value	Upper section (White)	Lower section (Green)	
AL01	Low level in tank abnormal	FLT	AL01	$LOW \Rightarrow LEVEL \Rightarrow FLT$	
AL02	Low level in tank	WRN	AL02	$LOW \Rightarrow LEVEL \Rightarrow WRN$	
AL04	Water leakage*6	WRN*1	AL04	WATER \Rightarrow LEAK	
AL09	Circulating fluid discharge pressure rise	FLT*2	AL09	HIGH ⇒ PRESS	
AL10	Flow rate reduction*7	WRN*1	AL10	$LOW \Rightarrow FLOW \Rightarrow WRN$	
AL11	Outside ambient temperature range*3	OFF*1	AL11	$AMB \Rightarrow TEMP \Rightarrow OUT$	
AL12	Electric conductivity rise*4	WRN*5	AL12	$DI \Rightarrow ERROR$	
AL13	NOT TEMP READY	OFF*1	AL13	$TEMP \Rightarrow READY \Rightarrow ERROR$	
AL14	Circulating fluid temperature range rise	OFF*1	AL14	TEMP ⇒ OUT.HI	
AL15	L15 Circulating fluid temperature range drop		AL15	$TEMP \Rightarrow OUT.LO$	
AL17	Flow rate failure*7	FLT*1	AL17	$LOW \Rightarrow FLOW \Rightarrow FLT$	
AL18	High circulating fluid discharge temp.	FLT	AL18	$TEMP \Rightarrow FLT$	
AL19	High circulating fluid return temp.	FLT	AL19	$RET \Rightarrow TEMP \Rightarrow FLT$	

- *1 Selectable from OFF/WRN/FLT
 - · OFF: Disables the alarm function
 - WRN: Operation of this product will continue when the alarm occurs.
 FLT: Operation of this product will stop when the alarm occurs.
- *2 Selectable from WRN/FLT
- *3 Only air-cooled refrigeration type can be set.

A I = # ===		امتناما	Display unit		
Alarm code	Alarm message	Initial value	Upper section (White)	Lower section (Green)	
AL21	High circulating fluid discharge pressure	FLT	AL21	$HIGH \Rightarrow PRESS \Rightarrow FLT$	
AL22	Low circulating fluid discharge pressure	FLT	AL22	$LOW \Rightarrow PRESS \Rightarrow FLT$	
AL24	Memory abnormal	FLT	AL24	$MEM \Rightarrow ERROR$	
AL25	Contact input 1 signal detection	FLT*1	AL25	INP1 ⇒ ERROR	
AL26	Contact input 2 signal detection	FLT*1	AL26	INP2 ⇒ ERROR	
AL27	Forced stop	FLT	AL27	$FORCE \Rightarrow STOP$	
AL28	Maintenance notice	OFF*1	AL28	$MANT \Rightarrow ALARM$	
AL29	Communication error	WRN*1	AL29	COMM ⇒ ERROR	
AL30	Refrigerant circuit abnormal	FLT	AL30	$REF \Rightarrow ERROR \Rightarrow 0000$	
AL31	Sensor abnormal	FLT	AL31	$SENS \Rightarrow ERROR \Rightarrow 0000$	
AL32	Controller abnormal	FLT	AL32	$CTRL \Rightarrow ERROR \Rightarrow 0000$	

- *4 Option DM (With electric conductivity control function, Applicable to DI water piping) only. When entering the range, the alarm is released automatically.
 *5 Selectable from OFF/WRN
- *6 Not generated for Option Z
- *7 Not generated for Options Z and Z1



Communication Functions

For details, refer to the "Operation Manual" on the SMC website.


Contact Input/Output Communication Specifications

Item		Specifications		
	Insulation method	Photocoupler		
	Rated input voltage	24 VDC		
Contact input signal 1, 2	Operating voltage range	21.6 to 26.4 VDC	Run/Stop signal External switch signal	
	Rated input current	5 mA TYP		
	Input impedance	4.7 kΩ		
	Rated load voltage	48 VAC or less/30 VDC or less	· Run status signal	
Contact output signal 1, 2, 3	Maximum load current	500 mA AC/DC (Resistance load)	· Alarm status signal · Signal for completion of preparation	
	Minimum load current	5 VDC 10 mA	(TEMP READY), etc.	
24 VDC Output voltage		24 VDC ± 10 % 500 mA MAX*1 (No inductive load)		

^{*1} When using the power supply of this product, make sure that the total load current is 500 mA or less.

Contact Input/Output Pin Nos.

Pin no.	Application	Division	Initial value (Default setting)
1	1 24 VDC output 0 2 24 VDC output 0		_
2			_
3	24 VDC output	Output	_
4	Contact input signal 1	Input	OFF
5	Common of contact output signal 1	Output	_
6	Common of contact output signal 2	Output	_
7 Common of contact output signal 3		Output	_
8	 8 Unusable 9 24 COM output 10 24 COM output 		_
9			_
10			_
11	Common of contact input signal	Output	_
12	12 Contact input signal 213 Contact output signal 1		OFF
13			Run status signal (N.O. type)
14	Contact output signal 2	Output	Remote status signal (N.O. type)
15	Contact output signal 3	Output	Alarm signal (N.C. type)



Contact input/output signal connector

For details, refer to the "Operation Manual" on the SMC website.

Communication Functions


Serial Communication

The serial communication (RS-485/RS-232C) enables the following items to be written and read out.

Writing		Readout		_	
willing	11	Readout		1	
Run/Stop	H	Circulating fluid discharge temperature	Status information	į	
Circulating fluid temperature setting		Circulating fluid flow rate	Alarm occurrence information	-	
		Circulating fluid discharge pressure			
		Electric conductivity*1		¦ *1	When
! 	11	•		i	Option

*1 When using the Option DM

Item	Specifications					
Connector type	D-sub 9-pin female connector					
Standard	EIA standards, RS-485 (ASCII mode/RTU mode)					
Circuit diagram	Terminal resistance SD+ SD- SG SD+ SD- SG Terminal resistance 120 Ω Master This product (1st slave) * Be sure to wire to the correct pin numbers according to the diagram.					
Standard	EIA standards, RS-232C (ASCII mode/RTU mode)					
Circuit diagram	RD 2 SD 3 SD 5 SG 5 SG Master This product * Be sure to wire to the correct pin numbers according to the diagram.					



HRR Series Options

 Options have to be selected when ordering the thermo-chiller.
 It is not possible to add them after purchasing the unit.

Option symbol

With Electric Conductivity Control Function, Applicable to DI Water Piping

HRR _____ - DM

With electric conductivity control function, Applicable to DI water piping

By entering the set value of electric conductivity and hysteresis, flow of circulating fluid to the DI filter is controlled by the solenoid valve to control electric conductivity. Contact material of the circulating fluid circuit is made from non-copper materials. (For details, refer to Option M.)


Applicable model	HRR010/012/018/024/030/050-□□-□-DM
Measurement range of electric conductivity	0.1 to 48.0 μS/cm
Set range of target electric conductivity	0.5 to 45.0 μS/cm*1
Set range of electric conductivity hysteresis	0.1 to 10.0 μS/cm

*1 Default setting is set to "Electric conductivity set value: 25.0 μS/cm" and "Hysteresis: 5.0 μS/cm."

Example of operation of electric conductivity control

· Electric conductivity target value : 25.0 [μS/cm]

· Electric conductivity control hysteresis: 5.0 [μ S/cm]





Applicable to DI Water Piping

Applicable to DI water piping

Contact material of the circulating fluid circuit is made from non-copper materials.

- · Available DI water is electric conductivity: 0.4 μS/cm or more. (Electric resistivity: 2.5 MΩ·cm or less)
- · This Option M does not have electric resistance/electric conductivity control function. If this function is necessary, Option DM should be selected.

Applicable model	HRR010/012/018/024/030/050-□□-□-M
Contact material for circulating fluid	Stainless steel (including heat exchanger brazing), Alumina ceramic, SiC, Carbon, PP, PE, POM, PA, FKM, EPDM, PVC, PPS, AS

* No change in external dimensions





 Options have to be selected when ordering the thermo-chiller.
 It is not possible to add them after purchasing the unit.



Inverter Pump Mounted

HRR010-□□-20-<u>T1</u>

Inverter pump mounted

Possible to choose an inverter pump in accordance with user's piping resistance

Cooling capacity will decrease by heat generated in the pump.


- · The inverter pump does not use a mechanical seal.
- · The 50 Hz and the 60 Hz inverter pumps have the same capacity. (There is no pump capacity difference between the 50 Hz and the 60 Hz.)

Applicable model			HRR010-□□-20-T1	
	Rated flow (Same for both the 50 Hz and the 60 Hz)*1, 2	l/min	5 (0.35 MPa)	
Pump	Maximum pump head (Same for both the 50 Hz and the 60 Hz)	m	35	
	Output	W	400	
Circuit protector		Α	10	
Recommended earth leakage breaker capacity		Α	10	
Cooling capacity*3		Cooling capacity*3 W The cooling capacity reduces about 300 W from the value in the car (due to an increase in the heat generation of the pump)		

- *1 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *2 Required minimum flow rate for maintaining the cooling capacity or temperature stability
- *3 Cooling capacity will decrease as pump power increases.
- * When the option, inverter pump mounted, is selected, the product weight increases by 2 kg.
- * No change in external dimensions of this product

Pump Capacity

HRR010-A/W-20-T1





High-Pressure Pump Mounted

□□−□− T/MT

High-pressure pump mounted

Possible to choose a high-pressure pump in accordance with user's piping resistance

Cooling capacity will decrease by heat generated in the pump.

- The high-pressure pump uses a mechanical seal.
- · The thermo-chiller indicates maintenance notification when driving time is passed a recommended preventive maintenance hours.

Please contact to service centre to ask for maintenance of the pump and mechanical seal.


Applicable model			HRR012/018-□□-10-T/MT*1		HRR012/018/024/030-□-20-MT*1
	Rated flow (50/60 Hz)*2,3	l/min	7 (0.36 MPa)/10 (0.42 MPa)	10 (0.42 MPa)/14 (0.40 MPa)	10 (0.32 MPa)/14 (0.32 MPa)
Pump	Maximum pump head (50/60 Hz)	m	50	50	50
	Output	W	350	550	
Circuit protector		Α	15	15 (10 A for standard)	
Recommended earth leakage breaker capacity		Α	15		
Cooling capacity*4		W	The cooling capacity reduces about 300 W from the value in the catalog. (due to an increase in the heat generation of the pump)		

- *1 Option MT: Applicable to DI water piping + High-pressure pump mounted
- *2 The capacity at the thermo-chiller outlet when the circulating fluid temperature is 20 °C
- *3 Required minimum flow rate for maintaining the cooling capacity or temperature stability
- *4 Cooling capacity will decrease as pump power increases.


 * When the option, high-pressure pump mounted, is selected, the product weight increases by 5 kg.
- * No change in external dimensions of this product

Pump Capacity


HRR012/018-□□-10-T/MT



HRR012/018/024/030-□□-20-T




HRR012/018/024/030-□□-20-MT



HRR Series

 Options have to be selected when ordering the thermo-chiller.
 It is not possible to add them after purchasing the unit.





Air-cooled refrigeration	HRR
Water-cooled refrigeration	$HRR \square -W \square -\square -\square U \square \overline{Z/Z1}$
	• Removed parts

Standard product without the parts below

Z	Flow sensor, Water leakage sensor, Particle filter, Bypass valve, Retaining clip*1
Z 1	Flow sensor, Retaining clip*1


^{*1} Only for the HRR010 to 030

HRR Series Optional Accessories

1) Concentration Meter

This meter can be used to control the concentration of ethylene glycol aqueous solution regularly.


Part number	Applicable model
HRZ-BR002	HRR012/018-□□-10 HRR010/012/018/024/030/050-□□-20



2 Particle Filter Element for Replacement

Element for the maintenance of the particle filter for circulating fluid

Part number	Applicable model	
HRR-PF001 HRR010-□□-20		
EJ202S-005X11	HRR012/018-□□-10 HRR012/018/024/030-□□-20	
	HRR012/018/024/030-LL-20	
EJ302S-005X11	HRR050-□□-20	



3 DI Filter Replacement Cartridge

DI filter cartridge for replacement for Option DM [Electric conductivity control type, DI water piping type]

Part number	Applicable model	
HRR-DF001	HRR012/018-□□-10-DM□ HRR010/012/018/024/030-□□-20-DM□	
HRR-DF002	HRR050-□□-20-DM□	




195

4 Anti-quake Bracket

Bracket for earthquakes

Prepare the anchor bolts (M8) which are suited to the floor material by the customer. (Anti-quake bracket material: Stainless steel, thickness: 1.5 mm)

Part number	Description	Qty.	Applicable model
HRR-TK001	Anti-quake bracket A Anti-quake bracket B Nut (M8) Bolt (M8)	2 2 4 4	HRR010/012/018-□-□-□Y HRR024/030-□-□-□Y HRR050-□□-□-□Y






⑤ Piping Conversion Fitting (For Air-cooled Refrigeration)

■ Conversion fitting for circulating fluid + Conversion fitting for drain outlet

This fitting changes the port size for circulating fluid from Rc1/2 to G1/2 or NPT1/2, and for drain from Rc1/4 to G1/4 or NPT1/4. It is not necessary to purchase this when pipe thread type F or N is selected in "How to Order" since it is included in the product.

	Part number	Applicable model
HRR-EP001	G thread conversion fitting set	HRR012/018-A-10
HRR-EP002	NPT thread conversion fitting set	HRR010/012/018/024/030/050-A-20




6 Piping Conversion Fitting (For Water-cooled Refrigeration)

■ Conversion fitting for circulating fluid + Conversion fitting for drain outlet


This fitting changes the port size for circulating fluid from Rc1/2 to G1/2 or NPT1/2, and for drain from Rc1/4 to G1/4 or NPT1/4. It is not necessary to purchase this when pipe thread type F or N is selected in "How to Order" since it is included in the product.

Part number		Applicable model	
HRR-EP003	G thread conversion fitting set	HRR012/018-W-10	
HRR-EP004	NPT thread conversion fitting set	HRR010/012/018/024/030/050-W-20	



Power Supply Cable

Part number	Applicable model
HRR-CA001	HRR012/018-□□-10 HRR010/012/018/024/030-□□-20



8 Caster Adjuster-foot Kit


This is a set of unfixed casters and adjuster feet stop.


This kit can only be used for Option Y of the thermo-chiller HRR series.

Do not mount this kit on other products.


Carefully read the procedure manual included with this kit before performing the installation.


Part number	Applicable model	A dimension [mm]	Weight [kg]
	HRR010-□-20-□UY	330	
	HRR012/018-□-10-□UY	417	
HRR-KS001	HRR012/018-□-20-□Y	417	Approx 7
IIKK-KOUUI	HRR024/030-□-20-□Y	506	Approx. 7
	HRR050-A-20-□UY	815	
	HRR050-W-20-□UY	637	





Mounting view (HRR012/018-A-□)





Parts List

Description	Qty.
Caster adjuster-foot base	1
Anti-quake bracket A	2
Anti-quake bracket B	2
Hexagon nut (M8)	4
Hexagon bolt (M8)	8
Mounting procedure manual	1



HRR Series

Cooling Capacity Calculation

Required Cooling Capacity Calculation

Example 1: When the heat generation amount in the user's equipment is known.

The heat generation amount can be determined based on the power consumption or output of the heat generating area — i.e. the area requiring cooling — within the user's equipment.*1 I: Current

1 Derive the heat generation amount from the power consumption.

Power consumption P: 1000 [W]

Q = P = 1000 [W]

Cooling capacity = Considering a safety factor of 20 %,

1000 [W] x 1.2 = 1200 [W]

2 Derive the heat generation amount from the power supply output.

Power supply output VI: 1.0 [kVA]

 $Q = P = V \times I \times Power factor$

In this example, using a power factor of 0.85:

$$= 1.0 [kVA] \times 0.85 = 0.85 [kW] = 850 [W]$$

Cooling capacity = Considering a safety factor of 20 %,

850 [W] x 1.2 = 1020 [W]

3 Derive the heat generation amount from the output.

V. Power

supply voltage

P

consumption

Q: Heat generation

User's equipment

Output (shaft power, etc.) W: 800 [W]

$$Q = P = \frac{W}{Efficiency}$$

In this example, using an efficiency of 0.7:

$$=\frac{800}{0.7}=1143$$
 [W]

Cooling capacity = Considering a safety factor of 20 %,

Example of conventional units (Reference)

*1 The examples above calculate the heat generation amount based on the power consumption. The actual heat generation amount may differ due to the structure of the user's equipment. Be sure to check it carefully

Example 2: When the heat generation amount in the user's equipment is not known.

Obtain the temperature difference between inlet and outlet by circulating the circulating fluid inside the user's equipment.

Heat generation amount by user's equipment **Q**: Unknown [W] ([J/s]) Circulating fluid : Tap water*1 Circulating fluid mass flow rate qm : $(= \rho \times qv \div 60) [kg/s]$ Circulating fluid density p : 1 [kg/dm³] Circulating fluid (volume) flow rate qv : 10 [dm³/min] Circulating fluid specific heat C : 4.2 x 10³ [J/(kg·K)] Circulating fluid outlet temperature T1 : 293 [K] (20 [°C]) Circulating fluid return temperature T2 : 295 [K] (22 [°C]) Circulating fluid temperature difference ΔT : $2.0 [K] (= T_2 - T_1)$

Conversion factor: minutes to seconds (SI units): 60 [s/min]


*1 Refer to page 40 for the typical physical property value of tap water or other circulating fluids.

$$Q = q_m \times C \times (T_2 - T_1)$$

$$= \frac{\rho \times q_{V} \times C \times \Delta T}{60} = \frac{1 \times 10 \times 4.2 \times 10^{3} \times 2.0}{60}$$

= 1400 [J/s] ≈ 1400 [W]

Cooling capacity = Considering a safety factor of 20 %,



^{*} Calculation example for the temperature and flow rate based on customer's piping condition For calculating the required cooling capacity based on the displayed value of temperature and flow rate in the chiller, fully close the bypass valve.

Required Cooling Capacity Calculation

Example 3: When there is no heat generation, and when cooling the object below a certain temperature and period of time.

Heat quantity by cooled substance (per unit time) Q: Unknown [W] ([J/s])

Cooled substance : Water

Cooled substance mass \mathbf{m} : $(= \rho \times \mathbf{V})$ [kg]

Cooled substance density ρ : 1 [kg/dm³]

Cooled substance total volume \mathbf{V} : 20 [dm³]


Cooled substance specific heat **C** : 4.2 x 10³ [J/(kg·K)] Cooled substance temperature when cooling begins **To**: 305 [K] (32 [°C])

Cooled substance temperature when cooling begins 10: 305 [K] (32 [C]) Cooled substance temperature after t hour T_t : 293 [K] (20 [°C]) Cooling temperature difference ΔT : 12 [K] (= $T_0 - T_t$) Cooling time Δt : 900 [s] (= 15 [min])

* Refer to the following for the typical physical property values by circulating fluid.

$$Q = \frac{m \times C \times (T_0 - T_t)}{\Delta t} = \frac{\rho \times V \times C \times \Delta T}{\Delta t}$$
$$= \frac{1 \times 20 \times 4.2 \times 10^3 \times 12}{900} = 1120 \text{ [J/s]} \approx 1120 \text{ [W]}$$

Cooling capacity = Considering a safety factor of 20 %,



Example of conventional units (Reference)

Heat quantity by cooled substance (per unit time) \mathbf{Q} : Unknown [cal/h] \rightarrow [W]

Cooled substance specific heat **C** : 1.0 x 10³ [cal/(kgf· °C)]

Cooled substance temperature when

cooling begins T_0 : 32 [°C] Cooled substance temperature after t hour T_t : 20 [°C]

Cooling temperature difference ΔT : 12 [°C] (= $T_0 - T_t$)

Cooling time Δt : 15 [min] Conversion factor: hours to minutes : 60 [min/h] Conversion factor: kcal/h to kW : 860 [(cal/h)/W]

$$Q = \frac{m \times C \times (T_0 - T_t)}{\Delta t \times 860} = \frac{\gamma \times V \times 60 \times C \times \Delta T}{\Delta t \times 860}$$

$$= \frac{1 \times 20 \times 60 \times 1.0 \times 10^{3} \times 12}{15 \times 860}$$

$$\approx 1120 \text{ [W]}$$

Cooling capacity = Considering a safety factor of 20 %,

1120 [W] x 1.2 = 1344 [W]

Precautions on Cooling Capacity Calculation

1. Heating capacity

When the circulating fluid temperature is set above room temperature, it needs to be heated by the thermo-chiller. The heating capacity depends on the circulating fluid temperature. Consider the radiation rate and heat capacity of the user's equipment and check beforehand if the required heating capacity is provided.

2. Pump capacity

<Circulating fluid flow rate>

Circulating fluid flow rate varies depending on the circulating fluid discharge pressure. Consider the installation height difference between the thermo-chiller and the user's equipment, and the piping resistance such as circulating fluid pipings, or piping size, or piping curves in the machine. Check beforehand if the required flow is achieved, using the pump capacity curves.

<Circulating fluid discharge pressure>

Circulating fluid discharge pressure has the possibility to increase up to the maximum pressure in the pump capacity curves. Check beforehand if the circulating fluid pipings or circulating fluid circuit of the user's equipment are fully durable against this pressure.

Circulating Fluid Typical Physical Property Values

1. This catalog uses the following values for density and specific heat in calculating the required cooling capacity.

Density Specific heat ρ : 1 [kg/dm³] (or, using conventional units, weight volume ratio $\gamma = 1$ [kg//L]) Specific heat ρ : 4.19 x 10³ [J/(kg·K)] (or, using conventional units, 1 x 10³ [cal/(kg·°C)])

2. Values for density and specific heat change slightly according to temperature shown below. Use this as a reference. Water 15 % Ethylene Glycol Aqueous Solution

Physical property value	Density ρ	Specific heat C	Conventional units	
Temperature	[kg/dm ³]	[J/(kg·K)]	Weight volume ratio γ [kgf/L]	Specific heat C [cal/(kgf- °C)]
5°C	1.00	4.2×10^3	1.00	1 x 10 ³
10 °C	1.00	4.19 x 10 ³	1.00	1 x 10 ³
15 °C	1.00	4.19 x 10 ³	1.00	1 x 10 ³
20 °C	1.00	4.18 x 10 ³	1.00	1 x 10 ³
25 °C	1.00	4.18 x 10 ³	1.00	1 x 10 ³
30 °C	1.00	4.18 x 10 ³	1.00	1 x 10 ³
35 °C	0.99	4.18 x 10 ³	0.99	1 x 10 ³
40 °C	0.99	4.18 x 10 ³	0.99	1 x 10 ³

,				
Physical property value	Density ρ	Specific heat C	C Conventional units	
Temperature	[kg/dm ³]	[J/(kg·K)]	Weight volume ratio γ [kgf/L]	Specific heat C [cal/(kgf- °C)]
5 °C	1.02	3.91 x 10 ³	1.02	0.93 x 10 ³
10 °C	1.02	3.91 x 10 ³	1.02	0.93 x 10 ³
15 °C	1.02	3.91 x 10 ³	1.02	0.93 x 10 ³
20 °C	1.01	3.91 x 10 ³	1.01	0.93 x 10 ³
25 °C	1.01	3.91 x 10 ³	1.01	0.93 x 10 ³
30 °C	1.01	3.91 x 10 ³	1.01	0.94 x 10 ³
35 °C	1.01	3.91 x 10 ³	1.01	0.94 x 10 ³
40 °C	1.01	3.92 x 10 ³	1.01	0.94 x 10 ³

Shown above are reference values. Contact circulating fluid supplier for details.



^{*} This is the calculated value by changing the fluid temperature only. Thus, it varies substantially depending on the water bath or piping shape.



Be sure to read this before handling the products. Refer to the back cover for safety instructions. For temperature control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

Design

<u> Marning</u>

- 1. This catalog shows the specifications of a single unit.
 - Check the specifications of the single unit (contents of this catalog) and thoroughly consider the adaptability between the user's system and this unit.
 - 2) Although a protection circuit as a single unit is installed, prepare a drain pan, water leakage sensor, discharge air facility, and emergency stop equipment, depending on the user's operating conditions. Also, the user is requested to carry out a safety design for the whole system.
- When attempting to cool areas that are open to the atmosphere (tanks, pipes), plan your piping system accordingly.

When cooling open-air external tanks, arrange the piping so that there are coil pipes for cooling inside the tanks and to carry back the entire flow volume of circulating fluid that is released.

Use non-corrosive material for circulating fluid contact parts.

The recommended circulating fluid is tap water or 15 % ethylene glycol aqueous solution. Using corrosive materials such as aluminium or iron for fluid contact parts such as piping may cause clogging or leakage in the circulating fluid circuit. Therefore, take sufficient care when selecting fluid contact part materials such as piping.

4. Design the piping so that no foreign matter enters the chiller.

If foreign matter, such as scales in the piping, enters the circulating fluid, this may cause the pump to malfunction.

Selection

Marning

1. Model selection

When selecting a thermo-chiller model, the amount of heat generation from the user's equipment must be known. Obtain this value, referring to "Cooling Capacity Calculation" on pages 39 and 40 before selecting a model.

Handling

1. Thoroughly read the operation manual.

Read the operation manual completely before operation. Also, keep the manual where it can be referred to as necessary.

Transportation / Carriage / Movement

Marning


- 1. This product is heavy. Pay attention to safety and the position of the product when it is transported, carried, and moved.
- Read the operation manual carefully before moving the product after unpacking.

Transportation / Carriage / Movement

⚠ Caution

1. Never put the product down on its side as this may cause failure.

The product will be delivered in the packaging shown below.



Model	Weight [kg]*1	Dimensions [mm]
HRR010-A	43	Height 485 x Width 610 x Depth 820
HRR010-W	41	Height 465 x Width 610 x Depth 620
HRR012-A HRR018-A	54	Height 575 x Width 610 x Depth 820
HRR012-W HRR018-W	55	neight 373 x width 610 x Depth 620
HRR024-A HRR030-A	61	Height 665 x Width 610 x Depth 820
HRR024-W HRR030-W	60	rieigiit oos x widii i i i x Deptii ozu
HRR050-A	91	Height 975 x Width 610 x Depth 820
HRR050-W	80	Height 800 x Width 610 x Depth 820

*1 For models with an option, the weight increases as shown below

Option	Description	Additional weight
-DM	With electric conductivity control function, Applicable to DI water piping	+1 kg
-M	Applicable to DI water piping	Not changed
-T1	Inverter pump mounted	+2 kg
-T	High-pressure pump mounted	+5 kg
-U	Compliant with UL Standards	Not changed
-Y	With feet/Without rack mounting brackets	Not changed
-Z	Without either a flow sensor, water leakage sensor, particle filter, bypass valve or retaining clip	
-Z1	Without either a flow sensor or retaining clip	Not changed

^{*2} Excludes the HRR010. For the HRR050: -2 kg

If this product is to be transported after delivery, please use the original packaging the product was delivered in. If other packaging is to be used, carefully package the product so as to prevent the product from incurring any damage during transport.





Be sure to read this before handling the products. Refer to the back cover for safety instructions. For temperature control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

Operating Environment / Storage Environment

Marning

- 1. Do not use in the following environment as it will lead to a breakdown.
 - 1) Outdoors
 - In locations where water, water vapour, salt water, and oil may splash on the product
 - 3) In locations where there are dust and particles
 - In locations where corrosive gases, organic solvents, chemical fluids, or flammable gases are present (This product is not explosion proof.)
 - 5) In locations where the ambient temperature exceeds the limits as mentioned below

During transportation/storage: 0 to 50 °C (But as long as water or circulating fluid are not left inside the pipings)

During operation: 5 to 40 °C

6) In locations where the ambient humidity is out of the following range or where condensation occurs

During transportation/storage: 15 to 85 % During operation: 30 to 70 %

- 7) In locations which receive direct sunlight or radiated heat
- 8) In locations where there is a heat source nearby and the ventilation is poor
- 9) In locations where temperature substantially changes
- In locations where strong magnetic noise occurs (In locations where strong electric fields, strong magnetic fields, and surge voltage occur)
- 11) In locations where static electricity occurs, or conditions which make the product discharge static electricity
- 12) In locations where high frequency occurs
- 13) In locations where damage is likely to occur due to lightning
- 14) In locations at an altitude of 3000 m or higher (Excluding: storage and transportation)
 - * For altitudes of 1000 m or higher Because of lower air density, the heat radiation efficiencies of the devices in the product will be lower in the location at an altitude of 1000 m or higher. Therefore, the maximum ambient temperature to use and the cooling capacity will lower according to the descriptions in the table below.
 - Select the thermo-chiller considering the descriptions.
 - ① Upper limit of ambient temperature: Use the product in ambient temperature of the described value or lower at each altitude.
 - ② Cooling capacity coefficient: The product's cooling capacity will lower to one that multiplied by the described value at each altitude.

	①Upper limit of ambient temperature [°C]	② Cooling	
Altitude [m]	40 °C products	capacity coefficient	
Less than 1000 m	40	1.00	
Less than 1500 m	38	0.85	
Less than 2000 m	36	0.80	
Less than 2500 m	34	0.75	
Less than 3000 m	32	0.70	

- 15) In locations where strong impacts or vibrations occur
- 16) In locations where a massive force strong enough to deform the product is applied or the weight from a heavy object is applied
- In locations where there is not sufficient space for maintenance

2. Install in an environment where the unit will not come into direct contact with rain or snow.

These models are for indoor use only.

Do not install outdoors where rain or snow may fall on them.

3. Conduct ventilation and cooling to discharge heat. (Air-cooled refrigeration)

The heat which is cooled down through air-cooled condenser is discharged.

When using in a room which is shut tightly, ambient temperature will exceed the specification range stipulated in this catalog, which will activate the safety detector and stop the operation. In order to avoid this situation, discharge the heat outside of a room by ventilation or cooling facilities.

4. The product is not designed for clean room usage. It generates particles internally.





Be sure to read this before handling the products. Refer to the back cover for safety instructions. For temperature control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

Mounting / Installation

⚠ Warning

- 1. Do not use the product outdoors.
- Do not place heavy objects on top of this product, or step on it.


The external panel can be deformed and danger can result.

∧ Caution

- 1. Make sure that the rack and the rack rail can support the weight of the product.
- 2. Refer to the operation manual for this product, and secure an installation space that is necessary for the maintenance and ventilation.

<Air-cooled refrigeration>

- 1. The air-cooled type product exhausts heat using the fan that is mounted to the product. If the product is operated with insufficient ventilation, ambient temperature may exceed 40 °C, and this will affect the performance and life of the product. To prevent this ensure that suitable ventilation is available (see below).
- 2. For installation indoors, ventilation ports and a ventilation fan should be equipped as needed.



<Heat radiation amount/Required ventilation rate>

	Heat radiation	Required ventilation rate [m ³ /min]		
Model	amount [kW]	Differential temp. of 3 °C between inside and outside of installation area	Differential temp. of 6 °C between inside and outside of installation area	
HRR010-A	Approx. 2	40	20	
HRR012-A	Approx. 2	40	20	
HRR018-A	Approx. 4	70	40	
HRR024-A	Approx. 5	90	50	
HRR030-A	Approx. 6	100	60	
HRR050-A	Approx. 10	140	70	

Piping

⚠ Caution

1. Regarding the circulating fluid pipings, consider carefully the suitability for shutoff pressure, temperature and circulating fluid.

If the operating performance is not sufficient, the pipings may burst during operation. Also, using corrosive materials such as aluminium or iron for fluid contact parts such as piping may cause clogging or leakage in the circulating fluid and facility water circuits. Provide protection against corrosion when you use the product.

Select the piping port size which can exceed the rated flow.

For the rated flow, refer to the pump capacity table.

- 3. When tightening at the circulating fluid inlet and outlet, drain port or overflow port of this product, use a pipe wrench to clamp the connection ports.
- 4. This product series are constant-temperature fluid circulating machines with built-in tanks.

Do not install equipment on your system side such as pumps that forcibly return the circulating fluid to the unit. Also, if you attach an external tank that is open to the air, it may become impossible to circulate the circulating fluid. Proceed with caution.

Electrical Wiring


Marning

 Grounding should never be connected to a water line, gas line or lightning rod.

∧ Caution

- Communication cable should be prepared by the customer.
- 2. Provide a stable power supply which is not affected by surge or distortion.

If the voltage increase ratio (dV/dt) at the zero cross should exceed 40 V/200 $\mu sec.,$ it may result in malfunction.





Be sure to read this before handling the products. Refer to the back cover for safety instructions. For temperature control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

Circulating Fluid

- 1. Avoid oil or other foreign matter entering the circulating fluid.
- 2. When water is used as a circulating fluid, use tap water that conforms to the appropriate water quality standards. Use tap water that conforms to the standards shown below (including water used for dilution of ethylene glycol aqueous solution).

Tap Water (as a Circulating Fluid) Quality Standards

The Japan Refrigeration and Air Conditioning Industry Association JRA GL-02-1994 "Cooling water system – Circulation type – Make-up water"

				Influ	ence
	Item	Unit	Unit Standard value		Scale generation
	pH (at 25 °C)	_	6.0 to 8.0	0	0
_	Electric conductivity (25 °C)	[µS/cm]	100*1 to 300*1	0	0
te	Chloride ion (CI ⁻)	[mg/L]	50 or less	0	
Standard item	Sulfuric acid ion (SO ₄ ²⁻)	[mg/L]	50 or less	0	
g	Acid consumption amount (at pH4.8)	[mg/L]	50 or less		0
tar	Total hardness	[mg/L]	70 or less		0
0)	Calcium hardness (CaCO ₃)	[mg/L]	50 or less		0
	Ionic state silica (SiO ₂)	[mg/L]	30 or less		0
٦	Iron (Fe)	[mg/L]	0.3 or less	0	0
<u>=</u>	Copper (Cu)	[mg/L]	0.1 or less	0	
Se	Sulfide ion (S ₂ -)	[mg/L]	Should not be detected	0	
Reference item	Ammonium ion (NH ₄ +)	[mg/L]	0.1 or less	0	
efe	Residual chlorine (CI)	[mg/L]	0.3 or less	0	
2	Free carbon (CO ₂)	[mg/L]	4.0 or less	0	

- *1 In the case of [M Ω ·cm], it will be 0.003 to 0.01.
- O: Factors that have an effect on corrosion or scale generation
- Even if the water quality standards are met, complete prevention of corrosion is not guaranteed.
- Use an ethylene glycol aqueous solution that does not contain additives such as preservatives.
- 4. When using ethylene glycol aqueous solution, maintain a maximum concentration of 15 %.

Overly high concentrations can cause a pump overload. Low concentrations, however, can lead to freezing when circulating fluid temperature is 10 °C or lower and cause the thermo-chiller to break down.

5. A magnet pump or mechanical seal pump is used as the circulating pump for the circulating fluid.

It is particularly impossible to use liquid including metallic powder such as iron powder.

The circulating fluids listed below have been tested for thermo-chiller compatibility. (Excludes the HRR010)

No.	Fluid	Manufacturer	Concentration
1	Dowcal™ 100 Heat	The Dow Chemical	Dilute to 30 % in
'	Transfer Fluid	Company	water
2	ControXid 1642	Oelheld GmbH	Ready to use
3	Hexid A4	Applied Thermal Control Limited	Ready to use
4	Coolflow IGE	Hydratech Division of Liquitherm Technologies Group Ltd	Dilute to 25 % in water
5	NALCO® CCL105	Nalco Water, an Ecolab Company	Ready to use

- The chiller cooling capacity and pump capacity performance may change with using the fluids listed. Customers should verify the performances with the fluid and decide to use the fluid.
- Check the compatibility with the piping and the wetted parts of the customer's equipment before use.
- Check with the circulating fluid manufacturer for the following.
 1) Countries and regions where it can be obtained and used 3) Safety data sheets
- 2) Handling and maintenance 4) Specifications and physical properties
- Concentration has to be value listed or less. Overly high concentrations can cause a
 pump overload. Low concentrations, however, can lead to freezing when circulating
 fluid temperature is 10 °C or lower and cause the thermo-chiller to break down.
- Using the fluid listed for a long time, the chiller heat exchanger performance may be reduced due to
 additive deposits. It is recommended to regularly flush the inside of the piping and chiller with clean water.
- In the case of a mechanical seal pump, additive deposits may appear on the outside, it is not a malfunction.

Facility Water Supply

Marning

<Water-cooled refrigeration>

- The water-cooled refrigeration type thermo-chiller radiates heat to the facility water.
 Prepare the facility water system that satisfies the heat radiation and the facility water specifications
- Required facility water system

<Heat radiation amount/Facility water specifications>

Model	Heat radiation [kW]	Facility water specifications
HRR010-W	Approx. 2	
HRR012-W	Approx. 2	5 ()
HRR018-W	Approx. 4	Refer to
HRR024-W	Approx. 5	"Facility water system" in the specifications.
HRR030-W	Approx. 6	in the specifications.
HRR050-W	Approx. 10	

2. When using tap water as facility water, use tap water that conforms to the appropriate water quality standards.

Use tap water that conforms to the standards shown below.

<Tap Water (as Facility Water) Quality Standards>

The Japan Refrigeration and Air Conditioning Industry Association JRA GL-02-1994 "Cooling water system – Circulation type – Circulating water"

	lá a na	Unit	Chamble and violes	Influ	ence
	Item	Unit	Standard value	Corrosion	Scale generation
	pH (at 25 °C)	_	6.5 to 8.2	0	0
	Electric conductivity (25 °C)	[µS/cm]	100*1 to 800*1	0	0
item	Chloride ion (Cl-)	[mg/L]	200 or less	0	
	Sulfuric acid ion (SO ₄ ²⁻)	[mg/L]	200 or less	0	
Standard	Acid consumption amount (at pH4.8)	[mg/L]	100 or less		0
Sta	Total hardness	[mg/L]	200 or less		0
	Calcium hardness (CaCO ₃)	[mg/L]	150 or less		0
	Ionic state silica (SiO ₂)	[mg/L]	50 or less		0
_	Iron (Fe)	[mg/L]	1.0 or less	0	0
item	Copper (Cu)	[mg/L]	0.3 or less	0	
Se	Sulfide ion (S ₂ -)	[mg/L]	Should not be detected	0	
rer	Ammonium ion (NH ₄ +)	[mg/L]	1.0 or less	0	
Reference	Residual chlorine (CI)	[mg/L]	0.3 or less	0	
Ľ	Free carbon (CO ₂)	[mg/L]	4.0 or less	0	

- *1 In the case of [M Ω ·cm], it will be 0.001 to 0.01.
- O: Factors that have an effect on corrosion or scale generation
- Even if the water quality standards are met, complete prevention of corrosion is not guaranteed.
- 3. Supply pressure of 0.5 MPa or less.

If the supply pressure is high, it will cause water leakage.

4. Be sure to prepare your utilities so that the pressure of the thermo-chiller facility water outlet is at 0 MPa (atmospheric pressure) or more.

If the facility water outlet pressure becomes negative, the internal facility water piping may collapse, and proper flow control of facility water will be impossible.

Using deionized water as facility water may cause problems such as clogging in the piping due to metal ion.

5. Do not use fluid that includes metallic powders and other foreign materials.

It can cause issues: clogging of the circulating fluid circuit or leakage.





Be sure to read this before handling the products. Refer to the back cover for safety instructions. For temperature control equipment precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

Operation

⚠ Warning

1. Confirmation before operation

 The fluid level of a tank should be within the specified range of "HIGH" and "LOW."

When exceeding the specified level, the circulating fluid will overflow.

2) Remove the air.

Conduct a trial operation, looking at the fluid level. Since the fluid level will go down when the air is removed from the user's piping system, supply water once again when the fluid level is reduced. When there is no reduction in the fluid level, the job of removing the air is completed.

2. Confirmation during operation

· Check the circulating fluid temperature.

The operating temperature range of the circulating fluid is between 5 and 35 °C.

When the amount of heat generated from the user's equipment is greater than the product's capability, the circulating fluid temperature may exceed this range. Use caution regarding this matter.

3. Emergency stop method

When an abnormality is confirmed, stop the machine immediately. When operation is stopped by the RUN/STOP key, turn off the power switch.

Operation Restart Time/Operation and Suspension Frequency

- 1. Wait five minutes or more before restarting operation after it has been stopped. If the operation is restarted within five minutes, the protection circuit may activate and the operation may not start properly.
- 2. Operation and suspension frequency should not exceed 10 times per day. Frequently switching between operation and suspension may result in the malfunction of the refrigeration circuit.

Protection Circuit

- 1. If operating in the conditions below, the protection circuit will activate and an operation may not be performed or will stop.
 - Power supply voltage is not within the rated voltage range of \pm 10 %.
 - In case the water level inside the tank is reduced abnormally.
 - · Circulating fluid temperature is too high.
 - Compared to the cooling capacity, the heat generation amount of the user's equipment is too high.
 - Ambient temperature is too high. (40 °C or more)
 - · Refrigerant pressure is too high.
 - · Ventilation grille is clogged with dust or dirt.

Maintenance

<Periodical inspection every one month>

1. Clean the ventilation grille.

If the dustproof filter becomes clogged with dust or debris, a decline in cooling performance can result.

In order to avoid deforming or damaging the dustproof filter, clean it with a long-haired brush or air gun.

<Periodical inspection every three months>

- 1. Inspect the circulating fluid.
 - 1) When using tap water
 - Replacement of tap water

Failure to replace the tap water can lead to the development of bacteria or algae. Replace it regularly depending on your usage conditions.

2) When using ethylene glycol aqueous solution

Use a concentration meter to confirm that the concentration does not exceed 15 %.

Dilute or add as needed to adjust the concentration.

<Periodical inspection during the winter season>

1. Make water-removal arrangements beforehand.

If there is a risk of the circulating fluid freezing when the product is stopped, release the circulating fluid in advance.

2. Consult a professional.

For additional methods to prevent freezing (such as commercially available tape heaters, etc.), consult a professional for advice.

■ Refrigerant with GWP reference

	Global warming pote	ential (GWP)
Refrigerant	Regulation (EU) No 517/2014 (Based on the IPCC AR4)	Revised Fluorocarbons Recovery and Destruction Law (Japanese law)
R134a	1,430	1,430
R404A	3,922	3,920
R407C	1,774	1,770
R410A	2,088	2,090

- * This product is hermetically sealed and contains fluorinated greenhouse gases (HFC). When this product is sold on the market in the EU after January 1, 2017, it needs to be compliant with the quota system of the F-Gas Regulation in the EU.
- See specification table for refrigerant used in the product.



△ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of **"Caution," "Warning"** or **"Danger."** They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) ¹⁾, and other safety regulations.

Caution: which, if

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate

injury.

Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious

njury.

⚠ Danger:

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious

njury.

ISO 4414: Pneumatic fluid power – General rules relating to systems.
 ISO 4413: Hydraulic fluid power – General rules relating to systems.
 IEC 60204-1: Safety of machinery – Electrical equipment of machines.
 (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety. etc.

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions
 - Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
 - 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
 - 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

∧ Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first. ²⁾ Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

⚠ Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country.

Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

Revision History Edition B - Single-phase 100 VAC (50/60 Hz) and 110 VAC (60 Hz) QS power supplies have been added. - The circulating fluid temperature, flow rate, and electric conductivity setting/display range have been expanded. - Number of pages has been increased from 32 to 36. Edition C - The HRR010 (air-cooled type, water-cooled type) has XU been added. - Number of pages has been increased from 36 to 44. **Edition D** - The HRR050 (air-cooled type, water-cooled type) has been added. - A caster adjuster-foot kit has been added as an optional accessory. - Number of pages has been increased from 44 to 48.



SMC Corporation (Europe)

		. ,	
Austria	+43 (0)2262622800	www.smc.at	office@smc.at
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	office@smc.bg
Croatia	+385 (0)13707288	www.smc.hr	office@smc.hr
Czech Republic	+420 541424611	www.smc.cz	office@smc.cz
Denmark	+45 70252900	www.smcdk.com	smc@smcdk.com
Estonia	+372 6510370	www.smcpneumatics.ee	info@smcee.ee
Finland	+358 207513513	www.smc.fi	smcfi@smc.fi
France	+33 (0)164761000	www.smc-france.fr	info@smc-france.fr
Germany	+49 (0)61034020	www.smc.de	info@smc.de
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office@smc.hu
Ireland	+353 (0)14039000	www.smcautomation.ie	sales@smcautomation.ie
Italy	+39 03990691	www.smcitalia.it	mailbox@smcitalia.it
Latvia	+371 67817700	www.smc.lv	info@smc.lv

Lithuania	+370 5 2308118	www.smclt.lt	info@smclt.lt
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post@smc-norge.no
Poland	+48 222119600	www.smc.pl	office@smc.pl
Portugal	+351 214724500	www.smc.eu	apoioclientept@smc.smces.es
Romania	+40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Russia	+7 8123036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	office@smc.sk
Slovenia	+386 (0)73885412	www.smc.si	office@smc.si
Spain	+34 945184100	www.smc.eu	post@smc.smces.es
Sweden	+46 (0)86031200	www.smc.nu	smc@smc.nu
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter@smc.ch
Turkey	+90 212 489 0 440	www.smcpnomatik.com.tr	info@smcpnomatik.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales@smc.uk