




Blow Nozzles



CONTENTS

Nozzle Selection Chart	p. 1
Nozzle Variations	p. 3
Applications	p. 6
Jet Shape and Impact Pressure Distribution Diagram	p. 7
Nozzles for Blowing KN Series	p. 9
Equipment for Blowing	p. 14

Technical Data: Comparison Table (Thrust, Noise, Flow consumption, Air flow)	p. 16
Model Selection: Recommended Circuit Configuration for Blowing...	p. 18
Glossary of Terms	p. 20
Safety Instructions.....	Back cover

What is the purpose of blowing?


Removal of foreign matter

Yes


Foreign matter type

① Small foreign matter
(Dust, Cutting chips, etc.)


② Machining chips, oil, etc. after cutting




③ Water droplets, etc. after cleaning



Removal of foreign matter across a wide area



Twin Nozzle



KQ2LU, KQ2U
+ KN-Q□A

Pivoting Nozzle




KNK Series

Fine adjustment of blowing
direction and nozzle position

Yes


Bar Type



KQ2VF + KN-Q□A



The applications described here are for reference only. For actual usage in various other applications, please conduct thorough evaluation and validation testing in order to determine the feasibility under your actual usage conditions.




⚠ Caution The applications described here are for reference only. For actual usage in various other applications, please conduct thorough evaluation and validation testing in order to determine the feasibility under your actual usage conditions.

Nozzle Variations

High-pressure blow with minimal pressure loss

Mono-porous Nozzle


KN Series



- Pressure loss is significantly reduced and increasing efficiency by implementing a design that uses a large conductance until just before the nozzle outlet.
- This enables a high-pressure blow with minimal pressure loss.
- Connection type: Self-align fitting, Male thread
- Nozzle cover (p. 12)

Nozzle diameter	Self-align fitting	Ø 1, Ø 1.5, Ø 2, Ø 2.5, Ø 3, Ø 3.5, Ø 4, Ø 6
	Male thread	Ø 1, Ø 1.5, Ø 2, Ø 2.5, Ø 4, Ø 6, Ø 8

Blow example



Flow rate can be adjusted at the most downstream side of the blow process.

Nozzle with flow rate adjustment function



KNC Series



- Nozzle with male thread - Flow rate can be adjusted to Ø 2.0 equivalent or less.

Nozzle diameter	Ø 2.6
-----------------	-------

Blow example



Nozzle length: 300 mm, 600 mm

Copper Extension Nozzle


KNL Series



- Secluded and difficult to reach areas
- Blowing at high places, etc.
- With fitting (p. 10)
- Nozzle cover (p. 12)

Nozzle diameter	Ø 1.5, Ø 2, Ø 2.5, Ø 3
-----------------	------------------------


Blow example



Fine adjustment of blow

Pivoting Nozzle


KNK Series



- The pivoting construction of the tip enables fine adjustment of the nozzle direction after setting.
- Connection type: Self-align fitting, Male thread

Nozzle diameter	Ø 4, Ø 6
-----------------	----------

Blow example



Nozzle Variations

Adjustable layout to match application

Nozzle for One-touch Fitting/Resin Type KN-Q□A




- Nozzle that fit One-touch fittings can be used to setup different blow system layouts.
- Uses highly efficient single hole nozzle to ensure high impact pressure.
- The nozzle diameter can be selected to change the impact pressure on the workpiece.
- This combination variation allows a significant reduction of air consumption by blowing an area wider than a comb-shaped nozzle.

Nozzle diameter Ø 1, Ø 1.5, Ø 2, Ø 2.5, Ø 3

Applicable One-touch fitting size Ø 6, Ø 8, Ø 10, Ø 12

Mounting examples * The nozzle size can be changed.




“Twin Nozzle”

Jet shape



Nozzle for One-touch fitting/
Resin type

KN-Q□A




“Triple Nozzle”

Jet shape



Nozzle for One-touch
fitting/Resin type

KN-Q□A



“High-thrust Type”


Jet shape



Nozzle for One-touch
fitting/Resin type

KN-Q□A

Double branch “Y”
KQ2UD



“Water-resistant Type”


Jet shape



Fitting: Stainless steel 316, Nozzle: POM

Nozzle for One-touch
fitting/Resin type

KN-Q□A



* Stainless steel products are available for heat resistance and anti-corrosion properties. Please contact SMC for further details.


“Bar Type Nozzle”

Jet shape



Nozzle for One-touch fitting/
Resin type

KN-Q□A









5





The use of fittings not manufactured by SMC is extremely dangerous since the nozzle for One-touch fitting may be released with no warning. Make sure to purchase the One-touch fitting KQ2 series by SMC and use it in combination with the nozzle. For details on fittings, refer to the **Web Catalogue**.



Applications

Nozzles for Blowing

Work process	Application example	Main series
Bottle cleaning	 High-pressure blow with minimal pressure loss Adjustable layout to match application	KN-Q□A 
Blowing water droplets off engine blocks	 High-pressure blow with minimal pressure loss Adjustable layout to match application Fine adjustment of blow	KN KNK KN-Q□A 
Water droplet removal		KNK 

Work process	Application example	Main series
Cooling during machining		KN 
Blowing for deburring after machining		KN 



Caution

The applications described here are for reference only. For actual usage in various other applications, please conduct thorough evaluation and validation testing in order to determine the feasibility under your actual usage conditions.

Jet Shape and Impact Pressure Distribution Diagram



Nozzle with Self-align Fitting KN Series Copper Extension Nozzle KNL Series

- Standard blow nozzle
- Highly effective with low pressure loss
- A wide variety of nozzle diameters are available for selection.
- Can be used with One-touch fittings, copper piping, and other applications in addition to mounting on male and female threads





High Efficiency Nozzle KNH Series

- Entraines the surrounding air and increases the blow flow rate
- Blow thrust improved by 10 %
- OSHA Standards compliant product (Operate at 0.5 MPa or less.)



Branch Male Elbow + Nozzle for One-touch Fitting/Resin Type KQ2LU + KN-Q□A (2 pcs.)



- A type with two nozzles (resin type) for One-touch fitting inserted in a branch elbow
- Can be used for blowing a wide area
- Provides high impact pressure and a jet shape similar to a general comb-shaped nozzle
- Low air consumption (Compared to a comb-shaped nozzle)



Jet Shape and Impact Pressure Distribution Diagram



One-touch Fittings Manifold + Nozzle for One-touch Fitting/ Resin Type KM13 + KN-Q□A (3 pcs.)

- Nozzle for One-touch fittings / resin type One-touch fittings manifold docking stations
- Optimum for blowing water, or other fluids off, a wide area
- For impact pressure and blowing area greater than a general comb-shaped nozzle!



Low Noise Nozzle with Self-align Fitting KNS Series

- Designed to blow with 4 to 8 nozzles and high noise reduction. Can be used for a smaller area



Nozzles for Blowing

KN Series

RoHS

Specifications

Nozzle (KN, KNK, KNH, KNS, KNL)

Applicable tubing material	Nylon, Soft nylon, Flexible copper pipe (C1220T-O), OST pipe	
Applicable tubing O.D.	Ø 4, Ø 6, Ø 8, Ø 10, Ø 12, Ø 16, Ø 20	
Fluid	Air, Coolant*1	
Max. operating pressure	1 MPa (0.3 MPa with OST pipe)	
Ambient and fluid temperatures	-5 to 60 °C (No freezing)	
Threads	Mounting	JIS B 0203 (Taper threads for piping)
	Nut	JIS B 0205 (Metric fine thread)
Seal on the threads	None	
Copper-free (Standard)	Brass parts are all electroless nickel plated.	

*1 Excludes the KNS and KN-Q□A

Principal Parts Material

KN, KNK, KNH, KNS

Body, Nut	C3604
Sleeve (Self-align fitting type)	C2700
Nozzle (Pivoting type)	Stainless steel 303

KN-Q□A

Nozzle	POM
--------	-----

KNL

Pipe	C1220T-0
Nozzle	C3604

KNC*1, *2

Body, Seat ring, Needle	C3604
Nozzle with scale, Lock nut	A2017
O-ring	NBR

*1 The KNC is not allowed for coolant liquid.


*2 Copper-free specification: Excludes the KNC

Nozzle with self-align fitting/KN

[mm]



Model	Nozzle dia. Ø D	Applicable tubing O.D.	Width across flats		L ₁	M	Weight [g]
			H ₁	H ₂			
KN-04-100	Ø 1	Ø 4	10	10	27	15	13
KN-04-150	Ø 1.5	Ø 4	10	10	27.7	15	14
KN-06-100	Ø 1	Ø 6	12	12	30.1	16	19
KN-06-150	Ø 1.5	Ø 6	12	12	30.8	16	20
KN-06-200	Ø 2	Ø 6	12	12	31.5	16	22
KN-08-150	Ø 1.5	Ø 8	14	14	33.8	16	28
KN-08-200	Ø 2	Ø 8	14	14	34.6	16	30
KN-10-250	Ø 2.5	Ø 10	14	17	35.6	17	35
KN-10-300	Ø 3	Ø 10	14	17	36.3	17	36
KN-10-350	Ø 3.5	Ø 10	14	17	37.1	17	37
KN-10-400	Ø 4	Ø 10	14	17	29.5	17	30
KN-10-600	Ø 6	Ø 10	14	17	27.7	17	28
KN-12-350	Ø 3.5	Ø 12	17	19	40.4	17	54
KN-12-400	Ø 4	Ø 12	17	19	41.3	17	55
KN-12-600	Ø 6	Ø 12	17	19	31.2	17	40
KN-16-400	Ø 4	Ø 16	22	24	40.1	17	77
KN-16-600	Ø 6	Ø 16	22	24	38.4	17	79
KN-20-400	Ø 4	Ø 20	26	27	45.6	17	117
KN-20-600	Ø 6	Ø 20	26	27	43.9	17	112




Nozzle with male thread/KN

[mm]



Model	Nozzle dia. Ø D	Connection thread	Width across flats	L ₁	A*1	Weight [g]
			H ₁			
KN-R01-100	Ø 1	R1/8	10	21.4	17.4	8
KN-R01-150	Ø 1.5	R1/8	10	21	17	8
KN-R02-100	Ø 1	R1/4	14	31.4	25.4	19
KN-R02-150	Ø 1.5	R1/4	14	31	25	20
KN-R02-200	Ø 2	R1/4	14	30.5	24.5	21
KN-R02-250	Ø 2.5	R1/4	14	30.1	24.1	21
KN-R02-600	Ø 6	R1/4	14	27.1	21.1	22
KN-R03-400	Ø 4	R3/8	17	31.8	25.4	36
KN-R03-600	Ø 6	R3/8	17	30.1	23.7	37
KN-R04-400	Ø 4	R1/2	22	41.8	33.6	75
KN-R04-600	Ø 6	R1/2	22	40.1	31.8	76
KN-R06-600	Ø 6	R3/4	27	49.6	40.1	149
KN-R06-800	Ø 8	R3/4	27	47.8	38	152
KN-R10-800	Ø 8	R1	36	62.8	52.4	328




*1 Reference dimensions after R thread installation

Copper extension nozzle/KNL

[mm]


Model	Nozzle dia. Ø D	Outside diameter	L ₁	Weight [g]
KNL3-06-150	Ø 1.5	Ø 6	300	43
KNL3-06-200	Ø 2	Ø 6	300	43
KNL3-08-200	Ø 2	Ø 8	300	61
KNL3-08-250	Ø 2.5	Ø 8	300	61
KNL3-10-250	Ø 2.5	Ø 10	300	94
KNL3-10-300	Ø 3	Ø 10	300	94
KNL6-06-150	Ø 1.5	Ø 6	600	84
KNL6-06-200	Ø 2	Ø 6	600	84
KNL6-08-200	Ø 2	Ø 8	600	117
KNL6-08-250	Ø 2.5	Ø 8	600	117
KNL6-10-250	Ø 2.5	Ø 10	600	183
KNL6-10-300	Ø 3	Ø 10	600	183



Copper extension nozzle set/VMG

[mm]

Model	Nozzle dia. D	Outside diameter	L ₁	L ₂ *1	L*1	Width across flats H ₁
VMG1-06-150-100	Ø 1.5	Ø 6	100	100	106	12
VMG1-06-200-100	Ø 2		150	150	156	
VMG1-06-150-150	Ø 1.5		300	300	306	
VMG1-06-200-150	Ø 2		600	600	606	
VMG1-06-150-300	Ø 1.5					
VMG1-06-200-300	Ø 2					
VMG1-06-150-600	Ø 1.5	Ø 8	100	100	106	14
VMG1-06-200-600	Ø 2		150	150	156	
VMG1-08-250-100	Ø 2.5		300	300	306	
VMG1-08-300-100	Ø 3		600	600	606	
VMG1-08-350-100	Ø 3.5					
VMG1-08-250-150	Ø 2.5					
VMG1-08-300-150	Ø 3					
VMG1-08-350-150	Ø 3.5					
VMG1-08-250-300	Ø 2.5					
VMG1-08-300-300	Ø 3					
VMG1-08-350-300	Ø 3.5					
VMG1-08-250-600	Ø 2.5					
VMG1-08-300-600	Ø 3					
VMG1-08-350-600	Ø 3.5					




*1 Reference dimensions after installation
 * Copper extension nozzle and self-align fitting are included in the same package but do not come assembled. Refer to "How to attach extension nozzle" in the VMG series operation manual for assembly procedures.

Nozzle with flow rate adjustment function/KNC

[mm]

Model	Nozzle dia. Ø D	Width across flats H ₁	L ₁	L ₂	Weight [g]
KNC-R02-200	Ø 2.6	17	38.7 (Max. 41.2)	43.4 (Max. 45.9)	42.4




* Please refer to the operation manual for the specific product precautions.

Nozzle for One-touch fitting (Resin type)/KN-Q□A

[mm]

Model	Nozzle dia. Ø D	Applicable fitting size Ø d	L ₁	A*1	Weight [g]
KN-Q06A-100	Ø 1	Ø 6	35	21.8	1
KN-Q06A-150	Ø 1.5	Ø 6	35	21.8	1
KN-Q06A-200	Ø 2	Ø 6	35	21.8	1
KN-Q08A-150	Ø 1.5	Ø 8	39	24.8	2
KN-Q08A-200	Ø 2	Ø 8	39	24.8	2
KN-Q10A-200	Ø 2	Ø 10	43	27.4	3
KN-Q10A-250	Ø 2.5	Ø 10	43	27.4	3
KN-Q12A-250	Ø 2.5	Ø 12	45.5	28.5	4
KN-Q12A-300	Ø 3	Ø 12	45.5	28.5	4



*1 Dimensions shown are for nozzle connected to the KQ2 series.

⚠ Warning [Mounting / Piping] Applicable nozzle: Nozzle for One-touch fitting (Resin/Metal type)

When connecting the nozzle to the One-touch fitting, insert it securely until it cannot move any further. After setting the nozzle deep into the fitting, be sure to pull on the nozzle to confirm that it is firm and does not budge. If the nozzle is not secured all the way at the back of the fitting or if there is insufficient engagement with the One-touch fitting, the nozzle may dislodge during pressurization, which is dangerous and may result in injury or accident.

KN Series


Nozzle for One-touch fitting (Metal type)/KN-Q□

[mm]



Air

Model	Nozzle dia. Ø D	Applicable fitting size Ø d	L ₁	A	Weight [g]
KN-Q06-100	Ø 1	Ø 6	35	18	5
KN-Q06-150	Ø 1.5	Ø 6	35	18	5
KN-Q06-200	Ø 2	Ø 6	35	18	5
KN-Q08-150	Ø 1.5	Ø 8	39	20.5	9
KN-Q08-200	Ø 2	Ø 8	39	20.5	9
KN-Q10-200	Ø 2	Ø 10	43	22	16
KN-Q10-250	Ø 2.5	Ø 10	43	22	16
KN-Q12-250	Ø 2.5	Ø 12	45.5	24	23
KN-Q12-300	Ø 3	Ø 12	45.5	24	23



Connecting products with metal rods


Products with metal rods cannot be connected to the KQ2 series One-touch fittings (Available as a special order). If connected, the metal rod cannot be retained by the chuck of the One-touch fitting and products with metal rods may project during pressurization, causing serious personal injury or accident. For details about One-touch fittings that can connect products with metal rods, contact SMC.

Pivoting nozzle with self-align fitting/KNK

[mm]



Model	Nozzle dia. Ø D	Applicable tubing O.D.	Width across flats		L ₁	M	Weight [g]
			H ₁	H ₂			
KNK-10-400	Ø 4	Ø 10	17	17	41.7	17	44
KNK-10-600	Ø 6	Ø 10	17	17	41.7	17	44
KNK-12-400	Ø 4	Ø 12	17	19	41.2	17	44
KNK-12-600	Ø 6	Ø 12	17	19	41.2	17	44
KNK-16-400	Ø 4	Ø 16	17	24	41.8	17	64
KNK-16-600	Ø 6	Ø 16	17	24	41.8	17	64
KNK-20-400	Ø 4	Ø 20	17	27	43.8	17	77
KNK-20-600	Ø 6	Ø 20	17	27	43.8	17	77




Pivoting nozzle with male thread/KNK

[mm]



Model	Nozzle dia. Ø D	Connection thread	Width across flats		L ₁	A* ₁	Weight [g]
			H ₁	H ₂			
KNK-R02-400	Ø 4	R1/4	17	17	38	31.9	32
KNK-R02-600	Ø 6	R1/4	17	17	38	31.9	32
KNK-R03-400	Ø 4	R3/8	17	17	39	32.4	40
KNK-R03-600	Ø 6	R3/8	17	17	39	32.4	40
KNK-R04-400	Ø 4	R1/2	17	22	42.2	34.1	54
KNK-R04-600	Ø 6	R1/2	17	22	42.2	34.1	54

*1 Reference dimensions after R thread installation



High efficiency nozzle/KNH (OSHA compliant: Operate at 0.5 MPa or less.)


[mm]

Amplifies the air blow flow rate (When operated at 0.5 MPa: amplifies by 2 to 3 times)



Model	Nozzle dia. Ø D	Connection thread	Width across flats	L ₁	A* ₁	Weight [g]
			H ₁			
KNH-R02-100	Ø 1	R1/4	14	52	46	38
KNH-R02-150	Ø 1.5	R1/4	14	52	46	38
KNH-R02-200	Ø 2	R1/4	14	52	46	38

*1 Reference dimensions after R thread installation




Low noise nozzle with self-align fitting/KNS

[mm]



Model	Nozzle dia. Ø D	Applicable tubing O.D.	Width across flats		L ₁	M	Weight [g]
			H ₁	H ₂			
KNS-08-075-4	Ø 0.75 x 4	Ø 8	12	14	24.3	16	17
KNS-08-100-4	Ø 1 x 4	Ø 8	12	14	24.3	16	17
KNS-10-075-4	Ø 0.75 x 4	Ø 10	14	17	24	17	24
KNS-10-090-8	Ø 0.9 x 8	Ø 10	14	17	24	17	24
KNS-10-100-4	Ø 1 x 4	Ø 10	14	17	24	17	24




Low noise nozzle with male thread/KNS

[mm]



Model	Nozzle dia. Ø D	Connection thread	Width across flats	L ₁	A* ₁	Weight [g]
			H ₁			
KNS-R01-075-4	Ø 0.75 x 4	R1/8	12	18	14	9
KNS-R01-100-4	Ø 1 x 4	R1/8	12	18	14	9
KNS-R01-090-8	Ø 0.9 x 8	R1/8	12	18	14	9
KNS-R02-075-4	Ø 0.75 x 4	R1/4	14	20	14	13
KNS-R02-090-8	Ø 0.9 x 8	R1/4	14	20	14	13
KNS-R02-100-4	Ø 1 x 4	R1/4	14	20	14	13
KNS-R02-110-8	Ø 1.1 x 8	R1/4	14	20	14	13

*1 Reference dimensions after R thread installation



Sensing Heads

Specifications

Sensing head (KNP)

Applicable tubing O.D.	Ø 4
Fluid	Air
Max. operating pressure (at 20 °C)	0.8 MPa
Ambient and fluid temperatures	-5 to 60 °C (No freezing)

Principal Parts Material

KNP-1

Pressure spindle	Stainless steel 303
One-touch fitting	POM, NBR, Stainless steel 303, Stainless steel 304
Polyurethane tube (Ø 4, 1 m)	Polyurethane

KNP-2

Pipe	Stainless steel 304
One-touch fitting	POM, NBR, Stainless steel 304
Polyurethane tube (Ø 4, 1 m)	Polyurethane


Standard sensing head/KNP

[mm]



Model	Nozzle dia. Ø D	Applicable tubing O.D.	Width across flats		M	L1	L2	Weight [g]
			H1	H2				
KNP-1	Ø 2.5	Ø 4	5	8	13.3	64.6	986.7	7

* A 1 m polyurethane tube is included.




Needle sensing head/KNP

[mm]




Model	Nozzle dia. Ø D	Applicable tubing O.D.	D2	M	L1	L2	L3	Weight [g]
KNP-2	Ø 0.7	Ø 4	Ø 8	12.7	41	987.3	23	4

* A 1 m polyurethane tube is included.




Use to measure workpiece impact pressure




Nozzle Covers

Cover for male thread nozzle


[mm]



Nozzle cover model	Material	Applicable blow gun model	
		Model	Nozzle type
P5670129-01	HNBR	VMG1□□-□01 to 04	Male thread nozzle Ø 1 to Ø 2.5
P5670129-01F	Fluororubber		
P5670129-02	HNBR	VMG1□□-□05 to 07	Male thread nozzle Ø 3 to Ø 4
P5670129-02F	Fluororubber		



VMG1□□-□01 to 04




VMG1□□-□05 to 07

Cover for copper extension nozzle

[mm]



Nozzle cover model	Material	Applicable blow gun model	
		Model	Nozzle type
P5670129-11	HNBR	VMG1□□-□31 to 38	Ø 6 copper extension nozzle
P5670129-11F	Fluororubber		



VMG1□□-□31 to 38

Equipment for Blowing


Blow Gun VMG

- A 20 % reduction in power consumption can be achieved with the SMC "Blow gun" + "S coupler" + "Coil tube."
- Pressure loss: 1 % or less (Nozzle diameter: Ø 2.5)
- Available nozzles:
Male thread nozzle, High efficiency nozzle with male thread, Low noise nozzle with male thread, Copper extension nozzle
- With flow rate adjustment function (-X54)



Pulse Blow Valve AXTS040□-□□-X2

- The peak pressure of repeatedly colliding air permits efficient blowing.
- Air consumption: Reduced by 50 % or more
- Pulse blow can be used by simply supplying air.




Air Saving Impact Blow Gun IBG

- Increased impact force due to higher peak pressure
- Drastic reduction in air consumption and labor time
- Application: It is capable of eliminating, in a short period of time, the dust, etc., that is difficult to remove with the existing blow gun.



Impact Blow Valve IBV1□-X5/X7(-Q)

- Increased impact force due to higher peak pressure
- Drastic reduction in air consumption and labor time
- High peak pressure: 3 times or more (Compared with the existing model)
- Air consumption: 93 % reduction
- Compact design allows for installation in narrow spaces.




Available nozzles

Long nozzle with a silencer



Pilot Operated 2-Port Solenoid Valve for Dry Air VQ20/30

- Applications: Air-blow, Blow-off of workpieces, etc.
- High-frequency operation is possible: High-speed response 7 ms or less (VQ20), 20 ms or less (VQ30)
- Easy piping with One-touch fittings
- The dust-tight, water-jet-proof enclosure (IP65) is compatible with the DIN terminal type.
- Manifold type no.: VV2Q22, VV2Q32



Equipment for Blowing

For Clean Blow

Clean Air Module LLB

- Modularized clean equipment (Reduced piping labor, Space saving)
Makes clean air easily available
- Nominal filtration rating: $0.01\ \mu\text{m}$ (Filtration efficiency: 99.99 %)
- Wetted parts: Grease-free, Silicone-free
- Assembled in a clean room, Shipped and packed in double packaging
- 24 combinations are available.



LLB4



LLB3


- Can perform the clean air blow of small workpieces with a flow rate of up to 100 l/min

Made to order



LLB1-X100

N₂ blow for the removal of lens dust



Bacteria Removal Filter/ Hollow Fiber Element SFDA

- Bacteria capture performance: $\text{LRV} \geq 9$
Uses FDA/Food Sanitation Law compliant materials*1
*1 Parts in contact with fluid: Resin/Rubber
- Grease-free
- Contributes to the hygiene control of HACCP, etc., and FSSC22000 certification acquisition!
- Nominal filtration rating: $0.01\ \mu\text{m}$ (Filtering efficiency: 99.99 %)
- Initial pressure drop: 0.03 MPa (Inlet pressure 0.7 MPa, at max. flow rate)
- Flow rate: 500 l/min (ANR)



Clean One-touch Fittings for Blowing KP





- One-touch fittings for clean room blowing systems
- Completely oil-free (Fluoro-coated rubber portions)
- Wetted parts are non-metallic.
- Parts washed and assembled in a clean room, Packed in double packaging
- Can be used in a vacuum (-100 kPa)



Technical Data

Comparison Table (Thrust, Noise, Flow consumption, Air flow)

Pressure right before the nozzle: 0.2 MPa





	Mono-porous nozzle (KN series)			Low noise nozzle (KNS series)			High efficiency nozzle (KNH series)			Twin/Triple nozzle (KQ2LU, KM13 + KN-Q□A series)		
												
Thrust [N]	Nozzle diameter	Noise dB(A)	Flow consumption l/min (ANR)	Nozzle diameter x Number of nozzles	Noise dB(A)	Flow consumption l/min (ANR)	Nozzle diameter	Noise dB(A)	Air flow [Flow consumption l/min (ANR)]	Nozzle diameter x Number of nozzles	Noise dB(A)	Flow consumption l/min (ANR)
0.2	Ø 1	65	27									
0.3							Ø 1	76.2	103 [25]			
0.4										Ø 1 x 2	66.5	46
0.5	Ø 1.5	74	58	Ø 0.75 x 4	64	52						
0.6							Ø 1.5	81	169 [54]			
0.7										Ø 1 x 3	70	76
0.8				Ø 1.0 x 4	70	96				Ø 1 x 4	69	93
0.9												
1.0	Ø 2	81.8	105				Ø 2	88.6	220 [111]	Ø 1.5 x 2	77	112
1.3				Ø 0.9 x 8	71	133						
1.5	Ø 2.5	87.2	172							Ø 1.5 x 3	75.4	163
1.6												
1.9										Ø 2 x 2	83.4	205
2.0				Ø 1.1 x 8	77	237						
2.2												
2.3	Ø 3	91.7	220									
2.7										Ø 2.5 x 2	87.1	298
3.0												
3.1	Ø 3.5	95.6	337									
4.0	Ø 4	98.7	430							Ø 3 x 2	90.1	443
5.6												
9.0	Ø 6	104	1030									
16.3	Ø 8	109	1605									

Pressure right before the nozzle: 0.4 MPa

...												
0.5	Ø 1	74.6	43				Ø 1	82	153 [41]			
0.8										Ø 1 x 2	75.3	78
0.9				Ø 0.75 x 4	72.6	87						
1.0	Ø 1.5	83	97									
1.1							Ø 1.5	90	231 [82]			
1.3										Ø 1 x 3	78.5	125
1.7				Ø 1.0 x 4	78.6	152				Ø 1 x 4	77.3	153
1.8												
1.9	Ø 2	91.4	176				Ø 2	91	308 [180]			
2.0										Ø 1.5 x 2	86	189
2.6				Ø 0.9 x 8	81.2	208						
2.7												
2.9	Ø 2.5	96.7	289							Ø 1.5 x 3	83.2	272
3.5												
3.6										Ø 2 x 2	93.5	338
4.0				Ø 1.1 x 8	87.6	391						
4.3												
4.4	Ø 3	101	363									
5.2										Ø 2.5 x 2	96.1	497
5.9	Ø 3.5	106	542									
6.4												
7.7	Ø 4	106	722							Ø 3 x 2	100	724
11.6												
17.6	Ø 6	110	1730									
30.9	Ø 8	112	3030									

Comparison Table (Thrust, Noise, Flow consumption, Air flow)

Pressure right before the nozzle: 0.6 MPa

	Mono-porous nozzle (KN series)			Low noise nozzle (KNS series)			High efficiency nozzle (KNH series)			Twin/Triple nozzle (KQ2LU, KM13 + KN-Q□A series)		
												
Thrust [N]	Nozzle diameter	Noise dB(A)	Flow consumption l/min (ANR)	Nozzle diameter x Number of nozzles	Noise dB(A)	Flow consumption l/min (ANR)	Nozzle diameter	Noise dB(A)	Air flow [Flow consumption l/min (ANR)]	Nozzle diameter x Number of nozzles	Noise dB(A)	Flow consumption l/min (ANR)
...												
0.7	Ø 1	79	60				Ø 1	84	202 [57]			
1.2										Ø 1 x 2	80	108
1.4				Ø 0.75 x 4	78	121						
1.5	Ø 1.5	86	135									
1.6							Ø 1.5	92	326 [125]			
1.9										Ø 1 x 3	83	177
2.3												
2.5				Ø 1.0 x 4	84	224				Ø 1 x 4	83	220
2.8							Ø 2	97	400 [253]			
2.9	Ø 2	95	243									
3.0										Ø 1.5 x 2	91	265
3.9				Ø 0.9 x 8	86	330						
4.1												
4.2										Ø 1.5 x 3	87	381
4.4	Ø 2.5	101	400									
5.3										Ø 2 x 2	98	475
5.4												
5.5												
5.9				Ø 1.1 x 8	93.1	554						
6.5	Ø 3	105	552									
7.6										Ø 2.5 x 2	100	694
8.7	Ø 3.5	109	771									
9.8												
11.1										Ø 3 x 2	103	1025
11.5	Ø 4	109	995									
17.5												
26.1	Ø 6	112	2430									
46.3	Ø 8	115	4320									

Model Selection

Recommended Circuit Configuration for Blowing




Optimization of an air blow system

For the optimization of an air blow system, it is important to make the ratio of the conductance of the components upstream and the conductance of the nozzle tip to the recommended value. By achieving this ratio, the system will allow high-pressure blow and flow rate reduction with a low pressure loss.

The conductance ratio recommended by SMC is 3:1 considering the energy-saving efficiency and installation cost.

* Conductance: Index of air flow ability

Optimization process




Optimization process complete


Model Selection

Recommended Circuit Configuration for Blowing


Piping lengths for conductance optimization



Optimization for 2-port valve with regulator model




Glossary of Terms





Term	Description
Pressure right before the nozzle (P_o)	The pressure right before the air is blown out from the nozzle. Pressure in the nozzle
Workpiece impact pressure (P_w)	Pressure when the air blown out of the nozzle collides with the workpiece
Conductance ratio	The ratio of conductance of the nozzle (C_n) and the upstream components (C_s) Setting the upstream side to 2 to 3 times the nozzle is recommended.
Pressure loss	Pressure loss of the supply pressure (difference between P_s and P_o) caused by the piping route. Lower pressure loss results in the better efficiency.
Jet range	Effective energy range inside the air that widens conically at the angle of 14 degrees from the nozzle opening
Effective diameter	The range in which the blowing effect is achieved in an area wider than the jet area
Potential core region	The range is equal to the nozzle diameter x 5. In this range, it interferes with the expansion thrust of the compressed air and the energy of the air blow cannot be used effectively.
Developing region	The range after the potential core region where the air blow thrust can be used effectively

* Conductance: Index of air flow ability



Air Blow System and Conductance






P_s : Supply pressure
 P_o : Pressure right before the nozzle
 C_s : Upstream conductance
 C_n : Nozzle conductance

Pressure ratio $\frac{P_o + 0.1}{P_s + 0.1}$
 Conductance ratio $\frac{C_s}{C_n}$

Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of “Caution,” “Warning” or “Danger.” They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) ¹⁾, and other safety regulations.

-  **Danger:** **Danger** indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.
-  **Warning:** **Warning** indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
-  **Caution:** **Caution** indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

- 1) ISO 4414: Pneumatic fluid power – General rules and safety requirements for systems and their components.
ISO 4413: Hydraulic fluid power – General rules and safety requirements for systems and their components.
IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1: Robots.
etc.

Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/equipment until safety is confirmed.

1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments.

Use under such conditions or environments is not covered.

1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogues and operation manuals.
3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in Japan.

Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following “Limited warranty and Disclaimer” and “Compliance Requirements”. Read and accept them before using the product.

Limited warranty and Disclaimer

1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first. ²⁾ Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty.
A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Safety Instructions

Be sure to read “Handling Precautions for SMC Products” (M-E03-3) before using.

SMC Corporation (Europe)

Austria	+43 (0)2262622800	www.smc.at	office.at@smc.com
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	sales.bg@smc.com
Croatia	+385 (0)13707288	www.smc.hr	sales.hr@smc.com
Czech Republic	+420 541424611	www.smc.cz	office.at@smc.com
Denmark	+45 70252900	www.smc.dk.com	smc.dk@smc.com
Estonia	+372 651 0370	www.smcee.ee	info.ee@smc.com
Finland	+358 207513513	www.smc.fi	smc.fi@smc.com
France	+33 (0)164761000	www.smc-france.fr	supportclient.fr@smc.com
Germany	+49 (0)61034020	www.smc.de	info.de@smc.com
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office.hu@smc.com
Ireland	+353 (0)14039000	www.smcautomation.ie	technical.ie@smc.com
Italy	+39 03990691	www.smcitalia.it	mailbox.it@smc.com
Latvia	+371 67817700	www.smc.lv	info.lv@smc.com

Lithuania	+370 5 2308118	www.smclt.lt	info.lt@smc.com
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post.no@smc.com
Poland	+48 22 344 40 00	www.smc.pl	office.pl@smc.com
Portugal	+351 214724500	www.smc.eu	apoiocliente.pt@smc.com
Romania	+40 213205111	www.smcromania.ro	office.ro@smc.com
Russia	+7 (812)3036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	sales.sk@smc.com
Slovenia	+386 (0)73885412	www.smc.si	office.si@smc.com
Spain	+34 945184100	www.smc.eu	post.es@smc.com
Sweden	+46 (0)86031240	www.smc.nu	order.se@smc.com
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter.ch@smc.com
Turkey	+90 212 489 0 440	www.smcturkey.com.tr	satis.tr@smc.com
UK	+44 (0)845 121 5122	www.smc.uk	sales.gb@smc.com
South Africa	+27 10 900 1233	www.smcza.co.za	Sales.za@smc.com