


# Parallel Type Air Gripper Series MHZ ø6, ø10, ø16, ø20, ø25, ø32, ø40




Series upgraded with the addition of new models and expanded size variations

Long stroke/MHZL2 and compact series/MHZA□2-6 introduced
 ø6, ø32 and ø40 added to standard MHZ2
 ø6 added to MHZJ2 with dust cover

**SMC** 


2.1-1

# Integral linear guide used for high




#### High degree of mounting flexibility


Can be mounted five ways from three directions.



# Finger positions can be selected (Standard type/MHZ2)



Finger options



**Body options** 


rigidity and high precision Body thickness tolerance: ±0.05mm


No guide protrusion in direction of body thickness

**Improved** remounting accuracy Positioning dowel pin holes provided

Top mounting centering location

Mounting is more secure with a depth 0.5 to 2mm greater than conventional types





## Accommodates diverse work piece diameters with a single unit

■ Nearly double the standard stroke

Long strokes are also compact and light weight

Opening/Closing		
(Open — Closed)	Weight g	Body thickness mm
8 ( 4)	60	16.4
12 ( 6)	135	23.6
18 (10)	270	27.6
22 (14)	470	33.6
	8 ( 4) 12 ( 6) 18 (10)	stroke mm (Open — Closed)     Weight g       8 ( 4)     60       12 ( 6)     135       18 (10)     270

Values inside ( ) are for standard series MHZ2.

Long strokes MHZL2



MHS

MHK


MHZ

MHQ

MHL<sub>2</sub>

**MHR** 

A wide variety of types and broad size variations



-----





MHC2

MHT2

MHY2


MHW2 **MRHQ** 

Auto Switch

# **Compact Series (Without Auto Switch)**

# Series MHZA2-6/MHZAJ2-6

#### **How to Order**



# Parallel Type/Compact Series Series MHZA2-6/MHZAJ2-6



#### **Specifications**

Fluid			Air
Double acting		acting	0.15 to 0.7MPa
pressure	Single Normally open	0.3 to 0.7MPa	
acting Normally closed 0.3 to 0.7MPs	0.5 to 0.7MPa		
Ambient and fluid temperature		temperature	−10 to 60 °C
Repeatability			±0.01mm
Maximum operating frequency		ng frequency	180c.p.m.
Lubrication			Non-lube
Action			Double acting, Single acting

#### **Models**

Dou	ble acti	ng ty	Эе

Symbols:

Single acting type, normally open



Single acting type, normally closed



Act	ion	Model	Bore size (mm)	Gripping force Note 1) Gripping force per finger Effective value N  External gripping force gripping force		Opening/ Closing stroke (both sides) mm	Weight g
Dou	ıble	MHZA2-6D	6	3.3	3.3 6.1	4	26
act	ing	MHZAJ2-6D	6	3.3	0.1	4	27
	Normally	MHZA2-6S	6	1.9		4	26
Single	open	MHZAJ2-6S	6		_	4	27
acting	Normally	MHZA2-6C	6		3.7	4	26
	closed	MHZAJ2-6C	6		3.7	4	27

Note 1) Values based on pressure of 0.5MPa, gripping point L = 20mm, at center of stroke.

#### **Options**

#### • Body options/End boss type

Curahal Dining na	Piping port position	Type of piping port	Applicab	le model	
Symbol	Piping port position	MHZA2-6/MHZAJ2-6	Double acting	Single acting	
Nil	Standard	M3	•	•	
E	Side ported  Axial port	M3	•	•	
K		With ø4 One-touch fitting	_	•	
Н		With ø4 hose nipple	_	•	
М		M3	_	•	

MHZ

MHQ

MHL2

MHR

MHK

MHS

MHC2

MHT2

MHY2


MHW2


MRHQ

#### Series MHZA2-6/MHZAJ2-6


#### Construction/Standard Type MHZA2-6

#### Double acting/with fingers open







#### Double acting/with fingers closed



#### Single acting/normally open



#### Single acting/normally closed



#### Parts list

No.	Description	Material	Note	
1	Body	Aluminum alloy	Hard anodized	
2	Piston	Stainless steel		
3	Lever	Stainless steel	Heat treated	
4	Guide	Stainless steel	Heat treated	
5	Finger	Stainless steel	Heat treated	
6	Roller stopper	Stainless steel		
7	Lever shaft	Stainless steel	Nitrided	
8	Holder	Brass	Electroless nickel plated	
9	Holder lock	Stainless steel		
10	Сар	Aluminum alloy	Clear anodized	
11	Bumper	Urethane rubber		
12	Steel balls	High carbon chromium bearing steel		
13	Needle roller	High carbon chromium bearing steel		

#### Replacement parts: Seal kits

replacemen	replacement parte. Coar kite		
Seal kit no. Description			
MHZA6-PS	Kit includes items 21, 22, 23 and 24 from the table above.		

 $<sup>\</sup>ast$  Seal kits consist of items 21, 22, 23 and 24 in one kit, and can be ordered using the seal kit number.

Note) Contact SMC when replacing seals.


#### Parts list

No.	Description	Material	Note
14	C type snap ring	Carbon steel	Nickel plated
15	Exhaust plug	Brass	Electroless nickel plated
16	Exhaust filter	Polyvinyl formal	
17	N.O. spring	Stainless steel spring wire	
18	N.C. spring	Stainless steel spring wire	
19	N.C. holder	Brass	Electroless nickel plated
20	N.C. spacer	Stainless steel	
21	Rod seal	NBR	
22	Piston seal	NBR	
23	Gasket	NBR	
24	Gasket	NBR	




#### Construction/With Dust Cover MHZAJ2-6


#### Double acting/with fingers open




#### Single acting/normally open



#### Single acting/normally closed



## Double acting/with fingers closed



#### Parts list

Parts	arts list				
No.	Description	Material	Note		
		CR	Chloroprene rubber		
14	Dust cover	FKM	Fluoro rubber		
		Si	Silicon rubber		
15	C type snap ring	Carbon steel	Nickel plated		
16	Exhaust plug	Brass	Electroless nickel plated		
17	Exhaust filter	Polyvinyl formal			
18	N.O. spring	Stainless steel spring wire			
19	N.C. spring	Stainless steel spring wire			
20	N.C. holder	Brass	Electroless nickel plated		
21	N.C. spacer	Stainless steel			
22	Rod seal	NBR			
23	Piston seal	NBR			
24	Gasket	NBR			
25	Gasket	NBR			

# Parts list

No.	Description	Material	Note	
1	Body	Aluminum alloy	Hard anodized	
2	Piston	Stainless steel		
3	Lever	Stainless steel	Heat treated	
4	Guide	Stainless steel	Heat treated	
5	Finger	Stainless steel	Heat treated	
6	Roller stopper	Stainless steel		
7	Lever shaft	Stainless steel	Nitrided	
8	Holder	Brass	Electroless nickel plated	
9	Holder lock	Stainless steel		
10	Сар	Aluminum alloy	Clear anodized	
11	Bumper	Urethane rubber		
12	Steel balls	High carbon chromium bearing steel		
13	Needle roller	High carbon chromium bearing steel	steel	

#### Replacement parts: Seal kits

Seal kit no. Description		Description	
	MH74 I6-PS	Kit includes items 22 23 24 and 25 from the table above	

 $\ast$  Seal kits consist of items 22, 23, 24 and 25  $\,$  in one kit, and can be ordered using the seal kit number.

Note) Contact SMC when replacing seals.

#### Replacement parts: Dust covers

Material	Part number
CR	MHZAJ2-J6
FKM	MHZAJ2-J6F
Si	MHZAJ2-J6S



MHZ

MHQ

MHL2

**MHR** 

MHK

MHS

MHC2

MHT2


MHY2

MHW2


**MRHQ** 

#### **Dimensions/Standard Type**

MHZA2-6□ Double acting/Single acting Basic Type Scale: 100%




\* For single action, the port on one side is a breathing hole




# Parallel Type/Compact Series Series MHZA2-6/MHZAJ2-6

#### **Dimensions/With dust cover**

MHZAJ2-6□ Double acting/Single acting Basic Type Scale: 100%



\* For single action, the port on one side is a breathing hole.



MHZ

MHQ

MHL2

MHR MHK

MUC

MHS

MHC2

MHT2


MHY2

MHW2

### Series MHZA2-6


# **Finger Options**

#### **Side Tapped Mounting [1]**




\* Specifications and dimensions other than the above are the same as the basic type.

#### **Through Holes in Opening/Closing Direction [2]**



 $\ast$  Specifications and dimensions other than the above are the same as the basic type.

### Flat Type Fingers [3]



Weight: 25g

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.

#### Series MHZA2-6/MHZAJ2-6


# **Body Options: End Boss Type**


#### **Applicable Models**

Symbol	Dining part position	Type of p	piping port	Applicable model		
Symbol Fibility port	Piping port position	MHZA2	MHZAJ2	Double acting	Single acting	
E	Side ported	N.	13	•	•	
Н		With ø4 h	ose nipple		•	
K	Axial port	With ø4 One	e-touch fitting	_	•	
М	·	N	13		•	

#### Side Ported [E]


#### MHZA2-6□□E MHZAJ2-6□□E





<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.

#### Axial Port (with Hose Nipple) [H]



<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.

#### **Applicable Tubing**

Description/Model	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coiled tubing
Specification	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter mm	4	4	4	4
Max. operating pressure MPa	1.0	0.8	0.5	0.5
Minimum bending radius mm	13	12	10	_
Operating temperature °C	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane

Refer to catalogue CAT.501-B "Air Fittings and Tubing" regarding One-touch fittings and tubing.



MHZ

MHQ

MHL2

MHR

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.


<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.

#### Series MHZA2-6/MHZAJ2-6

#### Axial Port (with One-touch Fitting) [K]

#### MHZA2-6 <sup>S</sup>□K

#### MHZAJ2-6 <sup>s</sup> □ K



<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.


#### **Applicable tubing**


Description/Model	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coiled tubing
Specification	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter mm	4	4	4	4
Max. operating pressure MPa	1.0	0.8	0.5	0.5
Minimum bending radius mm	13	12	10	_
Operating temperature °C	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane


Refer to catalogue CAT. 501-B "Air Fittings and Tubing" regarding One-touch fittings and tubing.

#### Axial Port (M3 Port) [M]

#### MHZA2-6 <sup>S</sup>□M







I Init: a

#### Weights

				Offit. 9					
Model	End boss type (symbol)								
	E	Н	K	M					
MHZA2-6□□	28	28	28	28					
MHZAJ2-6□□	29	29	29	29					



<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.


 $<sup>\</sup>ast$  Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.

# **Parallel Type Air Gripper**


## **Standard Type**

# Series MHZ2


#### **How to Order**




[Standard type] Nil: Basic type



1: Side tapped mounting



2: Through holes in opening/ closing direction



3: Flat type fingers



Applicable auto switches/\* Refer to pages 2.11-... for detailed auto switch specifications

, (pp.:	TPD TO CONTROLLED A PROJECT OF THE P														
				100	Load voltage		Auto switch part no.		Lead wire length (m)*			Note 2)	Δ 1	A 1: 1.1	
Type Special I		ecial Electrical		_			Electrical ent	Electrical entry direction		3	5	Flexible lead wire		icable	
	entry	light	(output)	D	С	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)	load		
		— Grommet		3 wire	(NPN)			F9NV	F9N	•	•	_	0		
tc				(NPN)			.,	F8N	_	•	•	0	0		
ž ja				3 wire		12V		F9PV	F9P	•	•	_	0		Relay,
So				(PNP)		120		F8P	_	•	•	0	0		PLC
Solid state switch				2 mina	2 wire			F9BV	F9B	•		_	0		
0,				2 wire				F8B		•	•	0	0		

\* Lead wire length symbols: 0.5m ..... Nil (Example) F9N

3m ...... L (Example) F9NL


5m ...... Z (Example) F9NZ

\* Auto switches marked with a "O" symbol are produced upon receipt of order.

Note 1) When using a D-F8□ switch, mount it at a distance of 10mm or more from magnetic substances such as iron, etc.

Note 2) Add "-61" at the end of the part number for the flexible lead wire. (Examples)

When ordering with an air gripper



These auto switches have been changed Contact SMC or view www.smcworld.com F9N**→M9N** F9NV**⇒M9NV** F9P**→M9P** F9PV⇒M9PV F9B**→M9B** F9BV**⇒M9BV** 

MHC2

MHZ

MHQ

MHL<sub>2</sub>

MHR

MHK

MHS


MHT2

MHY2

MHW2

**MRHQ** 

#### **How to Order**



Applicable auto switches/\* Refer to pages 2.11-1 for detailed auto switch specifications.

	0	F	tuin - I Indicator Minima				_	Auto switc	h part no.	Lead w	ire leng	th (m)*	Note 2) Flexible				olicab	le mo	del			
Type	Special	Electrical entry	light	Wiring (output)	L	oad voltag	е	Electrical en	try direction			5	lead wire	Applic		ø10	a16	ø20	a25			
	Turicuori eritiy iigin	(output)		DC	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)	102	au	טוש	טוש	W20	W23					
			_		5V, 12V		Y69A	Y59A	•	•	0	Standard	IC circuit		•	•	•	•				
				3 wire (NPN)		12V		F9NV	F9N	•	•	_	0				•	•	•			
						IZV		F8N	_	•	•	0	0				•	•	•			
ج							5V, 12V		Y7PV	Y7P	•	•	0	Standard	IC circuit		•	•	•	•		
ķ				(PNP)				3 wire		12V		F9PV	F9P	•	•	_	0				•	•
S							120		F8P	_	•	•	0	0				•	•	•		
auto		Grommet	Yes		24V			Y69B	Y59B	•		0	0		Relay,	•	•	•	•			
e a		Gionninet	165	2 wire	24 V	24 V	24 V	24 V	12V	_	F9BV	F9B	•		_	0		PLC		•	•	•
state								F8B	_	•	•	0	0				•	•	•			
9				3 wire		5V, 12V		Y7NWV	Y7NW	•	•	0	Standard	IC circuit				•	•			
Solid	Diagnostic			(NPN)		12V		F9NWV	F9NW	•	•	0	0					•	•			
0,	Diagnostic indication			3 wire		5V, 12V		Y7PWV	Y7PW	•	•	0	Standard	IC circuit				•	•			
	(2 colour indicator)	(PNP)				F9PWV	F9PW	•	•	0	0					•	•					
							Y7BWV	Y7BW	•	•	0	Standard					•	•				
				2 wire	2 wire			F9BWV	F9BW	•	•	0	0					•	•			

\* Lead wire length symbols: 0.5m ...... Nil (Example) F9N 3m ...... L (Example) F9N

3m ...... L (Example) F9NL 5m ..... Z (Example) Y59AZ

\* Auto switches marked with a "O" symbol are produced upon receipt of order.

Note 1) Use caution regarding hysteresis in the 2 color indicator types. When using this type, refer to "Auto Switch Hysteresis" on page 2.1-52.

Note 3) Through hole mounting is not possible when using auto switch types D-Y59. D-Y69. or D-Y7.

Note 2) Add "-61" at the end of the part number for the flexible lead wire.

(Examples)

When ordering with an air gripper

MHZ 2-16D-F9NVS-61


When ordering auto switches only



2.1-14



# Параллельный захват серия МНZ2




обеспечивает высокую надежность и точность позиционирования





Встроенная

продольная направляющая










Крепление

#### Крепление датчиков положения



Возможность крепления датчиков вдоль любой плоскости

## Параллельный захват

# MHZ2


Ø10~25

#### Технические характеристики

Среда		Очищенный сжатый воздух с содержанием масла или без него			
Рабочий	Двустороннего действия	0.2 ~ 0.7			
диапазон (МПа)	Одностороннего действия	0.35 ~ 0.7			
Диапазон рабочи	х температур (°C)	-10 ~ 60			
Воспроизводимо	сть (мм)	±0.01			
Макс. частота ср	абатывания (мин <sup>-1</sup> )	180			
Тип		Одностороннего, двустороннего действия			

#### Номер для заказа

Диам. поршня, мм	Двустороннего действия	Одностороннего действия Раскрыт без Закрыт без подачи давления подачи давления		
10	MHZ2=10DN	MHZ2=10SN	MHZ2-10CN	
16	MHZ2-16DN	MHZ2-16SN	MHZ2-16CN	
20	MHZ2-20DN	MHZ2-20SN	MHZ2-20CN	
25	MHZ2-25DN	MHZ2-25SN	MHZ2-25CN	



#### Условное обозначение

Двустороннего действия



Одностороннего действия, раскрыт без подачи давления



Одностороннего действия, закрыт без подачи давления



#### Исполнение

Тип		Модель	Диам. поршня	Удерживающее при 0.5 МПа (Н		Длина хода на раскрытие	Bec (r)
			(MM)	наруж. захват	внутр. захват	(мм)	
Двустороннего де	ействия	MHZ2-10DN	10	9.8	17	4	55
		MHZ2-16DN	16	30	40	6	115
		MHZ2-20DN	20	42	66	10	235
		MHZ2-25DN	25	65	104	14	430
Одностороннего	Раскрыт без	MHZ2-10SN	10	6.3		4	55
действия	подачи давления	MHZ2-16SN	16	24		6	115
		MHZ2-20SN	20	28		10	240
		MHZ2-25SN	25	45		14	435
	Закрыт без	MHZ2-10CN	10		12	4	55
	подачи давления	MHZ2-16CN	16		31	6	115
		MHZ2-20CN	20		56	10	240
		MHZ2-25CN	25		83	14	430

<sup>\*</sup> Усилие приводится для средней точки на одном пальце.


Более точные значения см. на диаграммах \*\* Вес указан без датчиков положения

Информация о датчиках положения - см. стр. 2-32




#### Конструкция


#### Двустороннего действия/пальцы в открытом положении




# Одностороннего действия/без давления открыт



#### Одностороннего действия/без давления закрыт



#### Двустороннего действия/пальцы в закрытом положении



#### Спецификация

Поз.	Описание	материал	примечание
1	Корпус	Алюм. сплав	
2	Поршень	ø10, ø16: нерж. сталь ø20, ø25: алюм. сплав	
3	Рычаг	нерж. сталь	Закаленная
4	Направляющая	нерж. сталь	Закаленная
5	Палец	нерж. сталь	Закаленная
6	Упор	нерж. сталь	Закаленная
7	Ось рычага	нерж. сталь	азотированная
8	Крышка	Синтетич. резина	
9	Демпфер	Полиуретан	
10	Магнит. кольцо	Синтетич. резина	

Поз.	Описание	материал	примечание
11	Шарики	высокоуглер, подшип, сталь	
12	Ось	высокоуглер. подшип. сталь	
13	Штифт	Нерж. сталь	
14	Стопорное кольцо	Сталь	Никелированная
15	Деаэрационная пробка	Латунь	Никелированная
16	Фильтр выхлопа	Полимер	
17	Пружина	Пружинная сталь	
18	Пружина	Пружинная сталь	
19	Уплотнение штока	Резина	
20	Уплотнение поршня	Резина	
21	Уплотнение крышки	Резина	

#### Принадлежности

#### Ремкомплект


Номер для за	Номер для заказа							
MHZ2-10D	MHZ2-10D MHZ2-16D MHZ2-20D MHZ2-25D							
MHZ10-PS	MHZ16-PS	MHZ20-PS	MHZ25-PS	поз. 19, 20, 21				

#### Эффективное удерживающее усилие: захват двустороннего действия


#### Критерии выбора захвата:

- вес детали
- коэфф. трения между захватом и деталью
- форма детали


Рекомендуется выбирать захват так, чтобы удерживающее усилие было в 10-20 раз больше веса детали




#### Захват снаружи




#### Захват изнутри




# Удерживающее усилие при захвате снаружи




MHZ2-16D




MHZ2-20D




MHZ2-25D




# Удерживающее усилие при захвате изнутри




MHZ2-16D



MHZ2-20D



MHZ2-25D






#### Эффективное удерживающее усилие: захват одностороннего действия


#### Критерии выбора захвата:

- вес детали
- коэфф. трения между захватом и деталью
- форма детали


Рекомендуется выбирать захват так, чтобы удерживающее усилие было в 10-20 раз больше веса детали




#### Захват снаружи





#### Захват изнутри




# Удерживающее усилие при захвате снаружи













# Удерживающее усилие при захвате изнутри











#### Параллельный захват МН7*9*

#### Приложение усилия не по центру

#### Захват снаружи





#### Захват изнутри





# На этих диаграммах искомое значение плеча L зависит от величины эксцентриситета H и рабочего давления в сети

#### При захвате снаружи













#### При захвате изнутри















#### Размеры

#### MHZ2-10










#### \* В случае одностороннего действия один из портов служит для выпуска воздуха


#### Паз для датчика положения





# Параллельный захват


#### Размеры

#### MHZ2-16










\* В случае одностороннего действия один из портов служит для выпуска воздуха


# Паз для датчика положения 6.2 Паз для датчика положения 2.1





#### Размеры

#### MHZ2-20












\* В случае одностороннего действия один из портов служит для выпуска воздуха




#### Размеры


#### MHZ2-25





#### **How to Order**





Applicable auto switches/\* Refer to pages 2.11-1 for detailed auto switch specifications.

Туре				oad voltag	ad voltage Auto switch part no. L		0 ( )		Note 2) Flexible lead wire	Applicable		Applicable model					
. )   -	function	entry	light	(output)		DC AC		Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)	loa	id	ø32	ø40
						5V, 12V		Y69A	Y59A	•	•	0	Standard	IC circuit		•	
				3 wire (NPN)		12\/	12V	F9NV	F9N	•	•	_	0			•	
				(INPIN)		120		F8N	_	•	•	0	0			•	
£				3 wire		5V, 12V	Y7PV	Y7P	•	•	0	Standard	IC circuit	-	•		
switch	_			(PNP)		12V	F9PV	F9P	•	•	_	0			•		
50							F8P		•	•	0	0			•		
auto		Grommet	Yes		24V	/ <sub>12V</sub>	_	Y69B	Y59B	•	•	0	0	_	Relay,	•	
9		0.0	1.00	2 wire			12V	F9BV	F9B	•	•	_	0	i	PLC	•	
state								F8B		•	•	0	0			•	
<u>.</u>				3 wire		5V, 12V	] [	Y7NWV	Y7NW	•	•	0	Standard	IC circuit		•	
Solid	Diagnostic			(NPN)		12V		F9NWV	F9NW	•	•	0	0			•	
	indication			3 wire		5V, 12V		Y7PWV	Y7PW	•	•	0	Standard	IC circuit		•	
	(2 colour			(PNP)				F9PWV	F9PW		•	0	0			•	
	indicator)			2 wire		12V	12V	Y7BWV	Y7BW	•		0	Standard	_	•		
								F9BWV	F9BW		•	0	0			•	

\* Lead wire length symbols: 0.5m ...... Nil (Example) F9N 3m ...... L (Example) F9NL

5m ...... Z (Example) Y59AZ

 $\ast$  Auto switches marked with a "O" symbol are produced upon receipt of order.

Note 1) Use caution regarding hysteresis in the 2 color indicator types. When using this type, refer to "Auto Switch Hysteresis" on page 2.1-52.

Note 2) Add "-61" at the end of the part number for the flexible lead wire.

(Examples)

When ordering with an air gripper

MHZ 2-16D-F9NVS-61

Flexible lead wire

D-F9PL-61

Flexible lead wire

These auto switches have been changed Contact SMC or view www.smcworld.com
F9N→M9N F9NV→M9NV
F9P→M9P F9PV→M9PV
F9B→M9B F9BV→M9BV

Note 3) Through hole mounting is not available when using auto switch types D-Y59, D-Y69, or D-Y7.

MHZ

MHQ

MHL2

MHR MHK

MHS

MHC2

MHT2

MHY2

MHW2

MRHQ

#### Series MHZ2

ø6



ø10 to ø25




ø32, ø40



#### Symbols:

#### **Double acting type**



#### Single acting type, normally open



Single acting type, normally closed



#### **Specifications**

Fluid			Air		
			ø6: 0.15 to 0.7MPa		
	Double	acting	ø10: 0.2 to 0.7MPa		
Operating			ø16 to ø40: 0.1 to 0.7MPa		
pressure	Single	Normally open	ø6: 0.3 to 0.7MPa		
	acting		ø10: 0.35 to 0.7MPa		
	J	Normally closed	ø16 to ø40: 0.25 to 0.7MPa		
Ambient a	Ambient and fluid temperature		−10 to 60°C		
Repeatabil	ity		ø6 to ø25: ±0.01mm		
Kepealabii	ity		ø32, ø40: ±0.02mm		
Maximum		a fraguesa	ø6 to ø25: 180c.p.m.		
waximum	operatir	ng frequency	ø32, ø40: 60c.p.m.		
Lubricatio	n		Non-lube		
Action			Double acting, Single acting		
Auto switch (option) Note)			Solid state switch (3 wire, 2 wire)		

Note) Refer to pages 2.11-1 for details regarding auto switch specifications.

#### **Models**

Action		Model	Bore size (mm)	Gripping for Effective External gripping force	ce per finger	Opening/ Closing stroke (both sides) mm	Note 2) Weight
		MHZ2-6D	6	3.3	6.1	4	27
		MHZ2-10D(N)	10	11	17	4	55
Doubl	^	MHZ2-16D(N)	16	34	45	6	115
acting	_	MHZ2-20D(N)	20	42	66	10	235
	,	MHZ2-25D(N)	25	65	104	14	430
		MHZ2-32D	32	158	193	22	715
		MHZ2-40D	40	254	318	30	1275
		MHZ2-6S	6	1.9		4	27
	open	MHZ2-10S(N)	10	7.1		4	55
	Normally op	MHZ2-16S(N)	16	27		6	115
		MHZ2-20S(N)	20	33	_	10	240
	Ë	MHZ2-25D(N)	25	45		14	435
	ž	MHZ2-32S	32	131		22	760
Single		MHZ2-40S	40	217		30	1370
acting		MHZ2-6C	6		3.7	4	27
	sed	MHZ2-10C(N)	10		13	4	55
	closed	MHZ2-16C(N)	16		38	6	115
		MHZ2-20C(N)	20	_	57	10	240
	Normally	MHZ2-25C(N)	25		83	14	430
	Š	MHZ2-32C	32		161	22	760
		MHZ2-40C	40		267	30	1370

Note 1) Values based on pressure of 0.5MPa, gripping point L = 20mm, at center of stroke. Note 2) Values excluding weight of auto switch.


#### **Options**

#### • Body options/End boss type

	Body options/End bods type										
	Piping port position	Type of piping port							Applicable model		
Symbol		MHZ2-6	MHZ2-10	MHZ2-16	MHZ2-20	MHZ2-25	MHZ2-32	MHZ2-40	Double acting	Single acting	
Nil	Basic type	M	13	M5					•	•	
E	Side ported		M3	M5					•	•	
W	Axial port		With ø4 C	One-touch t	fitting for co	axial tube	_		•	_	
K	Axial port		With ø4 One-touch fitting			fitting	_			•	
M	Axial port		M5			_	_		•		

<sup>\*</sup> For detailed body option specifications, refer to option specifications on page 2.1-29.

#### Clean Room Series: Air Gripper



#### Applicable auto switches/\* Refer to pages 2.11-1 for detailed auto switch specifications

										•					
	0			Wiring (output)				Auto switch	h part no.	. Lead wire length (r			Note 2) Flexible	A I	
Type	Special	Electrical			Load voltage		Electrical ent	ry direction	0.5	3	5	lead wire	Applicab load		
	function	entry	light		D	С	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)	loau	
				3 wire				F9NV	F9N	•	•	_	0		
5				(NPN)				F8N	_	•	•	0	0		
ĕ.ĕ.		Grommet	Yes	3 wire (PNP)	24V 12V	12)/		F9PV	F9P	•	•	_	0	]	Relay,
Sol	_	Gioillillet				12V   -		F8P	_	•	•	0	0	_	PLC
Solid state switch				2 wire				F9BV	F9B	•	•	_	0		
								F8B	_	•	•	0	0		

<sup>\*</sup> Lead wire length symbols: 0.5m ..... Nil (Example) F9N 3m ...... L (Example) F9NL 5m ...... Z (Example) F9NZ

Note 1) When using a D-F8□ switch, mount it at a distance of 10mm or more from magnetic substances such as iron, etc.

Note 2) Add "-61" at the end of the part number for the flexible lead wire.




These auto switches have been changed Contact SMC or view www.smcworld.com

F9N→M9N F9NV→M9NV F9P→M9P F9PV→M9PV F9B→M9B F9BV→M9BV

#### **Specifications**

Fluid	Air				
Operating pressure	ø10: 0.2 to 0.7MPa ø16 to ø25: 0.1 to 0.7MPa				
Ambient and fluid temperature	−10 to 60°C				
Repeatability	±0.01mm				
Maximum operating frequency	180 c.p.m.				
Lubrication	Non-lube				
Action	Double acting				
Particulate generation grade	Grade 2				
Auto switch (option)	Solid state switch (3 wire, 2 wire)				





#### Relief port

The concentrated vacuuming of internally generated particulates prevents them from spreading into the clean room.

For details, refer to SMC Information "Clean Series: Air Gripper Series 11-MHZ2" (98-E461).



MHZ

MHQ

MHL2

MHK

MHS

MHC2

MHT2

MHY2


MHW2


MRHQ

<sup>\*</sup> Auto switches marked with a "O" symbol are produced upon receipt of order.


#### Construction/MHZ2-6□

#### Double acting/with fingers open







#### Double acting/with fingers closed



#### Single acting/normally open



#### Single acting/normally closed



#### Parts list

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitrided
8	Magnet holder	Stainless steel	
9	Holder	Brass	Electroless nickel plated
10	Holder lock	Stainless steel	
11	Сар	Aluminum alloy	Clear anodized
12	Bumper	Urethane rubber	
13	Magnet	Rare earth magnet	Nickel plated

#### Parts list

No.	Description	Material	Note
14	Steel balls	High carbon chromium bearing steel	
15	Needle roller	High carbon chromium bearing steel	
16	C type snap ring	Carbon steel	Nickel plated
17	Exhaust plug	Brass	Electroless nickel plated
18	Exhaust filter	Polyvinyl formal	
19	N.O. spring	Stainless steel spring wire	
20	N.C. spring	Stainless steel spring wire	
21	Rod seal	NBR	
22	Piston seal	NBR	
23	Gasket	NBR	
24	Gasket	NBR	

#### Replacement parts: Seal kits

to prince in the part of the p									
Seal kit no.	Description								
MHZ6-PS	Kit includes items 21, 22, 23 and 24 from the table above.								


 $<sup>\</sup>ast$  Seal kits consist of items 21, 22, 23 and 24 in one kit, and can be ordered using the seal kit number.


Note) Contact SMC when replacing seals.




#### Construction/MHZ2-10□ to 40□

#### Double acting/with fingers open






#### Double acting/with fingers closed




#### Parts list

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	ø10, ø16: Stainless steel ø20 to ø40: Aluminum alloy	ø20 to ø40: Hard anodized
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitrided
8	Сар	ø10 to ø25: Synthetic resin ø32, ø40: Aluminum alloy	ø32, ø40: Clear anodized
9	Bumper	Urethane rubber	
10	Rubber magnet	Synthetic rubber	

#### Single acting/normally open



#### Single acting/normally closed



MHZ MHQ

MHL2

MHR MHK

MHS

MHC2

MHT2

MHY2

MHW2

MRHQ

Auto Switch

Parts list

No.	Description	Material	Note							
11	Steel balls	High carbon chromium bearing steel								
12	Needle roller	High carbon chromium bearing steel								
13	Parallel pin	Stainless steel								
14	C type snap ring	Carbon steel	Nickel plated							
15	Exhaust plug A	Brass	Electroless nickel plated							
16	Exhaust filter A	Polyvinyl formal								
17	N.O. spring	Stainless steel spring wire								
18	N.C. spring	Stainless steel spring wire								
19	Rod seal	NBR								
20	Piston seal	NBR								
21	Gasket	NBR								


#### Replacement parts: Seal kits

	•							
		Description						
MHZ2-10D	MHZ2-16D	MHZ2-20D	MHZ2-25D	MHZ2-32D	MHZ2-40D	Kits include items 19, 20 and 2		
MHZ10-PS	MHZ16-PS	MHZ20-PS	MHZ25-PS	MHZ32-PS	MHZ40-PS	from the table above.		


<sup>\*</sup> Seal kits consist of items 19, 20 and 21 in one kit, and can be ordered using the seal kit number for each cylinder bore size.

#### **Dimensions**


MHZ2-6□ Double acting/Single acting Basic type Scale: 100%




\* For single action, the port on one side is a breathing hole.




# Auto switch mounting groove dimensions




MHZ2-10□ Scale: 90% Double acting/Single acting






Finger position/Narrow type



Auto switch mounting groove dimensions

2-M3 thread depth 6 (mounting thread)



Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.

MHZ

MHQ

MHL2

MHK

MHS

MHC2

MHT2

MHY2

MHW2


MRHQ


#### **Dimensions**

#### MHZ2-16□


**Scale: 65%** 

Double acting/Single acting
Basic type






#### Finger position/Narrow type




# Auto switch mounting groove dimensions

2 x M4 thread depth 4.5 (mounting thread)





Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.


MHZ2-20□ Double acting/Single acting Basic type Scale: 60%



\* For single action, the port on one side is a breathing hole.








# Auto switch mounting groove dimensions

# MHZ2-20 N When closed 7.2.7 besod 7.2.7 hen open with the control of the control



Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.

MHZ

MHQ

MHR

MHL<sub>2</sub>

MHK

MHS

MHC2

MHT2

MHY2


MHW2


MRHQ

#### **Dimensions**


#### MHZ2-25□ Double acting/Single acting Basic type

**Scale: 50%** 






#### Finger position/Narrow type



#### Auto switch mounting groove dimensions




Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.


#### MHZ2-32□ Double acting/Single acting Basic Type


#### **Scale: 40%**


The values inside ( ) are dimensions for the single acting type.




\* For single action, the port on one side is a breathing hole.







Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.



MHR

MHZ

MHQ

MHL2

MHK MHS

MHC2

MHT2

MHY2

MHW2

#### **Dimensions**


#### **MHZ2-40**□ **Scale: 40%** Double acting/Single acting The values inside ( ) are dimensions for the single acting type. Basic type 4 x M8 М5 (attachment mounting thread) (finger closing port)\* 28 12 17 9 38 (45) M5 (finger opening port)\* ø5H9 $^{+0.030}_{0}$ depth 5 \* For single action, the port on one side is a breathing hole. 4 x M8 thread depth 16 (mounting thread) 14 ±0.02 14 0.1 Prepared hole dia. 6.6 through (mounting thread) Note) 0 <del>(</del> 119 72 56 56 29 ±0.02 ø42H9 <sup>+0.062</sup><sub>0</sub> depth 4 When open 60 $^{+2.7}_{0}$ When closed 30 $^0_{-0.5}$ 36 49 (62) 32 <u>15</u> 83 (96) 48±0.1 139 (152) 2 x M8 thread depth 17 (mounting thread) 58 (71) 6.2 Auto switch mounting groove 5 0 (for D-Y□) 0 33 2 x M8 thread depth 13 (mounting thread) Auto switch mounting groove (for D-F□)

Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.

# Standard Type/Series MHZ2 Finger Options

# **Side Tapped Mounting [1/N1]**

# Through Holes in Opening/Closing Direction [2/N2]



4-H Attachment mounting hole	ο · •
	<b>†</b>
	Unit: mm

				Unit: mm
Model	Α	В	С	MM
MHZ2- 6□1	2.5	5	2	M2
MHZ2-10□ 1 □	3	5.7	2	M2.5
MHZ2-16□ 1 □	4	7	2.5	M3
MHZ2-20□ 1 □	5	9	4	M4
MHZ2-25□ 1 □	6	12	5	M5
MHZ2-32□1□	7	14	6	M6
MHZ2-40□1□	9	17	7	M8

 $<sup>\</sup>ast$  Specifications and dimensions other than the above are the same as the basic type (including narrow type).

Model В Н MHZ2- 6□2 2.5 2.4 MHZ2-10□ 2 □ 3 5.7 2.9 MHZ2-16□ <sup>2</sup><sub>N2</sub>□ 3.4 MHZ2-20□ 2 □ 5 9 4.5 MHZ2-25 | 2 | | 6 5.5 12 MHZ2-32□2□ 14 6.6 MHZ2-40□2□ 17

# MHZ

MHQ

MHL2

MHR

MHK

MHS

MHC2

MHT2


MHY2

MHW2

MRHQ

Unit: mm Auto Switch

# Flat Type Fingers [3]



Model	Α	В	С	D	F		G Closed	J	К	ММ	L	w	Weight g
MHZ2- 6□3 *1)	2	3.5	7.2	7.5	_	5 +1.2 - 0.8	1 +0.2	_	_	M2	3	4 -0.05	26
MHZ2-10 3 *2), *3)	2.45	6	5.2	10.9	2	5.4 +2.2	1.4 -0.2	4.45	2H9 +0.025	M2.5	5	5 -0.05	55
MHZ2-16□3□ *2), *3)	3.05	8	8.3	14.1	2.5	7.4 +2.2	1.4 -0.2	5.8	2.5H9 <sup>+0.025</sup>	M3	6	8 -0.05	115
MHZ2-20 3 *2), *3)	3.95	10	10.5	17.9	3	11.6 +2.3	1.6 0	7.45	3H9 +0.025	M4	8	10 -0.05	235
MHZ2-25 3 *2), *3)	4.9	12	13.1	21.8	4	16 +2.5	2 0 -0.2	8.9	4H9 +0.030	M5	10	12 -0.05	420
MHZ2-32□3□	7.3	20	18	34.6	5	25 <sup>+2.7</sup>	3 0	14.8	5H9 +0.030	M6	12	15 -0.05	740 (785) *4)
MHZ2-40□3□	8.7	24	22	41.4	6	33 +2.9	3 0	17.7	6H9 +0.030	M8	16	18 -0.05	1335 (1430) *4)

 $<sup>*1)</sup> To mount attachments, use M2 hexagon socket head cap screws with \emptyset 3.3 top diameter, or JISB1101 type M2 round head screws.$ 

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type (including narrow type).

<sup>\*2)</sup> Specifications and dimensions other than the above are the same as the basic type (including narrow type).

<sup>\*3)</sup> The overall length is the same as the MHQ(G) flat finger type.

 $<sup>\</sup>ast 4)$  The values inside ( ) are for the single acting type


# **Standard Type/Series MHZ2**

# **Body Options: End Boss Type**

# Applicable Models

			Type of P	iping Port	Applicable model				
Symbol	Piping port position	MHZ2-10	MHZ2-16	MHZ2-20 MHZ2-25		Double acting	Single	acting	
		IVII122-10	WIF122-10	IVINZZ-ZU IVINZZ-Z5	Double acting	Normally open	Normally closed		
E	Side ported	M3		M5		•	•	•	
W		With	ø4 One-touch fi	itting for coaxial	tube	•		_	
K	Axial port	With ø4 One-touch fitting — ●						•	
M			M5 >	0.8		•	•		

# Side Ported [E]




					Ur	nit: mm
Model	Kit no.	Α	В	D1	D2	Е
MHZ2-10□□	MHZ-A1010	15	7	12f8 <sup>-0.016</sup> <sub>-0.043</sub>	11	52.8
MHZ2-16□□	MHZ-A1610	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	58.7
MHZ2-20□□	MHZ-A2010	22	12	20f8 -0.020 -0.053	19	70.5
MHZ2-25□□	MHZ-A2510	25	15	25f8 <sup>-0.020</sup> <sub>-0.053</sub>	24	82.9

Other dimensions and specifications correspond to the standard type.

- \* Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

# Axial Port (One-Touch Fitting for Coaxial Tubing) [W]




- \* Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

#### Unit: mm D1 D2 Ε Model 12f8 -0.016 MHZ2-10□□ 15 7 11 52.8 16f8 -0.016 MHZ2-16□□ 20 10 58.7 20f8 -0.020 -0.053 MHZ2-20□□ 12 19 70.5 25f8 -0.020 -0.053 MHZ2-25□□ 82.9

Other dimensions and specifications correspond to the standard type

# Reference symbol




Specification Model	TW04B-20		
Outside diameter	4mm		
Max. operating pressure	0.6MPa		
Min. bending radius	10mm		
Operating temperature	–20 to 60°C		
Material	Nylon 12		

Applicable coaxial tubing

# **Changing from Coaxial to Single Tubing**


Changing to single tubing is possible by using a branch "Y" or branch tee fitting

In this case particularly, single tube fittings and tubing for  $\emptyset 3.2$  will be necessary.




# Branch tee, Different diameter tee, Branch "Y", Male run tee

Refer to catalog CAT.E004-A "Coaxial Air Tubing System" regarding coaxial tubing.





# Axial Port (with One-touch Fitting) [K]



- \* Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

				Un	it: mm
Model	Α	В	D1	D2	E
MHZ2-10□□	15	7	12f8 <sup>-0.016</sup> <sub>-0.043</sub>	11	52.8
MHZ2-16□□	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	58.7
MHZ2-20□□	22	12	20f8 <sup>-0.020</sup> <sub>-0.053</sub>	19	70.5
MHZ2-25□□	25	15	25f8 -0.020 -0.053	24	82.9


Other dimensions and specifications correspond to the standard type.

# Applicable tubing

Description/ Model	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coiled tubing
Specification	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter mm	4	4	4	4
Max. operating pressure MPa	1.0	0.8	0.5	0.5
Min. bending radius mm	13	12	10	_
Operating temperature °C	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane

Refer to catalog CAT. E501-B "Air Fittings and Tubing" regarding One-touch fittings and tubing.

# Axial Port (M5 Port) [M]



				01	IIC. 1111111
Model	Α	В	D1	D2	E
MHZ2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	52.8
MHZ2-16□□	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	58.7
MHZ2-20□□	22	12	20f8 <sup>-0.020</sup> -0.053	19	70.5
MHZ2-25□□	25	15	25f8 -0.020 -0.053	24	82.9

Other dimensions and specifications correspond to the standard type.

MHR

MHS

- \* Refer to the dimension table
- \* When auto switches are used, side mounting with through holes is not possible

# Weights

Unit: a

				Offic. 9
Model		End boss ty	pe (symbol)	
Wodel	E	W	K	M
MHZ2-10□□	65	64	66	65
MHZ2-16□□	148	147	148	147
MHZ2-20□□	277	277	277	277
MHZ2-25□□	495	495	496	494

MHZ

MHQ MHL<sub>2</sub>

MHK

MHC2 MHT2

MHY2

MHW2


**MRHQ** Auto Switch

# **Parallel Type** Air Gripper

# **Long Stroke**

# Series MHZL2

**How to Order** 



Applicable auto switches/\* Refer to pages 2.11-1 for detailed auto switch specifications.

	Chasial	F1 1: 1	la dia atau	\A.C. :	L and valtage			Auto switc	h part no.	Lead w	ire leng	th (m)*	Note 2) Flexible		Applicable model		Applicab	el .																								
Type	Special function	Electrical entry	Indicator light	Electrical entry direction   0.5   3   5   lead wire   7		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		Load voltage		3			ø10	ø16	ø20	ø25
	Tarrottori	Citily	ligiti	(output)		DC	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)	load		טוש	טוש	W20	W23																							
						5V, 12V		Y69A	Y59A	•	•	0	Standard	IC circuit		•	•	•	•																							
				3 wire (NPN)	vire NP)	12V		F9NV	F9N	•	•	_	0				•	•	•																							
				(INPIN)		120		F8N	_	•	•	0	0				•	•	•																							
				2 veine		5V, 12V		Y7PV	Y7P	•	•	0	Standard	IC circuit	t	•	•	•	•																							
£	_			3 wire (PNP)		24V	24V	12V		F9PV	F9P	•	•	_	0				•	•	•																					
switch				(1 141 )				24V	24V	24V	24V	24V	24V	120		F8P	_	•	•	0	0				•	•	•															
		Grommet	Yes											24V	24V			Y69B	Y59B	•	•	0	0	—	Relay,	•	•	•	•													
tate		Giominici	163	2 wire												v		12V		F9BV	F9B	•	•	_	0		PLC		•	•	•											
S								F8B	_	•	•	0	0				•	•																								
Solid state				3 wire		5V, 12V		Y7NWV	Y7NW	•	•	0	Standard	IC circuit				•	•																							
	Diagnostic		(NI												(NPN)		12V		F9NWV	F9NW	•	•	0	0	_				•	•												
	indication			3 wire		5V, 12V		Y7PWV	Y7PW	•	•	0	Standard	IC circuit				•																								
	(2 colour			(PNP)			F9PWV	F9PW	•	•	0	0					•	•																								
	indicator)			2 wire			Y7BWV	Y7BW	•	•	0	Standard					•	•																								
				Z WIIE				F9BWV	F9BW			0	0					•																								

\* Lead wire length symbols: 0.5m ......Nil (Example) F9N 3m .....L (Example) F9NL

5m..... Z (Example) Y59AZ \* Auto switches marked with a "O" symbol are produced upon receipt of order.

Note 1) Use caution regarding hysteresis in the 2 color indicator types. When using this type, refer to "Auto Switch Hysteresis" on page 2.1-52.

Note 3) Through hole mounting is not possible when using auto switch types

Note 2) Add "-61" at the end of the part number for the flexible lead wire.

(Examples)

When ordering with an air gripper

MHZ 2-16D-F9NVS- 61 Flexible lead wire

When ordering auto switches only D-F9PL-61

Flexible lead wire



# Parallel Type/Long Stroke Series MHZL2




# **Specifications**

Fluid			Air				
	Double acting		Double seting		Double seting		ø10: 0.2 to 0.7MPa
Operating			ø16 to ø25: 0.1 to 0.7MPa				
pressure	Single	Normally open	ø10: 0.35 to 0.7MPa				
	acting	Normally closed	ø16 to ø25: 0.25 to 0.7MPa				
Ambient and	d fluid te	mperature	−10 to 60°C				
Repeatabi	lity		±0.01mm				
Maximum	operati	ng frequency	120c.p.m.				
Lubricatio	n		Non-lube				
Action			Double acting, Single acting				
Auto switch	h (opti	on) Note)	Solid state switch (3 wire, 2 wire)				

Note) Refer to pages 2.11-1 for details regarding auto switch specifications.

# Symbols: Double acting type



Single acting type, normally open



Single acting type, normally closed



# **Models**

Action		Model	Bore size (mm)	Gripping Gripping forc Effective External gripping force	Opening/ Closing stroke (both sides) mm	Note 2) Weight	
		MHZL2-10D	10	11	17	8	60
Double		MHZL2-16D	16	34	45	12	135
acting		MHZL2-20D	20	42	66	18	270
		MHZL2-25D	25	65	104	22	470
	oben	MHZL2-10S	10	7.1		8	70
	ly op	MHZL2-16S	16	27		12	145
	Normally	MHZL2-20S	20	33	_	18	290
Single		MHZL2-25S	25	50		22	515
acting	closed	MHZL2-10C	10		13	8	70
	y clo	MHZL2-16C	16		38	12	140
	Normally o	MHZL2-20C	20		57	18	290
Nor		MHZL2-25C	25		85	22	515

Note 1) Values based on pressure of 0.5MPa, gripping point L = 20mm, at center of stroke. Note 2) Values excluding weight of auto switch.

# **Options**

# Body options/End boss type

	Piping port		Applicable model				
Symbol	Piping port position	MHZL2-10	MHZL2-16	MHZL2-20	MHZL2-25	Double acting	Single acting
Nil	Basic type	M3		•	•		
E	Side ported	М3			•	•	
W	Axial port	With ø4	One-touch f	itting for coax	ial tube	•	_
K	Axial port		With ø4 One-touch fitting				
M	Axial port		M5				

st For detailed body option specifications, refer to option specifications on pages 2.1-39 and 2.1-40.

MHZ

MHQ MHL2

MHR

MHK

MHS

MHC2


MHT2 MHY2


MHW2

MRHQ


# Construction/MHZL2-10□ to 25□

# Double acting/with fingers open






# Double acting/with fingers closed




# Parts list

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	ø10, ø16: Stainless steel	ø20, ø25:
	Piston	ø20, ø25: Aluminum alloy	Hard anodized
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitrided
8	Сар	Aluminum alloy	Clear anodized
9	Bumper	Urethane rubber	
10	Rubber magnet	Synthetic rubber	

# Single acting/normally open



# Single acting/normally closed



# Parts list

Description	Material	Note
Steel balls	High carbon chromium bearing steel	
Needle roller	High carbon chromium bearing steel	
Parallel pin	Stainless steel	
C type snap ring	Carbon steel	Nickel plated
Exhaust plug A	Brass	Electroless nickel plated
Exhaust filter A	Polyvinyl formal	
Spring	Stainless steel spring wire	
Rod seal	NBR	
Piston seal	NBR	
O-ring	NBR	
	Steel balls Needle roller Parallel pin C type snap ring Exhaust plug A Exhaust filter A Spring Rod seal Piston seal	Steel balls       High carbon chromium bearing steel         Needle roller       High carbon chromium bearing steel         Parallel pin       Stainless steel         C type snap ring       Carbon steel         Exhaust plug A       Brass         Exhaust filter A       Polyvinyl formal         Spring       Stainless steel spring wire         Rod seal       NBR         Piston seal       NBR


# Replacement parts: Seal kits

	Seal	kit no.	Description	
MHZL2-10D	MHZL2-16D	MHZL2-20D	MHZL2-25D	Kits include items 18, 19 and 20 from the table above.
MHZL10-PS	MHZL16-PS	MHZL20-PS	MHZL25-PS	Nits include items 16, 19 and 20 nom the table above.

<sup>\*</sup> Seal kits consist of items 18, 19 and 20 in one kit, and can be ordered using the seal kit number for each cylinder bore size.




# **Dimensions**



Noe) When using auto switches D-Y59, D-Y69 and D-Y7, through hole mounting is not possible.

# **Dimensions**




Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.


MHZL2-20□ Double acting/Single acting Basic type


Scale: 60%

The values inside ( ) are dimensions for the single acting type.



\* For single action, the port on one side is a breathing hole.






2 x M5 thread depth 8

(mounting thread)

# Auto switch mounting groove dimensions



Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.

MHC2

MHZ

MHQ

MHL2

**MHR** 

MHK

MHS

MHT2

MHY2


MHW2

# **Dimensions**


MHZL2-25□ Double acting/Single acting **Basic type** 


**Scale: 50%** 

The values inside ( ) are dimensions for the single acting type.




\* For single action, the port on one side is a breathing hole.






2 x M6 thread depth 10 (mounting thread)

# Auto switch mounting groove dimensions




Note) When using D-Y59, D-Y69 and D-Y7 type auto switches, through hole mounting is not possible.



# Long Stroke/Series MHZL2 **Finger Options**

# **Side Tapped Mounting [1]**

# **Through Holes in Opening/Closing Direction [2]**




4-H Attachment mounting hole	σ.Φ-
	Ф Ф
	Φ Φ

				Unit: mm
Model	Α	В	С	MM
MHZL2-10□1□	3	5.7	2	M2.5
MHZL2-16□1□	4	7	2.5	M3
MHZL2-20□1□	5	9	4	M4
MHZL2-25□1□	6	12	5	M5

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.

Unit: mm Model В Н MHZL2-10□2□ 3 5.7 2.9 MHZL2-16□2□ 4 3.4 MHZL2-20□2□ 5 9 4.5 MHZL2-25□2□ 6 12 5.5

# Flat Type Fingers [3]



4-MM thread depth L  Attachment mounting thread						
(a) (b) (c) (c) (c) (c) (c) (c) (c) (c) (c) (c						
(A)						

			_	_			G						Weig	ght g
Model	A	В	С	D	F	Open	Closed	J	K	ММ	L	W		Single acting
MHZL2-10□3□	2.45	7	5.2	11.9	2	9.4 +2.2	1.4 -0.2	4.95	2H9 +0.025	M2.5	5	5 0 -0.05	60	70
MHZL2-16□3□	3.3	9	8.3	15.6	2.5	13.4 +2.2	1.4 -0.2	6.55	2.5H9 <sup>+0.025</sup>	M3	6	8 -0.05	135	145
MHZL2-20□3□	3.95	12	10.5	19.9	3	19.6 +2.4	1.6 0 -0.2	8.45	3H9 <sup>+0.025</sup>	M4	8	10 0	270	290
MHZL2-25□3□	4.9	14	13.1	23.8	4	24 +2.6	2 0 -0.2	9.9	4H9 +0.030	M5	10	12 -0.05	460	505

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.

MHZ

MHQ

MHL2

MHR

MHK

**MHS** 

MHC2

MHT2

MHY2

MHW2

MRHQ

Auto Switch

Unit: mm

<sup>\*</sup> Specifications and dimensions other than the above are the same as the basic type.


# Long Stroke/Series MHZL2

# **Body Options: End Boss Type**

# **Applicable Models**

		Type of Piping Port			Applicable model				
Symbol	Piping port position	MHZL2-10	MHZL2-16	MHZL2-20	MHZL2-25	Double acting	Single	acting	
		IVITIZEZ-10	IVITIZEZ-10	WITZLZ-20 WITZLZ-25		Double acting	Normally open	Normally closed	
E	Side ported	M3		M5		•	•	•	
W		With	ø4 One-touch f	itting for coaxial	tube	•	_	_	
K	Axial port		With ø4 One	-touch fitting		_	•	•	
M			M5 >	¢ 0.8	_	•	•		

# Side Ported [E]




						Unit	: mm
Model	Kit no.	Α	В	D1	D2	E1	E2
MHZL2-10□□	MHZ-A1010	15	7	12f8 <sup>-0.016</sup> <sub>-0.043</sub>	11	52.8	62.8
MHZL2-16□□	MHZ-A1610	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	61.4	66.4
MHZL2-20□□	MHZ-A2010	22	12	20f8 <sup>-0.020</sup> <sub>-0.053</sub>	19	75.7	81.7
MHZL2-25□□	MHZ-A2510	25	15	25f8 <sup>-0.020</sup> <sub>-0.053</sub>	24	86.2	96.2

Other dimensions and specifications correspond to the standard type

- Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

# Axial Port (One-touch Fitting for Coaxial Tubing) [W]



- \* Refer to the dimension table.
- $\ast$  When auto switches are used, side mounting with through holes is not possible.

#### Unit: mm В D1 D2 E1 Model 12f8 -0.016 MHZL2-10□□ 15 7 11 52.8 16f8 -0.016 MHZL2-16□□ 10 61.4 20f8 -0.020 -0.053 MHZL2-20□□ 22 12 19 75.7 25f8 -0.020 -0.053 MHZL2-25□□ 86.2

Other dimensions and specifications correspond to the standard type

# Reference symbol

Specification Model	TW04B-20
Outside diameter	4mm
Max. operating pressure	0.6MPa
Min. bending radius	10mm
Operating temperature	-20 to 60°C


Nylon 12

Applicable coaxial tubing

# **Changing from Coaxial to Single Tubing**


Changing to single tubing is possible by using a branch "Y" or branch tee fitting

In this case particularly, single tube fittings and tubing for ø3.2 will be necessary.




# Branch tee, Different diameter tee, Branch "Y", Male run tee

Refer to catalogue CAT.E004-A "Coaxial Air Tubing System" regarding coaxial tubing.



# Axial Port (with One-touch Fitting) [K]



- \* Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

				Ur	nit: mm
Model	Α	В	D1	D2	E2
MHZL2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	62.8
MHZL2-16□□	20	10	16f8 <sup>-0.016</sup> -0.043	15	66.4
MHZL2-20□□	22	12	20f8 <sup>-0.020</sup> -0.053	19	81.7
MHZL2-25□□	25	15	25f8 -0.020 -0.053	24	96.2


Other dimensions and specifications correspond to the standard type.

# Applicable tubing

Description Model	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coiled tubing
Specification	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter mm	4	4	4	4
Max. operating pressure MPa	1.0	0.8	0.5	0.5
Min. bending radius mm	13	12	10	_
Operating temperature °C	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane

Refer to catalog CAT. 501-B "Air Fittings and Tubing" regarding One-touch fittings and tubing.

# Axial Port (M5 Port) [M]



				UI	III. IIIIII
Model	Α	В	D1	D2	E2
MHZL2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	62.8
MHZL2-16□□	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	66.4
MHZL2-20□□	22	12	20f8 <sup>-0.020</sup> -0.053	19	81.7
MHZL2-25□□	25	15	25f8 -0.020 -0.053	24	96.2

Other dimensions and specifications correspond to the standard type.

MHK

- \* Refer to the dimension table.
- \* When auto switches are used, side mounting with through holes is not possible.

	 	,	 	,	 

# Weights

Unit: g End boss type (symbol) Model K M Double acting Single acting **MHZL2**□-10□□ 70 80 70 80 80 **MHZL2**□-16□□ 170 180 170 180 180 330 330 **MHZL2**□-20□□ 310 310 330 **MHZL2**□-25□□ 535 580 535 580 580

MHZ MHQ

I Initi mi

MHL<sub>2</sub>

MHR

MHS

MHC2

MHT2

MHY2

MHW2


**MRHQ** Auto Switch

# **Parallel Type** Air Gripper

# With Dust Cover

# Series MHZJ2

# **How to Order**



\* Switch types D-Y5/6 and D-Y7 cannot be mounted when equipped with dust cover/MHZJ2.

Applicable auto switches/ \* Refer to pages 2.11-1 for detailed auto switch specifications.

		Clootrical	호	\\/iring	Load voltage		Auto switc	h part no.	Lead w	ire leng	th (m)*	Note 3) Flexible		A P I. I .		Applicable model							
Type	Special function	Electrical entry	isigi Bigi	型 (output)	Г	C	AC	Electrical en	ry direction		3	5	lead wire		cable	ø6	ø10	ø16	ø20	ø25			
	G.	Citaly	드	(Output)	L	,,,	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	(-61)			90	טוש	סוש	Ø20	Ø25			
	switch			3 wire (NPN)				F9NV	F9N	•	•	_	0			•	•	•	•	•			
			3 WIIE (INFIN)				F8N	_	•	•	0	0			•	•	•	•	•				
동			2 wire	3 wire (PNP)	]			F9PV	F9P	•	•	_	0			•	•	•	•	•			
š.		3 WIIE (FINE)	<i>'</i>			F8P	_	•	•	0	0			•	•	•	•	•					
		Grommet	Yes	2 wire	24V	12V	_	F9BV	F9B	•	•	_	0	_	Relay, PLC	•	•	•	•	•			
state				2 WIIE								F8B	_	•	•	0	0		FLC	•	•	•	•
Solid	Diagnostic indication			3 wire (NPN)				F9NWV	F9NW	•	•	0	0						•	•			
တိ	Diagnostic indication (2 colour indicator)			3 wire (PNP)				F9PWV	F9PW	•	•	0	0						•	•			
	,			2 wire			F9BWV	F9BW	•	•	0	0						•	•				
	Water resistant (2 colour indicator)							_	F9BA	_	•	0	0			•	•	•	•	•			

\* Lead wire length symbols: 0.5m ..... Nil (Example) F9N

3m ..... L (Example) F9NL (Example) F9NWZ

\* Auto switches marked with a "O" symbol are produced upon receipt of order.

Note 1) Use caution regarding hysteresis in the 2 colour indicator types. When using this type, refer to "Auto Switch Hysteresis" on page 2.1-52

Note 2) When using a D-F8 switch on sizes ø6 and ø10, mount it at a distance of 10mm or more from magnetic substances such as iron, etc.

Note 3) Add "-61" at the end of the part number for the flexible lead wire.

(Examples) When ordering with an air gripper

MHZ 2-16D-F9NVS-61

D-F9PL- 61

Flexible lead wire

When ordering auto switches only





# Parallel Type/With Dust Cover Series MHZJ2





Symbols:

Double acting type

Single acting type, normally open

Single acting type, normally closed

Fluid			Air		
			ø6: 0.15 to 0.7MPa		
	Double acting		ø10: 0.2 to 0.7MPa		
Operating			ø16 to ø25: 0.1 to 0.7MPa		
pressure	Cinalo	Normally open	ø6: 0.3 to 0.7MPa		
	Single acting	<u> </u>	ø10: 0.35 to 0.7MPa		
		Normally closed	ø16 to ø25: 0.25 to 0.7MPa		
Ambient a	nd fluic	l temperature	−10 to 60°C		
Repeatabi	lity		±0.01mm		
Maximum	operati	ng frequency	180c.p.m.		
Lubrication			Non-lube		
Action			Double acting, Single acting		
Auto switch (option) Note)		on) <sup>Note)</sup>	Solid state switch (3 wire, 2 wire)		

Note) Refer to pages 2.11-1 for details regarding auto switch specifications.

# **Models**

					Gripping	force Note 1)	Opening/		
				Bore		ce per finger	Ċlosing	Note 2)	
	Action	า	Model	size	Éffective		stroke	Weight	
				(mm)	External gripping force	Internal gripping force	(both sides) mm	g	
		MHZJ2- 6D		6	3.3	6.1	4	28	
			MHZJ2-10D	10	9.8	17	4	60	
	Double acting MHZJ2-16D MHZJ2-20D		16	30	40	6	130		
			20	42	66	10	250		
		MHZJ2-25D		25	65	104	14	460	
		en	MHZJ2- 6S	6	1.9		4	28	
		open	MHZJ2-10S	10	6.3		4	60	
		Normally	MHZJ2-16S	16	24	_	6	130	
		m	MHZJ2-20S	20	28		10	255	
	Single		MHZJ2-25S	25	45		14	264	
	acting	closed	MHZJ2- 6C	6		3.7	4	28	
		clos	MHZJ2-10C	10		12	4	60	
				16	_	31	6	130	
	MHZJ2-16C MHZJ2-20C MHZJ2-25C		20		56	10	255		
			25		83	14	460		

Note 1) Values based on pressure of 0.5MPa, gripping point L = 20mm, at center of stroke. Note 2) Values excluding weight of auto switch.

# **Options**

# Body options/End boss type

	Type of piping port Applicable									
	Piping port position		mo	del						
Symbol		MHZJ2-10	MHZJ2-16	MHZJ2-20	MHZJ2-25	Double acting	Single acting			
Nil	Basic type	M3 x 0.5		•	•					
E	Axial port	M3 x 0.5		M5 x 0.8						
W	Axial port	With ø	With ø4 One-touch fitting for coaxial tube							
K	Axial port	With ø4 One-touch fitting					•			
M	Axial port		_	•						

 $<sup>* \</sup> For \ detailed \ body \ option \ specifications, \ refer \ to \ option \ specifications \ on \ pages \ 2.1-50 \ and \ 2.1-51.$ 

MHZ

MHQ MHL2

MHR

MHK MHS

MHC2

MHT2

MHY2

MHW2

# Параллельный захват с пылезащитным колпаком



Ø10~25

# Технические характеристики

Среда	Очищенный сжатый воздух с со	держанием масла или без него		
Рабочий	Двустороннего действия	0.2 ~ 0.7		
диапазон (МПа)	Одностороннего действия	0.35 ~ 0.7		
Диапазон рабочих т	емператур (°C)	-10 ~ +60		
Точность позициони	рования (мм)	±0.01		
Макс. частота сраба	180			
Тип	Односторонненго, двустороннего действия			

# Номер для заказа

Диам. поршня	Двустороннего	Одностороннего действия				
(мм)	действия	Раскрыт без Подачи давления	Закрыт без Подачи давления			
10	MHZJ2-10D	MHZJ2-10S	MHZJ2-10C			
16	MHZJ2-16D	MHZJ2-16S	MHZJ2-16C			
20	MHZJ2-20D	MHZJ2-20S	MHZJ2-20C			
25	MHZJ2-25D	MHZJ2-25S	MHZJ2-25C			

# Условное обозначение

Двустороннего действия



Односторон. действ., раскрыт без подачи давления



Односторон. действ., закрыт без подачи давления



# Исполнение

Тип		Модель	Диам. поршня	Удерживающее при 0.5 МПа (		Длина хода на раскрытие,	Bec, (r)
		(MM)		наруж. захват	внутр. захват	(мм)	3500
Двустороннего де	ействия	MHZJ2-10D	10	9.8	17	4	60
		MHZJ2-16D	16	30	40	6	130
		MHZJ2-20D	20	42	66	10	250
		MHZJ2-25D	25	65	104	14	460
Одностороннего	Раскрыт без	MHZJ2-10S	10	6.3		4	60
действия	подачи давления	MHZJ2-16S	16	24		6	130
	552 150	MHZJ2-20S	20	28		10	255
		MHZJ2-25S	25	45		14	465
	Закрыт без	MHZJ2-10C	10		12	4	60
	подачи давления	MHZJ2-16C	16		31	6	130
		MHZJ2-20C	20		56	10	255
		MHZJ2-25C	25		83	14	460

<sup>\*</sup> Усилие приводится для средней точки на одном пальце


Более точные значения см. на диаграммах

Примечание: диаграммы эффективного удерживающего усилия - см. серию МНZ2


<sup>\*\*</sup> Вес указан без датчиков положения

# **Construction/MHZJ2-6**□

# Double acting/with fingers open




# Double acting/with fingers closed




# Parts list

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitrided
8	Magnet holder	Stainless steel	
9	Holder	Brass	Electroless nickel plated
10	Holder lock	Stainless steel	
11	Сар	Aluminum alloy	Clear anodized
12	Bumper	Urethane rubber	
13	Magnet	Rare earth magnet	Nickel plated
14	Steel balls	High carbon chromium bearing steel	
15	Needle roller	High carbon chromium bearing steel	
		CR	Chloroprene rubber
16	Dust cover	FKM	Fluoro rubber
		Si	Silicon rubber
17	C type snap ring	Carbon steel	Nickel plated
18	Exhaust plug	Brass	Electroless nickel plated
19	Exhaust filter	Polyvinyl formal	
20	N.O. spring	Stainless steel spring wire	
21	N.C. spring	Stainless steel spring wire	
22	Rod seal	NBR	
23	Piston seal	NBR	
24	Gasket	NBR	
25	Gasket	NBR	
		•	•

# Single acting/normally open



# Single acting/normally closed



# Replacement parts: Seal kits

Seal kit no.	Description
MHZJ6-PS	Kit includes items 22, 23, 24 and 25 from the table on the left.

<sup>\*</sup> Seal kits consist of items 22, 23, 24 and 25 contained in one kit, and can be ordered using the seal kit number.

Note) Contact SMC when replacing seals.


# Replacement parts: Dust covers

Material	Part no.
CR	MHZJ2-J6
FKM	MHZJ2-J6F
Si	MHZJ2-J6S




# Construction/MHZJ2-10□ to 25□

# Double acting/with fingers open




# Double acting/with fingers closed




# Parts list

IIST		
Description	Material	Note
Body	Aluminum alloy	Hard anodized
Piston	ø10, ø16: Stainless steel ø20, ø25: Aluminum alloy	ø20, ø25: Hard anodized
Lever	Stainless steel	Heat treated
Guide	Stainless steel	Heat treated
Finger	Stainless steel	Heat treated
Roller stopper	Stainless steel	
Lever shaft	Stainless steel	Nitrided
Сар	Aluminum alloy	Hard anodized
Bumper	Urethane rubber	
Rubber magnet	Synthetic rubber	
Steel balls	High carbon chromium bearing steel	
Needle roller	High carbon chromium bearing steel	
Parallel pin	Stainless steel	
C type snap ring	Carbon steel	Nickel plated
Exhaust plug A	Brass	Electroless nickel plated
Exhaust filter A	Polyvinyl formal	
N.O. spring	Stainless steel spring wire	
N.C. spring	Stainless steel spring wire	
Rod seal	NBR	
Piston seal	NBR	
Gasket	NBR	
	CR	Chloroprene rubber
Dust cover	FKM	Fluoro rubber
	Si	Silicon rubber
	Description Body Piston Lever Guide Finger Roller stopper Lever shaft Cap Bumper Rubber magnet Steel balls Needle roller Parallel pin C type snap ring Exhaust plug A Exhaust filter A N.O. spring N.C. spring Rod seal Piston seal Gasket	Description Material Body Aluminum alloy Piston Ø10, Ø16: Stainless steel Ø20, Ø25: Aluminum alloy Lever Stainless steel Guide Stainless steel Finger Stainless steel Roller stopper Stainless steel Lever shaft Stainless steel Cap Aluminum alloy Bumper Urethane rubber Rubber magnet Synthetic rubber Steel balls High carbon chromium bearing steel Needle roller High carbon chromium bearing steel Parallel pin Stainless steel C type snap ring Carbon steel Exhaust plug A Brass Exhaust filter A Polyvinyl formal N.O. spring Stainless steel spring wire N.C. spring Stainless steel spring wire Rod seal NBR Piston seal NBR Gasket NBR CR Dust cover

# Single acting/normally open



# Single acting/normally closed



Replacement parts: Seal kits

	Description			
MHZJ2-10□	MHZJ2-16□	MHZJ2-20□	MHZJ2-25□	Kits include Note 27 items 19, 20
MHZJ10-PS	MHZJ16-PS	MHZJ20-PS	MHZJ25-PS	and 21 from the table on the left

Note 2) Seal kits consist of items 19, 20 and 21 in one kit, and can be ordered using the seal kit number for each cylinder bore size.

#### Replacement parts: Dust covers

replacem	ent parts. Dt	ist covers		
Material		Par	t no.	
iviateriai	MHZJ2-10□	MHZJ2-16□	MHZJ2-20□	MHZJ2-25□
CR	MHZJ2-J10	MHZJ2-J16	MHZJ2-J20	MHZJ2-J25
FKM	MHZJ2-J10F	MHZJ2-J16F	MHZJ2-J20F	MHZJ2-J25F
Si	MH7J2-J10S	MH7J2-J16S	MH7J2-J20S	MH7J2-J25S

MHZ

MHQ MHL2

MHR

MHK MHS

MHC2

WITICZ


MHT2

MHY2

MHW2


# **Dimensions**

MHZJ2-6□ Double acting/Single acting Basic type Scale: 100%




 $\ast$  For single action, the port on one side is a breathing hole.






# Auto switch mounting groove dimensions





# MHZJ2-10□ Double acting/Single acting Basic type






4 x M3 thread depth 5.5 (mounting thread)






# Auto switch mounting groove dimensions



Note) When using auto switches, through hole mounting is not possible.



\* For single action, the port on one side is a breathing hole.

MHZ

MHQ

MHL2

MHK

MHS

MHC2

MHT2

MHY2

MHW2


MRHQ

# **Dimensions**


# **MHZJ2-16**□

**Double acting/Single acting Basic type** 


Scale: 60%




\* For single action, the port on one side is a breathing hole.




# Auto switch mounting






# MHZJ2-20□ Double acting/Single acting Basic type

# Scale: 60%



 $\ast$  For single action, the port on one side is a breathing hole.



MHC2

MHZ

MHQ

MHL2

**MHR** 

MHK


MHS

MHT2

MHY2

MHW2

Auto Switch



2.1


**Ø**SMC

# **Dimensions**


# **MHZJ2-25**□

Double acting/Single acting Basic type

Scale: 50%



\* For single action, the port on one side is a breathing hole.




# With Dust Cover/Series MHZJ2

# **Body Options: End Boss Type**

# **Applicable Models**

Symbol		Type of piping port				/	Applicable mode	I
	Piping port position	MHZJ2-10	MHZJ2-16	MHZJ2-20 MHZJ2-25	MUZ 12 20 MUZ 12 25	MUZ 12 20 MUZ 12 25	AUT 12 20 MUT 12 25 Double seting	Single acting
		WITIZJZ-10	WITIZJZ-10	WITIZJZ-ZU	IVITIZJZ-Z5	2-25 Double acting	Normally open	Normally closed
E	Side ported	M3	M5			•	•	•
W	Axial port	With	ø4 One-touch f	itting for coaxial	tube	•	_	_
K			With ø4 One	-touch fitting		_	•	•
M			M5 x 0.8				•	•

# Side Ported [E]




	1				nit: mm
Model	Α	В	D1	D2	E
MHZJ2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	40
MHZJ2-16□□	20	10	16f8 <sup>-0.016</sup> -0.043	15	43.5
MHZJ2-20□□	22	12	20f8 <sup>-0.020</sup> -0.053	19	51.7
MHZJ2-25□□	25	15	25f8 <sup>-0.020</sup> <sub>-0.053</sub>	24	61.3

Other dimensions and specifications correspond to the standard type.

- \* Refer to the dimension table
- \* When auto switches are used on Ø10, side mounting with through holes is not possible.

# Axial Port (One-touch Fitting for Coaxial Tubing) [W]



- \*Refer to the dimension table
- \*When auto switches are used on ø10, side mounting with through holes is not possible.

#### Unit: mm Model Α **D1** D2 Е 12f8 -0.016 -0.043 MHZJ2-10□□ 15 7 40 16f8 -0.016 -0.043 MHZJ2-16□□ 20 10 15 43.5 20f8 -0.020 MHZJ2-20□□ 22 12 19 51.7 25f8 -0.020 -0.053 MHZJ2-25□□ 25 24 61.3

Other dimensions and specifications correspond to the standard type.

# Reference symbol

• •	
Model Specification	TW04B-20
Outside diameter	4mm
Max. operating pressure	0.6MPa
Min. bending radius	10mm
Operating temperature	–20 to 60°C
Material	Nylon 12


# Applicable coaxial tubing

Model Specification	TW04B-20
Outside diameter	4mm
Max. operating pressure	0.6MPa
Min. bending radius	10mm
Operating temperature	–20 to 60°C
Material	Nylon 12

# **Changing from Coaxial to Single Tubing**


Changing to single tubing is possible by using a branch "Y" or branch

In this case particularly, single tube fittings and tubing for ø3.2 will be necessary.



# Branch tee, Different diameter tee, Branch "Y", Male run tee

Refer to catalogue CAT.E004-A "Coaxial Air Tubing System"





MHZ

MHQ

MHL<sub>2</sub>

**MHR** 

MHK

**MHS** 

MHC<sub>2</sub>

MHT2

MHY2

MHW2

**MRHQ** 


Auto

Switch

# With Dust Cover/Series MHZJ2

# **Body Options: End Boss Type**

# Axial Port (with One-touch Fitting) [K]



- \* Refer to the dimension table.
- $\ast$  When auto switches are used on ø10, side mounting with through holes is not possible.

				Un	it: mm
Model	Α	В	D1	D2	Е
MHZJ2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	40
MHZJ2-16□□	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	43.5
MHZJ2-20□□	22	12	20f8 <sup>-0.020</sup> -0.053	19	51.7
MHZJ2-25□□	25	15	25f8 -0.020 -0.053	24	61.3


Other dimensions and specifications correspond to the standard type

# Max. 5 Applicable tubing

Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coiled tubing
T0425	TS0425	TU0425	TCU0425B-1
4	4	4	4
1.0	8.0	0.5	0.5
13	12	10	_
-20 to 60	-20 to 60	-20 to 60	–20 to 60
Nylon 12	Nylon 12	Polyurethane	Polyurethane
	tubing T0425 4 1.0 13 -20 to 60	tubing tubing T0425 TS0425 4 4 1.0 0.8 13 12 -20 to 60 -20 to 60 Nylon 12 Nylon 12	tubing         tubing         tubing           T0425         TS0425         TU0425           4         4         4           1.0         0.8         0.5           13         12         10           -20 to 60         -20 to 60         -20 to 60

Refer to catalog CAT. E501-B "Air Fittings and Tubing" regarding One-touch fittings and tubing.

# Axial Port (M5 Port) [M]



				Un	it: mm
Model	Α	В	D1	D2	Е
MHZJ2-10□□	15	7	12f8 <sup>-0.016</sup> -0.043	11	40
MHZJ2-16□□	20	10	16f8 <sup>-0.016</sup> <sub>-0.043</sub>	15	43.5
MHZJ2-20□□	22	12	20f8 -0.020 -0.053	19	51.7
MHZJ2-25□□	25	15	25f8 -0.020 -0.053	24	61.3

Other dimensions and specifications correspond to the standard type.


- \* Refer to the dimension table.
- \* When auto switches are used on ø10, side mounting with through holes is not possible.

# Weights

Unit: g End boss type (symbol) Model Ε W K M MHZJ2-10□□ 70 70 70 70 **MHZJ2-16**□□ 165 165 165 165 MHZJ2-20□□ 290 290 290 290 MHZJ2-25□□ 525 525 525 525

# **Auto Switch Hysteresis**

Auto switches have hysteresis similar to micro switches. The adjustment of switch positions should be performed using the table below as a guide.




# **Hysteresis**

i iyatereara									
	D-Y59A, B		D-Y7	□W(V)	D-F9	□W(V)	D-F9BAL		
	D-Y69A, B D-Y7P(V)	D-F9□(V) D-F8□	Red light ON	Green light ON	Red light ON	Green light ON	Red light ON Green light C		
MHZ2-6□	No setting	0.5							
MHZ2-10□, MHZL2-10□	0.4	No setting	No s	etting	No s	etting			
MHZ2-16□, MHZL2-16□	0.4	0.5							
MHZ2-20□, MHZL2-20□	0.4	0.5	0.5	1	0.5	1	No setting		
MHZ2-25□, MHZL2-25□	0.4	0.5	0.5	1	0.5	0.5 1			
MHZ2-32□	0.4	0.5	0.5	1	0.5	1			
MHZ2-40□	0.4	0.5	0.5	1	0.5	1			
MHZJ2-6□		0.5					0.4	0.8	
MHZJ2-10□		0.5		No setting		0.4	8.0		
MHZJ2-16□	No setting	0.5	No setting				0.4	0.8	
MHZJ2-20□		0.5			0.5	1	0.4	0.8	
MHZJ2-25□		0.5			0.5	1	0.4	0.8	

# **Auto Switch Mounting**

When mounting auto switches, insert them into one of the air gripper's switch mounting grooves from the direction shown in the figure below. After setting in the desired mounting position, tighten the switch mounting screw (included) using a flat head watchmakers screw driver.



Note) When tightening the auto switch mounting screw, use a watchmakers screw driver with a handle diameter of about 5 to 6mm.

The tightening torque should be about 0.05 to 0.1N·m. As a rule, it should be turned about  $90^\circ$  beyond the point at which tightening can be felt.

MHZ MHQ

MHL2

MHR MHK MHS

MHC2

MHT2

MHY2

MHW2



# **Auto Switch Protrusion from the Body End Surface**

- The amount of auto switch protrusion from the body's end surface is as shown in the table below.
- Use this as a guide when mounting, etc.
- $\bullet$  With D-F8  $\!\Box$  , there is no auto switch protrusion from the body's end surface.

# Standard body

		Lead w	rire type			In-line			Perpendicular			
											n	
		Illustra	ition								Д	
\												
\			·				<u></u>					
'	\	1 Plus			L		L				L **	
	\	Sh			-							
	\	Alto SWI	Cy \			_		_				
	\	CO.	/									
	\	Model	ii.	D-Y59□	B \/==\	D =0=	D =0=14	D 50041	D-Y69□	D \/==\	D ====1/	D ======
	\	Model Supplies	9	D-Y7P	D-Y7□W	D-F9□	D-F9□W	D-F9BAL	D-Y7PV	D-Y7□WV	D-F9□V	D-F9□WV
		MHZ2-6□	Open	No setting		11			No setting		9	
		WII IZZ-O	Closed			13					11	
		MHZ2-10□	Open	1	No setting	No setting	No setting			No setting	No setting	No setting
		IVITIZZ-1UL	Closed	7.5	140 octaing	140 Sctting	140 Setting		6.5	No setting	No setting	No setting
			Open			1						
7	2	MHZ2-16□	Closed	6		4			5		2	
3	<u>ק</u>		Open					N 44'				
3	=	MHZ2-20□	Closed	4	4	2	2	No setting	3	3		
3	Standard		Open									
Ú	ר	MHZ2-25□	Closed	1	1							
			Open									
		MHZ2-32□	Closed	3	3				2	2		
			Open									
		MHZ2-40□	Closed	2	2				1 1			
			Open			11		16		·	9	
,	_	MHZJ2-6□	Closed			11					11	
	<u> </u>					13	No setting	18				1
6	6 MHZJ2	MHZJ2-10□	Open Closed			5		12			3 5	No setting
9	ט	Ciose				7		16				_
7	MHZJ2-16  MHZJ2-20  MHZJ2-20	MHZJ2-16□	Open	No s	etting	2		9	No s	etting		
-			Closed			5		14.5			3	
2	=	MHZJ2-20□	Open					3	<u> </u>			
*	=		Closed			3	3	11			1	1
5	<b>&gt;</b>	MHZJ2-25□	Open									
			Closed			2	2	9.5				
		MHZL2-10D	Open	0.5		No setting					No setting	
	5		Closed	8.5	No setting		No setting		7.5	No setting		No setting
	acting	MHZL2-16D	Open				3					110 county
	ac	WITTELE TOD	Closed	8		6		No setting	7		4	
	ple	MHZL2-20D	Open					, recouning				
	Doul	WINZLZ-ZUD	Closed	7	7	5	5		6	6	3	3
	-	MUZIOSED	Open									
		MHZL2-25D	Closed	5.5	5.5	3.5	3.5		4.5	4.5	1.5	1.5
	eu)	MUZI 0 400	Open			No potting					No setting	
Φ	ď	MHZL2-10S	Closed		No sottine	No setting	No setting			No setting		No setting
8	nall	MII 5 100	Open		No setting		ino setting			INO Setting		INO SELLING
stroke	Single acting (normally open)	MHZL2-16S	Closed	3		1		N = = -44!	2			
5	] gr		Open					No setting	_			
Long	actii	MHZL2-20S	Closed	1	1							
Ľ	gle		Open					1				
	ŝ	MHZL2-25S	Closed					1				
	क्र		Open									
	Sol	MHZL2-10C	Closed	5.5		No setting	N1		4.5		No setting	
	2		Open		No setting		No setting			No setting		No setting
	l ma	MHZL2-16C	Closed	5.5		3.5			4.5		1.5	
	일		Open					No setting				
	ting	MHZL2-20C	Closed	3.5	3.5	1.5	1.5		2.5	2.5		
	Single acting (normally closed)		Open		J.5	1.5	1.0					
	ing	MHZL2-25C	Closed	1.5	1 5				0.5	0.5		
1	က			1.5	1.5 th no values ent			l	0.5	0.0		

Note) There is no protrusion for sections of the table with no values entered.



# End boss type

	Lead wire	e type		In-line				Perpendicular				
	Illustration  Value of the state of the stat					L 						
'	Model	3	D-Y59□ D-Y7P	D-Y7□W	D-F9□	D-F9□W	D-F9BAL	D-Y69□ D-Y7PV	D-Y7□WV	D-F9□V	D-F9□WV	
<u>.</u>	MUZ 12 40000	Open					4					
	MHZJ2-10	Closed				No setting	8				No setting	
ြ	MHZ 12-16	Open				140 octaing	1 6.5				140 octaing	
st	14111232-10	Closed	No s	etting				No setting				
밀	MHZJ2-20			og					Juli 19			
P	Closed						3					
With dust cover	MHZJ2-25											
>		Closed					1.5					

Note) There is no protrusion for sections of the table with no values entered.

MHZ

MHT2

MHY2

MHW2

MRHQ

# Series MHZ Order Made Specifications


Order Made

Contact SMC for detailed dimensions, specifications and lead times.


# 1 Spring Assisted Type



# Compact Type/MHZA2-6, MHZAJ2-6



# With Dust Cover/MHZJ2



#### **Specifications**

Туре	Spring assisted type		
Bore size	6		
Action	Double acting		
Fluid	Air		


Note) Dimensions are the same as the standard type.

#### **Specifications**

	- p					
Туре	Spring assisted type					
Bore size	6, 10, 16, 20, 25					
Action	Double acting					
Fluid	Air					

Note) Dimensions are the same as the standard type.

# Standard Type/MHZ2




Note) Dimensions of  $\emptyset 6$  to  $\emptyset 25$  are the same as the standard type. Dimensions of  $\emptyset 32$  and  $\emptyset 40$  are the same as the standard single acting type.

Spring assisted type 6, 10, 16, 20, 25, 32, 40

Double acting

# Long Stroke/MHZL2



# **Specifications**

Туре	Spring assisted type		
Bore size	10, 16, 20, 25		
Action	Double acting		
Fluid	Air		





Туре

Fluid


Bore size Action

Symbol

# **2** With Needle (with Variable Throttle)

-X46

Installation of a variable throttle allows adjustment of the finger opening/closing speed.




Model

MHZ2-25D□□-X46

Туре	With needle
Bore size	10, 16, 20, 25
Action	Double acting
Fluid	Air

#### **Dimensions**



Adjust so that the finger opening/closing speed will be no greater than necessary. If the finger opening/closing speed is greater than necessary, impact forces acting on the fingers and other parts will increase. This can cause a loss of repeatability when gripping work pieces and have an adverse effect on the life of the unit.

# Guide for internal needle adjustment

Model	Number of rotations from fully closed needle condition Note 1)
MHZ2-10D□□-X46	1/4 to 1/2
MHZ2-16D□□-X46	1/2 to 1
MHZ2-20D□□-X46	1 to 1 1/2
MHZ2-25D□□-X46	1 1/2 to 2

Note 1) The condition in which the needle is tightened gently until it stops.

С  $D^*$ В MHZ2-10D□□-X46 11 4.5 5.2 MHZ2-16D□□-X46 7.5 13 5.8 MHZ2-20D□□-X46 10 15 6

20

Dimensions other than the above are identical to the standard type; refer to pages 2.1-22 through 2.1-25.

\* Reference values to establish criteria for needle adjustment.

10.7

MHZ

MHQ

MHL2 MHR

MHK

MHS

MHC<sub>2</sub>

MHT2


MHY2

MHW2

**MRHQ** 

# 3 MHQ2/MHQG2 Compatible Flat Finger Type


The flat finger type can be selected depending on the intended application.



# **Specifications**

Туре	Flat finger type
Bore size	10, 16, 20, 25
Action	Double acting, Single acting (normally open, normally closed)
Fluid	Air

#### **Dimensions**



Unit: mm

Model			-	_	-	(	3	BABA		w
		Α	В	С	D	Open	Closed	MM	L	VV
MUZO 40000 VE4	MHQG2 compatible	3	6	5.2	12	9.7 +2.2	5.7 -0.4	M2	3.6	5 -0.05
MHZ2-10□□□-X51	MHQ2 compatible	2	5	5.2	9	9.7 +2.2	5.7 -0.4	M2	3.6	5 -0.05
MHZ2-16□□□-X51	MHQG2 compatible	4	8	8.3	16	12.6 +2.2	6.6 -0.4	M3	6	8 -0.05
WIHZ2-16X51	MHQ2 compatible	2.5	7	8.3	12	12.6 +2.2	6.6 -0.4	M3	6	8 -0.05
MHZ2-20□□□-X51	MHQG2 compatible	5	10	10.5	20.8	17.2 +2.2	7.2 -0.4	M4	8	10 -0.05
WHZ2-20   -X51	MHQ2 compatible	3.3	9	10.5	15.5	17.2 +2.2	7.2 -0.4	M4	8	10 -0.05
MHZ2-25□□□-X51	MHQG2 compatible	6.5	12	13.1	25	22.8 +2.5	8.8 -0.4	M5	10	12 -0.05
WII 122-23-1-X3 I	MHQ2 compatible	3.5	12	13.1	19	22.8 +2.5	8.8 -0.4	M5	10	12 -0.05


Dimensions other than the above are identical to the standard type; refer to pages 2.1-22 through 2.1-25.




# Series MHZ

# **Model Selection**

# **Model Selection**



# Model selection illustration



"Gripping force at least 10 to 20 times the work piece weight"

The "10 to 20 times or more of the work piece weight" recommended by SMC is calculated with a safety margin of a=4, which allows for impacts that occur during normal transportation, etc.

When μ = 0.2	When μ = 0.1
$F = \frac{mg}{2 \times 0.2} \times 4$	$F = \frac{mg}{2 \times 0.1} \times 4$
= 10 x mg	= 20 x mg
<u> </u>	<u></u>
10 x work piece weight	20 x work piece weight

Note) Even in cases where the coefficient of friction is greater than µ= 0.2, for reasons of safety, select a gripping force which is at least 10 to 20 times greater than the work piece weight, as recommended by SMC.

It is necessary to allow a greater safety margin for high accelerations and strong impacts, etc.

When gripping a work piece as in the figure to the left, and with the following definitions,

F: Gripping force (N)

 $\mu\textsc{:}$  Coefficient of friction between the attachments and the work piece

m: Work piece mass (kg)

g: Gravitational acceleration ( = 9.8m/s²)

mg: Work piece weight (N)

the conditions under which the work piece will not drop are

and therefore,


$$F > \frac{mg}{2 \times u}$$

With "a" representing the safety margin, F is determined by the following formula:


$$F = \frac{mg}{2 x \mu} x a$$

# Step 1 Effective gripping force: Series MHZ□2/Double acting/External gripping force -


· Expressing the effective gripping force The effective gripping force shown in the graphs to the right is expressed as F, which is the impellent force of one finger, when both fingers and attachments are in full contact with the work piece as shown in the figure below.




# **External gripping**




# External gripping force




# MHZ2-10D/MHZL2-10D




# MHZ2-16D/MHZL2-16D




# MHZ2-20D/MHZL2-20D




# **External gripping force**



# MHZ2-32D



# MHZ2-40D



MHZ

MHQ

MHL2 MHR

MHK

MHS

MHC2

MHT2


MHY2 MHW2

**MRHQ** 


# **Model Selection**

# Step 1 Effective gripping force: Series MHZ 2/Double acting/Internal gripping force


• Expressing the effective gripping force
The effective gripping force shown in the
graphs to the right is expressed as F, which is
the impellent force of one finger, when both
fingers and attachments are in full contact with
the work piece as shown in the figure below.




#### Internal gripping




# Internal gripping force




#### MHZ2-10D/MHZL2-10D




# MHZ2-16D/MHZL2-16D




# MHZ2-20D/MHZL2-20D




# Internal gripping force



#### **MHZ2-32D**




# MHZ2-40D




# Step 1 Effective gripping force: Series MHZ 2/Single acting/External gripping force


Expressing the effective gripping force
 The effective gripping force shown in the graphs to the right is expressed as F, which is the impellent force of one finger, when both fingers and attachments are in full contact with the work piece as shown in the figure below.




# **External gripping**




# External gripping force




# MHZ2-10S/MHZL2-10S




#### MHZ2-16S/MHZL2-16S




# MHZ2-20S/MHZL-20S




# **External gripping force**



#### MHZ2-32S



# MHZ2-40S



MHZ

MHQ

MHL2

MHK

MHS

MHC2

MHT2


MHY2

MRHQ


# **Model Selection**

# Step 1 Effective gripping force: Series MHZ 2/Single acting/Internal gripping force -


• Expressing the effective gripping force
The effective gripping force shown in the
graphs to the right is expressed as F, which is
the impellent force of one finger, when both
fingers and attachments are in full contact with
the work piece as shown in the figure below.




# Internal gripping




# Internal gripping force




# MHZ2-10C/MHZL2-10C




MHZ2-16C/MHZL2-16C




# MHZ2-20C/MHZL2-20C




# Internal gripping force



MHZ2-32C




MHZ2-40C




# Step 1 Effective gripping force: Series MHZ□2/Double acting/External gripping force


• Expressing the effective gripping force The effective gripping force shown in the graphs to the right is expressed as F, which is the impellent force of one finger, when both fingers and attachments are in full contact with the work piece as shown in the figure be-




# **External gripping**




# **External gripping force**




# MHZJ2-10D/11-MHZ2-10D




# MHZJ2-16D/11-MHZ2-16D



#### MHZJ2-20D/11-MHZ2-20D



# **External gripping force**



MHZ

MHQ

MHL2

MHR

MHK

MHS

MHC<sub>2</sub>

MHT2

MHY2


MHW2

**MRHQ** 


# **Model Selection**

# Step 1 Effective gripping force: Series MHZ 2/Double acting/Internal gripping force


• Expressing the effective gripping force
The effective gripping force shown in the
graphs to the right is expressed as F, which is
the impellent force of one finger, when both
fingers and attachments are in full contact with
the work piece as shown in the figure below.




# Internal gripping




# Internal gripping force




#### MHZJ2-10D/11-MHZ2-10D




# MHZJ2-16D/11-MHZ2-16D



#### MHZJ2-20D/11-MHZ2-20D




# Internal gripping force




# Step 1 Effective gripping force: Series MHZ 2/Single acting/External gripping force


• Expressing the effective gripping force
The effective gripping force shown in the
graphs to the right is expressed as F, which
is the impellent force of one finger, when
both fingers and attachments are in full contact with the work piece as shown in the figure below.




# **External gripping**




# External gripping force




# **MHZJ2-10S**




# **MHZJ2-16S**



# **MHZJ2-20S**



# **External gripping force**



MHZ

MHQ

MHL2

MHR

MHK

MHS

MHC2

MHT2

MHY2


MHW2

MRHQ


# **Model Selection**

# Step 1 Effective gripping force: Series MHZ 2/Single acting/Internal gripping force


• Expressing the effective gripping force
The effective gripping force shown in the
graphs to the right is expressed as F, which is
the impellent force of one finger, when both
fingers and attachments are in full contact with
the work piece as shown in the figure below.




# Internal gripping




# Internal gripping force




# MHZJ2-10C




# MHZJ2-16C



# MHZJ2-20C




# Internal gripping force





# Step 2 Confirmation of gripping point: Series MHZ□/External gripping –


# MHZI 2, 11-MHZ2 Gripping point MHZAJ2, MHZJ2 Gripping point

- The air gripper should be operated so that the work piece gripping point "L" and the amount of overhang "H" stay within the range shown for each operating pressure given in the graphs to the right.
- If the work piece gripping point goes beyond the range limits, this will have an adverse effect on the life of the air gripper.




















MHZ

MHQ MHL2

MHR

MHK

MHS

MHC2

MHT2


MHY2

MRHQ

# **Model Selection**


# Step 2 Confirmation of gripping point: Series MHZ□/Internal gripping


# Internal gripping





- The air gripper should be operated so that the work piece gripping point "L" and the amount of overhang "H" stay within the range shown for each operating pressure given in the graphs to the right.
- If the work piece gripping point goes beyond the range limits, this will have an adverse effect on the life of the air gripper.

# Internal gripping













# Internal gripping







# Step 3 Confirmation of external force on fingers: Series MHZ□2



L: Distance to the point at which the load is applied (mm)

		Maximum allowable moment						
Model	Allowable vertical load  Fv (N)	Pitch moment: Mp (N·m)	Yaw moment: <b>My (N·m)</b>	Roll moment: Mr (N·m)				
MHZ□2-6	10	0.04	0.04	0.08				
MHZ□2-10	58	0.26	0.26	0.53				
MHZ□2-16	98	0.68	0.68	1.36				
MHZ□2-20	147	1.32	1.32	2.65				
MHZ□2-25	255	1.94	1.94	3.88				
MHZ□2-32	343	3	3	6				
MHZ□2-40	490	4.5	4.5	9				

Note) Values for load and moment in the table indicate static values.

Calculation of allowable external force (when moment load is applied)	Calculation example
Allowable load F (N) = $\frac{M \text{ (maximum allowable moment) (N·m)}}{L \times \frac{10^{-3}}{*}}$ (* Unit conversion constant)	When a static load of f = 10N is operating, which applies pitch moment to point L = 30mm from the MHZ $\square$ 2-16D guide.  Allowable load F = $\frac{0.68}{30 \times 10^3}$ = 22.7 (N)  Load f = 10 (N) < 22.7 (N)  Therefore, it can be used.

MHZ

MHQ

MHL2

MHK

MHS

MHC2

MHT2

MHY2

MHW2

MRHQ