

Profile Design ISO/VDMA Air Cylinder




Series CP95

Ø32, Ø40, Ø50, Ø63, Ø80, Ø100




Profile design with enclosed tie-rods






Space is saved by setting switches completely into grooves provided on 4 surfaces.







Easy end of stroke cushion valve adjustment

Since adjustment of the cushion valve is performed with a hexagon wrench key, even fine control can be easily accomplished. Furthermore, the cushion valve has been recessed so that it does not protrude from the cover.

Appearance improved by enclosing the tie-rods

Tie-rods are enclosed in an extruded aluminium profile barrel, which is integrated with both end covers to achieve a smooth and attractive appearance.

Dust accumulation can be prevented with optional fastener strips

Auto switch mounting grooves can be covered with resin fastener strips, which adhere tightly to the tube to prevent the entry and accumulation of dirt.



Key Page Index

| | Page |
|--------------------------|-------------|
| Available Specifications | 4 |
| How to Order | 4-5 |
| Technical Specifications | 6, 13 |
| Dimensions (Cylinders) | 9-12, 15-17 |
| (Mounting Accessories) | 18 |
| Auto Switches | 19-22 |
| Guide Units | 23-25 |
| Safety Instructions | 30-34 |
| Main Index | 35 |
| | 1.8-3 |

Series CP95 ISO/VDMA Air Cylinders

Specifications

| Type Model | | Model | Bore | | | | | | cushioning | Rod specificati | ons | | | Upon receipt of order |
|------------|--------------|-----------|------|----|----|----|----|-----|------------|-----------------|-----|---|---|--------------------------|
| | | | 32 | 40 | 50 | 63 | 80 | 100 | | hard chromed | W | Е | R | XB6 |
| | Standard | CP95SB | • | • | • | • | • | • | • | • | • | • | • | • |
| acting | | CP95SDB | • | • | • | • | • | • | • | • | • | • | • | _ |
| act | Double | CP95SB•W | • | • | • | • | • | • | • | • | _ | • | • | • |
| <u>e</u> | rod | CP95SDB•W | • | • | • | • | • | • | • | • | _ | • | • | _ |
| Double | Non-rotating | CP95KB | • | • | • | • | • | • | • | _ | • | • | • | _ |
| Δ | rod | CP95KDB | • | • | • | • | • | • | • | _ | • | • | • | _ |

W = double/through rod E = extended rod


R = stainless rod

XB6= heat resistant (to 150° C)

• available

- not available

How to order: Cylinders




How to order: Accessories

| | | Page |
|--------------------------|---------------------|-------|
| Mounting accessories | Cylinder | 5 |
| | Rod | 5 |
| Switches and switch hold | ers | 19-22 |
| Snap-on switch groove co | overs | 22 |
| Seal kits | standard models | 8 |
| 1.8-4 | non-rotating models | 14 |

How to order mounting accessories

Mounting accessories, cylinders



Mounting accessories, rod


| Ø bore | GKM Rod clevis DIN 71752 | Piston rod ball joint DIN 648 | JA Floating joint |
|--------|--------------------------------|-------------------------------|----------------------------|
| | | | |
| | Supplied with bolts and safety | | 7 |
| | devices | | |
| 32 | GKM 10-20 | KJ10 D | JA30-10-125 |
| 40 | GKM12-24 | KJ12 D | JA40-12-125 |
| 50 | GKM16-32 | KJ16 D | JA50-16-150 |
| 63 | GKM16-32 | KJ16 D | JA50-16-150 |
| 80 | GKM20-40 | KJ20D | JAH50-20-150 |
| 100 | GKM20-40 | KJ20D | JAH50-20-150 |
| | See page 18 for dimensions | See page 18 for dimensions | See page 18 for dimensions |

Series CP95 VDMA

Double acting with end of stroke cushioning Ø32 - Ø100

- Conforms to VDMA 24 562 (parts 1 and 2), ISO 6431 and CETOP standards
- Combines lightweight profile barrel design with enclosed tie rods for extra strength
- Unique seal system ensures efficient performance and long life
- Fully adjustable cushioning at end of stroke
- Magnetic proximity sensing
- Superior cushioning performance and kinetic energy absorption





Technical specifications

| Bore [mm] | 32 | 40 | 50 | 63 | 80 | 100 | | |
|------------------------------------|---------------|---|---------------|-----------------|----------------|---------|--|--|
| Туре | Non-lube typ | Non-lube type | | | | | | |
| Action | Double actin | g single rod | | | | | | |
| Fluid | Compressed | air filtered to | <10 µm,lubrio | cated or non lu | ubricated (dry | air) | | |
| Proof pressure | 1.5MPa {15.3 | 3kgf/cm ² } | | | | | | |
| Maximum operating pressure | 1.0MPa {10.2 | 2kgf/cm ² } | | | | | | |
| Minimum operating pressure | 0.05MPa {0. | 5kgf/cm ² } | | | | | | |
| Piston force | Up to 7500N | | | | | | | |
| Piston rod | Hard chrome | ed steel (25µm | n finish) | | | | | |
| Lubrication | Not required | (non-lube) | | | | | | |
| Rod diameter [mm] | 12 | 16 | 20 | 20 | 25 | 30 | | |
| Piston rod thread | M10x1.25 | M12x1.25 | M16x1.5 | M16x1.5 | M20x1.5 | M20x1.5 | | |
| Ports | G1/8 | G1/4 | G1/4 | G3/8 | G3/8 | G1/2 | | |
| Cushioning stroke [mm] | 19 | 19 | 24 | 24 | 30 | 30 | | |
| Mounting position | Any | | | | | | | |
| Standard strokes | 25, 50, 80, 1 | 00, 125, 160, | 200, 250, 320 | 0, 400, 500, 60 | 00, 700, 800 | | | |
| (DIN ISO 4393) [mm] | Other stroke | lengths in acc | cordance with | ISO497 R 10 | | | | |
| Stroke tolerance [mm] | <250mm: + 1 | 1.0/-0mm, <10 | 000mm: + 1.4 | /-0mm, <1500i | mm: + 1.8/-0m | ım | | |
| Working pressure [MPa] | 0.05 - 1.0 | | | | | | | |
| Fluid and ambient temperature [°C] | -10°C to +60 | -10°C to +60°C, -10°C to +70°C without magnet | | | | | | |
| Piston speed [mm/s] | 50 - 1000 | | | | | | | |

| Standard strokes | | | | | | | |
|------------------|--|--------|--|--|--|--|--|
| Ø | Standard stroke | Max. | | | | | |
| Bore | | stroke | | | | | |
| 32 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500 | 700 | | | | | |
| 40 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500 | 800 | | | | | |
| 50 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500, 600 | 1200 | | | | | |
| 63 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500, 600 | 1200 | | | | | |
| 80 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500, 600, 700, 800 | 1400 | | | | | |
| 100 | 25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 450, 500, 600, 700, 800 | 1500 | | | | | |

Note: Intermediate strokes are also available

Theoretical output table [N]

| Theoretical | Theoretical output table [N] → OUT → OUT | | | | | | | — IN | | | | |
|-------------|---|-----------|--------------------|--------|---------|---------|------|------|------|------|------|------|
| Ø Bore | Ø Rod diam. | Operating | Piston area | Workii | ng pres | sure [N | 1Pa] | | | | | |
| [mm] | [mm] | direction | [mm ²] | 0.2 | 0.3 | 0.4 | 0.5 | 0.6 | 0.7 | 0.8 | 0.9 | 10 |
| 32 | 12 | OUT | 804 | 161 | 241 | 322 | 402 | 482 | 563 | 643 | 724 | 804 |
| | | IN | 691 | 138 | 207 | 276 | 346 | 415 | 484 | 553 | 622 | 691 |
| 40 | 16 | OUT | 1257 | 251 | 377 | 503 | 629 | 754 | 880 | 1006 | 1131 | 1257 |
| | | IN | 1056 | 211 | 317 | 422 | 528 | 634 | 739 | 845 | 950 | 1056 |
| 50 | 20 | OUT | 1963 | 393 | 589 | 785 | 982 | 1178 | 1374 | 1570 | 1767 | 1963 |
| | | IN | 1649 | 330 | 495 | 660 | 825 | 989 | 1154 | 1319 | 1484 | 1649 |
| 63 | 20 | OUT | 3117 | 623 | 935 | 1247 | 1559 | 1870 | 2182 | 2494 | 2805 | 3117 |
| | | IN | 2803 | 561 | 841 | 1121 | 1402 | 1682 | 1862 | 2242 | 2523 | 2803 |
| 80 | 25 | OUT | 5027 | 1005 | 1508 | 2011 | 2514 | 3016 | 3519 | 4022 | 4524 | 5027 |
| | | IN | 4536 | 907 | 1361 | 1814 | 2268 | 2722 | 3175 | 3629 | 4082 | 4536 |
| 100 | 30 | OUT | 7854 | 1571 | 2356 | 3142 | 3927 | 4712 | 5498 | 6283 | 7069 | 7854 |
| | | IN | 7147 | 1429 | 2144 | 2859 | 3574 | 4288 | 5003 | 5718 | 6432 | 7147 |

Weight table

| Worght table | | | | | | | [kg] |
|-------------------|--------------------------|-------|------|------|------|------|------|
| Ø Bore | Mounting type | 32 | 40 | 50 | 63 | 80 | 100 |
| | Basic type B | 0.59 | 0.87 | 1.44 | 2.00 | 3.37 | 4.45 |
| | Foot L | 0.16 | 0.20 | 0.38 | 0.46 | 0.89 | 1.09 |
| Basic weight | Front/rear flange F | 0.20 | 0.23 | 0.47 | 0.58 | 1.30 | 1.81 |
| | Male rear clevis C | 0.16 | 0.23 | 0.37 | 0.60 | 1.07 | 1.73 |
| | Female rear clevis D | 0.20 | 0.32 | 0.45 | 0.71 | 1.28 | 2.11 |
| | Angled rear clevis E | 0.16 | 0.22 | 0.42 | 0.52 | 0.94 | 1.40 |
| | Female rear clevis DS | 0.17 | 0.27 | 0.45 | 0.64 | 1.37 | 2.05 |
| | Spherical bearing ES | 0.18 | 0.27 | 0.46 | 0.55 | 0.97 | 1.33 |
| Additional weight | | 0.11 | 0.17 | 0.28 | 0.40 | 0.67 | 0.89 |
| per 50 mm stroke | | | | | | | |
| Accessories | Piston rod ball joint KJ | 0.15 | 0.23 | 0.26 | 0.26 | 0.60 | 0.83 |
| | Rod clevis GKM | 0.22 | 0.37 | 0.43 | 0.43 | 0.87 | 1.27 |
| | Floating joint JA | 0.015 | 0.20 | 0.26 | 0.26 | 0.9 | 0.9 |


Kinetic energy absorbable by air cushion mechanism

| Ø | Cushioning | Absorbable |
|------|-------------|------------|
| Bore | stroke [mm] | kinetic |
| [mm] | | energy [J] |
| 32 | 19 | 2.2 |
| 40 | 19 | 3.4 |
| 50 | 24 | 5.9 |
| 63 | 24 | 11 |
| 80 | 30 | 20 |
| 100 | 30 | 29 |

At the stroke end, when stopping a large amount of kinetic energy generated by a large load and high speed operation, compression of air is used to absorb the impact without transmitting vibration to the surroundings. The purpose of an air cushion is not to reduce the speed of a piston as it nears the stroke end. The kinetic energy of a load can be found using the following formula:

| _ | | 1 | | |
|---|---|-----------------|---|--|
| E | = | $\frac{1}{2}$ m | • | |

E: Kinetic energy [J = Nm] m: Load weight [kg] v: Piston speed [m/s]



Note: v is final velocity which is 1.4 • average

If the kinetic energy obtained is no greater than the absorbable kinetic energy shown in the table above, the life of the cushion seal should be 10 million cycles or more.

Note: Theoretical output OUT [N] = [kg] Pressure [MPa] x Piston area [mm²]

Weight calculation method Example: CP95S32-100


(basic Ø32, 100st)

• Basic weight 0.59kg
(Standard Ø32)

Additional weight . .0.11kg/50mm stroke
Cylinder stroke . . .100st


Cylinder weight = $0.59+(0.11 \times 100/50)=0.81$ kg

Moveable mass at various piston speeds



Example: Find the rod end load limit when a ø63 air cylinder is operated at a maximum drive speed of 500mm/s. Extend upward from 500mm/s on the horizontal axis of the graph to the intersection point with the line for a tube bore of 63mm, and then extend lefward from this point to find the load of 80kg.

Construction




Parts list

| No. | Description | Material |
|------------|-----------------------|-----------------------------|
| 0 | Head cover | Die-cast aluminum |
| 2 | End cover | Die-cast aluminum |
| 3 | Cylinder tube | Die-cast aluminum |
| 4 | Piston rod | Hard chromed steel C45 |
| 6 | Piston | Die-cast aluminum |
| 6 | Cushion ring | Brass |
| Ø | Tie rod | Steel, zinc chromate plated |
| 8 | Tie rod nut | Steel, zinc chromate plated |
| 9 | Rod end nut | Steel, zinc chromate plated |
| 0 | Snap ring | Steel nickel plated |
| 0 | Bushing | Lead-bronze casting |
| @ | Cushion valve | Steel, zinc chromate plated |
| ₿ | Cushion seal | Elastomer |
| (4) | Wear ring | Antifriction material |
| (| Piston seal | NBR |
| (| Rod seal | NBR |
| Ø | Cylinder tube gasket | NBR |
| B | Cushioning valve seal | NBR |
| Ø | Piston/rod gasket | NBR |
| a | Magnet ring | |

Replacement parts: Seal kits Ø32 includes order No. from ③ to ⑦, Ø40 - Ø100 includes from ② to ⑥

| Ø | Order No. |
|-----|-----------|
| 32 | CS95-32 |
| 40 | CS95-40 |
| 50 | CS95-50 |
| 63 | CS95-63 |
| 80 | CS95-80 |
| 100 | CS95-100 |

Maximum allowable radial loads



$$F_{B1} = W_S (1 + \frac{L2}{L1}) \le F_{B \text{ allowable}}$$

| Ø | L1 | L2 | F _{B1} allowable |
|-----|-------|-----------|---------------------------|
| 32 | 62.5 | 34.5 + st | 80 N |
| 40 | 74.0 | 39.0 + st | 125 N |
| 50 | 76.0 | 44.5 + st | 195 N |
| 63 | 91.0 | 44.5 + st | 310 N |
| 80 | 93.0 | 53.0 + st | 500 N |
| 100 | 104.0 | 57.5 + st | 785 N |

e.g. 63mm bore, 100mm stroke, $W_S = 20N$

W_S = (2kgs) 20N

$$F_{B1} = 20 (1 + \frac{144.5}{91}) = 51.76N$$


 $F_{B1} = 51.76N \le 310N$ (from table)

Therefore, side load is allowable


Dimensions - standard specifications

[mm]

CP95S□BØ-stroke




CP95S□BØ-stroke W




| Ø Bore | AM | ØB | ØD | EE | PL | RT | I ₁₂ | KK | sw | G | BG | I ₈ | VD | VA | WA | WB | WH | ZZ | ZY | □Е | □R | l ₂ | l ₉ |
|--------|----|----|----|------|------|-----|-----------------|----------|----|------|----|----------------|----|----|------|------|----|-----|-----|-----|------|----------------|----------------|
| 32 | 22 | 30 | 12 | G1/8 | 13 | M6 | 6 | M10x1.25 | 10 | 27 | 16 | 94 | 4 | 4 | 4 | 6.5 | 26 | 146 | 190 | 46 | 32.5 | 15 | 4 |
| 40 | 24 | 35 | 16 | G1/4 | 14 | M6 | 6.5 | M12x1.25 | 13 | 27 | 16 | 105 | 4 | 4 | 4 | 9 | 30 | 163 | 213 | 52 | 38 | 17 | 4 |
| 50 | 32 | 40 | 20 | G1/4 | 15.5 | M8 | 8 | M16x1.5 | 16 | 31.5 | 16 | 106 | 6 | 4 | 5 | 10.5 | 37 | 179 | 244 | 65 | 46.5 | 24 | 5 |
| 63 | 32 | 45 | 20 | G3/8 | 16.5 | M8 | 8 | M16x1.5 | 16 | 31.5 | 16 | 121 | 6 | 4 | 9 | 12 | 37 | 194 | 259 | 75 | 56.5 | 24 | 5 |
| 80 | 40 | 45 | 25 | G3/8 | 19 | M10 | 10 | M20x1.5 | 21 | 38 | 16 | 128 | 8 | 4 | 11.5 | 14 | 46 | 218 | 300 | 95 | 72 | 30 | 5 |
| 100 | 40 | 55 | 30 | G1/2 | 19 | M10 | 10 | M20x1.5 | 21 | 38 | 16 | 138 | 8 | 4 | 17 | 15 | 51 | 233 | 320 | 114 | 89 | 32 | 5 |


Dimensions – mounting accessories L, F, C and D

[mm]



Mounting type F





| Ø Bo | re | E1 | R | W | MF | ZF | ØFB | CD | EB | L | XD | UB | СВ | EW | MR | TR | AO | AT | XA | SA | АН | ØAB | TF | UF | E2 |
|------|-----|-----|----|----|----|-----|-----|----|-----|----|-----|-----|----|----|-----|----|----|----|-----|-----|----|-----|-----|-----|-----|
| | 32 | 48 | 32 | 16 | 10 | 130 | 7 | 10 | 65 | 12 | 142 | 45 | 26 | 26 | 9.5 | 32 | 10 | 4 | 144 | 142 | 32 | 7 | 64 | 79 | 50 |
| | 40 | 55 | 36 | 20 | 10 | 145 | 9 | 12 | 75 | 15 | 160 | 52 | 28 | 28 | 12 | 36 | 11 | 4 | 163 | 161 | 36 | 9 | 72 | 90 | 55 |
| | 50 | 68 | 45 | 25 | 12 | 155 | 9 | 12 | 80 | 15 | 170 | 60 | 32 | 32 | 12 | 45 | 12 | 5 | 175 | 170 | 45 | 9 | 90 | 110 | 10 |
| | 63 | 80 | 50 | 25 | 12 | 170 | 9 | 16 | 90 | 20 | 190 | 70 | 40 | 40 | 16 | 50 | 12 | 5 | 190 | 185 | 50 | 9 | 100 | 120 | 80 |
| | 80 | 100 | 63 | 30 | 16 | 190 | 12 | 16 | 110 | 20 | 210 | 90 | 50 | 50 | 16 | 63 | 14 | 6 | 215 | 210 | 63 | 12 | 126 | 153 | 100 |
| | 100 | 120 | 75 | 35 | 16 | 205 | 14 | 20 | 140 | 25 | 230 | 110 | 60 | 60 | 20 | 75 | 16 | 6 | 230 | 220 | 71 | 14 | 150 | 178 | 120 |


1.8-10


Mounting type D


Dimensions – mounting accessories C, D, E and CR

[mm]

Mounting type C









| Ø Bore | □E1 | EW | □TG1 | FL | l ₁ | L | l ₂ | Ød1 | CD | MR | d2 | R1 | □E2 | UB | СВ |
|--------|-----|----|------|----|----------------|----|----------------|-----|----|-----|-----|-----|-----|-----|----|
| | | | | | | | | | | | | | | | |
| 32 | 45 | 26 | 32.5 | 22 | 5 | 12 | 5.5 | 30 | 10 | 9.5 | 6.6 | 6.5 | 48 | 45 | 26 |
| 40 | 51 | 28 | 38 | 25 | 5 | 15 | 5.5 | 35 | 12 | 12 | 6.6 | 6.5 | 56 | 52 | 28 |
| 50 | 64 | 32 | 46.5 | 27 | 5 | 15 | 6.5 | 40 | 12 | 12 | 9 | 8.5 | 64 | 60 | 32 |
| 63 | 74 | 40 | 56.5 | 32 | 5 | 20 | 6.5 | 45 | 16 | 16 | 9 | 8.5 | 75 | 70 | 40 |
| 80 | 94 | 50 | 72 | 36 | 5 | 20 | 10 | 45 | 16 | 16 | 11 | 11 | 95 | 90 | 50 |
| 100 | 113 | 60 | 89 | 41 | 5 | 25 | 10 | 55 | 20 | 20 | 11 | 12 | 115 | 110 | 60 |


Mounting type E





| Ø Bore | Ød2 | ØCK | ØS5 | K1 | K2 | 13 | G1 | I ₁ | G2 | EM | G3 | CA | H6 | R1 |
|--------|-----|-----|-----|----|----|----|----|----------------|----|----|----|----|----|----|
| 32 | 11 | 10 | 6.6 | 38 | 51 | 10 | 21 | 7 | 18 | 26 | 31 | 32 | 8 | 10 |
| 40 | 11 | 12 | 6.6 | 41 | 54 | 10 | 24 | 9 | 22 | 28 | 35 | 36 | 10 | 11 |
| 50 | 15 | 12 | 9 | 50 | 65 | 12 | 33 | 11 | 30 | 32 | 45 | 45 | 12 | 12 |
| 63 | 15 | 16 | 9 | 52 | 67 | 14 | 37 | 11 | 35 | 40 | 50 | 50 | 12 | 15 |
| 80 | 18 | 16 | 11 | 66 | 86 | 18 | 47 | 12.5 | 40 | 50 | 60 | 63 | 14 | 15 |
| 100 | 18 | 20 | 11 | 76 | 96 | 20 | 55 | 13.5 | 50 | 60 | 70 | 71 | 15 | 19 |


Mounting type CR Rear clevis with ball joint




| Ø | Α | В | С | D | EN | ER | ØF | G | E | L | М | N | Р | Н | R |
|------|------|------|------|----|------|------|-----|----|-----|-----|------|------|---|------|------|
| (mm) | ±0.2 | maxi | JS15 | H7 | -0.1 | maxi | H11 | | H13 | | H13 | ±0.5 | | ±0.5 | ±0.5 |
| 32 | 32.5 | 10.5 | 22 | 10 | 14 | 15 | 30 | 10 | 6.6 | 45 | 10.5 | 5.5 | 5 | _ | _ |
| 40 | 38 | 12 | 25 | 12 | 16 | 18 | 35 | 10 | 6.6 | 55 | 11 | 5.5 | 5 | - | _ |
| 50 | 46.5 | 15 | 27 | 16 | 21 | 20 | 40 | 10 | 9 | 65 | 15 | 6.5 | 5 | 51 | 19 |
| 63 | 56.5 | 15 | 32 | 16 | 21 | 23 | 45 | 12 | 9 | 75 | 15 | 6.5 | 5 | _ | _ |
| 80 | 72 | 18 | 36 | 20 | 25 | 27 | 45 | 14 | 11 | 95 | 18 | 10 | 5 | - | _ |
| 100 | 89 | 18 | 41 | 20 | 25 | 30 | 55 | 16 | 11 | 115 | 18 | 10 | 5 | _ | _ |







Mounting type ES



| Ç | Ø Bore | Ød3 | ØCN | ØS5 | K1 | K2 | | G1 | G2 | G3 | EN | EU | СН | H6 | ER |
|---|--------|-----|-----|-----|----|----|------|----|----|----|----|------|----|----|----|
| 3 | 32 | 11 | 10 | 6.6 | 38 | 51 | 8.5 | 21 | 18 | 31 | 14 | 10.5 | 32 | 10 | 15 |
| 4 | 10 | 11 | 12 | 6.6 | 41 | 54 | 8.5 | 24 | 22 | 35 | 16 | 12 | 36 | 10 | 18 |
| 5 | 50 | 15 | 16 | 9 | 50 | 65 | 10.5 | 33 | 30 | 45 | 21 | 15 | 45 | 12 | 20 |
| 6 | 3 | 15 | 16 | 9 | 52 | 67 | 10.5 | 37 | 35 | 50 | 21 | 15 | 50 | 12 | 23 |
| 8 | 30 | 18 | 20 | 11 | 66 | 86 | 11.5 | 47 | 40 | 60 | 25 | 18 | 63 | 14 | 27 |
| • | 100 | 18 | 20 | 11 | 76 | 96 | 12.5 | 55 | 50 | 70 | 25 | 18 | 71 | 15 | 30 |


1.8-12

ISO/VDMA Air Cylinders

Series CP95K

Double acting with end of stroke cushioning and non-rotating rod Ø32 - Ø100

- Conforms to VDMA 24 562 (parts 1 and 2), ISO 6431 and CETOP standards
- Combines lightweight profile barrel design with enclosed tie rods for extra strength
- Unique seal system ensures efficient performance and long life
- Fully adjustable cushioning at end of stroke
- Magnetic proximity sensing
- Superior cushioning performance and kinetic energy absorption



Technical specifications

| Bore [mm] | 32 | 40 | 50 | 63 | 80 | 100 | | | |
|------------------------------------|----------------------------|-----------------------|------------------|-----------------|------------------|-----------|--|--|--|
| Туре | Non-lube type | e air cylinder | | | | | | | |
| Action | Double acting | single rod | | | | | | | |
| Fluid | Compressed | air filtered to < | c 10 μm, lubrica | ated or non lub | ricated (dry air |) | | | |
| Proof pressure | 1.5MPa {15.3 | kgf/cm ² } | | | | | | | |
| Maximum operating pressure | 1.0MPa {10.2 | kgf/cm ² } | | | | | | | |
| Minimum operating pressure | 0.05MPa {0.5 | kgf/cm ² } | | | | | | | |
| Piston force | Up to 7500N | | | | | | | | |
| Rod width across flats [mm] 1) | 12.2 | 14.2 | 19 | 19 | 23 | 27 | | | |
| Piston rod thread | M10 x 1.25 | M12 x 1.25 | M16 x 1.5 | M16 x 1.5 | M20 x 1.5 | M20 x 1.5 | | | |
| Ports | G1/8 | G1/4 | G1/4 | G3/8 | G3/8 | G1/2 | | | |
| Cushioning stroke [mm] | 19 | 19 | 24 | 24 | 30 | 30 | | | |
| Mounting position | Any | | | | | | | | |
| Standard strokes [mm] | 25, 50, 80, 10 | 00, 125, 160, 2 | 200, 250, 320, | 400, 500, 600, | 700, 800 | | | | |
| (DIN ISO 4393) [mm] | Other stroke | lengths in acco | ordance with IS | O 497 R 10 | | | | | |
| Stroke tolerance [mm] | <250mm: +1. | 0/-0mm, <100 | 0mm: +1.4/-0m | ım | | | | | |
| Working pressure [MPa] | 0.05 - 1.0 | | | | | | | | |
| Fluid and ambient temperature [°C] | -10°C to +60° | C built-in magn | et / -10°C to +7 | 70°C without ma | agnet | | | | |
| Piston speed [mm/s] | 50 - 1000 | | | | | | | | |
| Rod non-rotating accuracy | ± 0.5° | ± 0.5° | ± 0.5° | ± 0.5° | ± 0.3° | ± 0.3° | | | |
| Allowable maximum stroke [mm] 2) | 700 | 800 | 1200 | | 1400 | 1500 | | | |
| Allowable Torque [Nm] | 0.25 | 0.45 | 0.64 | 0.64 | 0.79 | 0.93 | | | |
| Rod material | I material Stainless steel | | | | | | | | |


²⁾ For longer stroke lengths please contact SMC.


Series CP95K

Construction

| Parts | list |
|-------|------|
| | |

| No. | Description | Material |
|------------|-----------------------|-----------------------------|
| 0 | Head cover | Die-cast aluminum |
| 2 | End cover | Die-cast aluminum |
| 8 | Cylinder tube | Die-cast aluminum |
| 4 | Piston rod | Stainless Steel |
| • | Piston | Die-cast aluminum |
| 6 | Cushion ring | Brass |
| Ø | Tie rod | Steel, zinc chromate plated |
| 8 | Tie rod nut | Steel, zinc chromate plated |
| 9 | Rod end nut | Steel, zinc chromate plated |
| • | Snap ring | Steel nickel plated |
| • | Bushing | Lead-bronze casting |
| Ø | Cushion valve | Steel, zinc chromate plated |
| ® | Cushion seal | Elastomer |
| (4) | Wear ring | Antifriction material |
| (| Piston seal | NBR |
| 13 | Rod seal | NBR |
| Ū | Cylinder tube gasket | NBR |
| B | Cushioning valve seal | NBR |
| ® | Piston/rod gasket | NBR |
| @ | Magnet ring | |





Replacement parts: Seal kits Ø32 includes the order No. from 13 to 17, Ø40-Ø100 includes from 12 to 18.

| Ø Bore | Order No. |
|--------|-----------|
| 32 | CK95-32 |
| 40 | CK95-40 |
| 50 | CK95-50 |
| 63 | CK95-63 |
| 80 | CK95-80 |
| 100 | CK95-100 |

Theoretical output table

The value at the OUT side is the same as the $\,$ double acting single rod type, but the value at the IN side is different. Refer to the table below.

| Bore size (mm) | Piston area (mm²) | Bore size (mm) | Piston area (mm²) |
|----------------|----------------------|----------------|----------------------|
| 32 | 675 | 63 | 2804 |
| 40 | 1082 | 80 | 4568 |
| 50 | 1651 | 100 | 7223 |


Theoretical output (N) =Pressure (MPa) x Piston area (mm²). 1N: approx. 0.102kgf 1MPa: approx. 10.2kgf/cm²

ISO/VDMA Air Cylinders **Series CP95K**


Dimensions – non-rotating rod specification

[mm]

CP95K□BØ-Stroke



CP95K□BØ-Stroke W




| Ø Bore | AM | ØB | ØD | EE | PL | RT | I ₁₂ | KK | SW | SW1 | G | BG | l ₈ | VD | VA | WA | WB | WH | ZZ | ZY | □Е | □R | l ₂ | Ig |
|--------|----|----|----|------|------|-----|-----------------|----------|----|------|------|----|----------------|----|----|------|------|----|-----|-----|-----|------|----------------|----|
| 32 | 22 | 30 | 12 | G1/8 | 13 | M6 | 6 | M10x1.25 | 10 | 12.2 | 27 | 16 | 94 | 4 | 4 | 4 | 6.5 | 26 | 146 | 190 | 46 | 32.5 | 15 | 4 |
| 40 | 24 | 35 | 16 | G1/4 | 14 | M6 | 6.5 | M12x1.25 | 13 | 14.2 | 27 | 16 | 105 | 4 | 4 | 4 | 9 | 30 | 163 | 213 | 52 | 38 | 17 | 4 |
| 50 | 32 | 40 | 20 | G1/4 | 15.5 | M8 | 8 | M16x1.5 | 16 | 19 | 31.5 | 16 | 106 | 6 | 4 | 5 | 10.5 | 37 | 179 | 244 | 65 | 46.5 | 24 | 5 |
| 63 | 32 | 45 | 20 | G3/8 | 16.5 | M8 | 8 | M16x1.5 | 16 | 19 | 31.5 | 16 | 121 | 6 | 4 | 9 | 12 | 37 | 194 | 259 | 75 | 56.5 | 24 | 5 |
| 80 | 40 | 45 | 25 | G3/8 | 19 | M10 | 10 | M20x1.5 | 21 | 23 | 38 | 16 | 128 | 8 | 4 | 11.5 | 14 | 46 | 218 | 300 | 95 | 72 | 30 | 5 |
| 100 | 40 | 55 | 30 | G1/2 | 19 | M10 | 10 | M20x1.5 | 21 | 27 | 38 | 16 | 138 | 8 | 4 | 17 | 15 | 51 | 233 | 320 | 114 | 89 | 32 | 5 |


Series CP95K


Cylinder mounting accessories dimensions L, F, C and D

[mm]



Mounting type F






| Ø Bore | E1 | R | W | MF | ZF | ØFB | CD | EB | L | XD | UB | СВ | EW | MR | TR | AO | AT | XA | SA | АН | ØAB | TF | UF | E2 |
|--------|-----|----|----|----|-----|-----|----|-----|----|-----|-----|----|----|-----|----|----|----|-----|-----|----|-----|-----|-----|-----|
| 32 | 48 | 32 | 16 | 10 | 130 | 7 | 10 | 65 | 12 | 142 | 45 | 26 | 26 | 9.5 | 32 | 10 | 4 | 144 | 142 | 32 | 7 | 64 | 79 | 50 |
| 40 | 55 | 36 | 20 | 10 | 145 | 9 | 12 | 75 | 15 | 160 | 52 | 28 | 28 | 12 | 36 | 11 | 4 | 163 | 161 | 36 | 9 | 72 | 90 | 55 |
| 50 | 68 | 45 | 25 | 12 | 155 | 9 | 12 | 80 | 15 | 170 | 60 | 32 | 32 | 12 | 45 | 12 | 5 | 175 | 170 | 45 | 9 | 90 | 110 | 10 |
| 63 | 80 | 50 | 25 | 12 | 170 | 9 | 16 | 90 | 20 | 190 | 70 | 40 | 40 | 16 | 50 | 12 | 5 | 190 | 185 | 50 | 9 | 100 | 120 | 80 |
| 80 | 100 | 63 | 30 | 16 | 190 | 12 | 16 | 110 | 20 | 210 | 90 | 50 | 50 | 16 | 63 | 14 | 6 | 215 | 210 | 63 | 12 | 126 | 153 | 100 |
| 100 | 120 | 75 | 35 | 16 | 205 | 14 | 20 | 140 | 25 | 230 | 110 | 60 | 60 | 20 | 75 | 16 | 6 | 230 | 220 | 71 | 14 | 150 | 178 | 120 |

ISO/VDMA Air Cylinders **Series CP95K**

Cylinder mounting accessory DS and ES






85

Mounting type ES

25

4.3

6.3




| Ø Bore | Ød3 | ØCN | ØS5 | K1 | K2 | I ₂ | G1 | G2 | G3 🗆 | EN | EU | СН | H6 | ER |
|--------|-----|-----|-----|----|----|----------------|----|----|------|----|------|----|----|----|
| 32 | 11 | 10 | 6.6 | 38 | 51 | 8.5 | 21 | 18 | 31 | 14 | 10.5 | 32 | 10 | 15 |
| 40 | 11 | 12 | 6.6 | 41 | 54 | 8.5 | 24 | 22 | 35 | 16 | 12 | 36 | 10 | 18 |
| 50 | 15 | 16 | 9 | 50 | 65 | 10.5 | 33 | 30 | 45 | 21 | 15 | 45 | 12 | 20 |
| 63 | 15 | 16 | 9 | 52 | 67 | 10.5 | 37 | 35 | 50 | 21 | 15 | 50 | 12 | 23 |
| 80 | 18 | 20 | 11 | 66 | 86 | 11.5 | 47 | 40 | 60 | 25 | 18 | 63 | 14 | 27 |
| 100 | 18 | 20 | 11 | 76 | 96 | 12.5 | 55 | 50 | 70 | 25 | 18 | 71 | 15 | 30 |

1.8-17

Piston Rod mounting accessory dimensions


Floating joint JA Carbon tool steel

| Ø Bore | M | Order No. | Α | В | С | ØD | E | F | G | Н | Р | U | Load [kN] | Weight [g] | Angle |
|--------|----------|--------------|------|------|----|------|------|----|------|----|----|------|-----------|------------|-------|
| 32 | M10x1.25 | JA30-10-125 | 49.5 | 19.5 | - | 24 | 5 | 8 | 8 | 17 | 9 | 0.5 | 2.5 | 70 | |
| 40 | M12x1.25 | JA40-12-125 | 60 | 20 | - | 31 | 6 | 11 | 11 | 22 | 13 | 0.75 | 4.4 | 160 | ±5° |
| 50/63 | M16x1.5 | JA50-16-150 | 71.5 | 22 | _ | 41 | 7.5 | 14 | 13.5 | 27 | 15 | 1.0 | 11 | 300 | |
| 80/100 | M20v1 5 | IAH50-20-150 | 101 | 28 | 31 | 50.5 | 11.5 | 2/ | 16 | 32 | 18 | 2.0 | 18 | 1080 | |



Rod clevis GKM (DIN 71752), supplied with bolt and safety device Chromed steel

| Ø Bore | е | Order No. | b | d | Øf | I 1 | С | а |
|--------|----------|-----------|----|----|----|------------|----|----|
| 32 | M10x1.25 | GKM10-20 | 10 | 40 | 10 | 52 | 20 | 20 |
| 40 | M12x1.25 | GKM12-24 | 12 | 48 | 12 | 62 | 24 | 24 |
| 50/63 | M16x1.5 | GKM16-32 | 16 | 64 | 16 | 83 | 32 | 32 |
| 80/100 | M20x1.5 | GKM20-40 | 20 | 80 | 20 | 105 | 40 | 40 |




Rod end nut (standard equipment)


| Order No. | Bore size (mm) | d | Н | В | С | D |
|-----------|-------------------|------------|----|----|------|------|
| NT-03 | 32 | M10 x 1.25 | 6 | 17 | 19.6 | 16.5 |
| NT-04 | 40 | M14 x 1.5 | 8 | 22 | 25.4 | 21 |
| NT-05 | 50, 63 | M18 x 1.5 | 11 | 27 | 31.2 | 26 |
| NT-08 | 80 | M22 x 1.5 | 13 | 32 | 37.0 | 31 |
| NT-10 | 100 | M26 x 1.5 | 16 | 41 | 47.3 | 39 |

[mm]

Piston rod ball joint KJ (DIN 648) Zinc chromate plated steel

| Ø Bore | d3 | Order No. | d1 | h | d6 | b3 | b1 | I | d7 | α | 13 | sw |
|--------|----------|-----------|----|----|----|------|----|----|----|-----|----|----|
| 32 | M10x1.25 | KJ10D | 10 | 43 | 28 | 10.5 | 14 | 20 | 19 | 13° | 14 | 17 |
| 40 | M12x1.25 | KJ12D | 12 | 50 | 32 | 12 | 16 | 22 | 22 | 13° | 16 | 19 |
| 50/63 | M16x1.5 | KJ16D | 16 | 64 | 42 | 15 | 21 | 28 | 27 | 15° | 26 | 32 |
| 80/100 | M20x1.5 | KJ20D | 20 | 77 | 50 | 18 | 25 | 33 | 34 | 15° | 26 | 32 |





1.8-18

Series CP95 Auto Switch Specifications

Reed switch D-Z73L / D-Z80L



Technical specifications

| D-Z73L, (with indicator light), lead | wire length: 3 m | | | | |
|---|------------------|-----------|--|--|--|
| Model | D-Z73L | | | | |
| Applicable load | Relay, PLC | | | | |
| Power supply voltage | 24VDC | 100VAC | | | |
| Load current | 5 - 40 mA | 5 - 20 mA | | | |
| Protection internal circuits | _ | | | | |
| Internal voltage drop < 2.4 V | | | | | |
| Indicator light Red LED lights up when ON | | | | | |


| D-Z80L (without indicator light), lea | nd wire length: 3 n | า | |
|---------------------------------------|---------------------|-----------|------------|
| Model | D-Z80L | | |
| Applicable load | Relay, SPS, IC c | ircuit | |
| Power supply voltage | < 24VAC, DC | 48VAC, DC | 100VAC, DC |
| Load current | 50 mA | 40 mA | 18 mA |
| Protection internal circuits | _ | | |
| Insulation resistance | Max. 1Ω | | |


- Indicator light
 Leakage current 0
- Operating time— 1.2ms
- Lead wires oil resistant vinyl cabtyre cable, Ø 3.4 mm, 0.2 mm², 2 wires (Brown, Blue)
- Impact resistance— 30G
- Insulation resistance >50M Ω with a 500VDC megohmmeter
- Withstand voltage 1500VAC (for 1 minute)
- Ambient and fluid temperature— -10 to 60°C
- Protective structure IEC IP67, waterproof (JISC0920), oil resistant

Internal circuits

D-Z73L / D-Z80L







Series CP95 Auto Switch Specifications

Solid state D-Y7, 3 wires



Technical specifications

| D-Y7PL (with indicator light), lead | wire length 3 m | |
|-------------------------------------|----------------------|-------------------|
| Model | D-Y7PL | D-Y7PVL |
| Wiring system | 3 wires, axial | 3 wires, vertical |
| Output system | PNP | |
| Applicable load | IC circuit, relay, I | PLC |
| Power supply voltage | 4.5VDC - 28 VD | С |
| Current consumption | OFF: < 1 mA, Ol | N: < 15 mA |
| Load current | < 80 mA | |
| Internal voltage drop | < 0.8V | |
| Leakage current | 0.1 mA | |
| Indicator light | Red LED lights u | up when ON |


- Operating time 1.2ms
- Lead wires— oil resistant vinyl cabtyre cable, Ø 3.4 mm, 0.2 mm², 3wires (Brown, Black, Blue)
- Impact resistance 30G
- Insulation resistance >50M Ω with a 500VDC megohmmeter
- Withstand voltage 1500VAC (for 1 minute)
- Ambient temperature -10 to 60°C
- Protective structure IEC IP67, waterproof (JISC0920), oil resistant


Internal circuits

Dimensions


D-Y7PL

[mm]





D-Y7PVL



Series CP95 **Auto Switch Specifications**

Solid state D-Y59, D-Y69, 2 wires





Technical specifications

| D-Y59BL / D-Y69BL (with indicato | r light), lead wire le | ength: 3 m |
|----------------------------------|------------------------|-------------------|
| Model | D-Y59BL | D-Y69BL |
| Wiring system | 2 wires, axial | 2 wires, vertical |
| Output system | _ | |
| Applicable load | relay DC, PLC | |
| Current consumption | _ | |
| Power supply voltage | 10 - 28VDC | |
| Load voltage | 40 mA | |
| Internal voltage drop | < 4V | |
| Leakage current | < 0.8 mA a 24V | |
| Indicator light | Red LED lights u | ıp when ON |

- Operating time 1ms
- Impact resistance 100 G
- Insulation resistance >50M Ω with a 500VDC megohmmeter
- Withstand voltage 1000VAC (for 1 minute)
- Ambient temperature -10 to 60°C
 Protective structure IEC IP67, waterproof (JISC0920), oil resistant


Internal cicuits

D-Y59BL / D-Y69BL ⇔ + Brown ─ Blue


Dimensions

[mm]

D-Y59BL



D-Y69BL



Auto switch mounting

[mm]




Minimum strokes for auto switches

| Auto switch type | Model | Amount* of | Ø32 | Ø40 | Ø50 | Ø63 | Ø80 | Ø100 |
|------------------|---------|------------|-----|-----|-----|-----|-----|------|
| | | switches | | | | | | |
| Reed | D-Z73L | 2 pcs. | 25 | | | | 15 | |
| | D-Z80L | 1 pcs. | | | | | | |
| Solid | D-Y59BL | 2 pcs. | 25 | | | | 15 | |
| state | D-Y69BL | 1 pcs. | | | | | | |
| | D-Y7PL | | | | | | | |

*Auto switches are mounted on the same side but in different grooves of the cylinder.

Recommended mounting position for stroke ends

[mm]



| Bore | D-Z73L, D-Z80L, D-Y7PL | | | | | | |
|------|------------------------|-------|--|--|--|--|--|
| (mm) | D-Y59BL, D-Y | ′69BL | | | | | |
| | Α | В | | | | | |
| 32 | 14 | 1 | | | | | |
| 40 | 25 | 1 | | | | | |
| 50 | 16 | 2 | | | | | |
| 63 | 31 | 2 | | | | | |
| 80 | 21.5 | 5.5 | | | | | |
| 100 | 31.5 | 5.5 | | | | | |

Mounting of Auto Switches

1N·m: approx. 10.2kgf·cm


When attaching an auto switch, first take a switch holder between your fingers and press it into a switch mounting groove. When doing this, confirm that it is set in the correct mounting orientation, or reattach if necessary. Next, insert an auto switch into the groove and slide it until it is positioned under the switch holder. After establishing the mounting position, use a watchmakers flat head screw driver to

tighten the switch mounting screw which is included.





Switch holder: BMP1-032



switch mounting screw, use a watchmakers screw driver with a handle about 5 to 6mm Tighten to a torque of approximately 0.05 to 0.1Nm

(0.51 to 1.02kgf·cm). As a rule, it is turned about 90° past the point at which tightening can be felt.

How to order: Auto Switches, holders and Groove Covers

Auto switch holder hand

| Auto SWI | item moraer ba | iiu | | | | | | |
|----------|----------------|---------------|--|--|--|--|--|--|
| | Order No. | | | | | | | |
| Ø | Auto | Switch holder | | | | | | |
| | switch | | | | | | | |
| 32 | D-Z73L | BMP1-032 | | | | | | |
| 40 | D-Z80L | | | | | | | |
| 50 | D-Y7PL | | | | | | | |
| 63 | D-Y59BL | | | | | | | |
| 80 | D-Y69BL | | | | | | | |
| 100 | | | | | | | | |

Groove cover of square tube

| Ø | Order No. | Cylinder length |
|--------------|-------------------------|-----------------------|
| | | without stroke |
| 32 | CP95-AL | 41.5 mm |
| 40 | | 52.5 mm |
| 50 | | 44.5 mm |
| 63 | | 59.5 mm |
| 80 | | 53.5 mm |
| 100 | | 63.5 mm |
| □ \M/rito th | o roquirod longth of th | o gracus cover in the |

Groove covers are available in progressive rates of 1 metre. Please, indicate round figures when ordering.


Order example: Groove cover for CP95SB63-160

59.5 mm + 160 mm = 239.5 x 8 grooves = 1916 mm
[Cylinder length without stroke] [Stroke] [8 grooves in the square tube]


Length to order: 1916 mm corresponds to a groove cover of 2 m for each cylinder Order No.: CP95-AL 2 length in metres

Series CP95 Guide Units

- Ball bush and Slide Bearing options.
- High resistance to side load.
- High non-rotating accuracy.
- Direct Mounting facility.
- Stroke adjusting unit option. Ø32~Ø63



How to order: Guide Units




How to order: Stroke Adjusting Unit* and Shock Absorber*

| Cylinder | | |
|-----------|-----------------------|----------------|
| Bore Size | Part Number | |
| (mm) | Stroke adjusting unit | Shock absorber |
| 32 | SFY(F)133 | RBC1412 |
| 40 | SFY(F)134 | RBC2015 |
| 50 | SFY(F)135 | RBC2015 |
| 63 | SFY(F)136 | RBC2015 |

^{*} Order separately






| Diameter | Α | В | С | D1 | D2 | D3 | E2 | E3 | E4 | F | L0 | L1 | L2 | L3L | L4 | L5 | L6 | L7 | L8 | L9 | М | Р | S |
|----------|----|----|-----|-----|-----|----|----|-----|-----|----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|-----|----|----------|
| 32 | 12 | 12 | 74 | m6 | 6.6 | 11 | 33 | 78 | 61 | 4 | 45 | 92 | 50 | 97 | 147 | 120 | 64 | 20 | 60 | 102 | 6.5 | 12 | M10x1.25 |
| 40 | 16 | 15 | 87 | M6 | 6.6 | 11 | 38 | 84 | 69 | 18 | 55 | 112 | 58 | 116 | 167 | 125 | 81 | 25 | 63 | 127 | 6 | 12 | M12x1.25 |
| 50 | 20 | 19 | 104 | M8 | 9 | 15 | 47 | 100 | 85 | 24 | 68 | 134 | 70 | 137 | 195 | 140 | 94 | 25 | 70 | 134 | 9 | 16 | M16x1.5 |
| 63 | 20 | 19 | 119 | M8 | 9 | 15 | 57 | 105 | 100 | 20 | 80 | 148 | 85 | 152 | 195 | 160 | 94 | 25 | 75 | 145 | 9 | 16 | M16x1.5 |
| 80 | 25 | 22 | 148 | M10 | 11 | 18 | 72 | 130 | 130 | 25 | 100 | 180 | 105 | 189 | 241 | 195 | 114 | 30 | 89 | 157 | 11 | 20 | M20x1.5 |
| 100 | 25 | 22 | 173 | M10 | 11 | 18 | 89 | 150 | 150 | 30 | 120 | 206 | 130 | 213 | 241 | 205 | 120 | 30 | 90 | 172 | 11 | 20 | M20x1.5 |

Dimensions Stroke Adjusting Unit

[mm]



A minimum length will have to be added on for stroke adjusting unit.

(mm)


| Diameter | Model | Α | В | D1 | D2 | Е | F | G | Н | J | Min. add on stroke |
|----------|-----------|------|----|---------|-----|----|-----|-----|----|----|--------------------|
| ø32 | SFY(F)133 | 35.5 | 15 | M14x1.5 | M8 | 51 | 95 | 78 | 17 | 53 | 51 |
| ø40 | SFY(F)134 | 45 | 20 | M20x1.5 | M10 | 59 | 114 | 87 | 25 | 62 | 65 |
| ø50 | SFY(F)135 | 45 | 25 | M20x1.5 | M10 | 72 | 135 | 98 | 28 | 68 | 70 |
| ø63 | SFY(F)136 | 45 | 25 | M25x1.5 | M10 | 86 | 150 | 118 | 28 | 88 | 70 |

1.8-24


Permissable Rotary Torque Plate


(Nm) Allowable Load

[daN]




| Diameter | Series | Stroke |) | | | | |
|----------|--------|--------|------|------|------|------|------|
| (mm) | | 50 | 100 | 200 | 300 | 400 | 500 |
| 32 | GUM | 11.4 | 7.5 | 4.0 | 2.7 | 2.2 | - |
| 32 | GUL | 6.0 | 4.5 | 3.1 | 2.3 | 1.8 | - |
| 40 | GUM | 21.7 | 16.6 | 9.9 | 7.0 | 5.1 | 3.6 |
| 40 | GUL | 11.1 | 8.4 | 5.7 | 4.35 | 3.48 | 2.9 |
| 50 | GUM | 37.4 | 28.7 | 15.3 | 11.5 | 9.1 | 6.7 |
| 50 | GUL | 18.5 | 14.5 | 10.0 | 7.6 | 5.9 | 4.7 |
| 63 | GUM | 47.6 | 36.1 | 20.1 | 13.9 | 10.7 | 8.0 |
| 63 | GUL | 22.6 | 17.9 | 12.7 | 9.8 | 8.0 | 6.4 |
| 80 | GUM | 81.4 | 65.1 | 42.1 | 28.8 | 21.8 | 17.3 |
| 80 | GUL | 45.5 | 37.2 | 27.3 | 21.6 | 17.8 | 15.1 |
| 100 | GUM | 95.1 | 76.1 | 49.3 | 33.7 | 25.5 | 20.3 |
| 100 | GUL | 53.1 | 43.5 | 32.0 | 25.2 | 20.8 | 17.7 |





Deflection (For max. allowable load)

[mm]




| Diameter | Series | Stroke | ! | | | | |
|----------|--------|--------|------|------|------|------|------|
| (mm) | | 50 | 100 | 200 | 300 | 400 | 500 |
| 32 | GUM | 0.09 | 0.32 | 1.06 | 2.10 | 3.90 | - |
| 32 | GUL | 0.05 | 0.20 | 0.80 | 1.80 | 3.30 | - |
| 40 | GUM | 0.05 | 0.19 | 0.70 | 1.50 | 2.40 | 3.30 |
| 40 | GUL | 0.02 | 0.10 | 0.40 | 0.90 | 1.60 | 2.60 |
| 50 | GUM | 0.03 | 0.12 | 0.38 | 0.90 | 1.50 | 2.10 |
| 50 | GUL | 0.015 | 0.06 | 0.25 | 0.57 | 1.00 | 1.50 |
| 63 | GUM | 0.04 | 0.15 | 0.47 | 0.96 | 1.60 | 2.30 |
| 63 | GUL | 0.018 | 0.07 | 0.30 | 0.70 | 1.20 | 1.80 |
| 80 | GUM | 0.03 | 0.10 | 0.36 | 0.70 | 1.15 | 1.69 |
| 80 | GUL | 0.015 | 0.06 | 0.24 | 0.54 | 0.95 | 1.50 |
| 100 | GUM | 0.03 | 0.10 | 0.36 | 0.70 | 1.15 | 1.69 |
| 100 | GUL | 0.015 | 0.06 | 0.24 | 0.54 | 0.95 | 1.50 |
| | | | | | | | |

The values are for maximum allowable load and are the same for both mounting examples shown.

Series CP95 Cylinder Flow Rate and Air Consumption

In order to determine the correct size of valves, piping and accessories the maximum air consumption should be calculated. Air consumption is determined by the total maximum air consumed by all the cylinders that operate during an operating cycle, and is dependant on the maximum cylinder speed.

Theoretical maximum air consumption



Thermal loss is not represented in this diagram. For this reason, the air consumption is multiplied by 1.4. This factor is an average value.

Example

Calculate the maximum effective air consumption of a \emptyset 63 cylinder at an average speed of 500 mm/s. The working pressure is 0.6 MPa.


Solution

- Determine the intersection point of the 0.6 MPa working pressure on the horizontal axis with the 500 mm/s average speed on the vertical axis.
- 2.Extend the intersection point **1** upward to the Ø63 cylinder. Intersection point **2** is obtained.
- 3. Extend the intersection point **②** rightward or leftward. A Q value of approximately 620 Ne/min is obtained.
- 4.The 620 Nt/min.theoretical value is multiplied by 1.4 Q = 620 Nt/min. \times 1.4 Q = 870 Nt/min.

Average air consumption of compressed air cylinders and piping

In order to find the appropiate size of the compressor and the compressed air supply. It is necessary to determine the average compressed air consumption.

Average theoretical air consumption of cylinders in a cycle/m. (1 cycle = SWITCH ON/SWITCH OFF)



Example:

Cylinder diameter: Ø50 mm Stroke: 600 mm Working pressure: 0.5 MPa Cycles: 5 per minute Bore size: 6 mm


Piping length (between the cylinder and the valve): 2 m

Cylinder air consumption

- 1. Determine the intersection point of a 0.5 MPa working pressure with a stroke of 600 mm.
- 2. Extend the intersection point upward to the intersection point 2 where a Ø50 mm is represented.3. Extend the intersection point rightward or leftward. The Q
- value of 13.5 Nt/min. is obtained.
 4. The value of 13.5 Nt/min. is multiplied by 1.4 and by the
- number of cycles. $Q_1 = 13.5 \text{ Ne/min.} \times 1.4 \times 5 \text{ cycles}$
 - = 94.5 Ne/min.

Thermal loss is not represented in this diagram. For this reason, the air consumption is multiplied by 1.4. This factor is an average value.

Theoretical air consumption of compressed air piping



Air consumption of compressed air piping

- 5. Determine the intersection point **1** of a 0.5 MPa working pressure with a piping length of 2m.
- 6. Extend the intersection point upward to a Ø6 piping bore size. Intersection point is obtained.
- 7. Extend the intersection point **②** rightward or leftward. Value: Q = 0.56 Nℓ/min.
- 8. The value of 0.56 Nd/min. is multiplied by 1.4 and by the number of cycles.

 $Q_2 = 0.56$ Nd/min. \times 1.4 \times 5 cycles = 3.92 Nd/min.

Total air consumption of compressed air cylinder and piping:

 $Q = Q_1 + Q_2 = 94.5 \text{ Ne/min.} + 4 \text{ Ne/min.}$

Q = 98.5 Ne/min.

Maximum stroke determination

The table below indicates the maximum stroke with different mounting accessories. The values are for standard applications when a cylinder drives a load (m) that corresponds to the cylinder theoretical output which results from a determined working pressure. If the rod diameter is not the appropiate one in relation to the pressure and the stroke, a longer stroke cylinder should be selected or pressure should be reduced.

Allowable theoretical strokes (mm)

| | Mounting | type | | Accessories | Pressure | | | | | | (mm) |
|--------|---|-----------|------------|-------------|----------|-----|-----|------|-----|------|------|
| | | | | | [MPa] | 32 | 40 | 50 | 63 | 80 | 100b |
| | L | F (front) | G (rear) | | 0.2 | 680 | _ | _ | 980 | 1220 | 1410 |
| | | | | | 0.3 | 540 | _ | 1020 | 790 | 980 | 1140 |
| | | | | L | 0.4 | 460 | 700 | 880 | 680 | 840 | 980 |
| | | | | • | 0.5 | 410 | 630 | 780 | 610 | 750 | 880 |
| | | | | F (front) | 0.6 | 370 | 580 | 710 | 550 | 680 | 800 |
| | | | r Tan | | 0.7 | 340 | 520 | 650 | 500 | 620 | 730 |
| | | m | | | 0.8 | 310 | 480 | 600 | 460 | 580 | 680 |
| | | 7 | | | 0.9 | 290 | 450 | 570 | 430 | 540 | 630 |
| m | | | | | 1 | 270 | 420 | 530 | 400 | 510 | 590 |
| \ | | | | | 0.2 | 580 | 450 | 580 | 430 | 540 | 630 |
| Ì | | | | | 0.3 | 450 | 350 | 460 | 340 | 420 | 500 |
| 77977 | | | | | 0.4 | 370 | 300 | 390 | 280 | 350 | 420 |
| 7.1477 | | | MINITAL IN | G (rear) | 0.5 | 310 | 260 | 340 | 250 | 310 | 370 |
| | | | | | 0.6 | 270 | 230 | 300 | 220 | 270 | 330 |
| | | | | | 0.7 | 240 | 210 | 270 | 190 | 240 | 290 |
| | | | | | 8.0 | 210 | 190 | 250 | 170 | 220 | 270 |
| | | | | | 0.9 | 190 | 170 | 230 | 160 | 200 | 240 |
| | | | | | 1 | 170 | 160 | 210 | 140 | 190 | 220 |
| | C•D | | | | 0.2 | _ | _ | 1200 | 920 | 1150 | 1330 |
| | | | | | 0.3 | _ | 760 | 960 | 730 | 910 | 1050 |
| | | | | С | 0.4 | _ | 640 | 820 | 620 | 770 | 890 |
| | | | | • | 0.5 | _ | 570 | 720 | 540 | 680 | 780 |
| | | | | D | 0.6 | 630 | 510 | 650 | 490 | 610 | 700 |
| | | | | | 0.7 | 560 | 460 | 600 | 440 | 550 | 640 |
| | (m) | | | | 0.8 | 510 | 430 | 550 | 400 | 510 | 580 |
| | \ \delta | | | | 0.9 | 470 | 400 | 510 | 380 | 470 | 550 |
| m | | | | | 1 | 430 | 370 | 480 | 350 | 440 | 510 |
| uuu | | | | | | | | | | | |
| Ţ | | | | | | | | | | | |
| | | | | | | | | | | | |
| À | | | | | | | | | | | |
| 777777 | *************************************** | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |
| | | | | | | | | | | | |

G - Rear flange F - Front flange L - Foot

C - Male rear clevis
D - Female rear clevis

ISO/VDMA Air Cylinders Series CP95

Maximum stroke determination

Allowable theoretical strokes (mm)

| | Mounting | type | | Accessories | Pressure | Bore | | | | | (mm) |
|-------------|----------|------------|----------|-------------|----------|------|----------|------|------|----------|------|
| | | | | | [MPa] | 32 | 40 | 50 | 63 | 80 | 100 |
| | L | F (front) | G (rear) | L | 0.2 | | | | | | |
| | | | | • | 0.3 | | | | | | |
| | | | | F (front) | 0.4 | | | | | | |
| | | | | | 0.5 | 1 | | | | | |
| | | | | | 0.6 | | | | | | |
| | | | | | 0.7 | | | | | | |
| | 4 6 | Jaca J. | | | 0.8 | 1 | | | | | |
| | | | | | 0.9 | 1 | | | | | |
| m | | * P | | | 1 | *) | *) | *) | *) | *) | *) |
| | | | | | 0.2 | | <u> </u> | | | <u> </u> | |
| Ÿ | | | | G (rear) | 0.3 | 1 | _ | _ | 1160 | 1360 | _ |
| | | | | | 0.4 | 1 | _ | _ | 940 | 1160 | 1350 |
| | | | <u> </u> | | 0.5 | 1 | _ | 1080 | 830 | 1020 | 1190 |
| | 3 | | | | 0.6 | 1 | 770 | 980 | 750 | 920 | 1080 |
| | | | | | 0.7 | 1 | 700 | 900 | 680 | 850 | 990 |
| | | | | | 0.8 | 1 | 650 | 830 | 630 | 780 | 910 |
| | | | | | 0.9 | 1 | 610 | 790 | 590 | 740 | 860 |
| | | | | | 1 | *) | 580 | 740 | 560 | 690 | 810 |
| | L | F (front) | F (rear) | L | 0.2 | | | | | | |
| | | | | • | 0.3 | 1 | | | | | |
| | | | | F (front) | 0 .4 | 1 | | | | | |
| | | | | | 0.5 | 1 | | | | | |
| | | | | | 0.6 | 1 | | | | | |
| | المسالة | | | | 0.7 | 1 | | | | | |
| | | m | | | 0.8 | 1 | | | | | |
| m I | | 4 (| | | 0.9 | | | | | | |
| 444 | | 44 | | | 1 | *) | *) | *) | *) | *) | *) |
| / | | | | G (rear) | 0.2 | | | _ | _ | _ | _ |
| \] | | | | | 0.3 | | | _ | _ | _ | _ |
| | | | 1 111 | | 0.4 | | | _ | _ | _ | _ |
| | | | | | 0.5 | | | _ | _ | _ | _ |
| | | | | | 0.6 |] | | _ | 1010 | 1380 | _ |
| | | | | | 0.7 |] | | _ | 1020 | 1270 | 1470 |
| | | | | | 0.8 | 1 | | _ | 950 | 1180 | 1380 |
| | | | | | 0.9 | 1 | | 1160 | 890 | 1110 | 1290 |
| | | | | | 1 | *) | *) | 1090 | 840 | 1040 | 1220 |

^{*)} The maximum standard stroke should be used depending on the cylinder diameter (Refer to page 11 below for standard strokes).

G - Rear flange
F - Front flange
L - Foot
C - Male rear clevis
D - Female rear clevis



These safety instructions are intended to prevent a hazardous situation and/or equipment damage. These instructions indicate the level of potential hazard by a label of "Caution", "Warning" or "Danger". To ensure safety, be sure to observe ISO 4414 Note 1), JIS B 8370 Note 2) and other safety practices.

Caution: Operator error could result in injury or equipment damage.

Warning: Operator error could result in serious injury or loss of life.

⚠ Danger : In extreme conditions, there is a possible result of serious injury or loss of life.

Note 1) ISO 4414 : Pneumatic fluid power - Recommendations for the application of equipment to transmission and control systems.

Note 2) JIS B 8370: Pneumatic system axiom.

Marning

1 The compatibility of pneumatic equipment is the responsibility of the person who designs the pneumatic system or decides its specifications.

Since the products specified here are used in various operating conditions, their compatibility for the specific pneumatic system must be based on specifications or after analysis and/or tests to meet your specific requirements.

2 Only trained personnel should operate pneumatically operated machinery and equipment.

Compressed air can be dangerous if an operator is unfamiliar with it. Assembly, handling or repair of pneumatic systems should be performed by trained and experienced operators.

- 3 Do not service machinery/equipment or attempt to remove components until safety is confirmed.
- 1.Inspection and maintenance of machinery/equipment should only be performed after confirmation of safe locked-out control positions.
- 2. When equipment is to be removed, confirm the safety process as mentioned above. Cut the supply pressure for this equipment and exhaust all residual compressed air in the system.
- 3.Before machinery/equipment is re-started, take measures to prevent shooting-out of cylinder piston rod, etc. (Bleed air into the system gradually to create back-pressure.)
- 4 Contact SMC if the product is to be used in any of the following conditions:
- 1.Conditions and environments beyond the given specifications, or if product is used outdoors.
- Installation on equipment in conjuction with atomic energy, railway, air navigation, vehicles, medical equipment, food and beverages, recreation equipment, emergency stop circuits, press applications, or safety equipment.
- 3.An application which has the possibility of having negative effects on people, property, or animals, requiring special safety analysis.



Series CP95 Cylinder precautions

Be sure to read before handling.

Precautions on design

Marning

- 1. When mounting a cylinder in vertical position, the rod may come out due to an abnormal pressure drop.
- 2. A protective cover is recommended to minimize the risk of personal injury.
- 3. Securely tighten all stationary parts and connected parts so that they will not become loose.
- 4. Consider a possible drop in operating pressure due to a power outage, etc.
- 5. Design the system circuitry in order to prevent sudden lurching of driven objects.
- 6. Consider emergency stops.
- 7. Consider the action when operation is restarted after an emergency stop or abnormal stop. Design the machinery so that human injury or equipment damage will not occur upon restart of operation.

Selection

⚠ Caution

- 1. Check the catalogue specifications.
- Use a speed controller to adjust the cylinder drive speed, gradually increasing from a low speed to the desired speed setting.

Security precautions

- 1. Strokes must not exceed the specified limits.
- 2. Higher speed than specified may cause malfunction to the end of stroke cushioning.
- 3. When operating with long strokes, an intermediate band should be used to stabilize the rod (danger of bending).

Piston maximum speed

When an auto switch is placed at an intermediate position of the stroke and the piston speed is too high, the operating time will be shortened and the load may not operate properly. The maximum detectable piston speed is:

Example:

The operating range of a D-A73L Reed switch mounted in a CP95 cylinder is 8 mm. The operating time required to operate an electric valve is 30 ms = 0.003 s.

Maximum piston speed V =
$$\frac{8 \text{ mm}}{0.0305 \text{ s}}$$
 = 266 mm/s

Mounting


⚠ Warning

- 1. Make sure that there are no variations in the alignment between the rod centre and the load centre.
- If a guide is required, make sure transverse forces do not occur.
- 3. Avoid scratches on the rod.
- 4. Do not use until you verify that the equipment can operate properly.
- 5. The product should be mounted and operated after thoroughly reading the manual and understanding its contents.
- 6. Remove the packing of the air components, only at the moment of its mounting.

Wiring

⚠ Caution

- 1. Be sure that piping diameters are bigger than the connection thread diameters.
- 2. Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove dust or other debris from inside the pipe.
- Be certain that sealing material does not get inside the piping.
- 4. When pipe tape is used, leave 1.5 to 2 thread ridges exposed at the end of the pipe fitting.



Lubrication

Caution

1. The cylinders have been lubricated for life at the factory and can be used without any further lubrication.

Air supply

⚠ Warning

- 1. Use clean air.
- 2. Install air filters.
- 3. Install a water separator after the cooler.
- 4. Use the product within the specified range of fluid and ambient temperature.

(continued overleaf...)

Cylinder precautions continued

Operating Environment

Marning

- 1. Do not operate in environments with corrosive gases, sea water, water or steam.
- In locations where there is contact with spatter from water or oil, implement suitable protective measures.
- 3. If the cylinders are equipped with auto switches, do not operate in locations where there are strong magnetic fields.

End of stroke cushioning

⚠ Caution

1. Set screw adjusting.


The set screw has been already adjusted at the factory. Once it has been used, the set screw must be readjusted. Take into account the operating environment as well as the load size and weight. The effectivity of the end of stroke cushioning is shortened by the clockwise screw turn. The set screw should be secured by a locking washer.

Do not operate the cylinder when the set screw has been completely tightened.

Cylinder mounting

⚠ Warning

- 1. The maximum tightening torque must not exceed the specified diameter limits, because it may reduce the non-rotating guide accuracy.
- 2. When mounting rod accessories, be sure that moment does not occur to the ball joint piston rod in the cylinder headcover. Do not use an adjustable angle wrench on the operating surface of the rod.





Series CP95 Auto Switch Precautions

Be sure to read before handling.

Auto Switch Precautions

⚠ Caution

- 1. Confirm the specifications.
- When multiple auto switch cylinders are used in close proximity, magnetic field interference may cause the switches to malfunction. Maintain a minimum cylinder separation of 40 mm.
- 3. Wiring should be kept as short as possible.
- 4. Do not touch the piston rod when operating the cylinder.
- 5. Avoid close contact with magnetic substances (something attracted by a magnet), as the piston has a magnet ring which detects the magnetic force.
- Lead wire colours of Reed and Solid state switches have been changed. These changes have been validated for production beginning September 1997.

2 wire

| | Old | New |
|------------|-------|-------|
| Output (+) | Red | Brown |
| Output (–) | Black | Blue |

3 wire

| | Old | New |
|-----------------|-------|-------|
| Power supply(+) | Red | Brown |
| GND (-) | Black | Blue |
| Output | White | Black |

Auto switch wiring

- Load must not exceed the specified current and voltage limits.
- 2. Be sure to connect the load before power is applied.
- 3. Switches with indicator light have polarity. The brown lead wire is (+), and the blue lead wire is (-). If connections are reversed, a switch will operate, however, the light emitting diode will not light up.
- 4. When a switch with an indicator light operates under the specified current, even though the switch operates normally, the indicator light may hardly light up or may not light up.
- A voltage drop affects every auto switch when connected in series because of internal resistance in the light emitting diode.
- 6. When operating under a specified voltage, the internal voltage drop in the indicator light may cause the load malfunction.
- 7. If the internal voltage drop causes a problem, select a switch with no indicator light.

Auto Switch mounting

- 1. Although Reed switches have a 30G impact resistance, avoid bumps or excessive impacts.
- 2. Do not use in an area where magnetic fields are generated in order to avoid switches malfunction.
- 3. Avoid repeatedly bending or stretching lead wires.
- Although switches satisfy the IEC standard IP67 structure (JIS C 0920: anti-immersion structure), do not use switches in applications where continually exposed to water, oil, coolant liquid, etc.

Wiring

⚠ Warning

- 1. Confirm proper insulation of wiring.
- 2. Do not wire with high voltage lines.
- 3. Avoid incorrect wiring.

Operating environment

⚠ Warning

- 1. Never use in an atmosphere of explosive gases.
- 2.Do not use in an area where magnetic fields are generated.
- 3. Do not use in an environment where the auto switch will be continually exposed to water.
- $4.\mbox{Do}$ not use in an environment with oil or chemicals.
- Consult SMC if switches are used where there are temperature cycles other than normal temperature changes.
- 6.Do not use in locations where excessive impacts are generated. If an impact of 30G or more is applied to a switch, the signal may be interrupted for 1ms or less. Consult SMC the need of using a solid state switch depending on the environment.
- 7. Avoid accumulation of iron powder or close contact with magnetic substances.

Auto Switch precautions continued

Reed switch precautions


⚠ Caution

Noncontact switches are generally used in applications where other switches which are operated mechanically do not provide an optimal functioning in adverse environmental conditions, such as high frequency, dusty, dirty or very humid conditions.

Specifications

Reed switches have a Reed contact. There are two fine ferronickel-alloy contacts in a glass body. The force applied to close the contacts is minimal due to the short distance between them. Reed switches do not have protection circuits. For this reason, they should be provided with an external contact protection box.

- 1. The operating load is an inductive load
- 2. The length of wiring to the load is > 5 m
- 3. The load voltage is > 100 V AC




Contact protection box specifications

| Part No. | CD-P11 | | CD-P12 |
|-------------------|---------|----------|--------|
| Load voltage | 110V AC | 220 V AC | 24V DC |
| Max. load current | 23 mA | 11.5 mA | 50 mA |

Lead wire length: Switch connection side 0.5 m Load connection side 0.5 m

Contact protection box / Internal circuits



Contact protection box / Connection

To connect a switch unit to a contact protection box, connect the lead wire from the side of the contact protection box marked SWITCH to the lead wire coming out of the switch unit. The length of lead wire should be as short as possible, with a maximum of 1 m.

Main Index Series CP95

| | Page No. |
|---|---|
| Key Features | |
| Available Specifications | |
| How to Order | Cylinders |
| Switches | |
| | Switch Holder |
| Seal Kits | Standard Model |
| Technical Specification | Standard Model |
| Theoretical Output Table | Standard Model |
| Kinetic Energy Absorption | |
| Moveable Mass | |
| Cylinder Weight | |
| Cylinder Construction | |
| Moveable Mass | |
| Allowable Loads | |
| Cylinder Dimension | Standard Model |
| Accessory Dimensions | Standard Model |
| Piston Rod Accessories | |
| Auto Switch Specifications | |
| Auto Switch Mounting | |
| Auto Switch Holders | |
| Groove Covers | |
| Guide Units | How To Order 24 Dimensions 24 |
| Stroke Adjusting Unit (for guide unit) | How To Order 23 Dimensions 24 |
| Shock Absorber (for guide unit) | How To Order |
| Air Consumption | Cylinder (max.) 26 Cylinder and Piping 27 |
| Max. Stroke Determination | Theoretical |
| Safety Instructions | Cylinder 30 – 32 Auto Switches 33 – 34 |