

3-Colour Display



* PF3A□H(-L) series only

IP65

Digital Flow Switch for Large Flow

Applicable fluid **Air, N₂**

IO-Link
*1 For the PF3A□□H-L

Flow ratio *2 **100:1** A wide range of flow measurement is possible with 1 product.

*2 The flow ratio is 20 : 1 for the existing model (PF2A7□H/Large flow type).

Series	Output type	Rated flow range [l/min]
Body ported type PF3A703/706/712H(-L) Series	Switch output	30 3000 L type 3000
	Analogue output	60 6000 L type 6000
	IO-Link	120 12000 L type 12000
Modular type PF3A701/702H(-L) Series	Switch output	10 1000 L type 1000
	Analogue output	20 2000 L type 2000
	IO-Link	
New Modular type With pressure/ temperature sensor PF3A801/802H-L Series	Switch output	10 1000 L type 1000
	IO-Link	20 2000 L type 2000

New

IO-Link

4-Screen Display

Digital Flow Switch with Pressure/ Temperature Sensor

Simultaneous
measurement of the
(accumulated) flow
rate, pressure, and
temperature is
possible.



PF3A8□H-L Series **p. 6**

Modular type

Can be connected to the air combination **p. 5**



3-Screen Display Digital Flow Monitor



Allows for the monitoring of remote lines **p. 7**

IO-Link Compatible

The measured value and the device status can
be figured out easily via the process data. **p. 3**

Improved resistance to moisture and foreign matter

The bypass construction reduces sensor
accuracy deterioration and damage. **p. 1**


PF3A□H(-L) Series



CAT.EUS100-117D-UK

Improved resistance to moisture and foreign matter

The bypass construction reduces the moist air or foreign matter in contact with the sensor, reducing sensor accuracy deterioration and damage.



* The figure shows the PF3A703/6/12H(-L).

Through bore construction ^{*1}

- **Pressure loss:**
75 % reduction ^{*2}
(20 kPa / 5 kPa)
- **Maintenance-free fluid passage**

*1 Excludes the modular type
*2 Compared with the existing model (PF2A7□H/
Large flow type)



3-colour/2-screen display

* 2-screen display: 2-row display of main screen and sub screen

Upper Main display: **Green** At set point

Instantaneous flow rate **Green** **Red** (Upper Main display)




Upper Main display: **Red** At set point



Set value **Orange** (Lower Sub display)

The lower/sub display can be changed by pressing the up/down buttons.

* Either "Input of line name" or "Display OFF" can be added via the function settings.



Display rotates 90° and can be reversed.


Clockwise 90° **Easy operation, improved visibility**

The display can be rotated in increments of 90° according to the installation. The display can be reversed for easy operation.




Installation Example

Reversed display OFF



Reversed display ON (Can be set with the "Reversible display mode")



Smallest settable increment: 2 l/min

- * For the PF3A703H
- * 5 l/min for the existing model (PF2A703H/Large flow type)


Functions p. 37 to 39

- Output operation
- Simple setting mode
- Display colour
- Reference condition
- Response time (Digital filter)
- FUNC output switching function (Analogue output ⇔ External input)
- Selectable analogue output function
- External input function
- Forced output function
- Accumulated value hold
- Peak/Bottom value display
- Display OFF mode
- Setting of a security code
- Key-lock function
- Reset to the default settings
- Reversible display mode
- Zero cut-off function
- Delay time setting
- Selection of the display on the sub screen
- Analogue output free range function
- Error display function
- Zero-clear function
- Display fine adjustment function
- Measurement display setting

Grease-free

Application

Flow control of equipment, main line, and branch line




Select a digital flow switch to increase energy savings!

Flow control is necessary for promoting energy saving in any application. Saving energy starts from numerical control of the flow consumption of equipment and lines and clarification of the purpose and effect.

- Digital display allows **visualization**.
- **3-colour/2-screen display**, Improved visibility
- **Remote control** is possible with accumulated pulse.

Energy Saving Program

For details, refer to the SMC website.




IO-Link Compatible PF3A□□H-□□-L□-□□ p. 15

Supports the IO-Link communication protocol



IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard: IEC 61131-9.



Configuration File (IODD File*1)

· Manufacturer · Product part no. · Set value

*1 IODD File:
IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.

Device settings can be set by the master.

- Threshold value
- Operation mode, etc.

Read the device data.

- Switch ON/OFF signal and analogue value
- Device information:
Manufacturer, Product part number, Serial number, etc.
- Normal or abnormal device status
- Cable breakage

IO-Link Master




IO-Link Compatible Device:
Digital Flow Switch for Large Air Flow
PF3A7□H-L Series













IO-Link Compatible Device:
Digital Flow Switch for Large Air Flow
PF3A8□H-L Series

Display function

Displays the output communication status and indicates the presence of communication data



Operation and Display

Communication with master	IO-Link status indicator light	Status			Screen display*2	Description
Yes	 *1	IO-Link mode	Normal	Operate		Normal communication status (readout of measured value)
	Start up				At the start of communication	
	Preoperate					
No	 *1 (Flashing)		Abnormal	Version does not match		The IO-Link version does not match that of the master. * The applicable IO-Link version is 1.1.
				Communication disconnection		Normal communication was not received for 1 s or longer.
						
						
No	OFF	SIO mode				General switch output

*1 In IO-Link mode, the IO-Link indicator is ON or flashing. *2 When the lower line (sub screen) is set to mode display (Upper line for the PF3A8□H-L)

* "ModE LoC" is displayed when the data storage lock is enabled. (Except for when the version does not match or when in SIO mode)

Implement diagnostic bits in the process data.


The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment. It is possible to find problems with the equipment in real time using the cyclic (periodic) data and to monitor such problems in detail with the noncyclic (aperiodic) data.

For the PF3A7□H-L

Process Data

Bit offset	Item	Note	Diagnosis items
0	OUT1 output	0: OFF 1: ON	<ul style="list-style-type: none"> · Over current error · Rated flow error · Accumulated flow error · Flow sensor failure · Temperature sensor failure · Internal product malfunction
1	OUT2 output	0: OFF 1: ON	
8	Flow rate diagnosis	0: OFF 1: ON	
14	Fixed output	0: OFF 1: ON	
15	Error (Failure)	0: OFF 1: ON	
16 to 31	Measured flow rate value	Signed 16 bit	

Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Measured flow rate value (PD)															
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	Error (Failure)	Fixed output	Reservation					Flow rate diagnosis	Reservation						OUT2	OUT1
																Switch output



For the PF3A8□H-L

Process Data


Bit offset	Item	Note	Bit offset	Item	Note
0	Accumulated flow SW1	0: OFF 1: ON	11	Temperature diagnosis	0: Normal 1: HHH/LLL
1	Accumulated flow SW2	0: OFF 1: ON	12	Pressure diagnosis	0: Normal 1: HHH/LLL
2	Flow rate SW1	0: OFF 1: ON	13	Fixed output	0: Normal output 1: Fixed output
3	Flow rate SW2	0: OFF 1: ON	14	Error	0: Normal 1: Abnormal
4	Temperature SW1	0: OFF 1: ON	15	System error	0: Normal 1: Abnormal
5	Temperature SW2	0: OFF 1: ON	16 to 31	Measured pressure value	Signed 16 bit
6	Pressure SW1	0: OFF 1: ON	32 to 47	Measured temperature value	Signed 16 bit
7	Pressure SW2	0: OFF 1: ON	48 to 63	Measured flow rate value	Signed 16 bit
8	Flow rate unit	0: L 1: ft3	64 to 79	Accumulated flow rate lower limit	Unsigned 32 bit
9	Flow rate criteria	0: STD 1: nor	80 to 95	Accumulated flow rate upper limit	
10	Flow rate diagnosis	0: Normal 1: HHH			

Bit offset	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80
Item	Accumulated flow rate upper limit (PD)															
Bit offset	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64
Item	Accumulated flow rate lower limit (PD)															
Bit offset	63	62	61	60	59	58	57	56	55	54	53	52	51	50	49	48
Item	Measured flow rate value (PD)															
Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32
Item	Measured temperature value (PD)															
Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Measured pressure value (PD)															
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	System error	Error	Fixed output	Pressure diagnosis	Temperature diagnosis	Flow rate diagnosis	Flow rate criteria	Flow rate unit	Pressure 2	Pressure 1	Temperature 2	Temperature 1	Flow rate 2	Flow rate 1	Accumulated flow 2	Accumulated flow 1

Diagnosis items
<ul style="list-style-type: none"> · Rated flow error · Above/Below the rated pressure range · Above/Below the rated temperature range · Error (Over current, Outside of zero-clear range, Version does not match) · System error (Flow/Temperature sensor failure, Internal malfunction)



Application Example



3-Colour Display Modular Type Digital Flow Switch PF3A701H/702H(-L) Series

pp. 17, 19

Can be connected to the air combination


Series	AC30-D	AC40-D	Flow range
PF3A701H(-L)	●		1000 l/min
PF3A702H(-L)		●	2000 l/min




Air Combination Connection Examples

Products do not come assembled.
They should be ordered separately and assembled by the customer.

For the AC30B-D + PF3A701H



For the AW30-D + PF3A701H



Simple Specials System


Unit with F.R.L is available with the simple special ordering system.
The lead time is almost the same as the standard product.

Please contact your local sales representative for more details.

A right to left (-R) flow direction is also available.




90° rotation




The flow switch can be installed/removed without removing the piping.

Reduced maintenance time for inspection, cleaning, replacement, etc.



When the PF3A703H is used with steel pipes

Loosen the bracket-retaining ring.



Remove the steel pipe from the flow switch.

4-Screen Display Modular Type Digital Flow Switch with Pressure/Temperature Sensor

PF3A801H/802H-L Series p. 21

Can be connected to the air combination

Series	AC30-D	AC40-D	Flow range	Pressure	Temperature
PF3A801H-L	●		1000 l/min	1 MPa	50 °C
PF3A802H-L		●	2000 l/min		



3-colour/4-screen display


Simultaneous measurement of the instantaneous flow rate, accumulated flow rate, pressure, and temperature

Pressure sensor

Rated pressure range: 0 to 1 MPa

Temperature sensor


Rated temperature range: 0 to 50 °C




Space-saving design, Reduced labour

Both the flow rate and pressure can be measured with 1 product.

The installation of a digital pressure switch and a cross spacer is not necessary, thus reducing the face-to-face and depth dimensions. In addition, only 1 cable is required for wiring. This reduces the required installation space, piping, and wiring work.



Reduced wiring labour
(2 wires → 1 wire)



Depth dimension
reduced by 35 mm


Face-to-face dimension
reduced by 35 mm

3-Screen Display Digital Flow Monitor

PFG300 Series p. 31




Allows for the monitoring of remote lines



Visualization of settings


The sub screen (label) shows the item to be set.




Mode Examples	Hysteresis mode					
	Normal output	Set value (Threshold value)	Reversed output	Set value (Threshold value)	Hysteresis	Set hysteresis value
	P.1	1500	n.1	1500	H.1	150
Window comparator mode	Normal output/Lo side			Normal output/Hi side		
	Normal output/Lo side	Set value (Threshold value)		Normal output/Hi side	Set value (Threshold value)	
	P.L	900		P.H	1800	
	Reversed output/Lo side			Reversed output/Hi side		
	Reversed output/Lo side	Set value (Threshold value)		Reversed output/Hi side	Set value (Threshold value)	
	n.L	900		n.H	1800	

Easy screen switching

It is possible to change the settings while checking the measured value.




The sub screen can be switched by pressing the up/down buttons.



* Either "Input of line name" or "Display OFF" can be added via the function settings.


Simple 3-step setting

When the S button is pressed and the set value (P_1) is being displayed, the set value (threshold value) can be set. When the S button is pressed and the hysteresis (H_1) is being displayed, the hysteresis value can be set.




With a snap shot function for set value reading

Pressing the up and down buttons simultaneously for a minimum of 1 second will make the set value (threshold value) the same as the current flow value.




NPN/PNP switch function

The number of stock items can be reduced.



Input range selection (for Pressure/Flow rate)




The displayed value to the sensor input can be set as required.
(Voltage input: 1 to 5 V/Current input: 4 to 20 mA)
Pressure switch/Flow switch can be displayed.

A is displayed for 1 V (or 4 mA). B is displayed for 5 V (or 20 mA).
The range can be set as required.

Analogue output of 0 to 10 V is also available.

Voltage output	1 to 5 V	Switchable
	0 to 10 V	
Current output	4 to 20 mA	Fixed

■ Pressure Sensor for General Fluids/PSE570




	A	B
PSE570	0	1000
PSE573	-100	100
PSE574	0	500

Set A and B to the values shown in the table above.

Convenient functions

● Copy function

The settings of the master monitor can be copied to the slave monitors.



● Security code

The key locking function keeps unauthorized persons from tampering with the settings.

● Power saving mode

Power consumption is reduced by turning off the monitor.

Current consumption*1	Reduction rate*2
25 mA or less	Approx. 50 % reduction

*1 During normal operation *2 In power saving mode


● External input function

The accumulated value, peak value, and bottom value can be reset remotely.

Compact & Lightweight

● Compact: Max. 6 mm shorter

● Lightweight: Max. 5 g lighter (30 g / 25 g)




Functions pp. 40 to 42

- Output operation
- Simple setting mode
- Display colour
- Delay time setting
- Digital filter setting
- FUNC output switching function
- Selectable analogue output function
- External input function
- Forced output function
- Accumulated value hold
- Peak/Bottom value display
- Setting of a security code
- Key-lock function
- Reset to the default settings
- Display with zero cut-off setting
- Selection of the display on the sub screen
- Analogue output free range function
- Error display function
- Copy function
- Selection of power saving mode

Mounting


The bracket configuration allows for mounting in four orientations.

Bracket A



Mounting example

Bracket B




Mounting example

Panel mounting









Mountable side by side both vertically and horizontally


One opening!

- Reduced panel fitting labour
- Space saving










Flow Switch Flow Rate Variations

Series		Applicable fluid	Detection method	Smallest settable increment	Rated flow range [l/min]																					
	Compatibility with the PFG300 digital flow monitor				0.1	0.2	0.5	1	2	5	10	20	25	50	100	150	200	300	500	600	1000	2000	3000	6000	12000	
PF2A 	—	Air N ₂	Thermal type (Thermistor)	0.1 l/min				1																		
				0.5 l/min					5																	
				1 l/min						10																
				2 l/min							20															
				5 l/min									50													
PF3A□H(-L)  Body ported type p. 13, 15  PFG300 p. 31 Modular type p. 17, 19	—	Air N ₂	Thermal type (Platinum sensor)	2 l/min																			3000			
				5 l/min																					6000	
				10 l/min																					12000	
			Bypass flow type	1 l/min																						1000
				2 l/min																						2000
PF2M7(-L) 	—	Dry air N ₂ Ar CO ₂	Thermal type (MEMS)	0.001 l/min	0.01																					
					0.02																					
				0.1 l/min	0.05																					
					0.1																					
				0.1 l/min	0.3																					
					0.5																					
				1 l/min	1																					
PFMB   PFG300	—	Dry air N ₂	Thermal type (MEMS)																							
			Bypass flow type	1 l/min																						
PFMC(-L)   PFG300	—	Dry air N ₂	Thermal type (MEMS)	1 l/min																						
			Bypass flow type																							

Series	Applicable fluid	Detection method	Rated flow range [l/min]									
			-3	-2	-1	-0.5	0	0.5	1	2	3	
PFMV 	Dry air N ₂	Thermal type (MEMS)						0	0.5			
								0	1			
								0			3	
						-0.5		0.5				
					-1				1			
			-3									3

Flow Switch Variations / Basic Performance Table

Series	PFMV  PFMV3	PF2M7(-L) 	PFMB  PFG300	PFMC(-L)  PFG300	PF2A 	PF3A□H(-L) p. 13  PFG300 p. 31 
Enclosure	IP40	IP40	IP40	IP65 [Monitor unit: IP40]	IP65	IP65 [Monitor unit: IP40]
Fluid	Dry air, N ₂	Dry air, N ₂ , Ar, CO ₂	Dry air, N ₂	Dry air, N ₂	Air, N ₂	Air, N ₂
Setting	Digital	Digital	Digital	Digital	Digital	Digital
Rated flow range [l/min]	0 to 0.5 -0.5 to 0.5 0 to 1 -1 to 1 0 to 3 -3 to 3	0.01 to 1 0.02 to 2 0.05 to 5 0.1 to 10 0.3 to 25 0.5 to 50 1 to 100 2 to 200	2 to 200 5 to 500 10 to 1000 20 to 2000	5 to 500 10 to 1000 20 to 2000	1 to 10 5 to 50 10 to 100 20 to 200 50 to 500	30 to 3000 10 to 1000 60 to 6000 20 to 2000 120 to 12000
Power supply voltage	12 to 24 VDC ±10 %	PF2M7 12 to 24 VDC ±10 % PF2M7-L 18 to 30 VDC ±10 %	12 to 24 VDC ±10 %	PFMC 12 to 24 VDC ±10 % PFMC-L 18 to 30 VDC ±10 %	12 to 24 VDC ±10 %	PF3A7□H 24 VDC ±10 % PF3A7□H-L 18 to 30 VDC ±10 % PF3A701H/ 702H-L 21.6 to 30 VDC PF3A8□H-L 21.6 to 30 VDC
Temperature characteristics (25 °C standard)	±2 % F.S. (15 to 35 °C) [Monitor unit: ±0.5 % F.S. (0 to 50 °C)] ±5 % F.S. (0 to 50 °C)	±3 % F.S. ±1 digit (15 to 35 °C) ±5 % F.S. ±1 digit (0 to 50 °C)	±2 % F.S. (15 to 35 °C) [Monitor unit: ±0.5 % F.S. (0 to 50 °C)] ±5 % F.S. (0 to 50 °C)	±2 % F.S. (15 to 35 °C) [Monitor unit: ±0.5 % F.S. (0 to 50 °C)] ±5 % F.S. (0 to 50 °C)	±3 % F.S. (15 to 35 °C) ±5 % F.S. (0 to 50 °C)	±5 % F.S. [Monitor unit: ±0.5 % F.S. (0 to 50 °C)]
Repeatability	±2 % F.S. (Fluid: Dry air) [Monitor unit: ±0.1 % F.S. Analogue output: ±5 % F.S.] Analogue output: ±5 % F.S.	±1 % F.S. ±1 digit (Fluid: Dry air)	±1 % F.S. [Monitor unit: ±0.1 % F.S.] (Fluid: Dry air)	±1 % F.S. [Monitor unit: ±0.1 % F.S.] (Fluid: Dry air)	±1 % F.S. (PF2A7□0) ±2 % F.S. (PF2A7□1)	±1 % F.S. [Monitor unit: ±0.1 % F.S.]
Hysteresis	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Fixed (3 digits)	Hysteresis mode: Variable Window comparator mode: Variable
Output	NPN/PNP open collector Analogue voltage output Analogue current output	NPN/PNP open collector Accumulated pulse output Analogue voltage output Analogue current output IO-Link	NPN/PNP open collector Accumulated pulse output Analogue voltage output Analogue current output	NPN/PNP open collector Accumulated pulse output Analogue voltage output Analogue current output IO-Link	NPN/PNP open collector Accumulated pulse output	NPN/PNP open collector Accumulated pulse output Analogue voltage output Analogue current output IO-Link
Display	[Monitor unit: 2-colour LCD display]	2-colour LCD display	2-colour LED/2-colour LCD display display [Monitor unit: 3-colour LCD display]	3-colour LCD display	LED display	3-colour LCD display

* The monitor unit values are for the PFG300 and PFMV3.

CONTENTS



Body Ported Type

3-Colour Display Digital Flow Switch *PF3A7□H Series*

Body Ported Type IO-Link Compatible

3-Colour Display Digital Flow Switch *PF3A7□H-L Series*

Modular Type

3-Colour Display Digital Flow Switch *PF3A7□H Series*

Modular Type IO-Link Compatible

3-Colour Display Digital Flow Switch *PF3A7□H-L Series*

Modular Type IO-Link Compatible

4-Screen Display Digital Flow Switch with Pressure/Temperature Sensor
PF3A8□H-L Series

3-Screen Display Digital Flow Monitor *PFG300 Series*



Body Ported Type

3-Colour Display Digital Flow Switch

PF3A7□H Series

How to Order p. 13

Specifications p. 14

Body Ported Type IO-Link Compatible

3-Colour Display Digital Flow Switch

PF3A7□H-L Series

How to Order p. 15

Specifications p. 16

Modular Type

3-Colour Display Digital Flow Switch

PF3A7□H Series

How to Order p. 17

Specifications p. 18

Modular Type IO-Link Compatible

3-Colour Display Digital Flow Switch

PF3A7□H-L Series

How to Order p. 19

Specifications p. 20

Modular Type

IO-Link Compatible

4-Screen Display Digital Flow Switch

with Pressure/Temperature Sensor

PF3A8□H-L Series

How to Order p. 21

Specifications p. 22

Flow Range p. 23

Analogue Output p. 23

Pressure Loss p. 24

Flow Rate Characteristics p. 24

IN Side Straight Section and Accuracy p. 25

Temperature Accuracy p. 25

Internal Circuits and Wiring Examples p. 26

Construction: Parts in Contact with Fluid p. 28

Dimensions p. 28

Optional Accessories p. 30

3-Screen Display Digital Flow Monitor PFG300 Series

How to Order p. 31

Specifications p. 32

Internal Circuits and Wiring Examples .. p. 33

Dimensions p. 34

PF3A□H(-L)/Function Details p. 37


PFG300/Function Details p. 40

Safety Instructions Back cover


Body Ported Type

3-Colour Display Digital Flow Switch

PF3A7□H Series



How to Order



PF3A 7 03 H - 10 - CS - M

Type

7	Integrated display
---	--------------------

Rated flow range

03	30 to 3000 l/min
06	60 to 6000 l/min
12	120 to 12000 l/min

Large flow type

Thread type

—	Rc
N	NPT
F*1	G

*1 ISO 1179-1 compliant

Port size

Symbol	Port size	Rated flow range		
		03	06	12
10	1	●	—	—
14	1 1/2	—	●	—
20	2	—	—	●

Calibration certificate*7

—	None
A*9	Yes

*7 The certificate is in both English and Japanese.

Unit specification

—	Units selection function
M	SI units only*6

*6 Fixed units: Instantaneous flow: l/min
Accumulated flow: L

Options

—	With lead wire with M12 connector (3 m)*5
N	Without lead wire with M12 connector

*5 Options are shipped together with the product but do not come assembled.

Output specification

Symbol	OUT	FUNC*2	Applicable monitor unit model
CS	NPN	Analogue voltage output*3 ⇔ External input*4	PFG300 series
DS	NPN	Analogue current output ⇔ External input*4	PFG310 series
ES	PNP	Analogue voltage output*3 ⇔ External input*4	PFG300 series
FS	PNP	Analogue current output ⇔ External input*4	PFG310 series

*2 Analogue output or external input can be selected by pressing the buttons. Analogue output is set as default setting.

*3 1 to 5 V or 0 to 10 V can be selected by pressing the button. The default setting is 1 to 5 V.

*4 The accumulated value, peak value, and bottom value can be reset.

Option/Part No.

When only optional parts are required, order with the part number listed below.

Part no.	Option	Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications

Model		PF3A703H	PF3A706H	PF3A712H
Fluid	Applicable fluid*1	Air, Nitrogen		
	Fluid temperature	0 to 50 °C		
Flow	Detection method	Thermal type		
	Rated flow range	30 to 3000 l/min	60 to 6000 l/min	120 to 12000 l/min
	Set point range*2	30 to 3150 l/min	60 to 6300 l/min	120 to 12600 l/min
		Instantaneous flow	Instantaneous flow	Instantaneous flow
	Smallest settable increment	0 to 999,999,999,990 L	0 to 999,999,999,900 L	0 to 999,999,999,900 L
		Accumulated flow	Accumulated flow	Accumulated flow
	Accumulated volume per pulse (Pulse width = 50 ms)	2 l/min	5 l/min	10 l/min
Pressure	Accumulated value hold function*3	10 L	100 L	100 L
	Rated pressure range	Select from 100 L/pulse or 1000 L/pulse.		
	Proof pressure	Intervals of 2 or 5 minutes can be selected.		
	Pressure loss	0.1 to 1.5 MPa		
	Pressure characteristics*4	2.25 MPa		
Electrical	Power supply voltage	Refer to the "Pressure Loss" graph on page 24.		
	Current consumption	±2.5 % F.S. (0.1 to 1.0 MPa, 0.5 MPa standard)		
	Protection	24 VDC ±10 %		
Accuracy	Display accuracy	150 mA or less		
	Analogue output accuracy	Polarity protection		
	Repeatability	±3.0 % F.S.		
	Temperature characteristics	±3.0 % F.S.		
Switch output	Output type	Switch output/Display: ±1.0 % F.S.		
	Output mode	Analogue output: ±1.0 % F.S.		
	Switch operation	Select from Instantaneous output (Hysteresis mode or Window comparator mode), Accumulated output, or Accumulated pulse output.		
	Max. load current	NPN open collector		
	Max. applied voltage (NPN only)	PNP open collector		
	Internal voltage drop (Residual voltage)	Select from Normal or Reversed output.		
	Response time*5	80 mA		
	Hysteresis*6	28 VDC		
Analogue output*7	Protection	NPN output type: 1 V or less (at load current of 60 mA)		
	Output type	PNP output type: 2 V or less (at load current of 60 mA)		
	Impedance	Select from 1 s, 2 s, or 5 s.		
	Response time*9	Variable from 0		
External input*10	Input type	Over current protection		
	Input mode	Voltage output: 1 to 5 V (0 to 10 V can be selected*8), Current output: 4 to 20 mA		
	Input time	Output impedance: Approx. 1 kΩ		
	Reference condition*11	Maximum load impedance: Approx. 600 Ω		
Display	Unit*12	Linked to the response time of the switch output		
	Display range*13	No-voltage input: 0.4 V or less		
	Minimum display unit	Select from Accumulated value external reset or Peak/Bottom value reset.		
	Display	30 ms or longer		
	Indicator LED	Select from Standard conditions or Normal conditions.		
	Enclosure	I/min, CFM (ft ³ /min)		
	Withstand voltage	L, ft ³		
	Insulation resistance	0 to 3150 l/min (Flow under 30 l/min is displayed as "0")		
Environmental resistance	Operating temperature range	0 to 6300 l/min (Flow under 60 l/min is displayed as "0")		
	Operating humidity range	0 to 999,999,999,990 L		
	Standards	0 to 999,999,999,900 L		
	Piping	0 to 12600 l/min (Flow under 120 l/min is displayed as "0")		
Main materials of parts in contact with fluid	Piping specification	Instantaneous flow		
	Length of lead wire with connector	Accumulated flow		
	Weight	2 l/min		
	Lead wire with connector	10 L		
Weight	Piping specification	5 l/min		
	Length of lead wire with connector	100 L		
	Weight	LCD, 2-screen display (Main screen/Sub screen)		
	Lead wire with connector	Main screen: Red/Green, Sub screen: Orange		
Environmental resistance	Withstand voltage	Main screen: 5 digits, 7 segment, Sub screen: 6 digits, 7 segment		
	Insulation resistance	OUT indicator: Red LED is ON when output is ON		
	Operating temperature range	IP65		
	Operating humidity range	1000 VAC for 1 minute between terminals and housing		
Standards	Piping specification	50 MΩ (500 VDC measured via megohmmeter) between terminals and housing		
	Length of lead wire with connector	Operating: 0 to 50 °C, Stored: -10 to 60 °C (No freezing or condensation)		
	Weight	Operating/Stored: 35 to 85 % RH (No condensation)		
	Lead wire with connector	CE/UKCA marking, UL(CSA)		
Main materials of parts in contact with fluid	Piping specification	Rc1, NPT1, G1		
	Length of lead wire with connector	Rc1 1/2, NPT1 1/2, G1 1/2		
	Weight	Rc2, NPT2, G2		
	Lead wire with connector	Aluminium alloy, PPS, HNBR [Sensor: Pt, Au, Fe, Lead glass (exempted from the RoHS application), Al ₂ O ₃]		
Weight	Piping specification	3 m		
	Length of lead wire with connector	610 g		
	Weight	1190 g		
	Lead wire with connector	1680 g		
Environmental resistance	Piping specification	610 g		
	Length of lead wire with connector	1190 g		
	Weight	1220 g		
	Lead wire with connector	1720 g		

- *1 The air quality class is according to JIS B 8392-1:2012 [6:6:4] and ISO8573 1:2010 [6:6:4]. Use an air filter with 5 μm or less filtration rating on the inlet side.
- *2 Set point range will change according to the setting of the zero cut-off function.
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
- 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 - 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years
- If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 When the pressure range is 1.0 to 1.5 MPa, the pressure characteristics will be ±5 % F.S. (standard pressure is 0.5 MPa). Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port released to atmosphere, accuracy may vary.
- *5 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the switch output turns ON (or OFF) when set to be 90 % of the rated flow rate

- *6 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- *7 Analogue output or external input can be selected by pressing the buttons. Refer to the graph for analogue output.
- *8 When selecting 0 to 10 V, refer to the analogue output graph for the allowable load current.
- *9 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analogue output reaches 90 % of the rated flow rate
- *10 Analogue output or external input can be selected by pressing the buttons.
- *11 The flow rate given in the specifications is the value under standard conditions.
- *12 Setting is only possible for models with the units selection function.
- *13 Display range will change according to the setting of the zero cut-off function.
- *14 The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. The upper 6 digits and the lower 6 digits are displayed alternately, with "x 10⁶" lighting up when the upper digits are displayed.
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Body Ported Type

IO-Link

3-Colour Display

Digital Flow Switch

PF3A7□H-L Series



How to Order



PF3A 7 03 H - 10 - L Q - M

Type

7	Integrated display
---	--------------------

Rated flow range

03	30 to 3000 l/min
06	60 to 6000 l/min
12	120 to 12000 l/min

Large flow type

Thread type

—	Rc
N	NPT
F*1	G

*1 ISO 1179-1 compliant

Port size

Symbol	Port size	Rated flow range		
		03	06	12
10	1	●	—	—
14	1 1/2	—	●	—
20	2	—	—	●

Calibration certificate*8

—	None
A*10	Yes

*8 The certificate is in both English and Japanese.

Unit specification

—	Units selection function
M	SI units only*7

*7 Fixed units: Instantaneous flow: l/min
Accumulated flow: L

Options

—	With lead wire with M12 connector (3 m)*5
N	Without lead wire with M12 connector
Q	Lead wire with M12-M12 connector (3 m)*6

*5 Options are shipped together with the product but do not come assembled.

*6 The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Output specification

Symbol	OUT	FUNC*2	Applicable monitor unit model
L	IO-Link/ Switch output (N/P)	—	—
L3	IO-Link/ Switch output (N/P)	Analogue voltage output*3 ⇔ External input*4	PFG300 series
L4	IO-Link/ Switch output (N/P)	Analogue current output ⇔ External input*4	PFG310 series

*2 Analogue output or external input can be selected by pressing the buttons.

Analogue output is set as default setting.

Output symbol "L" cannot be used as the FUNC terminal is not connected.

*3 1 to 5 V or 0 to 10 V can be selected by pressing the button.
The default setting is 1 to 5 V.

*4 The accumulated value, peak value, and bottom value can be reset.

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

For flow switch precautions and specific product precautions, refer to the “Operation Manual” on the SMC website.

Specifications

Model			PF3A703H-L	PF3A706H-L	PF3A712H-L
Electrical	Power supply voltage	When used as a switch output device	24 VDC ±10 %		
		When used as an IO-Link device	21.6 to 30 VDC		
Switch output	Output type		Select from NPN or PNP open collector output.		
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.		
	Max. applied voltage		30 V (NPN output)		
	Internal voltage drop (Residual voltage)		1.5 V or less (at load current of 80 mA)		
	Delay time*1		3.3 ms or less, variable from 0 to 60 s/0.01 s increments		
Analogue output	Response time*2		Linked to the set value of the digital filter		
Display	Display		LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: Orange Main screen/Sub screen: 9 digits (7 segments 7 digits, 11 segments 2 digits)		
	Digital filter*3		Select from 1 s, 2 s, or 5 s.		
Standards			CE/UKCA marking, UL(CSA)		

*1 The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.

*2 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analogue output reaches 90 % of the rated flow rate

*3 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90 % in relation to the step input.

Communication Specifications (IO-Link mode)

IO-Link type	Device
IO-Link version	V 1.1
Communication speed	COM2 (38.4 kbps)
Configuration file	IODD file*1
Minimum cycle time	3.3 ms
Process data length	Input data: 4 bytes, Output data: 0 byte
On request data communication	Yes
Data storage function	Yes
Event function	Yes
Vendor ID	131 (0 x 0083)
Device ID*2	PF3A703H-□□-L□-□□ : 400 (0 x 0190)
	PF3A703H-□□-L3□-□□: 401 (0 x 0191)
	PF3A703H-□□-L4□-□□: 402 (0 x 0192)
	PF3A706H-□□-L□-□□ : 403 (0 x 0193)
	PF3A706H-□□-L3□-□□: 404 (0 x 0194)
	PF3A706H-□□-L4□-□□: 405 (0 x 0195)
	PF3A712H-□□-L□-□□ : 406 (0 x 0196)
	PF3A712H-□□-L3□-□□: 407 (0 x 0197)
	PF3A712H-□□-L4□-□□: 408 (0 x 0198)

*1 The configuration file can be downloaded from the SMC website, <https://www.smcworld.com>

*2 The device ID differs according to each product type (output specification).

Other specifications that are not listed are the same as those of the standard product. For details, refer to page 14.

Modular Type

3-Colour Display Digital Flow Switch

PF3A7□H Series



How to Order

PF3A 7 01 H - CS □ - M □ - □

Type

7	Integrated display
---	--------------------

Rated flow range

Symbol	Rated flow range	Applicable air combination model
01	10 to 1000 l/min	AC30-D
02	20 to 2000 l/min	AC40-D

Large flow type

Output specification

Symbol	OUT	FUNC*1	Applicable monitor unit model
CS	NPN	Analogue voltage output*2 ⇄ External input*3	PFG300 series
DS	NPN	Analogue current output ⇄ External input*3	PFG310 series
ES	PNP	Analogue voltage output*2 ⇄ External input*3	PFG300 series
FS	PNP	Analogue current output ⇄ External input*3	PFG310 series

- *1 Analogue output or external input can be selected by pressing the buttons. Analogue output is set as default setting.
 *2 1 to 5 V or 0 to 10 V can be selected by pressing the button. The default setting is 1 to 5 V.
 *3 The accumulated value, peak value, and bottom value can be reset.

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

Flow direction

—	Left to right
R	Right to left

Calibration certificate*7

—	None
A*9	Yes

*7 The certificate is in both English and Japanese.

Unit specification

—	Units selection function
M	SI units only*6

*6 Fixed units: Instantaneous flow: l/min
Accumulated flow: L

Option*4

—	With lead wire with connector (3 m)
N	Without lead wire with connector
Q	Lead wire with M12-M12 connector (3 m)*5


*4 Options are shipped together with the product but do not come assembled.

*5 The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



- * Avoid mounting the lubricator on the inlet side.
 * If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

Assembly example

- ① Digital flow switch PF3A701H-CS-M 1 pc.
- ② Air combination AC30B-03E-D 1 pc.
- ③ Spacer with bracket Y300T-D 2 pcs.
- ④ Piping adapter E300-03-D 1 pc.

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

Please contact your local sales representative for more details.

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications

Model		PF3A701H	PF3A702H
Fluid	Applicable fluid*1	Air, Nitrogen	
	Fluid temperature	0 to 50 °C	
Flow	Detection method	Thermal type (Bypass flow type)	
	Rated flow range	10 to 1000 l/min	20 to 2000 l/min
	Set point range*2	Instantaneous flow 10 to 1050 l/min	20 to 2100 l/min
	Accumulated flow	0 to 999,999,999 L	
	Smallest settable increment	Instantaneous flow 1 l/min	2 l/min
	Accumulated flow	10 L	
	Accumulated volume per pulse (Pulse width = 50 ms)	Select from 10 L/pulse or 100 L/pulse.	
	Accumulated value hold function*3	Intervals of 2 or 5 minutes can be selected.	
Pressure	Rated pressure range	0 to 1.0 MPa	
	Proof pressure	1.5 MPa	
	Pressure loss	Refer to the "Pressure Loss" graph on page 24.	
	Pressure characteristics*4	±5.0 % F.S. (0 to 1.0 MPa, 0.5 MPa standard)	
Electrical	Power supply voltage	24 VDC ±10 %	
	Current consumption	150 mA or less	
	Protection	Polarity protection	
Accuracy	Display accuracy*5	±3.0 % F.S.	
	Analogue output accuracy*5	±3.0 % F.S.	
	Repeatability	±1.0 % F.S.	
	Temperature characteristics	±5.0 % F.S. (Ambient temperature of 0 to 50 °C, 25 °C standard)	
	Effects of connecting modular products*6	±5.0 % F.S.	
Switch output	Output type	NPN open collector, PNP open collector	
	Output mode	Select from Instantaneous output (Hysteresis mode or Window comparator mode), Accumulated output, or Accumulated pulse output.	
	Switch operation	Select from Normal or Reversed output.	
	Max. load current	80 mA	
	Max. applied voltage (NPN only)	28 VDC	
	Internal voltage drop (Residual voltage)	NPN output type: 1 V or less (at load current of 60 mA), PNP output type: 2 V or less (at load current of 60 mA)	
	Response time*7	Select from 1 s, 2 s, or 5 s.	
	Hysteresis*8	Variable from 0	
Analogue output*9	Protection	Over current protection	
	Output type	Voltage output: 1 to 5 V (0 to 10 V can be selected*10), Current output: 4 to 20 mA	
	Impedance	Output impedance: Approx. 1 kΩ	
	Response time*11	Maximum load impedance: 600 Ω, Minimum load impedance: 50 Ω Linked to the response time of the switch output	
External input*12	Input type	No-voltage input: 0.4 V or less	
	Input mode	Select from Accumulated value external reset or Peak/Bottom value reset.	
	Input time	30 ms or longer	
Display	Reference condition*13	Select from Standard conditions or Normal conditions.	
	Unit*14	Instantaneous flow l/min, CFM (ft ³ /min)	
	Accumulated flow	L, ft ³	
	Display range*15	Instantaneous flow 0 to 1050 l/min (Flow under 10 l/min is displayed as "0")	0 to 2100 l/min (Flow under 20 l/min is displayed as "0")
	Accumulated flow*16	0 to 999,999,999 L	
	Minimum display unit	Instantaneous flow 1 l/min	2 l/min
	Accumulated flow	10 L	
	Display	LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: Orange Main screen: 4 digits, 7 segment, Sub screen: 6 digits, 7 segment	
Environmental resistance	Indicator LED	OUT indicator: Red LED is ON when output is ON	
	Enclosure	IP65	
	Withstand voltage	1000 VAC for 1 minute between terminals and housing	
	Insulation resistance	50 MΩ (500 VDC measured via megohmmeter) between terminals and housing	
	Operating temperature range	Operating: 0 to 50 °C, Stored: -10 to 60 °C (No freezing or condensation)	
Standards		Operating/Stored: 35 to 85 % RH (No condensation) CE/UKCA marking, UL(CSA)	
Piping	Piping specification	Modular (Body size: 30)	Modular (Body size: 40)
Main materials of parts in contact with fluid		Stainless steel 304, Aluminium alloy, PPS, HNBR [Sensor: Pt, Au, Ni, Fe, Lead glass (exempted from the RoHS application), Al ₂ O ₃]	
Length of lead wire with connector		3 m	
Weight	Body	350 g	400 g
	Lead wire with connector	+90 g	

- *1 The air quality class is according to JIS B 8392-1:2012 [6:6:4] and ISO8573 1:2010 [6:6:4]. Use an air filter with 5 µm or less filtration rating on the inlet side.
- *2 Set point range will change according to the setting of the zero cut-off function.
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
 · 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 · 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years
 If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port released to atmosphere, accuracy may vary.
- *5 The value when connecting a product with a port size of 3/8 (PF3A701H) or 1/2 (PF3A702H)
- *6 The value when the port size of the modular product is 3/8 (PF3A701H) or 1/2 (PF3A702H) and the product is operated at a supply pressure of 0.5 MPa
- *7 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the switch output turns ON (or OFF) when set to be 90 % of the rated flow rate

- *8 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- *9 Analogue output or external input can be selected by pressing the buttons. Refer to the graph for analogue output.
- *10 When selecting 0 to 10 V, refer to the analogue output graph for the allowable load current.
- *11 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analogue output reaches 90 % of the rated flow rate
- *12 Analogue output or external input can be selected by pressing the buttons.
- *13 The flow rate given in the specifications is the value under standard conditions.
- *14 Setting is only possible for models with the units selection function.
- *15 Display range will change according to the setting of the zero cut-off function.
- *16 The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. When the upper digits are displayed, x 10⁶ lights up.
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.


Modular Type

IO-Link

3-Colour Display

Digital Flow Switch

PF3A7□H-L Series



How to Order



PF3A 7 01 H-L Q-M - -

Type

7 Integrated display

Rated flow range

Symbol	Rated flow range	Applicable air combination model
01	10 to 1000 l/min	AC30-D
02	20 to 2000 l/min	AC40-D

Large flow type

Output specification

Symbol	OUT	FUNC*1	Applicable monitor unit model
L	IO-Link/ Switch output (N/P)	—	—
L3	IO-Link/ Switch output (N/P)	Analogue voltage output*2 ⇔ External input*3	PFG300 series
L4	IO-Link/ Switch output (N/P)	Analogue current output ⇔ External input*3	PFG310 series

- *1 Analogue output or external input can be selected by pressing the buttons. Analogue output is set as default setting.
 *2 1 to 5 V or 0 to 10 V can be selected by pressing the button. The default setting is 1 to 5 V.
 *3 The accumulated value, peak value, and bottom value can be reset.

Flow direction

—	Left to right
R	Right to left

Calibration certificate*7

—	None
A*9	Yes

*7 The certificate is in both English and Japanese.

Unit specification

—	Units selection function
M	SI units only*6

*6 Fixed units: Instantaneous flow: l/min
Accumulated flow: L

Option*4

—	With lead wire with M12 connector (3 m)
N	Without lead wire with M12 connector
Q	Lead wire with M12-M12 connector (3 m)*5

*4 Options are shipped together with the product but do not come assembled.

*5 The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Options/Part Nos.


When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



- * Avoid mounting the lubricator on the inlet side.
 * If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

- ① Digital flow switch PF3A701H-L-M 1 pc.
 ② Air combination AC30B-03E-D 1 pc.
 ③ Spacer with bracket Y300T-D 2 pcs.
 ④ Piping adapter E300-03-D 1 pc.

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

Please contact your local sales representative for more details.

For flow switch precautions and specific product precautions, refer to the “Operation Manual” on the SMC website.

Specifications

Model			PF3A701H-L	PF3A702H-L
Electrical	Power supply voltage	When used as a switch output device	24 VDC ±10 %	
		When used as an IO-Link device	21.6 to 30 VDC	
Switch output	Output type		Select from NPN or PNP open collector output.	
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.	
	Max. applied voltage		30 V (NPN output)	
	Internal voltage drop (Residual voltage)		1.5 V or less (at load current of 80 mA)	
	Delay time*1		3.3 ms or less, variable from 0 to 60 s/0.01 s increments	
Analogue output	Response time*2		Linked to the set value of the digital filter	
Display	Display		LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: Orange Main screen/Sub screen: 9 digits (7 segments 7 digits, 11 segments 2 digits)	
	Digital filter*3		Select from 1 s, 2 s, or 5 s.	
Standards			CE/UKCA marking, UL(CSA)	

*1 The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.

*2 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analogue output reaches 90 % of the rated flow rate

*3 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90 % in relation to the step input.

Communication Specifications (IO-Link mode)

IO-Link type	Device
IO-Link version	V 1.1
Communication speed	COM2 (38.4 kbps)
Configuration file	IODD file*1
Minimum cycle time	3.3 ms
Process data length	Input data: 4 bytes, Output data: 0 byte
On request data communication	Yes
Data storage function	Yes
Event function	Yes
Vendor ID	131 (0 x 0083)
Device ID*2	PF3A701H-□□-□□-□□ : 394 (0 x 018A)
	PF3A701H-□□-□□-□□ : 395 (0 x 018B)
	PF3A701H-□□-□□-□□ : 396 (0 x 018C)
	PF3A702H-□□-□□-□□ : 397 (0 x 018D)
	PF3A702H-□□-□□-□□ : 398 (0 x 018E)
	PF3A702H-□□-□□-□□ : 399 (0 x 018F)

*1 The configuration file can be downloaded from the SMC website, <https://www.smcworld.com>

*2 The device ID differs according to each product type (output specification).

Other specifications that are not listed are the same as those of the standard product. For details, refer to page 18.

Modular Type  IO-Link    

4-Screen Display Digital Flow Switch with Pressure/Temperature Sensor

PF3A8□H-L Series

How to Order



PF3A8□01H-L2N-M□-□

Type

8 With pressure/temperature sensor

Rated flow range

Symbol	Rated flow range	Applicable air combination model
01	10 to 1000 l/min	AC30-D
02	20 to 2000 l/min	AC40-D

Output specification

Symbol	OUT1	OUT2
L2	IO-Link/Switch output (N/P)	Switch output (N/P)

Option*1

—	With lead wire with M12 connector (3 m)
N	Without lead wire with M12 connector
Q	Lead wire with M12-M12 connector (3 m)*2

*1 Options are shipped together with the product but do not come assembled.

*2 The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Flow direction

—	Left to right
R	Right to left

Calibration certificate*5 (For flow/pressure sensors only)

—	None
A	Yes

*5 The certificate is in both English and Japanese.

Unit specification

—	Units selection function
M	SI units only*3

*3 Fixed units: Instantaneous flow : l/min
Accumulated flow : L
Pressure : kPa, MPa
Temperature : °C

Options/Part Nos.


When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



Assembly example

- ① Digital flow switch PF3A801H-L2-M 1 pc.
- ② Air combination AC30B-03E-D 1 pc.
- ③ Spacer with bracket Y300T-D 2 pcs.
- ④ Piping adapter E300-03-D 1 pc.

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

Please contact your local sales representative for more details.

- * Avoid mounting the lubricator on the inlet side.
- * If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Model		PF3A801H	PF3A802H
Fluid	Applicable fluid*1	Air, Nitrogen	
	Fluid temperature	0 to 50 °C	
Flow	Detection method	Thermal type (Bypass flow type)	
	Rated flow range	10 to 1000 l/min	20 to 2000 l/min
	Set point range*2	10 to 1050 l/min	20 to 2100 l/min
	Instantaneous flow	0 to 9,999,999,990 L	
	Accumulated flow		
	Smallest settable increment	1 l/min	2 l/min
	Accumulated flow	10 L	
Pressure	Accumulated volume per pulse (Pulse width = 50 ms)	Select from 10 L/pulse or 100 L/pulse.	
	Accumulated value hold function*3	Intervals of 2 or 5 minutes can be selected.	
	Rated pressure range	0.000 to 1.000 MPa	
	Set pressure range*2	-0.050 to 1.050 MPa	
	Smallest settable increment	0.001 MPa	
	Proof pressure	1.5 MPa	
Temperature	Pressure loss	Refer to the "Pressure Loss" graph on page 24.	
	Rated temperature range	0.0 to 50.0 °C	
	Set temperature range	-10.0 to 60.0 °C	
	Smallest settable increment	0.1 °C	
Electrical	Power supply voltage	21.6 to 30 VDC	
	Current consumption	150 mA or less	
	Protection	Polarity protection	
Accuracy	Accuracy	Flow rate*4	±3.0 % F.S.
		Pressure	±3.0 % F.S.
		Temperature*5	±2.5 °C (Flow range: 100 to 1000 l/min, 200 to 2000 l/min)
	Repeatability (Flow rate/Pressure)		±1.0 % F.S.
	Temperature characteristics (Flow rate/Pressure)		±5.0 % F.S. (Ambient temperature of 0 to 50 °C, 25 °C standard)
	Pressure characteristics (Flow rate)*6		±5.0 % F.S. (0 to 1.0 MPa, 0.5 MPa standard)
	Effects of connecting modular products (Flow rate)*7		±5.0 % F.S.
Switch output	Output type	Select from NPN or PNP open collector. (2 outputs)	
	Output mode	Hysteresis mode, Window comparator mode, Error output, Output OFF, Accumulated output, Accumulated pulse output (Only flow rate)	
	Switch operation	Select from Normal or Reversed output.	
	Max. load current	80 mA	
	Max. applied voltage (NPN only)	30 VDC	
	Internal voltage drop (Residual voltage)	1.5 V or less (at load current of 60 mA)	
	Response time	5 ms or less	
	Delay time*8	Variable from 0 to 60 s/0.01 s increments	
	Hysteresis*9	Variable from 0	
	Protection	Over current protection	
	Reference condition*10	Select from Standard conditions or Normal conditions.	
Display	Unit*11	Instantaneous flow	l/min, CFM (ft³/min)
		Accumulated flow	L, ft³
		Pressure	MPa, KPa, kgf/cm², bar, psi
		Temperature	°C, °F
	Display range	Instantaneous flow	0 to 1050 l/min (Flow under 10 l/min is displayed as "0")
		Accumulated flow	0 to 9,999.99 x 10 ⁶ L (6-digit display)
		Pressure*12	0 to 9,999,999.99 x 10 ³ L (9-digit display)
		Temperature	-0.050 to 1.050 MPa
	Min. display unit	Instantaneous flow	-10.0 to 60.0 °C
		Accumulated flow	1 l/min
		Pressure	2 l/min
		Temperature	10 L
	Display	Pressure	0.001 MPa
		Temperature	0.1 °C
		LCD, 4-screen display	
		Upper line: Red/Green, Lower line: Orange	
Digital filter*13	Indicator LED	OUT indicator: Orange LED is ON when output is ON	
	Flow rate	1 s (2 s or 5 s can be selected.)	
	Pressure	0.1 s (Variable from 0 to 30 s/0.01 s increments)	
	Temperature	1 s	
Environmental resistance	Enclosure	IP65	
	Withstand voltage	1000 VAC for 1 minute between terminals and housing	
	Insulation resistance	50 MΩ (500 VDC measured via megohmmeter) between terminals and housing	
	Operating temperature range	Operating: 0 to 50 °C, Stored: -10 to 60 °C (No freezing or condensation)	
Standards	Operating humidity range	Operating/Stored: 35 to 85 % RH (No condensation)	
		CE/UKCA marking, UL(CSA)	
Piping	Piping specification	Modular (Body size: 30)	Modular (Body size: 40)
Main materials of parts in contact with fluid		Stainless steel 304, Aluminium alloy, PPS, HNBR [Sensor: Pt, Au, Ni, Fe, Lead glass (exempted from the RoHS application), Al ₂ O ₃]	
Length of lead wire with connector		3 m	
Weight	Body	350 g	400 g
	Lead wire with connector	+90 g	

- *1 The air quality class is according to JIS B 8392-1:2012 [6:6:4] and ISO8573 1:2010 [6:6:4]. Use an air filter with 5 μm or less filtration rating on the inlet side.
- *2 Set point range will change according to the setting of the zero cut-off function.
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
- 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 - 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years
- If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 The value when connecting a product with a port size of 3/8 (PF3A801H) or 1/2 (PF3A802H)
- *5 In the low flow rate range, the temperature value fluctuates (rises). Refer to the "Temperature Accuracy" graph on page 25.
- *6 Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port released to atmosphere, accuracy may vary.
- *7 The value when the port size of the modular product is 3/8 (PF3A801H) or 1/2 (PF3A802H) and the product is operated at a supply pressure of 0.5 MPa
- *8 The time from when the measured value reaches the set value to when the switch output operates can be set.
- *9 If the measured value fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- *10 The flow rate given in the specifications is the value under standard conditions.
- *11 Setting is only possible for models with the units selection function.
- *12 Display range will change according to the setting of the zero cut-off function.
- *13 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90 % in relation to the step input.
- *14 The configuration file can be downloaded from the SMC website, <https://www.smc.eu>
- *15 The device ID differs according to each product type (output specification).
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Communication Specifications (IO-Link mode)

IO-Link type	Device
IO-Link version	V 1.1
Communication speed	COM2 (38.4 kbps)
Configuration file	IODD file*14
Minimum cycle time	5.8 ms
Process data length	Input data: 12 bytes, Output data: 0 byte
On request data communication	Yes
Data storage function	Yes
Event function	Yes
Vendor ID	131 (0 x 0083)
Device ID*15	PF3A801H-L2□-□□□: 562 (0 x 0232)
	PF3A802H-L2□-□□□: 563 (0 x 0233)

PF3A□H(-L) Series

Flow Range

Model	Flow range				
	0 l/min	1000 l/min	3000 l/min	6000 l/min	12000 l/min
PF3A701H(-L) PF3A801H-L	10 l/min	1000 l/min			
	10 l/min	1050 l/min			
	0 l/min	1050 l/min			
PF3A702H(-L) PF3A802H-L	20 l/min	2000 l/min			
	20 l/min	2100 l/min			
	0 l/min	2100 l/min			
PF3A703H(-L)	30 l/min	3000 l/min			
	30 l/min	3150 l/min			
	0 l/min	3150 l/min			
PF3A706H(-L)	60 l/min	6000 l/min			
	60 l/min	6300 l/min			
	0 l/min	6300 l/min			
PF3A712H(-L)	120 l/min	12000 l/min			
	120 l/min	12600 l/min			
	0 l/min	12600 l/min			

Rated flow range Set point range Display range

Analogue Output



Flow/Analogue Output

	0 l/min	A*2	B
Voltage output (1 to 5 V)*1	1 V	1.04 V	5 V
Current output*1	4 mA	4.16 mA	20 mA

	0 l/min	C*2	D
Voltage output (0 to 10 V)*1*3	0 V	0.1 V	10 V


Model	Min. value of the rated flow range*4	Max. value of the rated flow range
PF3A701H(-L)	10 l/min	1000 l/min
PF3A702H(-L)	20 l/min	2000 l/min
PF3A703H(-L)	30 l/min	3000 l/min
PF3A706H(-L)	60 l/min	6000 l/min
PF3A712H(-L)	120 l/min	12000 l/min

- *1 Analogue output accuracy is within $\pm 3\%$ F.S.
- *2 A and C will change according to the setting of the zero cut-off function.
- *3 The analogue output current from the connected equipment should be 20 μ A or less when selecting 0 to 10 V. When more than 20 μ A current flows, it is possible that the accuracy is not satisfied below 0.5 V.
- *4 The minimum value of the rated flow range will change according to the setting of the zero cut-off function.




Pressure Loss (Reference Data)


PF3A701H(-L) (for 1000 l/min)
PF3A801H-L




PF3A702H(-L) (for 2000 l/min)
PF3A802H-L




PF3A703H(-L) (for 3000 l/min)



PF3A706H(-L) (for 6000 l/min)




PF3A712H(-L) (for 12000 l/min)




Flow Rate Characteristics (Reference Data)


AC30B-D + PF3A701H/PF3A801H-L Rc3/8




AC40B-D + PF3A702H/PF3A802H-L Rc1/2



AW30-D + PF3A701H/PF3A801H-L Rc3/8



AW40-D + PF3A702H/PF3A802H-L Rc1/2




* This product cannot be used for applications in which the flow exceeds the rated flow range. Use caution when selecting a product.


PF3A□H(-L) Series

IN Side Straight Section and Accuracy (Reference Data)


PF3A703H(-L) (for 3000 l/min)




PF3A706H(-L) (for 6000 l/min)



PF3A712H(-L) (for 12000 l/min)




- Do not connect equipment or piping which may generate fluctuations in the flow or drift on the IN side of the product. When installing a regulator on the IN side of the product, make sure that chatter is not generated.
 - The piping on the IN side must have a straight section of piping whose length is more than 8 times the piping I.D.
- If a straight section of piping is not installed, the accuracy may vary by $\pm 3\%$ F.S. or more.
- * The "straight section" refers to a section of piping without any bends or rapid changes in the cross sectional area.



Temperature Accuracy (Reference Data)

PF3A801H/802H-L




Model	A	B
PF3A801H-L	100 l/min	1000 l/min
PF3A802H-L	200 l/min	2000 l/min

- < Temperature Measurement >
- When there is no (low) fluid flow, the heat of the platinum sensor heated for flow detection is transmitted to the temperature sensor, so the temperature measurement value in the low flow range (less than 10 % of the rated flow rate) tends to increase in relation to the fluid temperature.
- < Detection Principle (Flow) >
- When a heated platinum sensor is installed in the branch passage, and fluid flows through it, the fluid removes heat from the platinum sensor. The resistance value of the platinum sensor decreases as it loses heat. As the resistance value decrease ratio has a uniform relationship to the fluid flow, the flow rate can be detected by measuring the resistance value.


Internal Circuits and Wiring Examples

NPN + Analogue output selected PF3A7□□H-□□-CS/DS□-□□




Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less
CS: Analogue output: 1 to 5 V or 0 to 10 V
Output impedance: 1 k Ω
DS: Analogue output: 4 to 20 mA
Max. load impedance: 600 Ω
Min. load impedance: 50 Ω

PNP + Analogue output selected PF3A7□□H-□□-ES/FS□-□□




Max. load current: 80 mA, Internal voltage drop: 2 V or less
ES: Analogue output: 1 to 5 V or 0 to 10 V
Output impedance: 1 k Ω
FS: Analogue output: 4 to 20 mA
Max. load impedance: 600 Ω
Min. load impedance: 50 Ω

NPN + External input selected PF3A7□□H-□□-CS/DS□-□□




Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less
External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PNP + External input selected PF3A7□□H-□□-ES/FS□-□□




Max. load current: 80 mA, Internal voltage drop: 2 V or less
External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

Accumulated pulse output wiring examples PF3A7□□H-□□-CS/DS□-□□



PF3A7□□H-□□-ES/FS□-□□




PF3A□H(-L) Series

Internal Circuits and Wiring Examples


PF3A7□□H-□□-L□-□□

NPN output type



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


PNP output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

PF3A7□□H-□□-L3/L4□-□□

NPN + Analogue output selected



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

L3: Analogue output: 1 to 5 V or 0 to 10 V


Output impedance: 1 k Ω

L4: Analogue output: 4 to 20 mA

Max. load impedance: 600 Ω

Min. load impedance: 50 Ω

PNP + Analogue output selected



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

L3: Analogue output: 1 to 5 V or 0 to 10 V

Output impedance: 1 k Ω


L4: Analogue output: 4 to 20 mA

Max. load impedance: 600 Ω

Min. load impedance: 50 Ω

PF3A7□□H-□□-L3/L4□-□□


NPN + External input selected



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PNP + External input selected




Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer


PF3A8□-L2□-□

NPN 2 output type




Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

PNP 2 output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


When used as an IO-Link device



* The numbers in the diagram show the connector pin layout.

Construction: Parts in Contact with Fluid


PF3A703H(-L)/706H(-L)/712H(-L)



Component Parts

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodized
2	Branch passage	PPS	—
3	Gasket	HNBR	—
4	Sensor base	PPS	—
5	Gasket	HNBR	—
6	Sensor	Au, Pt, Al ₂ O ₃	—


PF3A701H(-L)/702H(-L)



Component Parts


No.	Description	Material	Note
1	Body	ADC	
2	Branch passage	PPS	
3	Gasket	HNBR	
4	Sensor base	PPS	
5	Gasket	HNBR	
6	Sensor	Au, Pt, Al ₂ O ₃	
7	Attachment	ADC	
8	O-ring	HNBR	
9	O-ring	HNBR	
10	Mesh	Stainless steel 304	
11	Spacer	PPS	
12	Pressure sensor	Silicon, PPS	
13	O-ring	HNBR	

PF3A801H-L/802H-L



Dimensions

PF3A703H(-L)/706H(-L)/712H(-L)




Model \ Symbol	Port size										
	Rc1, NPT1, G1	130	45	79.1	55.3	22.5	25	35	60	30	M4 x 0.7 depth 7
	Rc1 1/2, NPT1 1/2, G1 1/2	170	60	94.1	70.3	30	68	45	80	40	M5 x 0.8 depth 8
	Rc2, NPT2, G2	200	70	104.1	80.3	35	85	50	100	50	M6 x 1.0 depth 9

PF3A□H(-L) Series


Dimensions

PF3A701H/702H
PF3A801H/802H



Model	Symbol	A	B	D	E	F
PF3A701H/PF3A801H		68.3	43	64.4	55.4	28.9
PF3A702H/PF3A802H		72.3	51	73	71	35.5

Lead wire with M12 connector (Part no.: ZS-37-A)




Pin no.	Pin name	Wire colour
1	DC(+)	Brown
2	FUNC	White
3	DC(-)	Blue
4	OUT(C/Q)	Black

* 4-wire type lead wire with M 1 2 connector used for the PF3A series

Cable Specifications

Conductor	Nominal cross section	AWG23
Insulator	Outside diameter	Approx. 1.1 mm
	Colour	Brown, Blue, Black, White
Sheath	Finished outside diameter	Ø 4

Lead wire with M12-M12 connector (Part no.: ZS-49-A)



M12 (Female)	M12 (Male)
① L+	①
② N.C. or other	②
③ L-	③
④ C/Q	④

Wiring diagram


* For wiring, refer to the "Operation Manual" on the SMC website, <https://www.smcworld.com>

PF3A□H(-L) Series

Optional Accessories

Piping Adapter: 1/4, 3/8, 1/2, 3/4

A piping adapter allows for the installation/removal of the component without removing the piping and thus makes maintenance easier.




Model	P	A	B	C	D	Applicable air combination model
E300-□02-D	1/4	27	43	53	30	AC30-D
E300-□03-D	3/8					
E300-□04-D	1/2					
E400-□02-D	1/4	30	51	71	36	AC40-D
E400-□03-D	3/8					
E400-□04-D	1/2					
E400-□06-D	3/4					

* □ in model numbers indicates a pipe thread type. No indication is necessary for Rc; however, indicate N for NPT, and F for G.
 * Separate spacers are required for modular unit.


Spacer/Spacer with Bracket

Spacer




Model	A	B	C	D	E	Applicable air combination model
Y300-D	4.2	43	16.2	53	—	AC30-D
Y400-D	5.2	51	19.2	71	—	AC40-D

Spacer with bracket



Model	A	B	C	D	E	EE	F	G	H	J	K	Applicable air combination model
Y300T-D	4.2	85	42.5	67.5	35	—	14	7	20	6	41	AC30-D
Y400T-D	5.2	115	50	85.5	40	55	18	9	26	7	50	AC40-D

Mounting Position Example



Applicable air combination model	A	B	C	D	E
AC30-D	55.1	57.2	104.2	245.6	46.8
AC40-D	72.6	75.2	105.2	285.6	46.8

3-Screen Display

Digital Flow Monitor

PFG300 Series



How to Order

PFG 3 0 0 - RT - M - L

Type

3 Remote type monitor unit

Input specification

Symbol	Description	Applicable flow switch model
0	Voltage input	PF3A7□H-CS/ES/L3 series
1	Current input	PF3A7□H-DS/FS/L4 series

* The PFG3 (monitor unit) cannot be used as an IO-Link communication device.

Output specification

RT	2 outputs (NPN/PNP switching type) + Analogue voltage output*1, 2
SV	2 outputs (NPN/PNP switching type) + Analogue current output*2
XY	2 outputs (NPN/PNP switching type) + Copy function

*1 Can switch between 1 to 5 V and 0 to 10 V

*2 Can be switched to external input or copy function

Unit specification

—	Units selection function*3
M	SI units only*4

*3 This product is for overseas use only.
(The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)

*4 Fixed units: Instantaneous flow: l/min
Accumulated flow: L

Option 4

	Operation manual	Calibration certificate
—	○	—
Y	—	—
K	○	○
T	—	○

Option 3

—	None
C	ZS-28-CA-4 Sensor connector

Option 2

Symbol	Description
—	None
A1	Bracket A (Vertical mounting) ZS-46-A1
A2	Bracket B (Horizontal mounting) ZS-46-A2
B	Panel mount adapter ZS-46-B
D	Panel mount adapter + Front protection cover ZS-46-D

Option 1


Symbol	Description
—	Without lead wire
L	Power supply/output connection lead wire (Lead wire length: 2 m) ZS-46-5L

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-28-CA-4	Sensor connector	For PF3A7□H
ZS-46-A1	Bracket A	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-A2	Bracket B	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-B	Panel mount adapter	
ZS-46-D	Panel mount adapter + Front protection cover	
ZS-46-5L	Power supply/output connection lead wire	5-core, 2 m
ZS-27-01	Front protection cover	

Connection Example



Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Model		PFG300 series				
Applicable SMC flow switch	Model		PF3A701H	PF3A702H	PF3A703H	PF3A706H	PF3A712H
	Rated flow range*1		10 to 1000 l/min	20 to 2000 l/min	30 to 3000 l/min	60 to 6000 l/min	120 to 12000 l/min
Flow	Set point range	Instantaneous flow	–50 to 1050 l/min	–100 to 2100 l/min	–150 to 3150 l/min	–300 to 6300 l/min	–600 to 12600 l/min
		Accumulated flow	0 to 999,999,999,990 L		0 to 999,999,999,990 L		0 to 999,999,999,900 L
	Smallest settable increment	Instantaneous flow	1 l/min		2 l/min		5 l/min 10 l/min
		Accumulated flow	10 L		10 L		100 L
	Accumulated volume per pulse (Pulse width = 50 ms)		10 L/pulse		10 L/pulse		100 L/pulse
Accumulated value hold function*3		Intervals of 2 or 5 minutes can be selected. The stored accumulated flow is held even when the power supply is OFF.					
Electrical	Power supply voltage		12 to 24 VDC ±10 % (24 VDC when the PF3A7□H is connected)				
	Current consumption		25 mA or less				
	Protection		Polarity protection				
Accuracy	Display accuracy		±0.5 % F.S. ± Minimum display unit (Ambient temperature of 25 °C)				
	Analogue output accuracy		±0.5 % F.S. (Ambient temperature of 25 °C)				
	Repeatability		±0.1 % F.S. ± Minimum display unit				
	Temperature characteristics		±0.5 % F.S. (Ambient temperature: 0 to 50 °C, 25 °C standard)				
Switch output	Output type		Select from NPN or PNP open collector output.				
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.				
	Switch operation		Select from Normal or Reversed output.				
	Max. load current		80 mA				
	Max. applied voltage (NPN only)		30 VDC				
	Internal voltage drop (Residual voltage)		NPN output: 1 V or less (at load current of 80 mA), PNP output: 1.5 V or less (at load current of 80 mA)				
	Response time*2		3 ms or less				
	Delay time*2		Select from 0.00, 0.05 to 0.1 s (increment of 0.01 s), 0.1 to 1.0 s (increment of 0.1 s), 1 to 10 s (increment of 1 s), 20 s, 30 s, 40 s, 50 s, or 60 s.				
	Hysteresis*4		Variable from 0				
Analogue output*5	Protection		Short circuit protection				
	Output type		Voltage output: 1 to 5 V, 0 to 10 V (only when the power supply voltage is 24 VDC) Current output: 4 to 20 mA (0 l/min to maximum value of the rated flow)				
	Impedance	Voltage output	Output impedance: 1 kΩ				
		Current output	Maximum load impedance: 300 Ω (at power supply voltage of 12 V), 600 Ω (at power supply voltage of 24 VDC)				
	Response time*2		50 ms or less				
External input*6	External input		Input voltage: 0.4 V or less (Reed or Solid state) for 30 ms or longer				
	Input mode		Select from Accumulated value external reset or Peak/Bottom value reset.				
Sensor input	Input type		Voltage input: 1 to 5 VDC (Input impedance: 1 MΩ), Current input: 4 to 20 mA DC (Input impedance: 51 Ω) (0 l/min to maximum value of the rated flow)				
	Connection method		Connector (e-CON)				
	Protection		Over voltage protection (Up to 26.4 VDC)				
Display	Display mode		Select from Instantaneous flow or Accumulated flow.				
	Unit*7	Instantaneous flow	l/min, cfm (ft³/min)				
		Accumulated flow	L, ft³, L x 10⁶, ft³ x 10⁶				
	Display range	Instantaneous flow	–50 to 1050 l/min	–100 to 2100 l/min	–150 to 3150 l/min	–300 to 6300 l/min	–600 to 12600 l/min
		Accumulated flow*9	0 to 999,999,999,990 L		0 to 999,999,999,990 L		0 to 999,999,999,900 L
	Minimum display unit	Instantaneous flow	1 l/min		2 l/min		5 l/min 10 l/min
		Accumulated flow	10 L		10 L		100 L
	Display type		LCD				
	Number of displays		3-screen display (Main screen, Sub screen)				
	Display colour		1) Main screen: Red/Green, 2) Sub screen: Orange				
	Number of display digits		1) Main screen: 5 digits (7 segments), 2) Sub screen: 9 digits (7 segments)				
Indicator LED		LED ON when switch output is ON. OUT1/2: Orange					
Digital filter*8		Select from 0.00, 0.05 to 0.1 s (increment of 0.01 s), 0.1 to 1.0 s (increment of 0.1 s), 1 to 10 s (increment of 1 s), 20 s, or 30 s.					
Environment	Enclosure		IP40				
	Withstand voltage		1000 VAC for 1 minute between terminals and housing				
	Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing				
	Operating temperature range		Operating: 0 to 50 °C, Stored: –10 to 60 °C (No condensation or freezing)				
	Operating humidity range		Operating/Stored: 35 to 85 % RH (No condensation or freezing)				
Standards		CE marking (EMC directive/RoHS directive)					
Weight	Body		25 g (Excluding the power supply/output connection lead wire)				
	Lead wire with connector		+39 g				

*1 Rated flow range of the applicable flow switch

*2 Value without digital filter (at 0.00 s)

*3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum access limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:

• 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years

• 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years

If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.

*4 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.

*5 Setting is only possible for models with analogue output.

*6 Setting is only possible for models with external input.

*7 Setting is only possible for models with the units selection function.


*8 The response time indicates when the set value is 90 % in relation to the step input.

*9 The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. When the upper digits are displayed, x 10⁶ lights up.


* Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Internal Circuits and Wiring Examples


-XY
-RT
-SV
NPN (2 outputs) + Copy function




-XY
-RT
-SV
PNP (2 outputs) + Copy function




-RT: NPN (2 outputs) + Analogue voltage output
-SV: NPN (2 outputs) + Analogue current output




-RT: PNP (2 outputs) + Analogue voltage output
-SV: PNP (2 outputs) + Analogue current output



-RT: NPN (2 outputs) + External input
-SV: NPN (2 outputs) + External input




-RT: PNP (2 outputs) + External input
-SV: PNP (2 outputs) + External input




Accumulated pulse output wiring examples


NPN (2 outputs) type




PNP (2 outputs) type






Dimensions






Bracket A (Part no.: ZS-46-A1)




* Bracket configuration allows for mounting in four orientations.



Bracket B (Part no.: ZS-46-A2)




* Bracket configuration allows for mounting in four orientations.




PFG300 Series

Dimensions


Panel mount adapter (Part no.: ZS-46-B)



Panel mount adapter + Front protection cover (Part no.: ZS-46-D)




Power supply/output connection lead wire (Part no.: ZS-46-5L)



Sensor connector (Part no.: ZS-28-CA-4)

Pin no.	Terminal
1	DC (+)
2	N.C.
3	DC (-)
4	IN*1

*1 1 to 5 V or 4 to 20 mA




Cable Specifications

Conductor cross section		0.15 mm ² (AWG26)
Insulator	Outside diameter	1.0 mm
	Colour	Brown, Blue, Black, White, Gray (5-core)
Sheath	Finished outside diameter	Ø 3.5


Dimensions

Panel fitting dimensions


Individual mounting




Multiple (2 pcs. or more) secure mounting <Horizontal>




Panel mount example <Horizontal>



<Vertical>



Panel mount example <Vertical>



PF3A□H(-L) Series Function Details

* The pressure and temperature settings are only available for the PF3A8□H-L series.

For the setting of functions and operation methods, refer to the "Operation Manual" on the SMC website.

Output operation

The output operation can be selected from the following:

Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow, pressure, and temperature, or output (accumulated output and pulse output) corresponding to accumulated flow

(Default setting: Hysteresis mode, Normal output)

Simple setting mode

Only the set values for instantaneous flow, accumulated flow, pressure, and temperature can be changed. The output mode, output type, display colour, and accumulated pulse output cannot be changed.

Display colour

The display colour can be selected for each output status. The selection of the display colour provides visual identification of abnormal values.

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

Reference condition

The display unit can be selected from standard conditions or normal conditions.

Standard conditions: Flow rate converted to a volume at 20 °C and 101.3 kPa (absolute pressure)
Normal conditions: Flow rate converted to a volume at 0 °C and 101.3 kPa (absolute pressure)

Response time (Digital filter)

The response time (digital filter) can be set to suit the application.

(Default setting: Flow rate: 1 s, Pressure: 0.1 s)

The effects of fluctuation and the flickering of the display can be reduced by changing the response time (digital filter).

Flow rate	Pressure	Temp.
1 s	0 to 30 s	
2 s	(Increments of	1 s
5 s	0.01 s)	

FUNC output switching function

Analogue output or external input can be selected. (Default setting: Analogue output)

Selectable analogue output function

1 to 5 V or 0 to 10 V can be selected for the analogue voltage output type. (Default setting: 1 to 5 V)

External input function

The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: The accumulated flow value is reset via external input signal.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory will be accessed. Take into consideration that the max. number of times the memory can be accessed is 1.5 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1.5 million times.

Peak/Bottom value reset: The peak value and bottom value are reset.

Forced output function

The output is forced ON/OFF when starting the system or during maintenance. This enables confirmation of the wiring and prevents system errors due to unexpected output.

For the analogue output type: When ON, the output will be 5 V or 20 mA, and when OFF, 1 V or 4 mA.

For the IO-Link compatible PF3A□H-L series, diagnostic bit (error and flow rate) and process data (PD) flow measurement can be checked.

* Also, the increase or decrease of the flow will not change the ON/OFF status of the output while the forced output function is activated.

Accumulated value hold

The accumulated value is not cleared even when the power supply is turned OFF. The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned ON again.

The max. writable limit of the memory device is 1.5 million times, which should be taken into consideration.

Peak/Bottom value display

The max. (min.) flow rate is detected and updated from when the power supply is turned ON. In peak (bottom) value display mode, this max. (min.) flow rate as well as the pressure and temperature are displayed.

Display OFF mode

This function will turn the display OFF.

In the display OFF mode, three digits " _ _ _ " on the right side of the sub display will flash.

If any button is pressed during this mode, the display reverts to normal for 30 seconds to allow the flow, pressure, temperature, etc., to be quickly checked.

When a flow monitor (PFG300 series) is connected, the displayed values might be different due to an error. When a flow monitor display is to be used, it is recommended that this product be set to the display OFF mode.

Setting of a security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

Key-lock function


Prevents operation errors such as accidentally changing setting values

Reset to the default settings

The product can be returned to its factory default settings.

Reversible display mode


When the switch is used upside down, the orientation of the display can be rotated to make it easier to read by using the reversible display function.



Zero cut-off function

When the flow is close to 0 l/min, the product will round the value down and zero will be displayed. A flow value may be displayed even when the flow rate is 0 l/min due to high pressure or depending on the installation. The zero cut-off function will force the display to zero. The range to display zero can be changed. (For the PF3A8□H-L series, the pressure is also subject to this function.)

Example) Vertical mounting, Fluid direction: Bottom to top



Delay time setting (PF3A□H-L series only)

The time from when the instantaneous flow, pressure, and temperature reach the set values to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.









The total switching time is the switch operation time and the set delay time.

(Default setting: 0 s)

0 to 60 s (Increments of 0.01 s)

■ Selection of the display on the sub screen

The display on the sub screen in measuring mode can be set.



 <p>Sub screen</p>	Accumulated value display	Set value display	Peak value display
	Displays the accumulated value 	Displays the set value 	Displays the peak value 
 <p>Switch output/Communication mode display (Only for the IO-Link compatible products)</p>	Bottom value display	Line name display	OFF
	Displays the bottom value 	Displays the line name 	Displays nothing 

■ Analogue output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed.

The value can be changed between 10 % of the max. value of the rated flow and the max. value of the display range.

For analogue voltage output of 0 to 10 V



■ Error display function

When an error or abnormality arises, the location and contents are displayed.

Display	Error name	Description	Action
<i>E r 1</i> <i>E r 2</i>	OUT over current error * Er2: PF3A8□-L series only	A load current of 8 0 mA or more has been applied to the switch output (OUT).	Eliminate the cause of the over current by turning OFF the power supply and then turning it ON again.
<i>HHH</i>	Instantaneous flow error Pressure/Temperature error*1 *1 PF3A8□-L series only	The flow rate, pressure, or temperature exceeds the upper limit of the setting range.	Decrease the flow rate, pressure, or temperature.
<i>LLL</i>	Pressure/Temperature error * PF3A8□-L series only	The pressure or temperature exceeds the lower limit of the setting range.	Increase the pressure or temperature.
<i>999999</i> (Flashing)	Accumulated flow error	The accumulated flow has exceeded the accumulated flow range. (For accumulated increment)	Reset the accumulated flow.
<i>0</i> (Flashing)	Accumulated flow error	The accumulated flow has reached the set accumulated flow value. (For accumulated decrement)	
<i>E r 3</i> <i>E r 0</i> <i>E r 4</i> <i>E r 6</i> <i>E r 7</i> <i>E r 8</i> <i>E r 10</i> <i>E r 12</i> <i>E r 14</i> <i>E r 16</i> <i>E r 40</i>	Outside of zero-clear range * PF3A8□-L series only	During zero-clear operation, a pressure of 7 % F.S. or more has been applied. (The mode is returned to measurement mode after 1 s.)	Retry the zero-clear operation without pressure.
	System error		
		An internal data error has occurred.	Turn the power OFF and then ON again.
<i>E r 15</i>	Version does not match * Only for the IO-Link compatible products	The IO-Link version does not match that of the master.	Ensure that the master IO-Link version matches the device version.

If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.

PF3A□H(-L) Series

■ Zero-clear function (PF3A8□H-L series only)






This function clears and resets the zero value on the display of the measured pressure. The indicated value can be adjusted within $\pm 7\%$ F.S. of the pressure at the time of shipment from the factory.

■ Display fine adjustment function (PF3A8□H-L series only)

Fine adjustment of the indicated value of the pressure sensor can be made within the range of $\pm 5\%$ of the read value. (This eliminates wide variations of the indicated value.)

■ Measurement display setting (PF3A8□H-L series only)

Display/hide the measured accumulated flow rate, pressure, and temperature.

Normal display Displays the instantaneous flow, accumulated flow, pressure, and temperature 	Accumulated flow display OFF Displays items other than the accumulated flow 	Pressure display OFF Displays items other than the pressure 
Temperature display OFF Displays items other than the temperature The accumulated flow display changes from 6 digits to 9 digits. 	Accumulated flow, pressure, and temperature display OFF Displays the instantaneous flow 	

PFG300 Series

Function Details

For the setting of functions and operation methods, refer to the "Operation Manual" on the SMC website.

Output operation

The output operation can be selected from the following:
Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow or output (accumulated output and pulse output) corresponding to accumulated flow

(Default setting: Hysteresis mode, Normal output)

Simple setting mode

Only the set values for instantaneous flow and accumulated flow can be changed. The output mode, output type, display colour, and accumulated pulse output cannot be changed.

Display colour

The display colour can be selected for each output status. The selection of the display colour provides visual identification of abnormal values.

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

Delay time setting

The time from when the instantaneous flow reaches the set value to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.

(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (Increments of 0.01 s)
0.1 to 1.0 s (Increments of 0.1 s)
1 to 10 s (Increments of 1 s)
20 s
30 s
40 s
50 s
60 s

Digital filter setting

The time for the digital filter can be set to the sensor input. Setting the digital filter can reduce chattering of the switch output and flickering of the analogue output and the display.

The response time indicates when the set value is 90 % in relation to the step input.

(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (Increments of 0.01 s)
0.1 to 1.0 s (Increments of 0.1 s)
1 to 10 s (Increments of 1 s)
20 s
30 s

FUNC output switching function

Analogue output, external input, or copy function can be selected.
(Default setting: Analogue output)

Selectable analogue output function

1 to 5 V or 0 to 10 V can be selected for the analogue voltage output type. (Default setting: 1 to 5 V)

External input function

The accumulated flow, peak value, and bottom value can be reset remotely.
Accumulated value external reset: The accumulated flow value is reset via external input signal.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory will be accessed. Take into consideration that the max. number of times the memory can be accessed is 1.5 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1.5 million times.

Peak/Bottom value reset: The peak value and bottom value are reset.

Forced output function

The output is forced ON/OFF when starting the system or during maintenance. This enables confirmation of the wiring and prevents system errors due to unexpected output.

For the analogue output type: When ON, the output will be 5 V (or 10 V when 0 to 10 V is selected) or 20 mA, and when OFF, 1 V (or 0 V when 0 to 10 V is selected) or 4 mA.

* Also, the increase or decrease of the flow will not change the ON/OFF status of the output while the forced output function is activated.

Accumulated value hold

The accumulated value is not cleared even when the power supply is turned OFF. The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned ON again.

The max. writable limit of the memory device is 1.5 million times, which should be taken into consideration.

Peak/Bottom value display

The max. (min.) flow rate is detected and updated from when the power supply is turned ON. In peak (bottom) value display mode, this max. (min.) flow rate is displayed.

Setting of a security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

Key-lock function

Prevents operation errors such as accidentally changing setting values

Reset to the default settings

The product can be returned to its factory default settings.


Display with zero cut-off setting

When the flow is close to 0 l/min, the product will round the value down and zero will be displayed. A flow value may be displayed even when the flow rate is 0 l/min due to high pressure or depending on the installation. The zero cut-off function will force the display to zero. The range to display zero can be changed.

PFG300 Series

■ Selection of the display on the sub screen



The display on the sub screen in measuring mode can be set.



Set value display	Accumulated value display	Peak value display
Displays the set value 	Displays the accumulated value 	Displays the peak value
Bottom value display	Line name display	OFF
Displays the bottom value 	Displays the line name (Up to 5 alphanumeric characters can be input.) 	Displays nothing

■ Analogue output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed. The value can be changed between 10 % of the max. value of the rated flow and the max. value of the display range.



■ Error display function

When an error or abnormality arises, the location and contents are displayed.

Display	Error name	Description	Action
Er1 Er2	OUT over current error	A load current of 80 mA or more has been applied to the switch output (OUT).	Eliminate the cause of the over current by turning OFF the power supply and then turning it ON again.
HHH	Instantaneous flow error	The flow rate exceeds the max. value of the display range.	Decrease the flow rate.
LLL	Reverse flow error	There is a reverse flow equivalent to -5 % or more. (Except PF3A7□H series)	Change the flow to the correct direction.
999999 flashes x 10 ⁶	Accumulated flow error	The flow rate exceeds the accumulated flow rate range.	Clear the accumulated flow rate.
Er0 Er4 Er6 Er7 Er8 Er14 Er40	System error	An internal data error has occurred.	Turn the power OFF and then ON again.
Er13	Copy error	The copy function does not operate properly.	After clearing the error by pressing the and buttons simultaneously for a minimum of 1 second, check the wiring and the model, and then attempt to copy again.


If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.

■ Copy function

The settings of the master monitor can be copied to the slave monitors, reducing setting labour and minimizing the risk of setting mistakes.

The set value can be copied to up to 10 flow monitors simultaneously.

(Maximum transmission distance: 4 m)



- 1) Wire as shown in the figure on the left.
- 2) Select the slave monitor which is to be the master, and change it into a master using the buttons. (In the default setting, all flow monitors are set as slaves.)
- 3) Press the **S** button on the master monitor to start copying.

■ Selection of power saving mode

The power saving mode can be selected.

With this function, if no buttons are pressed for 30 s, it shifts to power saving mode.

At the time of shipment from the factory, the product is set to the normal mode (the power saving mode is turned off).

(During power saving mode, [ECo] will flash in the sub screen and the operation light will be ON (only when the switch is ON).)

* There may be a difference in the displayed value on the connected flow switch and the flow monitor. When the flow monitor display is being used, it is recommended to set the flow switch display to OFF mode.

Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of “Caution,” “Warning” or “Danger.” They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)¹⁾, and other safety regulations.

Danger:

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

Warning:

Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

Caution:

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

- 1) ISO 4414: Pneumatic fluid power – General rules and safety requirements for systems and their components.
ISO 4413: Hydraulic fluid power – General rules and safety requirements for systems and their components.
IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
ISO 10218-1: Robots and robotic devices – Safety requirements for industrial robots – Part 1: Robots.
etc.

Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/equipment until safety is confirmed.

1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments.

Use under such conditions or environments is not covered.

1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogues and operation manuals.
3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in Japan.

Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following “Limited warranty and Disclaimer” and “Compliance Requirements”. Read and accept them before using the product.

Limited warranty and Disclaimer

1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.²⁾ Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty.
A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Safety Instructions

Be sure to read “Handling Precautions for SMC Products” (M-E03-3) before using.

SMC Corporation (Europe)

Austria	+43 (0)2262622800	www.smc.at	office.at@smc.com
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	sales.bg@smc.com
Croatia	+385 (0)13707288	www.smc.hr	sales.hr@smc.com
Czech Republic	+420 541424611	www.smc.cz	office.at@smc.com
Denmark	+45 70252900	www.smc.dk.com	smc.dk@smc.com
Estonia	+372 651 0370	www.smcee.ee	info.ee@smc.com
Finland	+358 207513513	www.smc.fi	smc.fi@smc.com
France	+33 (0)164761000	www.smc-france.fr	smc.fi@smc.com
Germany	+49 (0)61034020	www.smc.de	info.de@smc.com
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office.hu@smc.com
Ireland	+353 (0)14039000	www.smcautomation.ie	technical.ie@smc.com
Italy	+39 03990691	www.smcitalia.it	mailbox.it@smc.com
Latvia	+371 67817700	www.smc.lv	info.lv@smc.com

Lithuania	+370 5 2308118	www.smclt.lt	info.lt@smc.com
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post.no@smc.com
Poland	+48 222119600	www.smc.pl	technical.ie@smc.com
Portugal	+351 214724500	www.smc.eu	apoiocliente.pt@smc.com
Romania	+40 213205111	www.smcromania.ro	office.ro@smc.com
Russia	+7 (812)3036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	sales.sk@smc.com
Slovenia	+386 (0)73885412	www.smc.si	office.si@smc.com
Spain	+34 945184100	www.smc.eu	post.es@smc.com
Sweden	+46 (0)86031240	www.smc.nu	order.se@smc.com
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter.ch@smc.com
Turkey	+90 212 489 0 440	www.smcturkey.com.tr	satis@smcturkey.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales.gb@smc.com
South Africa	+27 10 900 1233	www.smcza.co.za	Sales.za@smc.com