

3-Color Display Digital Flow Switch



IP65



Applicable fluid **Dry air, N₂**

3-color/2-screen display*1

*1 2-row display of main screen and sub screen




Expanded flow range

A wide range of flow measurement is possible with 1 product.

Flow ratio*2

100:1

*2 Rated flow ratio is 10 : 1 for the existing PF2A series model.



Smallest settable increment

1 L/min

5 L/min for the for the existing PF2A series model



New

IO-Link Compatible

The flow rate value and the device status can be figured out easily via the process data. **p. 2**

Diagnosis items

- Over current error
- Above the rated/accumulated flow range
- Below the rated/accumulated flow range
- Internal product malfunction



3-Screen Display

Digital Flow Monitor
Allows for the monitoring of remote lines



PFG300 Series

PFMC7□(-L) Series



CAT.ES100-115C

3-Color Display Digital Flow Switch


PFMC7(-L) Series p. 9




Rotary display

Display can be rotated in increments of 45° to suit the installation conditions.
Easy operation, improved visibility

Counterclockwise 90°
Clockwise 225°



Installation example




Functions pp. 24, 25

- Output operation
- Display color
- Reference condition
- Display mode
- Response time
- External input function
- Forced output function
- Accumulated value hold
- Selection of display on sub screen
- Display OFF mode
- Setting of security code
- Peak/Bottom value display
- Key-lock function
- Analog output free range function
- Error display function

Bypass structure

Bypass structure with protruding part at the main piping, reduces the contact of moist air with the sensor, reducing degradation of the sensor and maintaining accuracy.



Response time (Digital filter)

Can be selected from **50 ms** (0.05 s) / **0.1 s** / **0.5 s** / **1.0 s** / **2.0 s**


Response time can be set depending on application.

* For IO-Link compatible products, 5.0 s can also be selected.


Grease-free

Applications

Flow control of equipment, main line and branch line



The accumulated indication shows the operating flow rate or residual amount (of N₂, etc.) in a gas cylinder.



Flow control of the air for spray painting



Example of recommended pneumatic circuit

Compressed air line




* Recommended air quality class: JIS B 8392-1 1.1.2 to 1.6.2 (ISO 8753-1 1.1.2 to 1.6.2)

Select a digital flow switch to increase energy savings!

Flow control is necessary for promoting energy saving in any application.

Saving energy starts from numerical control of the flow consumption of equipment and lines and clarification of the purpose and effect.

- Digital display allows **visualization**.
- **3-color/2-screen** display, Improved visibility
- **Remote control** is possible with accumulated pulse.




IO-Link Compatible PPMC7□-□□-L□-□□□

p. 11

Supports the IO-Link communication protocol



IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard: IEC 61131-9.



Configuration File (IODD File*1)

· Manufacturer · Product part no. · Set value

*1 IODD File:
IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.

Device settings can be set by the master.

- Threshold value
- Operation mode, etc.

Read the device data.

- Switch ON/OFF signal and analog value
- Device information:
Manufacturer, Product part number, Serial number, etc.
- Normal or abnormal device status
- Cable breakage

IO-Link Master

IO-Link Compatible Device:
Digital Flow Switch for Air

Implement diagnostic bits in the process data.

The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment.

It is possible to find problems with the equipment in real time using the cyclic (periodic) data and to monitor such problems in detail with the noncyclic (aperiodic) data.

Process Data

Bit offset	Item	Note
0	OUT1 output	0: OFF 1: ON
1	OUT2 output	0: OFF 1: ON
8	Flow rate diagnosis	0: OFF 1: ON
14	Fixed output	0: OFF 1: ON
15	Error (Failure)	0: OFF 1: ON
16 to 31	Measured flow rate value	Signed 16 bit


Diagnosis items
• Over current error
• Above the rated flow range
• Above the accumulated flow range
• Below the rated flow range
• Below the accumulated flow range
• Internal product malfunction

Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Measured flow rate value (PD)															

Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	Error (Failure)	Fixed output	Reservation				Flow rate diagnosis		Reservation				OUT2		OUT1	
													Switch output			


Application Example

For the control of air consumption



Display function

Displays the output communication status and indicates the presence of communication data



Operation and Display

Communication with master	IO-Link status indicator light	Status			Screen display*2	Description
Yes	*1	Normal	Operate	ModE aPE	Normal communication status (readout of measured value)	
			Start up	ModE StPt	At the start of communication	
			Preoperate	ModE PrE		
No	*1 (Flashing)	Abnormal	Version does not match	Er 15	The IO-Link version does not match that of the master. * The applicable IO-Link version is 1.1.	
			Communication disconnection	ModE aPE ModE StPt ModE PrE	Normal communication was not received for 1 s or longer.	
	OFF	SIO mode			ModE SIO	General switch output

*1 In IO-Link mode, the IO-Link indicator is ON or flashing. *2 When the lower line (sub screen) is set to mode display


* "ModE LoC" is displayed when the data storage lock is enabled. (Except for when the version does not match or when in SIO mode)

3-Screen Display Digital Flow Monitor

PFG300 Series p. 18




Allows for the monitoring of remote lines



Visualization of settings


The sub screen (label) shows the item to be set.




Mode Examples	Hysteresis mode					
	Normal output	Set value (Threshold value)	Reversed output	Set value (Threshold value)	Hysteresis	Set hysteresis value
	P.L	1500	n.L	1500	H.L	150
Window comparator mode	Normal output/Lo side		Normal output/Hi side		Reversed output/Lo side	
	Set value (Threshold value)		Set value (Threshold value)		Set value (Threshold value)	
	P.L	900	P.H	1800	n.L	900
	Reversed output/Hi side		Set value (Threshold value)			

Easy screen switching

It is possible to change the settings while checking the measured value.




The sub screen can be switched by pressing the up/down buttons.



* Either "Input of line name" or "Display OFF" can be added via the function settings.

Simple 3-step setting


When the S button is pressed and the set value (P_1) is being displayed, the set value (threshold value) can be set. When the S button is pressed and the hysteresis (H_1) is being displayed, the hysteresis value can be set.



With a snap shot function for set value reading


Pressing the **▲** and **▼** buttons simultaneously for a minimum of 1 second will make the set value (threshold value) the same as the current flow value.

Snap shot function



NPN/PNP switch function

The number of stock items can be reduced.



Analog output of 0 to 10 V is also available.


Voltage output	1 to 5 V	Switchable
	0 to 10 V	
Current output	4 to 20 mA	Fixed

Input range selection (for Pressure/Flow rate)

The displayed value to the sensor input can be set as required.


(Voltage input: 1 to 5 V/Current input: 4 to 20 mA)

Pressure switch/Flow switch can be displayed.



A is displayed for 1 V (or 4 mA).
B is displayed for 5 V (or 20 mA).
The range can be set as required.

■ Pressure Sensor for General Fluids/PSE570




	A	B
PSE570	0	1000
PSE573	-100	100
PSE574	0	500

Set A and B to the values shown in the table above.

Convenient functions

● Copy function

The settings of the master monitor can be copied to the slave monitors.



● Security code

The key locking function keeps unauthorized persons from tampering with the settings.

● Power saving function

Power consumption is reduced by turning off the monitor.

Current consumption*1	Reduction rate*2
25 mA or less	Approx. 50% reduction

*1 During normal operation *2 In power saving mode


● External input function

The accumulated value, peak value, and bottom value can be reset remotely.

Compact & Lightweight

● Compact: Max. 6 mm shorter

● Lightweight: Max. 5 g lighter (30 g → 25 g)




Functions pp. 26 to 28

- Output operation
- Simple setting mode
- Display color
- Delay time setting
- Digital filter setting
- FUNC output switching function
- Selectable analog output function
- External input function
- Forced output function
- Accumulated value hold
- Peak/Bottom value display
- Setting of security code
- Key-lock function
- Reset to the default settings
- Display with zero cut-off setting
- Selection of display on sub screen
- Analog output free range function
- Error display function
- Copy function
- Selection of power saving mode


Mounting

Bracket configuration allows for mounting in four orientations.

Bracket A



Bracket B




Panel mounting

Mountable side by side without clearance































One opening!

- Reduced panel fitting labor
- Space saving













Flow Switch Flow Rate Variations

Series	Applicable fluid	Detection method	Rated flow range [L/min]									
			-3	-2	-1	-0.5	0	0.5	1	2	3	
PFMV	Dry air N ₂	Thermal type (MEMS)					0	0.5				
							0	1				
							0	3				
					-0.5		0.5					
				-1			1					
			-3									3

Series	Compatibility with the PFG300 digital flow monitor	Applicable fluid	Detection method	Smallest settable increment	Rated flow range [L/min]																			
					0.1	0.2	0.5	1	2	5	10	20	25	50	100	150	200	300	500	600	1000	2000	3000	6000
PF2M7(-L)		Dry air N ₂ Ar CO ₂	Thermal type (MEMS)	0.001 L/min																				
																								
																								
				0.01 L/min																				
																								
																								
PFMB		Dry air N ₂	Thermal type (MEMS) Bypass flow type	1 L/min																				
																								
																								
																								
																								
																								
PFMC7(-L) p. 9		Dry air N ₂	Thermal type (MEMS) Bypass flow type	1 L/min																				
																								
																								
PF2A		Air N ₂	Thermal type (Thermistor)	0.1 L/min																				
				0.5 L/min																				
				1 L/min																				
				2 L/min																				
				5 L/min																				
				PF3A7□H(-L)	 Large flow type	Air N ₂	Thermal type (Platinum sensor) Bypass flow type	2 L/min																
5 L/min																								
10 L/min																								
1 L/min																								
2 L/min																								

Flow Switch Variations / Basic Performance Table

Series	 PFMV  PFMV3	 PF2M7(-L)	 PFMB  PFG300	 PFMC7(-L) <small>p. 9</small>  PFG300 <small>p. 18</small>	 PF2A	 PF3A7□H(-L)  PFG300
Enclosure	IP40	IP40	IP40	IP65 [Monitor unit: IP40]	IP65	IP65 [Monitor unit: IP40]
Fluid	Dry air, N ₂	Dry air, N ₂ , Ar, CO ₂	Dry air, N ₂	Dry air, N ₂	Air, N ₂	Air, N ₂
Setting	Digital	Digital	Digital	Digital	Digital	Digital
Rated flow range [L/min]	0 to 0.5 0 to 1 0 to 3 -0.5 to 0.5 -1 to 1 -3 to 3	0.01 to 1 0.02 to 2 0.05 to 5 0.1 to 10 0.3 to 25 0.5 to 50 1 to 100	2 to 200 5 to 500 10 to 1000 20 to 2000	5 to 500 10 to 1000 20 to 2000	1 to 10 5 to 50 10 to 100 20 to 200 50 to 500	30 to 3000 60 to 6000 120 to 12000
Power supply voltage	12 to 24 VDC ±10%	PF2M7 12 to 24 VDC ±10% PF2M7-L 18 to 30 VDC ±10%	12 to 24 VDC ±10%	PFMC 12 to 24 VDC ±10% PFMC-L 18 to 30 VDC ±10%	12 to 24 VDC ±10%	PF3A7□H 24 VDC ±10% PF3A7□H-L 18 to 30 VDC ±10% PF3A701/ 702H-L 21.6 to 30 VDC
Temperature characteristics (25°C standard)	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) [Monitor unit: ±0.5% F.S. (0 to 50°C)]	±3% F.S. ±1 digit (15 to 35°C) ±5% F.S. ±1 digit (0 to 50°C)	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) [Monitor unit: ±0.5% F.S. (0 to 50°C)]	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) [Monitor unit: ±0.5% F.S. (0 to 50°C)]	±3% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C)	±5% F.S. (0 to 50°C) [Monitor unit: ±0.5% F.S. (0 to 50°C)]
Repeatability	±2% F.S. (Fluid: Dry air) Analog output: ±5% F.S. [Monitor unit: ±0.1% F.S. Analog output: ±0.3% F.S.]	±1% F.S. ±1 digit (Fluid: Dry air)	±1% F.S. (Fluid: Dry air) [Monitor unit: ±0.1% F.S. ±1 digit]	±1% F.S. (Fluid: Dry air) [Monitor unit: ±0.1% F.S. ±1 digit]	±1% F.S. (PF2A7□0) ±2% F.S. (PF2A7□1)	±1% F.S. [Monitor unit: ±0.1% F.S. ±1 digit]
Hysteresis	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Fixed (3 digits)	Hysteresis mode: Variable Window comparator mode: Variable
Output	NPN/PNP open collector Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output
Display	[Monitor unit: 2-color LCD display]	2-color LCD display	2-color LED display 2-color LCD display [Monitor unit: 3-color LCD display]	3-color LCD display	LED display	3-color LCD display

* The monitor unit values are for the PFG300 and PFMV3.

CONTENTS

3-Color Display

Digital Flow Switch *PPMC7 Series*

3-Color Display

IO-Link Compatible

Digital Flow Switch *PPMC7-L Series*

3-Screen Display

Digital Flow Monitor *PFG300 Series*



3-Color Display Digital Flow Switch PPMC7 Series

How to Order	p. 9
Specifications	p. 10



3-Color Display IO-Link Compatible Digital Flow Switch PPMC7-L Series

How to Order	p. 11
Specifications	p. 12

Flow Range	p. 13
Analog Output	p. 13
Pressure Loss	p. 13
IN Side Straight Piping Length and Accuracy	p. 13
Internal Circuits and Wiring Examples	p. 14
Construction: Parts in Contact with Fluid	p. 16
Dimensions	p. 17



3-Screen Display Digital Flow Monitor PFG300 Series

How to Order	p. 18
Specifications	p. 19
Internal Circuits and Wiring Examples	p. 20
Dimensions	p. 21

PPMC7(-L)/Function Details	p. 24
PFG300/Function Details	p. 26
Safety Instructions	Back cover

PPMC7

PPMC7-L

PFG300

Function
Details

3-Color Display

Digital Flow Switch

PFMC7 Series



How to Order

PFMC 7 **501** - **04** - **A** - **M**

Rated flow range

501	5 to 500 L/min
102	10 to 1000 L/min
202	20 to 2000 L/min

Thread type

Nil	Rc
N	NPT
F	G*1

*1 ISO 228 compliant

Port size

Symbol	Port size	Rated flow range		
		501	102	202
04	1/2	●	●	—
06	3/4	—	—	●

Output specification

Symbol	OUT1	OUT2	Applicable monitor unit model
A	NPN	NPN	—
B	PNP	PNP	—
C	NPN	Analog (1 to 5 V)	PFG300 series
D	NPN	Analog (4 to 20 mA)	PFG310 series
E *2	PNP	Analog (1 to 5 V)	PFG300 series
F *2	PNP	Analog (4 to 20 mA)	PFG310 series
G *2	NPN	External input*3	—
H *2	PNP	External input*3	—

*2 Made to order


*3 Can be selected from accumulated value external reset or peak/bottom value reset

Calibration certificate

Nil	None
A *8	Yes

*8 Made to order
The certificate is in both English and Japanese.

Option 2

Nil	No bracket
R	With bracket*7 

*7 Options are shipped together with the product but do not come assembled.


Unit specification

Nil	Units selection function*5
M	SI units only*6

*5 This product is for overseas use only. (The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)

*6 Fixed units: Instantaneous flow: L/min, Accumulated flow: L

Option 1

Nil	With lead wire with M8 connector (3 m)*4 
N	Without lead wire with M8 connector

*4 Options are shipped together with the product but do not come assembled.

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-40-A	Lead wire with M8 connector	Length: 3 m
ZS-42-A	Bracket	Mounting screw for PFMC7501/7102 (M3 x 5, 2 pcs.)
ZS-42-B	Bracket	Mounting screw for PFMC7202 (M3 x 5, 2 pcs.)

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Model			PFMC7501		PFMC7102		PFMC7202	
Fluid	Applicable fluid		Dry air, N ₂ (Air quality grade is JIS B 8392-1 1.1.2 to 1.6.2, ISO 8573-1 1.1.2 to 1.6.2.)					
	Fluid temperature range		0 to 50°C					
Flow	Detection method		Thermal type					
	Rated flow range		5 to 500 L/min		10 to 1000 L/min		20 to 2000 L/min	
	Set point range	Instantaneous flow	5 to 525 L/min		10 to 1050 L/min		20 to 2100 L/min	
		Accumulated flow	0 to 999,999,990 L					
	Smallest settable increment	Instantaneous flow	1 L/min					
		Accumulated flow	10 L					
	Accumulated volume per pulse (Pulse width = 50 ms)		1 L/pulse		10 L/pulse			
	Accumulated value hold function *1		Intervals of 2 or 5 minutes can be selected.					
Pressure	Rated pressure range		0 to 0.8 MPa					
	Proof pressure		1.2 MPa					
	Pressure loss		Refer to the "Pressure Loss" graph.					
	Pressure characteristics *2		±5% F.S. (0 to 0.8 MPa, 0.6 MPa standard)					
Electrical	Power supply voltage		12 to 24 VDC ±10% Ripple (p-p) 10% or less					
	Current consumption		55 mA or less					
	Protection		Polarity protection					
Accuracy	Display accuracy		±3% F.S.					
	Analog output accuracy		±3% F.S.					
	Repeatability		±1% F.S. (±2% F.S. when the response time is set to 0.05 s)					
	Temperature characteristics		±5% F.S. (0 to 50°C, 25°C standard)					
Switch output	Output type		NPN open collector PNP open collector					
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, or Accumulated pulse output modes.					
	Switch operation		Select from Normal or Reversed output.					
	Max. load current		80 mA					
	Max. applied voltage (NPN only)		28 VDC					
	Internal voltage drop (Residual voltage)		NPN output type: 1 V or less (at load current of 80 mA) PNP output type: 1.5 V or less (at load current of 80 mA)					
	Response time *3		Select from 0.05 s, 0.1 s, 0.5 s, 1 s, or 2 s.					
	Hysteresis *4		Variable from 0					
Analog output *5	Protection		Short circuit protection					
	Output type		Voltage output: 1 to 5 V, Current output: 4 to 20 mA Output impedance: Approx. 1 kΩ					
	Impedance	Voltage output	Maximum load impedance at power supply voltage of 24 V: 600 Ω, at power supply voltage of 12 V: 300 Ω					
		Current output	Minimum load impedance: 50 Ω					
	Response time *6		Linked to the response time of the switch output					
External input *7	External input		Input voltage: 0.4 V or less (Reed or Solid state) for 30 ms or longer					
	Input mode		Accumulated value external reset, Peak/Bottom value reset Select from Standard conditions or Normal conditions.					
Display	Reference condition *8		Select from Standard conditions or Normal conditions.					
	Unit *9	Instantaneous flow	L/min, cfm (ft ³ /min)					
		Accumulated flow	L, ft ³					
	Display range	Instantaneous flow	-25 to 525 L/min (Displays [0] when value is within the -4 to 4 L/min range)		-50 to 1050 L/min (Displays [0] when value is within the -9 to 9 L/min range)		-100 to 2100 L/min (Displays [0] when value is within the -19 to 19 L/min range)	
		Accumulated flow *10	0 to 999,999,999 L					
	Minimum display unit	Instantaneous flow	1 L/min					
		Accumulated flow	10 L					
	Display		LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: White Main screen: 4 digits, 7 segments, Sub screen: 6 digits, 11 segments					
Indicator LED		LED ON when switch output is ON (OUT1/OUT2: Orange)						
Environmental resistance	Enclosure		IP65					
	Withstand voltage		250 VAC for 1 min between terminals and housing					
	Insulation resistance		2 MΩ or more (50 VDC measured via megohmmeter) between terminals and housing					
	Operating temperature range		Operating: 0 to 50°C, Stored: -10 to 60°C (No condensation or freezing)					
	Operating humidity range		Operating/Stored: 35 to 85% RH (No condensation or freezing)					
Standards			CE marking (EMC Directive, RoHS Directive), UL (CSA)					
Piping specification			Rc1/2, NPT1/2, G1/2				Rc3/4, NPT3/4, G3/4	
Materials of parts in contact with fluid			Stainless steel 304, PPS, Aluminum alloy, HNBR, Si, Au, GE4F					
Weight	Piping specification	Rc thread NPT thread	160 g				240 g	
		G thread	170 g				245 g	
	Lead wire		+80 g					
	Bracket		+25 g				+30 g	

*1 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum access limit of the memory device is 1 million times. If the product is operated 24 hours per day, the product life will be as follows:

- 5 min interval: life is calculated as 5 min x 1 million = 5 million min = 9.5 years
- 2 min interval: life is calculated as 2 min x 1 million = 2 million min = 3.8 years

If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.

*2 Do not release the OUT side piping port of the product directly to the atmosphere without connecting piping. If the product is used with the piping port released to atmosphere, accuracy may vary.

*3 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the switch output turns ON (or OFF) when set to be 90% of the rated flow rate

*4 If the flow fluctuates around the set value, be sure to keep a sufficient margin.

Otherwise, chattering will occur.

*5 Setting is only possible for models with analog output.

*6 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate

*7 Setting is only possible for models with external input.

*8 The flow rate given in the specifications is the value under standard conditions.

*9 Setting is only possible for models with the units selection function.

*10 The accumulated flow display is the upper 3-digit and lower 6-digit (total of 9 digits) display. The position of the dots on the upper part of the screen indicates which digits are displayed.

* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

How to Order

PPMC 7 501 - 04 - L Q - M

Type

7	Integrated display
---	--------------------

Rated flow range

501	5 to 500 L/min
102	10 to 1000 L/min
202	20 to 2000 L/min

Thread type

Nil	Rc
N	NPT
F	G*1

*1 ISO 228 compliant

Port size

Symbol	Port size	Rated flow range		
		501	102	202
04	1/2	●	●	—
06	3/4	—	—	●

Output specification

Symbol	OUT1	OUT2*2	Applicable monitor unit model
L	IO-Link/ Switch output (N/P)	—	—
L2	IO-Link/ Switch output (N/P)	Switch output (N/P) ⇔ External input*4	—
L3	IO-Link/ Switch output (N/P)	Analog voltage output*3	PFG300 series
L4	IO-Link/ Switch output (N/P)	Analog current output	PFG310 series

*2 Switch output (analog output) or external input can be selected by pressing the buttons.

Switch output (analog output) is set as default setting.

Output symbol "L" cannot be used as the OUT 2 terminal is not connected.

*3 1 to 5 V or 0 to 10 V can be selected by pressing the button.

The default setting is 1 to 5 V.

*4 Can be selected from accumulated value external reset or peak/bottom value reset

Calibration certificate

Nil	None
A*9	Yes

*9 Made to order

The certificate is in both English and Japanese.

Option 2

Nil	No bracket
R	With bracket*8

*8 Options are shipped together with the product but do not come assembled.

Unit specification

Nil	Units selection function*6
M	SI units only*7

*6 This product is for overseas use only. (The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)

*7 Fixed units: Instantaneous flow: L/min, Accumulated flow: L

Option 1

Nil	With lead wire with M8 connector (3 m)*5
N	None
Q	With M12-M8 conversion lead wire (0.1 m)*5

*5 Options are shipped together with the product but do not come assembled.

Options/Part Nos.


When only optional parts are required, order with the part numbers listed below.

Part no.	Description	Note
ZS-40-A	Lead wire with M8 connector	Length: 3 m
ZS-42-A	Bracket	Mounting screw for PPMC7501/7102(-L) (M3 x 5, 2 pcs.)
ZS-42-B	Bracket	Mounting screw for PPMC7202(-L) (M3 x 5, 2 pcs.)
ZS-40-M12M8-A	M12-M8 conversion lead wire	Length: 0.1 m



ZS-40-M12M8-A

M12-M8 conversion lead wire

* The lead wire with an M 8 connector and the M12-M8 conversion lead wire are interchangeable with those for the existing PPMC series.



M8 connector



M12 connector

M8 (Female)	M12 (Male)
① Brown	① Brown
② White	② White
③ Blue	③ Blue
④ Black	④ Black

Wiring diagram

* For wiring, refer to the Operation Manual on the SMC website, <https://www.smcworld.com>

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications

Model			PFMC7-L
Electrical	Power supply voltage	When used as a switch output device	12 to 24 VDC ±10%
		When used as an IO-Link device	18 to 30 VDC ±10%
Switch output	Output type		Select from NPN or PNP open collector output.
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.
	Max. applied voltage		30 V (NPN output)
	Internal voltage drop (Residual voltage)		1.5 V or less (at load current of 80 mA)
	Delay time*1		3.4 ms or less Variable from 0 to 60 s/0.01 s increments
Analog output	Response time*2		Linked to the set value of the digital filter
	Output type		Voltage output: 1 to 5 V (0 to 10 V can be selected, only when the power supply voltage is 24 VDC)*3, Current output: 4 to 20 mA
	Impedance	Voltage output	Output impedance: Approx. 1 kΩ
		Current output	Maximum load impedance: 600 Ω at power supply voltage of 24 V, 300 Ω at power supply voltage of 12 V
Display	Display		2-screen display (Main screen, Sub screen) Main screen: 4-digit, 7-segment, 2-color, Red/Green; Sub screen: 9-digit, 11-segment (Only the 5th digit is a 7-segment LED.), White Display values updated 5 times per second
Digital filter*4			Select from 0.05 s, 0.1 s, 0.5 s, 1.0 s, 2.0 s, or 5.0 s.
Standards			CE marking (EMC Directive, RoHS Directive)

*1 The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.

*2 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate

*3 When selecting 0 to 10 V, refer to the analog output graph for the allowable load current.

*4 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90% in relation to the step input.

Communication Specifications (IO-Link mode)

IO-Link type	Device
IO-Link version	V 1.1
Communication speed	COM2 (38.4 kbps)
Configuration file	IODD file*1
Minimum cycle time	3.4 ms
Process data length	Input data: 4 bytes, Output data: 0 byte
On request data communication	Yes
Data storage function	Yes
Event function	Yes
Vendor ID	131 (0 x 0083)
Device ID*2	PFMC7501-□□-L□-□□□ : 541 (0 x 021D)
	PFMC7501-□□-L2□-□□□ : 542 (0 x 021E)
	PFMC7501-□□-L3□-□□□ : 543 (0 x 021F)
	PFMC7501-□□-L4□-□□□ : 544 (0 x 0220)
	PFMC7102-□□-L□-□□□ : 545 (0 x 0221)
	PFMC7102-□□-L2□-□□□ : 546 (0 x 0222)
	PFMC7102-□□-L3□-□□□ : 547 (0 x 0223)
	PFMC7102-□□-L4□-□□□ : 548 (0 x 0224)
	PFMC7202-□□-L□-□□□ : 549 (0 x 0225)
	PFMC7202-□□-L2□-□□□ : 550 (0 x 0226)
	PFMC7202-□□-L3□-□□□ : 551 (0 x 0227)
	PFMC7202-□□-L4□-□□□ : 552 (0 x 0228)

*1 The configuration file can be downloaded from the SMC website, <https://www.smcworld.com>

*2 The device ID differs according to each product type (output specification).

Other specifications that are not listed are the same as those of the standard product. For details, refer to page 10.

PFMC7

PFMC7-L

PFG300

Function Details

PFMC7(-L) Series

Flow Range

Model	Flow range					
	-100 L/min	0 L/min	200 L/min	500 L/min	1000 L/min	2000 L/min
PFMC7501(-L)		5 L/min		500 L/min		
		5 L/min		525 L/min		
	-25 L/min			525 L/min		
PFMC7102(-L)		10 L/min		1000 L/min		
		10 L/min		1050 L/min		
	-50 L/min			1050 L/min		
PFMC7202(-L)		20 L/min		2000 L/min		
		20 L/min		2100 L/min		
	-100 L/min			2100 L/min		

Rated flow range Set point range Display range

Analog Output

Flow/Analog Output

	0 L/min	A*2	B
Voltage output (1 to 5 V)*1	1 V	1.04 V	5 V
Current output*1	4 mA	4.16 mA	20 mA

	0 L/min	C*2	D
Voltage output (0 to 10 V)*1, 3	0 V	0.1 V	10 V


*1 Analog output accuracy is within $\pm 3\%$ F.S.

*2 A and C will change according to the setting of the zero cut function.


*3 The analog output current from the connected equipment should be 20 μ A or less when selecting 0 to 10 V. When more than 20 μ A current flows, it is possible that the accuracy is not satisfied below 0.5 V.

* The minimum value of the rated flow range will change according to the setting of the zero cut function.

Model	Min. value of the rated flow range	Max. value of the rated flow range
PFMC7501(-L)	5 L/min	500 L/min
PFMC7102(-L)	10 L/min	1000 L/min
PFMC7202(-L)	20 L/min	2000 L/min



Voltage output (1 to 5 V)
Current output (4 to 20 mA)




Voltage output (0 to 10 V)


* PFMC7-L only

Pressure Loss (Reference Data)


PFMC7501(-L) (for 500 L/min)



PFMC7102(-L) (for 1000 L/min)





PFMC7202(-L) (for 2000 L/min)



IN Side Straight Piping Length and Accuracy (Reference Data)


- The piping on the IN side must have a straight section of piping with a length of 8 cm or more. If a straight section of piping is not installed, the accuracy can vary by approximately $\pm 2\%$ F.S.
- * "Straight section" means a part of the piping without any bends or rapid changes in the cross sectional area.
- When the PFMC7501 or 7102 is connected to tubing, use a tube I.D. 9 mm or more just before the product. The accuracy can vary by approximately $\pm 2\%$ F.S. when such tubing is not used.



Internal Circuits and Wiring Examples

NPN (2 outputs) type


PFG7□□□-□□-**A**□-□□□



Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less

PNP (2 outputs) type

PFG7□□□-□□-**B**□-□□□




Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

NPN (1 output) + Analog (1 to 5 V) output type

PFG7□□□-□□-**C**□-□□□

NPN (1 output) + Analog (4 to 20 mA) output type

PFG7□□□-□□-**D**□-□□□



Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less

C: Analog output: 1 to 5 V

Output impedance: 1 kΩ

D: Analog output: 4 to 20 mA

Max. load impedance: 600 Ω


Min. load impedance: 50 Ω

PNP (1 output) + Analog (1 to 5 V) output type

PFG7□□□-□□-**E**□-□□□

PNP (1 output) + Analog (4 to 20 mA) output type

PFG7□□□-□□-**F**□-□□□



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

E: Analog output: 1 to 5 V

Output impedance: 1 kΩ


F: Analog output: 4 to 20 mA

Max. load impedance: 600 Ω

Min. load impedance: 50 Ω

NPN (1 output) + External input type

PFG7□□□-□□-**G**□-□□□




Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less

External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PNP (1 output) + External input type

PFG7□□□-□□-**H**□-□□□



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

Accumulated pulse output wiring examples

NPN (2 outputs) type

PFG7□□□-□□-**A**□-□□□



NPN (1 output) + Analog output type

PFG7□□□-□□-**C**□-□□□

PFG7□□□-□□-**D**□-□□□

NPN (1 output) + External input type

PFG7□□□-□□-**G**□-□□□



PNP (2 outputs) type

PFG7□□□-□□-**B**□-□□□



PNP (1 output) + Analog output type

PFG7□□□-□□-**E**□-□□□

PFG7□□□-□□-**F**□-□□□

PNP (1 output) + External input type

PFG7□□□-□□-**H**□-□□□




PFMC7(-L) Series

Internal Circuits and Wiring Examples


PFMC7□-□□-L□-□□

NPN output type



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


PNP output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


PFMC7□-□□-L2□-□□

NPN 2 output type



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


PNP 2 output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

PFMC7□-□□-L3/L4□-□□

NPN + Analog output selected



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

L3: Analog output: 1 to 5 V or 0 to 10 V


Output impedance: 1 k Ω

L4: Analog output: 4 to 20 mA

Max. load impedance: 600 Ω

Min. load impedance: 50 Ω

PNP + Analog output selected



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

L3: Analog output: 1 to 5 V or 0 to 10 V

Output impedance: 1 k Ω


L4: Analog output: 4 to 20 mA

Max. load impedance: 600 Ω

Min. load impedance: 50 Ω

PFMC7□-□□-L2□-□□


NPN + External input selected



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer


PNP + External input selected



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less


External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer

When used as an IO-Link device



* The numbers in the diagrams show the connector pin layout.

Construction: Parts in Contact with Fluid



Component Parts

No.	Description	Material	Note
1	Sensor body	PPS	
2	Gasket	HNBR	
3	Flow rectifier	Stainless steel 304	
4	Sensor chip	Silicon	
5	Printed circuit board	GE4F	
6	Gasket	HNBR	
7	Body	Aluminum alloy	Anodized
8	Mesh	Stainless steel 304	
9	Spacer	PPS	
10	O-ring	HNBR	
11	Holder	Stainless steel 304	
12	C retaining ring	Stainless steel 304	

PFG300

PFG300-L


PFG300

Function
Details

PFMC7(-L) Series

Dimensions


PFMC7501/7102/7202(-L)



Model	Symbol	Port size	A	B	D	E	F	H	K	L	N
PFMC7501/7102(-L)		Rc1/2, NPT1/2	70	30	60.6	41.2	15	14	26	18	13.6
PFMC7202(-L)		Rc3/4, NPT3/4, G3/4	90	35	66.1	46.7	17.5	24	31	28	16.8
PFMC7501/7102(-L)		G1/2	76	30	60.6	41.2	15	14	26	18	13.6

Model	Symbol	Bracket dimensions				
		S	T	U	V	W
PFMC7501/7102(-L)		24	22	32	40	50
PFMC7202(-L)		30	30	42	48	58

Lead wire with M8 connector (Part no.: ZS-40-A)



Pin no.	Pin name	Wire color
1	DC (+)	Brown
2	OUT2	White
3	DC (-)	Blue
4	OUT1	Black

* 4-wire type lead wire with M8 connector used for the PFMC7(-L) series
 * For wiring, refer to the "Operation Manual" on the SMC website,
<https://www.smcworld.com>

Cable Specifications

Conductor	Nominal cross section	AWG23
	Outside diameter	Approx. 0.7 mm
Insulator	Material	Heat-resistant PVC
	Outside diameter	Approx. 1.1 mm
	Color	Brown, White, Black, Blue
Sheath	Material	Heat- and oil-resistant PVC
	Finished outside diameter	ø4

3-Screen Display

Digital Flow Monitor

PFG300 Series



RoHS



How to Order

PFG 3 0 0 - RT - M - L

Type

3 Remote type monitor unit

Input specification

Symbol	Description	Applicable flow switch model
0	Voltage input	PFMC7□-C/E/L3 series
1	Current input	PFMC7□-D/F/L4 series

* The PFG3 (monitor unit) cannot be used as an IO-Link communication device.

Output specification

RT	2 outputs (NPN/PNP switching type) + Analog voltage output*1, 2
SV	2 outputs (NPN/PNP switching type) + Analog current output*2
XY	2 outputs (NPN/PNP switching type) + Copy function

*1 Can switch between 1 to 5 V and 0 to 10 V

*2 Can be switched to external input or copy function

Unit specification

Nil	Units selection function*3
M	SI units only*4


*3 This product is for overseas use only. (The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)

*4 Fixed units: Instantaneous flow: L/min
Accumulated flow: L


Option 4

	Operation manual	Calibration certificate
Nil	○	—
Y	—	—
K	○	○
T	—	○





Option 3

Nil	None
C	ZS-28-CA-4 

Option 1

Symbol	Description
Nil	Without lead wire
L	Power supply/output connection lead wire (Lead wire length: 2 m) 

Option 2


Symbol	Description
Nil	None
A1	Bracket A (Vertical mounting) 
A2	Bracket B (Horizontal mounting) 
B	Panel mount adapter 
D	Panel mount adapter + Front protection cover 

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-28-CA-4	Sensor connector	For PFMC
ZS-46-A1	Bracket A	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-A2	Bracket B	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-B	Panel mount adapter	
ZS-46-D	Panel mount adapter + Front protection cover	
ZS-46-5L	Power supply/output connection lead wire	5-core, 2 m
ZS-27-01	Front protection cover	

Connection Example



PFG300 Series

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications

Model			PFG300 series		
Applicable SMC flow switch	Model		PFMC7501	PFMC7102	PFMC7202
	Rated flow range*1		5 to 500 L/min	10 to 1000 L/min	20 to 2000 L/min
Flow	Set point range	Instantaneous flow	–25 to 525 L/min	–50 to 1050 L/min	–100 to 2100 L/min
		Accumulated flow	0 to 999,999,999,990 L		
	Smallest settable increment	Instantaneous flow	1 L/min		
		Accumulated flow	10 L		
	Accumulated volume per pulse (Pulse width = 50 ms)		1 L/pulse	10 L/pulse	
	Accumulated value hold function*3		Intervals of 2 or 5 minutes can be selected. The stored accumulated flow is held even when the power supply is OFF.		
Electrical	Power supply voltage		12 to 24 VDC ±10%		
	Current consumption		25 mA or less		
	Protection		Polarity protection		
Accuracy	Display accuracy		±0.5% F.S. ± Minimum display unit (Ambient temperature at 25°C)		
	Analog output accuracy		±0.5% F.S. (Ambient temperature at 25°C)		
	Repeatability		±0.1% F.S. ±1 digit		
	Temperature characteristics		±0.5% F.S. (Ambient temperature: 0 to 50°C, 25°C standard)		
Switch output	Output type		Select from NPN or PNP open collector output.		
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.		
	Switch operation		Select from Normal or Reversed output.		
	Max. load current		80 mA		
	Max. applied voltage (NPN only)		30 VDC		
	Internal voltage drop (Residual voltage)		NPN output: 1 V or less (at load current of 80 mA), PNP output: 1.5 V or less (at load current of 80 mA)		
	Response time*2		3 ms or less		
	Delay time*2		Select from 0.00, 0.05 to 0.1 s (increment of 0.01 s), 0.1 to 1.0 s (increment of 0.1 s), 1 to 10 s (increment of 1 s), 20 s, 30 s, 40 s, 50 s, or 60 s.		
	Hysteresis*4		Variable from 0		
	Protection		Short circuit protection		
	Analog output*5	Output type		Voltage output: 1 to 5 V, 0 to 10 V (only when the power supply voltage is 24 VDC) Current output: 4 to 20 mA (0 L/min to maximum value of the rated flow)	
Impedance		Voltage output	Output impedance: 1 kΩ		
		Current output	Maximum load impedance: 300 Ω (at power supply voltage of 12 V), 600 Ω (at power supply voltage of 24 VDC)		
Response time*2		50 ms or less			
External input*6	External input		Input voltage: 0.4 V or less (Reed or Solid state) for 30 ms or longer		
	Input mode		Select from Accumulated value external reset or Peak/Bottom value reset.		
Sensor input	Input type		Voltage input: 1 to 5 VDC (Input impedance: 1 MΩ), Current input: 4 to 20 mA DC (Input impedance: 51 Ω) (0 L/min to maximum value of the rated flow)		
	Connection method		Connector (e-CON)		
	Protection		Over voltage protection (Up to 26.4 VDC)		
Display	Display mode		Select from Instantaneous flow or Accumulated flow.		
	Unit*7	Instantaneous flow	L/min, cfm (ft³/min)		
		Accumulated flow	L, ft³, L x 10⁶, ft³ x 10⁶		
	Display range	Instantaneous flow	–25 to 525 L/min	–50 to 1050 L/min	–100 to 2100 L/min
		Accumulated flow*9	0 to 999,999,999,990 L		
	Minimum display unit	Instantaneous flow	1 L/min		
		Accumulated flow	10 L		
	Display type		LCD		
	Number of displays		3-screen display (Main screen, Sub screen)		
	Display color		1) Main screen: Red/Green, 2) Sub screen: Orange		
Number of display digits		1) Main screen: 5 digits (7 segments), 2) Sub screen: 9 digits (7 segments)			
Indicator LED		LED ON when switch output is ON. OUT1/2: Orange			
Digital filter*8		Select from 0.00, 0.05 to 0.1 s (increment of 0.01 s), 0.1 to 1.0 s (increment of 0.1 s), 1 to 10 s (increment of 1 s), 20 s, or 30 s.			
Environmental resistance	Enclosure		IP40		
	Withstand voltage		1000 VAC for 1 min between terminals and housing		
	Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing		
	Operating temperature range		Operating: 0 to 50°C, Stored: –10 to 60°C (No condensation or freezing)		
	Operating humidity range		Operating/Stored: 35 to 85% RH (No condensation or freezing)		
Standards		CE marking (EMC directive/RoHS directive)			
Weight	Body		25 g (Excluding the power supply/output connection lead wire)		
	Lead wire with connector		+39 g		

*1 Rated flow range of the applicable flow switch

*2 Value without digital filter (at 0.00 s)

*3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum access limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
 • 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 • 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years
 If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.

*4 If the flow fluctuates around the set value, be sure to keep a sufficient margin. Otherwise, chattering will occur.

*5 Setting is only possible for models with analog output.

*6 Setting is only possible for models with external input.

*7 Setting is only possible for models with the units selection function.


*8 The response time indicates when the set value is 90% in relation to the step input.

*9 The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. When the upper digits are displayed, x 10⁶ lights up.


* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

Internal Circuits and Wiring Examples


-XY
-RT
-SV
NPN (2 outputs) + Copy function




-XY
-RT
-SV
PNP (2 outputs) + Copy function




-RT: NPN (2 outputs) + Analog voltage output
-SV: NPN (2 outputs) + Analog current output




-RT: PNP (2 outputs) + Analog voltage output
-SV: PNP (2 outputs) + Analog current output



-RT: NPN (2 outputs) + External input
-SV: NPN (2 outputs) + External input





-RT: PNP (2 outputs) + External input
-SV: PNP (2 outputs) + External input





Accumulated pulse output wiring examples

NPN (2 outputs) type



PNP (2 outputs) type



PFMC7


PFMC7-L

PFG300


Function
Details

PFG300 Series

Dimensions




Bracket A (Part no.: ZS-46-A1)



* Bracket configuration allows for mounting in four orientations.


Bracket B (Part no.: ZS-46-A2)




* Bracket configuration allows for mounting in four orientations.

Dimensions


Panel mount adapter (Part no.: ZS-46-B)



Panel mount adapter + Front protection cover (Part no.: ZS-46-D)




Power supply/output connection lead wire (Part no.: ZS-46-5L)



Sensor connector (Part no.: ZS-28-CA-4)

Pin no.	Terminal
1	DC (+)
2	N.C.
3	DC (-)
4	IN*1

*1 1 to 5 V or 4 to 20 mA




Cable Specifications

Conductor cross section		0.15 mm ² (AWG26)
Insulator	Outside diameter	1.0 mm
	Color	Brown, Blue, Black, White, Gray (5-core)
Sheath	Finished outside diameter	ø3.5


Dimensions

Panel fitting dimensions


Individual mounting




Multiple (2 pcs. or more) secure mounting <Horizontal>




<Vertical>



Panel mount example <Horizontal>



Panel mount example <Vertical>



PFMC7(-L) Series

Function Details

■ Delay time setting (PFMC7-L series only)

The time from when the instantaneous flow reaches the set value to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.

The total switching time is the switch operation time and the set delay time.
(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (increment of 0.01 s)
0.1 to 1.0 s (increment of 0.1 s)
1 to 10 s (increment of 1 s)
20 s
30 s
40 s
50 s
60 s

■ Output operation

The output operation can be selected from the following:
Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow, output (accumulated output and pulse output) corresponding to accumulated flow, error output, or output OFF (PFMC7-L series only)

* At the time of shipment from the factory, it is set to hysteresis mode and normal output.

■ Display color

The display color can be selected for each output condition. The selection of the display color provides visual identification of abnormal values. (The display color depends on OUT1 setting.)

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

■ Reference condition

The display unit can be selected from standard condition or normal condition.

Standard condition: Flow rate converted to a volume at 20°C and 1 atm (atmosphere)
Normal condition: Flow rate converted to a volume at 0°C and 1 atm (atmosphere)

■ Display mode

The display mode can be selected from instantaneous flow or accumulated flow.

Instantaneous flow display
Accumulated flow display

■ Response time (Digital filter)

The response time can be selected to suit the application.
(Default setting : 1 s)

Abnormalities can be detected more quickly by setting the response time to 0.05 seconds.

The effect of fluctuation and flickering of the display can be reduced by setting the response time to 2 seconds.

* 5 s can only be selected for the PFMC7-L series.

0.05 s
0.1 s
0.5 s
1 s
2 s
5 s

■ External input function

This function can be used only when the optional external input is present. The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: A function to reset the accumulated flow value when an external input signal is applied.
In accumulated increment mode, the accumulated value will reset to and increase from zero.
In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory (EEPROM) will be accessed. Take into consideration that the maximum number of times the memory can be accessed is 1 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1 million times.

Peak/Bottom value reset: Peak and bottom value are reset.

■ Forced output function

The output is turned on/off in a fixed state when starting the system or during maintenance. This enables the confirmation of wiring and prevents system errors due to unexpected output.

For the analog output type, when ON the output will be 5 V or 20 mA, and when OFF, it will be 1 V or 4 mA.

* Also, an increase or decrease of the flow and temperature will not change the on/off status of the output while the forced output function is activated.

■ Accumulated value hold



The accumulated value is not cleared even when the power supply is turned off.

The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned on again.

The life time of the memory device is 1 million access times. Take this into consideration before using this function.

■ Display

The display of the PFMC7 series and that of the PFMC7-L series differs slightly.



■ Display OFF mode

This function will turn the display OFF. In this mode, decimal points flash on the main screen. If any button is pressed during this mode, the display reverts to normal for 30 seconds to allow checking of the flow, etc.

■ Setting of security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

■ Peak/Bottom value display

The maximum (minimum) flow rate is detected and updated from when the power supply is turned on. In peak (bottom) value display mode, this maximum (minimum) flow rate is displayed.

■ Key-lock function



Prevents operation errors such as accidentally changing setting values

PFMC7(-L) Series

■ Analog output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed.

The value can be changed between 10 % of the maximum value of the rated flow and the maximum value of the display range.



■ Error display function

When an error or abnormality arises, the location and contents are displayed.

Display	Error name	Description	Action	Applicable model	
				PFMC7 series	PFMC7-L series
Er1	OUT1 over current error	A load current of 80 mA or more is applied to the switch output (OUT1).	Eliminate the cause of the over current by turning off the power supply and then turning it on again.	●	●
Er2	OUT2 over current error	A load current of 80 mA or more is applied to the switch output (OUT2).		●	●
HHH	Instantaneous flow error	The flow has exceeded the upper limit of the flow display range.	Decrease the flow rate.	●	●
LLL	Reverse flow error	There is a reverse flow equivalent to -5% or more.	Change the flow to the correct direction.	●	●
999999999 (Alternately displays [999] and [999999])	Accumulated flow error	The accumulated flow has exceeded the accumulated flow range.	Reset the accumulated flow.	●	—
999999 (Flashing) x 10 ⁶	Accumulated flow error	The accumulated flow has exceeded the accumulated flow range.	Reset the accumulated flow.	—	●
Er0 Er4 Er6 Er8	System error	An internal data error has occurred.	Turn the power OFF and turn it ON again.	●	●
Er16 Er40					
Er3					
Er15					
Er3	Outside of zero-clear range	During zero-clear operation, the flow rate of $\pm 5\%$ F.S. or more is applied. (The mode is returned to measurement mode after 1 second.)	Retry the zero-clear operation without applying fluid.	—	●
Er15	Version does not match	The IO-Link version does not match that of the master.	Ensure that the master IO-Link version matches the device version.	—	●

If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.

PFG300 Series

Function Details

■ Output operation

The output operation can be selected from the following:
Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow or output (accumulated output and pulse output) corresponding to accumulated flow.

(Default setting: Hysteresis mode, Normal output)

■ Simple setting mode

Only the set values for instantaneous flow and accumulated flow can be changed. Output mode, output type, display color, and accumulate pulse output cannot be changed.

■ Display color

The display color can be selected for each output condition. The selection of the display color provides visual identification of abnormal values.

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

■ Delay time setting

The time from when the instantaneous flow reaches the set value to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.

(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (increment of 0.01 s)
0.1 to 1.0 s (increment of 0.1 s)
1 to 10 s (increment of 1 s)
20 s
30 s
40 s
50 s
60 s

■ Digital filter setting

The time for the digital filter can be set to the sensor input. Setting the digital filter can reduce chattering of the switch output and flickering of the analog output and the display.

The response time indicates when the set value is 90% in relation to the step input.

(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (increment of 0.01 s)
0.1 to 1.0 s (increment of 0.1 s)
1 to 10 s (increment of 1 s)
20 s
30 s

■ FUNC output switching function

Analog output, external input, or copy function can be selected.
(Default setting: Analog output)

■ Selectable analog output function

1 to 5 V or 0 to 10 V can be selected for the analog voltage output type.
(Default setting: 1 to 5 V)

■ External input function

The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: A function to reset the accumulated flow value when an external input signal is applied.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory will be accessed. Take into consideration that the maximum number of times the memory can be accessed is 1.5 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1.5 million times.

Peak/Bottom value reset: Peak and bottom value are reset.

■ Forced output function

The output is turned on/off in a fixed state when starting the system or during maintenance. This enables the confirmation of wiring and prevents system errors due to unexpected output.

For the analog output type: When ON, the output will be 5 V (or 10 V when 0 to 10 V is selected) or 20 mA, and when OFF, 1 V (or 0 V when 0 to 10 V is selected) or 4 mA.

* Also, an increase or decrease of the flow will not change the on/off status of the output while the forced output function is activated.

■ Accumulated value hold

The accumulated value is not cleared even when the power supply is turned off. The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned on again.

The maximum writable limit of the memory device is 1.5 million times, which should be taken into consideration.

■ Peak/Bottom value display

The maximum (minimum) flow rate is detected and updated from when the power supply is turned on. In peak (bottom) value display mode, this maximum (minimum) flow rate is displayed.

■ Setting of security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

■ Key-lock function

Prevents operation errors such as accidentally changing setting values

■ Reset to the default settings

The product can be returned to its factory default settings.

■ Display with zero cut-off setting

When the flow is close to 0 L/min, the product will round the value down and zero will be displayed. A flow value may be displayed even when the flow rate is 0 L/min due to high pressure or depending on the installation. The zero-cut function will force the display to zero. The range to display zero can be changed.

PFG300

PFG300-L

PFG300

Function
Details

PFG300 Series

■ Selection of display on sub screen



The display on the sub screen in measuring mode can be set.



Set value display	Accumulated value display	Peak value display
Displays the set value 	Displays the accumulated value 	Displays the peak value
Bottom value display	Line name display	OFF
Displays the bottom value 	Displays the line name (Up to 5 alphanumeric characters can be input.) 	Displays nothing

■ Analog output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed. The value can be changed between 10% of the maximum value of the rated flow and the maximum value of the display range.



■ Error display function

When an error or abnormality arises, the location and contents are displayed.


Display	Description	Contents	Action
Er1 Er2	OUT over current error	A load current of 80 mA or more is applied to the switch output (OUT).	Eliminate the cause of the over current by turning off the power supply and then turning it on again.
HHH	Instantaneous flow error	The flow rate exceeds the maximum value of the display range.	Decrease the flow rate.
LLL	Reverse flow error	There is a reverse flow equivalent to -5% or more.	Change the flow to the correct direction.
999999 flashes x 10 ⁶	Accumulated flow error	The flow rate exceeds the accumulated flow rate range.	Clear the accumulated flow rate.
Er0 Er4 Er6 Er7 Er8 Er14 Er40	System error	An internal error has occurred.	Turn the power off and then on again.
Er13	Copy error	The copy function does not operate properly.	After clearing the error by pressing the and buttons simultaneously for a minimum of 1 second, check the wiring and the model, and then attempt to copy again.


If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.

■ Copy function

The settings of the master monitor can be copied to the slave monitors, reducing setting labor and minimizing the risk of setting mistakes.

**The set value can be copied to up to 10 flow monitors simultaneously.
(Maximum transmission distance: 4 m)**



- 1) Wire as shown in the figure on the left.
- 2) Select the slave monitor which is to be the master, and change it into a master using the buttons. (In the default setting, all flow monitors are set as slaves.)
- 3) Press the  button on the master monitor to start copying.

■ Selection of power saving mode

The power saving mode can be selected.

With this function, if no buttons are pressed for 30 s, it shifts to power saving mode.


At the time of shipment from the factory, the product is set to the normal mode (the power saving mode is turned off).


(During power saving mode, [ECo] will flash in the sub screen and the operation light will be ON (only when the switch is ON).)


* There may be a difference in the displayed value on the connected flow switch and the flow monitor. When the flow monitor display is being used, it is recommended to set the flow switch display to OFF mode.

Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of “**Caution**,” “**Warning**” or “**Danger**.” They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

 **Caution:** **Caution** indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

 **Warning:** **Warning** indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

 **Danger :** **Danger** indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

*1) ISO 4414: Pneumatic fluid power – General rules relating to systems.
ISO 4413: Hydraulic fluid power – General rules relating to systems.
IEC 60204-1: Safety of machinery – Electrical equipment of machines.
(Part 1: General requirements)
ISO 10218-1: Manipulating industrial robots – Safety.
etc.

Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/equipment until safety is confirmed.

1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.
If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.
If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following “Limited warranty and Disclaimer” and “Compliance Requirements”.

Read and accept them before using the product.

Limited warranty and Disclaimer

1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2)
Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided.
This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.

*2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.
Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

Revision History

Edition B	* The digital flow monitor PFG300 series has been added. * Number of pages has been increased from 16 to 28.	VU
Edition C	* IO-Link compatible products (PFMC7-L) have been added. * Number of pages has been increased from 28 to 32.	ZP

 **Safety Instructions** Be sure to read the “Handling Precautions for SMC Products” (M-E03-3) and “Operation Manual” before use.

SMC Corporation

Akihabara UDX 15F,
4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN
Phone: 03-5207-8249 Fax: 03-5298-5362
<https://www.smcworld.com>
© 2021 SMC Corporation All Rights Reserved

Specifications are subject to change without prior notice
and any obligation on the part of the manufacturer.

D-G

1st printing TS printing ZP 7820KS Printed in Japan.